

**OpreX**<sup>™</sup>Analyzers

**TDLS8200** Probe type Tunable Diode Laser Spectrometer

Bulletin 11Y01D02-01EN

# Easy install, the best just got better

Yokogawa's new probe type TDLS greatly reduces installation costs.

- Easy installing probe type
- Long-term stable measurement realized by excellent probe design
- Intuitive touchscreen HMI
- Fully field repairable with 50 days of data and spectra storage
- Hazardous area classification Zone1 / Division 1







# Management

- Combustion Efficiency Improvement Safety Improvement
- Longer Life time of the coils and coil hangers

# Limiting O<sub>2</sub> Concentration for safety and process monitoring & control

- - No Sampling system required so less maintenance
  - Fast Response Analysis
  - No Interference Analysis (TruePeak measurement technology)


# System Configuration

- Standard System configuration
  - LCD display for process parameters and system status
  - HART communication available



### System configuration with HMI


- Up to 4 units connection available
- TDLS8000 mixed system available



## **Easy installation**

### Access on one side only

• One flange only: no alignment required



Easy replacement of existing analyzer





Easy replacement from gas sampling system

## **High Reliability**

#### Long-term stable measurement

• Optical, hydrodynamics, thermal and vibration designed Probe to stabilize laser optical axis and optical path length for a long time





Reference cell • Internal reference cell in the laser module ensures peak locking during trace measurement (for O<sub>2</sub> and CO only)

# Fired Heater Combustion, Safety, and Lifecycle

Yokogawa TDLS8200 simultaneously measures multi-gas like O<sub>2</sub>, CO, and CH<sub>4</sub>, providing, FAST, quick and reliable information to achieve;

Higher throughput thru optimizing heating

Yokogawa TDLS8200 O<sub>2</sub> analyzer achieves;

Internal reference cell for peak locking during trace measurement

#### TDLS8200

STANDARD SPECIFIC	CATI	ons					
Measurement object	O2+CO, O2+CO or CH4, O2, CO, CO or CH4, NH3, HCI						
Measurement system	Tunable diode laser spectroscopy						
Measured component			Min. range	Max. range			
O <sub>2</sub>			0-1%	0-25%			
CO (ppm)			0-200 ppm	0-10,000 ppm			
CO or CH4		CO	0-200 ppm	0-10,000 ppm			
		CH <sub>4</sub>	0-5%				
NH3			0-30 ppm	0-5,000 ppm			
HCI		0-50 ppm	0-5,000 ppm				
Probe length	0.7 m, 1.0 m, 1.5 m, 2.0 m						
Optical path length	1 m	1 m					
Analog output	5 points, 4 to 20 mA DC Output types: Gas concentration, Transmission, Process gas temperature, Process gas pressure						
Digital communication	HART, Ethernet						
Digital output	2 points, contact rating 24 V DC, 1 A DO: Function: Activate during Warning / Calibration / Validation / Warm up / Maintenance conditions Fault: Function: Activate during Fault condition or when the system power is off						
Power supply	24 V DC ±10%						
Protection degree	IP66/NEMA 4X						
Process gas condition	Process gas temperature: Max 850°C Process gas pressure: 90 to 500 kPa abs. Process gas flow velocity: 1 to 30 m/sec						
Installation condition	Ambient operating temperature: -20 to +55°C Storage temperature: -30 to +70°C Humidity: 0 to 95%RH at 40°C (non-condensing)						
Functional safety	IEC61508 SIL2 (SC3)						
Hazardous area classifications	Division1, Zone1: Explosionproof FM (US, Canada), ATEX, IECEx, NEPSI, Korea, Japan						

Measured component		Repeatability	Linearity
<b>O</b> <sub>2</sub>		$\pm 1\%$ reading or $\pm 0.01\%$ O2, whichever is greater	±1% F.S.
CO (ppm)		±2% reading or ±1 ppm CO, whichever is greater	±1% F.S.
CO or CH₄	со	±2% reading or ±1 ppm CO, whichever is greater	±2% F.S.
	CH₄	$\pm 4\%$ reading or $\pm 0.02\%$ CH <sub>4</sub> , whichever is greater	±4% F.S.
NH3		$\pm 2\%$ reading or $\pm 1$ ppm NH <sub>3</sub> , whichever is greater	±2% F.S.
нсі		±1% reading or ±2.5 ppm HCl, whichever is greater	±2% F.S.

Measurement conditions: 25°C, 0.1 MPa abs., optical path length 1 m

YH8000							
	Toucherroop 7 Einch TET color I CD papel 640 x 480 (VCA)						
Display	Touchscreen 7.5 inch TFT color LCD panel, 640 x 480 (VGA)						
Communication	Ethernet: RJ-45 connector, Communication speed; 100 Mbps						
Protection degree of enclosure	IP65, NEMA Type 4X						
Weight	Approx. 4 kg						
Mounting	Analyzer mount (Front, left-side, right-side) with tilt function, Pipe mount or Panel mount						
Cable Entries	1/2NPT or M20 x 1.5 mm, two holes						
Installation conditions	Ambient operating temperature Storage temperature: Humidity:	: -20 to +55°C -30 to +70°C 10 to 90%RH at 40°C (Non- condensing)					
Power Supply	24 V DC ±10%						
Hazardous area classifications	Division 2, Zone2: Non-Incendive/Type n; FM (US, Canada), ATEX, IECEx, Korea, NEPSI, EAC						

**OpreX**<sup>TM</sup> Through the comprehensive OpreX portfolio of products, services, and solutions, Yokogawa enables operational excellence across the enterprise.

#### Trademarks

Co-innovating tomorrow, OpreX and all product names of Yokogawa Electric Corporation in this bulletin are either trademarks or registered trademarks of Yokogawa Electric Corporation. All other company brand or product names in this bulletin are trademarks or registered trademarks of their respective holders.

World Headquarters 9-32, Nakacho 2-chome, Musashino-shi, Tokyo 180	-8750, JAPAN		Represented by:	
YOKOGAWA CORPORATION OF AMERICA YOKOGAWA EUROPE B.V. YOKOGAWA ENGINEERING ASIA PTE. LTD.	https://www.yokogawa.com/us/			1
	https://www.yokogawa.com/eu/ https://www.yokogawa.com/sg/			
			1	i
YOKOGAWA CHINA CO., LTD.	https://www.yokogawa.com/cn/		I	
YOKOGAWA MIDDLE EAST & AFRICA B.S.C.(c)	https://www.yokogawa.com/bh/		1	ANA-02E

Subject to change without notice. All Rights Reserved, Copyright © 2019, Yokogawa Electric Corporation. [Ed:05/b]

Printed in Japan, 404(KP)

YOKOGAWA 🔶 Co-innovating tomorrow 🛚