

Updated on : 16 June 2026

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
1.	ABB	264DS	Differential Pressure Transmitter	0004	01/01		
2.	ABB	264DS	Differential Pressure Transmitter	0004	02/01		
3.	ABB	264IB	Multivariable Field Indicator	0006	01/01		
4.	ABB	265DS	Pressure Transmitter	0089	02/01		
5.	ABB	267CS	Multivariable Pressure Transmitter	008A	02/01		
6.	ABB	2600T series-Model 266 P-dP	Differential,Gauge Absolute-Pressure Transmitter	0007	01/01	Firmware Rev :7.01.04	
7.	ABB	2600T Series · Model 266 P-dP	Differential, Gauge, Absolute Pressure Transmitter	0007	02/03	Enhanced DD	
8.	ABB	FCM2000	Coriolis Mass Flowmeter	0018	01/01		
9.	ABB	ProcessMaster/ HygienicMaster FEX300/FEX 500	Electromagnetic Flowmeter	0124	01/01		
10.	ABB	FSM4000	Magmeter	0017	01/01		
11.	ABB	FXE4000	Magmeter	0016	02/01		
12.	ABB	TB82EC	Four-Electrode Conductivity Transmitter	0051	01/01		
13.	ABB	TB82PH	pH/ORP/pION Transmitter	0050	01/01		
14.	ABB	TB82PH	pH/ORP/pION Transmitter	0050	02/02		
15.	ABB	TB82TC	Toroidal Conductivity Transmitter	0053	01/01		
16.	ABB	TB82TE	Two-Electrode Conductivity Transmitter	0052	01/01		
17.	ABB	TF02(-Ex) / TF202(-Ex)	Temperature Transmitter	001E	01/01		

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
18.	ABB	TRIO-WIRL VT40	Vortex Flowmeter	0015	01/01		
19.	ABB	TRIO-WIRL FV4000/ FS4000	Vortex Flowmeter	0015	02/01		
20.	ABB	TTX300	Temperature Transmitter	001F	01/01	Enhanced DD	
21.	ABB	TZID-C120/220	Valve Positioner	0028	02/02		
22.	ABB	LMT100/200/300	Magnetostrictive Level Transmitters	0096	01/01	Firmware revision 15.05.04	
23.	ASCO	ASCO FF 4449	Valve Controller	4449	01/01		
24.	AUMA	AUMATIC AC 01.2 ACExC 01.2 FF H1	Electric Actuator / Valve Positioner	0001	01/01	Enhanced DD	
25.	AUMA	AUMATIC FF H1	Valve Positioner	01F8	01/01		
26.	AZBIL CORPORATION	AVP303	Valve Positioner	0203	01/01		
27.	AZBIL CORPORATION	AVP303	Valve Positioner	0203	02/01		X: Supported
28.	AZBIL CORPORATION	AVP304	Valve Positioner	1101	02/01		
29.	AZBIL CORPORATION	AVP703	Valve Positioner	1701	01/03		
30.	AZBIL CORPORATION	DSTJ3000, New Ace	Pressure Transmitter	0103	01/02		
31.	AZBIL CORPORATION	MagNew	Magnetic Flow Meter	0001	02/02		
32.	AZBIL CORPORATION	ST3000	Pressure Transmitter	0103	01/02		
33.	AZBIL CORPORATION	Thermonex	Temperature Transmitter	0401	01/02		
34.	AZBIL CORPORATION	MagneW3000 PLUS+/FLEX+	Electromagnetic Flowmeter	1601	01/03	Enhanced DD	
35.	AZBIL CORPORATION	AT9000 Advanced Transmitter Model GTX	Pressure Transmitter	1501	01/01	Enhanced DD	
36.	BEKA	BA414DF (BA414DF Series )	Fieldbus Indicator	0414	01/01		

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
37.	BEKA	BA484DF (BA488CF Series )	Fieldbus Display	0488	01/01		X: Supported
38.	BEKA	BA484DF (BA488CF Series )	Fieldbus Display	0488	02/01		
39.	BIFFI	ICON2000	Valve Positioner	0100	01/02	Obsolete	
40.	BIFFI	ICON2000	Valve Positioner	0100	01/01	Obsolete	
41.	BIFFI	FF2000 v4	Electric Actuator-Valve Positioner	0001	01/01		
42.	BIFFI	FF2000 v4	Electric Actuator-Valve Positioner	0001	02/01	5.71(major) A2.02(minor)	
43.	BIFFI	FF2000 v4	Electric Actuator-Valve Positioner	0001	03/01	Enhanced DD Firmware 6.15	
44.	BIFFI	FF 2000 v4	Electric Actuator-Valve Positioner	0001	03/01	Enhanced DD Firmware 7.00 Tested with STARDOM/CENTUM	
45.	ChongQing ChuanYi Automation Co., Ltd.	FlowMaster EM Flow Meter	Electromagnetic Flowmeter	0001	01/01		
46.	ChongQing ChuanYi Automation Co., Ltd.	PDS	Pressure Transmitter	0004	01/01		
47.	CSI	9210	Machinery Health Transmitter	9210	02/01		
48.	DET-TRONICS	FlexVu UD10	Universal Display	0001	01/01		
49.	DRAEGER SAFETY	Polytron7xxx	Gas Detector	00EB	01/01		
50.	DRAEGER SAFETY	Polytron8000	Gas Detector	0001	01/01	Enhanced DD	
51.	DREHMO GMBH	DREHMO i-matic	Electric Actuator	0007	01/01		
52.	DREHMO GMBH	DREHMO i-matic	Electric Actuator	0007	02/01		
53.	DRESSER INC	FVP	Valve Positioner	0001	03/04		X: Supported
54.	DRESSER INC	FVP	Valve Positioner	0001	04/01		X: Supported
55.	DRESSER INC	FVP	Valve Positioner	0001	05/01		
56.	DRESSER INC	FVP (Software Download)	Valve Positioner	0007	02/01		X: Supported
57.	DRESSER INC	FVP (Software Download)	Valve Positioner	0007	03/01		X: Supported

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
58.	EIM CONTROLS INC	DCM Fieldbus Actuator	Electric Valve Actuator	EDC2	01/01	1.11.00 Mon Aug 03 11:13:01 2009by WangPeng	
59.	EIM CONTROLS INC	DCM Fieldbus Actuator	Electric Valve Actuator	EDC2	02/01	1.13.00 Fri Dec 25 14:22:11 2009 by WangPeng	
60.	EMERSON AUTOMATION SOLUTIONS	Magtech LTM-350FF	Magnetostrictive Level Transmitter	0102	01/01		
61.	EMERSON AUTOMATION SOLUTIONS	2051	Pressure Transmitter	2051	01/01		
62.	EMERSON AUTOMATION SOLUTIONS	2051	Pressure Transmitter	2051	02/01	Enhanced DD	
63.	EMERSON AUTOMATION SOLUTIONS	2240	16 Input Temperature Transmitter	2240	02/01		
64.	EMERSON AUTOMATION SOLUTIONS	2230	Graphic Field Display	2230	03/03	Enhanced DD	
65.	EMERSON AUTOMATION SOLUTIONS	3051C	Pressure Transmitter	3051	07/02		
66.	EMERSON AUTOMATION SOLUTIONS	3051C	Pressure Transmitter	3051	08/01	Tested with STARDOM/CENTUM Enhanced DD	
67.	EMERSON AUTOMATION SOLUTIONS	3051S	Pressure Transmitter	3051	14/02		X: Supported
68.	EMERSON AUTOMATION SOLUTIONS	3051S	Pressure Transmitter	3051	17/03		

<b>No.</b>	<b>Vendor</b>	<b>Model</b>	<b>Description</b>	<b>Device Type</b>	<b>Dev/DD REV</b>	<b>Remarks</b>	<b>Device Viewer</b>
69.	EMERSON AUTOMATION SOLUTIONS	3051S	Pressure Transmitter	3051	18/01	Enhanced DD	
70.	EMERSON AUTOMATION SOLUTIONS	3051S	MultiVariable Transmitter	3151	01/01	Enhanced DD	
71.	EMERSON AUTOMATION SOLUTIONS	3095	Pressure Transmitter	3095	01/01		
72.	EMERSON AUTOMATION SOLUTIONS	3244MV	Temperature Transmitter	3244	05/02		X: Supported
73.	EMERSON AUTOMATION SOLUTIONS	3144P	Temperature Transmitter	3144	01/01		X: Supported
74.	EMERSON AUTOMATION SOLUTIONS	3144P	Temperature Transmitter	3144	01/03	Firmware 001.01.010	
75.	EMERSON AUTOMATION SOLUTIONS	3144P	Temperature Transmitter	3144	02/01		
76.	EMERSON AUTOMATION SOLUTIONS	3144P	Temperature Transmitter	3144	03/03	Enhanced DD	
77.	EMERSON AUTOMATION SOLUTIONS	3900	Radar Level Transmitter	3900	01/01		
78.	EMERSON AUTOMATION SOLUTIONS	5300 Series	Guided Wave Radar Level and Interface Transmitter	5300	01/03		
79.	EMERSON AUTOMATION SOLUTIONS	5300 Series	Guided Wave Radar Level and Interface Transmitter	5300	02/01		

<b>No.</b>	<b>Vendor</b>	<b>Model</b>	<b>Description</b>	<b>Device Type</b>	<b>Dev/DD REV</b>	<b>Remarks</b>	<b>Device Viewer</b>
80.	EMERSON AUTOMATION SOLUTIONS	5300 Series	Guided Wave Radar Level and Interface Transmitter	5300	03/01		
81.	EMERSON AUTOMATION SOLUTIONS	5300 Series	Guided Wave Radar Level and Interface Transmitter	5300	04/01	Enhanced DD	
82.	EMERSON AUTOMATION SOLUTIONS	5300 Series	Guided Wave Radar Level and Interface Transmitter	5300	04/05	Enhanced DD	
83.	EMERSON AUTOMATION SOLUTIONS	5400 Series	Radar Level Transmitter	5400	02/01		
84.	EMERSON AUTOMATION SOLUTIONS	5400 Series	Radar Level Transmitter	5400	03/01		
85.	EMERSON AUTOMATION SOLUTIONS	5400 Series	Radar Level Transmitter	5400	04/01	Enhanced DD	
86.	EMERSON AUTOMATION SOLUTIONS	5408	Level Transmitter	5408	01/01	Enhanced DD	
87.	EMERSON AUTOMATION SOLUTIONS	5600	Radar Level Transmitter	5600	01/01		
88.	EMERSON AUTOMATION SOLUTIONS	5900	Radar Level Transmitter	5900	02/01		
89.	EMERSON AUTOMATION SOLUTIONS	5900	Radar Level Transmitter	5900	03/01	Enhanced DD	
90.	EMERSON AUTOMATION SOLUTIONS	644	Temperature Transmitter	0644	01/01		X: Supported

<b>No.</b>	<b>Vendor</b>	<b>Model</b>	<b>Description</b>	<b>Device Type</b>	<b>Dev/DD REV</b>	<b>Remarks</b>	<b>Device Viewer</b>
91.	EMERSON AUTOMATION SOLUTIONS	644	Temperature Transmitter	0644	02/01		
92.	EMERSON AUTOMATION SOLUTIONS	752	Remote Indicator	0752	02/01		X: Supported
93.	EMERSON AUTOMATION SOLUTIONS	752	Remote Indicator	0752	03/01		
94.	EMERSON AUTOMATION SOLUTIONS	752	Remote Indicator	0752	04/01	Enhanced DD	
95.	EMERSON AUTOMATION SOLUTIONS	848L	Discrete IO	848D	01/01		
96.	EMERSON AUTOMATION SOLUTIONS	848T	Eight Input Temperature Transmitter	0848	04/09		X: Supported
97.	EMERSON AUTOMATION SOLUTIONS	848T	Eight Input Temperature Transmitter	0848	05/04		
98.	EMERSON AUTOMATION SOLUTIONS	848T	Eight Input Temperature Transmitter	0848	06/01		
99.	EMERSON AUTOMATION SOLUTIONS	848T	Temperature Transmitter	0848	07/01		
100	EMERSON AUTOMATION SOLUTIONS	848T	Temperature Transmitter	0848	08/01	Enhanced DD	
101	EMERSON AUTOMATION SOLUTIONS	8732E	Magnetic Flow Transmitter	8732	02/01		

<b>No.</b>	<b>Vendor</b>	<b>Model</b>	<b>Description</b>	<b>Device Type</b>	<b>Dev/DD REV</b>	<b>Remarks</b>	<b>Device Viewer</b>
102	EMERSON AUTOMATION SOLUTIONS	8732E	Magnetic Flow Transmitter	8732	03/01	Enhanced DD	
103	EMERSON AUTOMATION SOLUTIONS	8742	Mag Flow Meter	8742	04/02		
104	EMERSON AUTOMATION SOLUTIONS	8742	Mag Flow Meter	8742	05/01		
105	EMERSON AUTOMATION SOLUTIONS	8800	Vortex Flowmeter	8800	04/02		
106	EMERSON AUTOMATION SOLUTIONS	8800	Vortex Flowmeter	8800	05/01		X: Supported
107	EMERSON AUTOMATION SOLUTIONS	8800	Vortex Flowmeter	8800	07/01		
108	EMERSON AUTOMATION SOLUTIONS	8800	Vortex Flowmeter	8800	09/01		
109	EMERSON AUTOMATION SOLUTIONS	8800	Vortex Flowmeter	8800	10/03	Enhanced DD	
110	EMERSON AUTOMATION SOLUTIONS	2240S	Multi-Input Temperature Transmitter	2240	03/01	Enhanced DD	
111	EMERSON AUTOMATION SOLUTIONS	700XA	Gas Chromatograph	2001	01/03		
112	EMERSON AUTOMATION SOLUTIONS	1500XA	Gas Chromatograph	2002	01/01		

<b>No.</b>	<b>Vendor</b>	<b>Model</b>	<b>Description</b>	<b>Device Type</b>	<b>Dev/DD REV</b>	<b>Remarks</b>	<b>Device Viewer</b>
113	EMERSON AUTOMATION SOLUTIONS	5081-A-FF	Amperometric Transmitter	4083	02/01		
114	EMERSON AUTOMATION SOLUTIONS	5081C/T	Conductivity Transmitter	4084	01/01		X: Supported
115	EMERSON AUTOMATION SOLUTIONS	5081-C/T-FF	Conductivity Transmitter	4084	02/01		
116	EMERSON AUTOMATION SOLUTIONS	5081pH/ORP	Conductivity Transmitter	4085	01/01		X: Supported
117	EMERSON AUTOMATION SOLUTIONS	5081-P-FF	pH/ORP Transmitter	4085	02/01		
118	EMERSON AUTOMATION SOLUTIONS	5081-P-FF	pH/ORP Transmitter	4085	03/03	Enhanced DD	
119	EMERSON AUTOMATION SOLUTIONS	Oxymitter 5000	Oxygen Transmitter	4000	03/01		
120	EMERSON AUTOMATION SOLUTIONS	Oxymitter 5000	Oxygen Transmitter	4000	04/01		
121	EMERSON AUTOMATION SOLUTIONS	MLT Analyzer	Multi-Component Continuous Gas Analyzer	1100	01/01		
122	EMERSON AUTOMATION SOLUTIONS	1066-CT-FF	Conductivity Transmitter	4091	01/03	Enhanced DD	
123	EMERSON AUTOMATION SOLUTIONS	1066-P-FF	pH/ORP/Redox Transmitter	4089	01/05	Enhanced DD	

<b>No.</b>	<b>Vendor</b>	<b>Model</b>	<b>Description</b>	<b>Device Type</b>	<b>Dev/DD REV</b>	<b>Remarks</b>	<b>Device Viewer</b>
124	EMERSON AUTOMATION SOLUTIONS	1066-DO-CL-OZ-FF	Oxygen/Chlorine and Ozone Transmitter	4090	01/03	Enhanced DD	
125	EMERSON AUTOMATION SOLUTIONS	DLC3020F	Digital Level Controller	3020	01/01		
126	EMERSON AUTOMATION SOLUTIONS	DLC3020F	Digital Level Controller	3020	01/05		
127	EMERSON AUTOMATION SOLUTIONS	DVC5000F-SC	Digital Valve Controller	5420	08/03		X:Supported
128	EMERSON AUTOMATION SOLUTIONS	DVC5000F-SC	Digital Valve Controller	5420	09/03		X:Supported
129	EMERSON AUTOMATION SOLUTIONS	DVC6000F	Digital Valve Controller	4601	01/02	SOFTWARE REVISION: 1.0.7.2.1	X:Supported
130	EMERSON AUTOMATION SOLUTIONS	DVC6000F	Digital Valve Controller	4601	01/02	SOFTWARE REVISION: 1.3.2.2.2	X:Supported
131	EMERSON AUTOMATION SOLUTIONS	DVC6000F	Digital Valve Controller	4601	01/02	SOFTWARE REVISION: 1.4.6.2.2	X:Supported
132	EMERSON AUTOMATION SOLUTIONS	DVC6000F	Digital Valve Controller	4601	01/02	SOFTWARE REVISION: 1.5.18.2.2	X:Supported
133	EMERSON AUTOMATION SOLUTIONS	DVC6000F	Digital Valve Controller	4601	01/02	SOFTWARE REVISION: 1.5.19.2.2	
134	EMERSON AUTOMATION SOLUTIONS	DVC6200F/DVC6000F	Digital Valve Controller	4602	02/01	Tested with STARDOM/CENTUM	

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
135	EMERSON AUTOMATION SOLUTIONS	Fisher DVC6200f / DVC6000f	Digital Valve Controller	4602	04/03	Enhanced DD	
136	ENDRESS+HAUSER	Cerabar S	Pressure Transmitter	1007	06/01		
137	ENDRESS+HAUSER	Cerabar S	Pressure Transmitter	1007	06/03		
138	ENDRESS+HAUSER	Cerabar S	Pressure Transmitter	1007	07/02		X: Supported
139	ENDRESS+HAUSER	Cerabar M 5x	Pressure Transmitter	1019	01/01		X: Supported
140	ENDRESS+HAUSER	Cerabar M 5x	Pressure Transmitter	1019	01/03	Enhanced DD	X: Supported
141	ENDRESS+HAUSER	Deltabar M 5x	Differential Pressure Transmitter	1021	01/01		X: Supported
142	ENDRESS+HAUSER	Deltabar M 5x	Differential Pressure Transmitter	1021	01/03	Enhanced DD	X: Supported
143	ENDRESS+HAUSER	Deltabar S	Differential Pressure Transmitter	1009	06/01		
144	ENDRESS+HAUSER	Deltabar S	Differential Pressure Transmitter	1009	06/03	V03.00.08	
145	ENDRESS+HAUSER	Deltabar S	Differential Pressure Transmitter	1009	07/02	Enhanced DD	X: Supported
146	ENDRESS+HAUSER	Deltapilot M 5x	Hydrostatic Level Transmitter	1023	01/01	01.00.01 (Build 1024)	X: Supported
147	ENDRESS+HAUSER	Deltapilot M 5x	Hydrostatic Level Transmitter	1023	01/03	Enhanced DD	X: Supported
148	ENDRESS+HAUSER	Deltapilot S	Hydrostatic Level Transmitter	100B	01/02		
149	ENDRESS+HAUSER	Deltapilot S	Hydrostatic Level Transmitter	100B	06/01		
150	ENDRESS+HAUSER	Deltapilot S	Hydrostatic Level Transmitter	100B	06/01	03.00.04	X: Supported
151	ENDRESS+HAUSER	Deltapilot S	Hydrostatic Level Transmitter	100B	07/02	Enhanced DD	X: Supported
152	ENDRESS+HAUSER	Gammapilot M	Radiometric Density / Level Transmitter	1013	03/01		X: Supported
153	ENDRESS+HAUSER	Levelflex FMP5x	Guided Radar Level Measurement Device	1022	01/01	Enhanced DD	

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
154	ENDRESS+HAUSER	Levelflex FMP5x	Guided Radar Level Measurement Device	1022	02/01	Enhanced DD	
155	ENDRESS+HAUSER	Levelflex FMP5x	Guided Radar Level Measurement Device	1022	02/02	Enhanced DD	X: Supported
156	ENDRESS+HAUSER	Levelflex M	Guided Wave Level Transmitter	1012	03/01	Firmware V01.02.00 (FF)	X: Supported
157	ENDRESS+HAUSER	Levelflex M	Guided Wave Level Transmitter	1012	03/01	Firmware V01.02.06 (FF)	X: Supported
158	ENDRESS+HAUSER	Levelflex M	Guided Wave Level Transmitter	1012	04/01		X: Supported
159	ENDRESS+HAUSER	Levelflex M	Guided Wave Level Transmitter	1012	04/03		
160	ENDRESS+HAUSER	Liquiline M CM42 Cond	Conductivity Transmitter	1090	01/03		
161	ENDRESS+HAUSER	Liquiline M CM42 Doxygen	Dissolved Oxygen Transmitter	109B	01/01	Firmware 20.02.07 - 0008	
162	ENDRESS+HAUSER	Liquiline M CM42 pH/ORP	pH/ORP Transmitter	108F	01/01		
163	ENDRESS+HAUSER	Liquiline Oxygen	Oxygen Transmitter	10A2	01/02	Enhanced DD	X: Supported
164	ENDRESS+HAUSER	Liquiline Oxygen	Oxygen Transmitter	10A2	02/01	Enhanced DD	X: Supported
165	ENDRESS+HAUSER	Liquiline Oxygen	Oxygen Transmitter	10A2	04/01	Enhanced DD	X: Supported
166	ENDRESS+HAUSER	Liquiline Cond	Conductivity Transmitter	10A1	02/02	Enhanced DD	X: Supported
167	ENDRESS+HAUSER	Liquiline Cond	Conductivity Transmitter	10A1	03/01	Enhanced DD	X: Supported
168	ENDRESS+HAUSER	Liquiline Cond	Conductivity Transmitter	10A1	04/01	Enhanced DD	X: Supported
169	ENDRESS+HAUSER	Liquiline pH/ORP	pH/ORP Transmitter	10A0	02/02	Enhanced DD	X: Supported
170	ENDRESS+HAUSER	Liquiline pHORP	pH/ORP Transmitter	10A0	03/01	Enhanced DD	X: Supported
171	ENDRESS+HAUSER	Liquiline pHORP	pH/ORP Transmitter	10A0	04/01	Enhanced DD	X: Supported
172	ENDRESS+HAUSER	Micropilot FMR5x	Radar Level Transmitter	1028	01/01	Enhanced DD	
173	ENDRESS+HAUSER	Micropilot FMR5x	Radar Level Transmitter	1028	02/01	Enhanced DD	
174	ENDRESS+HAUSER	Micropilot FMR5x	Radar Level Transmitter	1028	02/02	Enhanced DD	X: Supported
175	ENDRESS+HAUSER	Micropilot M	Radar Level Transmitter	100F	02/01		
176	ENDRESS+HAUSER	Micropilot M	Radar Level Transmitter	100F	03/01	Firmware V01.02.00 (FF)	X: Supported
177	ENDRESS+HAUSER	Micropilot M	Radar Level Transmitter	100F	03/01	Firmware V01.02.04 (FF)	X: Supported

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
178	ENDRESS+HAUSER	Micropilot M	Radar Level Transmitter	100F	04/01		
179	ENDRESS+HAUSER	Micropilot M	Radar Level Transmitter	100F	05/03		
180	ENDRESS+HAUSER	Micropilot M	Radar Level Transmitter	100F	05/05		
181	ENDRESS+HAUSER	Promag53	Magnetic Flowmeter	1042	02/01		X: Supported
182	ENDRESS+HAUSER	PROline Promag53/55	Electromagnetic Flowmeter	1042	03/01		X: Supported
183	ENDRESS+HAUSER	PROline Promag53/55	Electromagnetic Flowmeter	1042	04/01		X: Supported
184	ENDRESS+HAUSER	PROline Promag53/55	Electromagnetic Flowmeter	1042	05/01	Enhanced DD	X: Supported
185	ENDRESS+HAUSER	Promag 200	2-wire Electromagnetic Flow Meter	1048	01/01	Enhanced DD	X: Supported
186	ENDRESS+HAUSER	Promag 200	2-wire Electromagnetic Flow Meter	1048	01/02	Enhanced DD	X: Supported
187	ENDRESS+HAUSER	Promag 300/500	4-wire Electromagnetic Flowmeter	103C	01/01	Enhanced DD	X: Supported
188	ENDRESS+HAUSER	PROline T-mass 65	Thermal Mass Flowmeter	1065	01/01		
189	ENDRESS+HAUSER	PROline T-mass 65	Thermal Mass Flowmeter	1065	02/01	Enhanced DD	X: Supported
190	ENDRESS+HAUSER	Promass83	Mass Flowmeter	1051	02/01		X: Supported
191	ENDRESS+HAUSER	PROline Promass83	Mass Flowmeter	1051	03/01		X: Supported
192	ENDRESS+HAUSER	PROline Promass83	Mass Flowmeter	1051	04/01		X: Supported
193	ENDRESS+HAUSER	PROline Promass83	Mass Flowmeter	1051	05/01	Enhanced DD	X: Supported
194	ENDRESS+HAUSER	Promass 200	Coriolis Flowmeter	1054	01/01	Enhanced DD	X: Supported
195	ENDRESS+HAUSER	Promass 200	Coriolis Flowmeter	1054	01/02	Enhanced DD	X: Supported
196	ENDRESS+HAUSER	Promass 300/500	4-wire Coriolis Flowmeter	103B	01/01	Enhanced DD	X: Supported
197	ENDRESS+HAUSER	Prosonic Flow92	Ultrasonic Flowmeter	1061	01/01	Firmware V1.00.00D	
198	ENDRESS+HAUSER	Prosonic Flow93	Ultrasonic Flowmeter	1059	01/01		X: Supported
199	ENDRESS+HAUSER	Prosonic Flow93	Ultrasonic Flowmeter	1059	02/01		X: Supported
200	ENDRESS+HAUSER	Prosonic Flow93	Ultrasonic Flowmeter	1059	03/01		X: Supported
201	ENDRESS+HAUSER	Prosonic Flow93	Ultrasonic Flowmeter	1059	04/01	Enhanced DD	X: Supported
202	ENDRESS+HAUSER	Prosonic M	Ultrasonic Level Transmitter	1011	03/01	Firmware V01.02.00 (FF)	X: Supported

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
203	ENDRESS+HAUSER	Prosonic M	Ultrasonic Level Transmitter	1011	03/01	Firmware V01.02.06 (FF)	X: Supported
204	ENDRESS+HAUSER	Prosonic M	Ultrasonic Level Transmitter	1011	04/01		X: Supported
205	ENDRESS+HAUSER	Prosonic M	Ultrasonic Level Transmitter	1011	04/03		X: Supported
206	ENDRESS+HAUSER	Prowirl72	Vortex Flowmeter	1056	01/01		
207	ENDRESS+HAUSER	Prowirl73	Vortex Flowmeter	1057	01/01		
208	ENDRESS+HAUSER	Prowirl200	Vortex Flowmeter	1038	01/01		
209	ENDRESS+HAUSER	Prowirl200	2-wire Vortex Flowmeter	1038	01/02	Enhanced DD	X: Supported
210	ENDRESS+HAUSER	Prowirl200	2-wire Vortex Flowmeter	1038	02/01	Enhanced DD	X: Supported
211	ENDRESS+HAUSER	RID1x (RID14/RID16)	8 Channel Field Indicator	10CF	01/01		X: Supported
212	ENDRESS+HAUSER	RID1x (RID14/RID16)	8 Channel Field Indicator	10CF	02/01		
213	ENDRESS+HAUSER	TMT125	Temperature Multiplexer	10CD	01/06		
214	ENDRESS+HAUSER	TMT162	Temperature Transmitter	10CC	01/01		X: Supported
215	ENDRESS+HAUSER	TMT162	Temperature Transmitter	10CC	02/01		X: Supported
216	ENDRESS+HAUSER	TMT162	Temperature Transmitter	10CC	03/02	Enhanced DD	
217	ENDRESS+HAUSER	TMT162	Temperature Head Transmitter	10CC	03/04	Enhanced DD	
218	ENDRESS+HAUSER	TMT85	Temperature Head Transmitter	10CE	01/01	Firmware 01.00.03	
219	ENDRESS+HAUSER	TMT85	Temperature Head Transmitter	10CE	01/01	Firmware 01.00.04	X: Supported
220	ENDRESS+HAUSER	TMT85	Temperature Head Transmitter	10CE	01/01	Firmware 01.00.07	X: Supported
221	ENDRESS+HAUSER	TMT85	Temperature Head Transmitter	10CE	02/04	Enhanced DD	X: Supported
222	ENOTEC GMBH	COMTEC 6000	Oxygen and COe Analyzer System	0002	01/01		
223	ENOTEC GMBH	OXITEC 5000	Oxygen Analyzer System	0001	01/01		
224	ENRAF	97x SmartRadar Series	Level Gauge	0384	01/01		
225	FCI	ST100/ST80/ST100A	Thermal Mass Flow Meter	0001	01/01		
226	FIELDQ	FieldQ	Pneumatic Valve Actuator	D3A0	02/01		

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
227	FINT	T610/T710	Modbus to Foundation Fieldbus Gateway	0013	01/01	Enhanced DD	
228	FLOWERVE	Mx Actuator	Valve Actuator	4D58	02/01		
229	FLOWERVE	LIMITORQUE MX QX	Electric Valve Actuator	4D58	05/01	Tested with STARDOM/CENTUM	
230	FLOWERVE	LIMITORQUE MX QX	Electric Valve Actuator	4D58	06/05	Enhanced DD	
231	FLOWERVE	Logix1400	Digital Positioner	0202	05/01		
232	FLOWERVE	Logix3400IQ/ 1400	Digital Positioner	0202	06/01		
233	FLOWERVE	Logix 3400MD	Valve Positioner	0203	01/02		
234	FLOWERVE	Logix 3400MD	Valve Positioner	0203	02/01	Firmware revision 310(1) , 250(2) , 3(3), 0(4)	
235	FLOWERVE	Logix 3400MD	Valve Positioner	0203	02/01	Firmware revision 310(1) , 250(2) , 3(3), 4(4)	
236	FLOWERVE	Logix 3400MD	Valve Positioner	0203	02/03	Firmware revision 310(1) , 250(2) , 3(3), 4(4)	
237	FLOWERVE	Logix 3400MD	Valve Positioner	0203	02/03	Firmware revision 350(1) , 250(2) , 3(3), 4(4)	
238	FLOWERVE	PMV D3	Digital Valve Positioner	00D3	02/02		
239	FLOWERVE	Logix 3800	Positioner	0301	01/02	Enhanced DD	
240	FLOWERVE	Logix 3800	Positioner	0301	01/04	Enhanced DD	
241	FUJI ELECTRIC CORPORATION	FCX-A2	Pressure Transmitter	0032	01/01		
242	FUJI ELECTRIC CORPORATION	FCX-AIII Series	Pressure Transmitter	0033	01/01	Firmware revision V2.20.D.16	
243	FUJI ELECTRIC CORPORATION	FFX-P	Fiber Optic Pressure Transmitter	0001	01/02		
244	GE	XMT868	Ultrasonic Liquid Flowmeter	0001	01/01	GE Flow Liquid 868 Rev 1.2.0	
245	GE	XMT868i	Ultrasonic Liquid Flowmeter	0001	03/01	Enhanced DD	

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
246	GE	XMT910	Ultrasonic Flowmeter	0007	01/01	Enhanced DD	
247	GE	XMT1000	Ultrasonic Flowmeter	0010	01/01	Enhanced DD	
248	GE	GE Flow Gas 868	Gas Flow Transmitter	0002	01/01		
249	GE	SVI FF	Pneumatic Valve Positioner	0008	01/01		
250	GE	SVI FF	Pneumatic Valve Positioner	0008	02/02	Enhanced DD	
251	GE	XGF868I	Ultrasonic Flare Gas Flowmeter	0002	02/06	Enhanced DD	
252	HAWK MEASUREMENT SYSTEM	Hawk FF Level Series - AW-XXXX	Sultan Acoustic Wave Series	0001	01/01	Enhanced DD	
253	HONEYWELL	SmartLine ST700	Pressure Transmitter	0004	01/01	Enhanced DD	
254	HONEYWELL	SmartLine ST700	Pressure Transmitter	0004	04/01	Enhanced DD	
255	HONEYWELL	SmartLine ST800	Pressure Transmitter	0003	01/02	Enhanced DD	
256	HONEYWELL	SmartLine ST800	Pressure Transmitter	0003	04/01	Enhanced DD	
257	HONEYWELL	ST3000FF	Pressure Transmitter	0002	09/01		
258	HONEYWELL	STT35F	Temperature Transmitter	0101	04/01	Enhanced DD	
259	HONEYWELL	SmartLine / STT850	Temperature Transmitter	0006	01/02	Enhanced DD	
260	HONEYWELL	STT650	Temperature Transmitter	0020	01/01		
261	HONEYWELL	STT17F	Temperature Transmitter	1101	01/01		
262	HONEYWELL	SmartLine/RMA 803	Remote Indicator	0005	01/01	Enhanced DD	
263	ISE-MAGTECH	LTM-300FF	Magnetostrictive Level Transmitter	0101	01/01		
264	K-TEK	AT100/ AT100S/ AT200	Magnetostrictive Level Transmitter	0100	02/01	02_FB302- 20080319_AF080306	
265	K-TEK	AT100/ AT100S/ AT200	Magnetostrictive Level Transmitter	0100	03/01		
266	K-TEK	MT5000/ MT5100/ MT5200	Guided Radar Level Transmitter	5000	01/01	01_FB302- 20080530_MF080530	
267	K-TEK	MT5000/ MT5100/ MT5200	Guided Radar Level Transmitter	5000	02/01		
268	K-TEK	MT5000/ MT5100/ MT5200	Guided Radar Level Transmitter	5000	03/01		

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
269	KNICK	COMFF 3400 -085	Measuring System for Liquid Analysis	0D48	01/01		
270	KNICK	Stratos FF2231X Cond	Conductivity Transmitter	5728	01/01		
271	KNICK	Stratos FF2231X Oxy	OXY Transmitter	5727	01/01		
272	KNICK	Stratos FF2231X pH	pH Transmitter	08B7	01/01		
273	KNICK	Stratos FF2232X Condi	Torodial Conductivity Transmitter	08B8	01/01		
274	KNICK	Stratos Pro FF A231N/A231X	Measuring System for Liquid Analysis	A231	01/01	Enhanced DD	
275	KROHNE MESSTECHNIK	BM100	Reflex Radar	EE01	02/01		
276	KROHNE MESSTECHNIK	BM70	Radar Level Meter	F901	03/01		
277	KROHNE MESSTECHNIK	IFC090	Electromagnetic Flowmeter	F401	01/01		
278	KROHNE MESSTECHNIK	IFC100	Electromagnetic Flowmeter	0100	01/01	Enhanced DD	
279	KROHNE MESSTECHNIK	IFC300	Electromagnetic Flowmeter	0300	01/01		
280	KROHNE MESSTECHNIK	M40 ESK4-FF	Variable Area Flowmeter, Level Meter	0700	01/01	Enhanced DD	
281	KROHNE MESSTECHNIK	Optiflux IFC300	Electromagnetic Flowmeter	0300	03/01	Enhanced DD	
282	KROHNE MESSTECHNIK	Optimass MFC300	Coriolis Mass Flowmeter	0320	03/01	Enhanced DD	
283	KROHNE MESSTECHNIK	M40 ESK4-FF	Variable Area Flowmeter and Level Meter	0700	02/01	Enhanced DD	
284	KROHNE MESSTECHNIK	OptiSwirl 4200	Vortex Flowmeter	0200	01/03	Enhanced DD	
285	KROHNE MESSTECHNIK	OptiWave_x400/x500	FMCW Radar Level Transmitter	0280	01/01	Enhanced DD	
286	KROHNE MESSTECHNIK	Optimass MFC400	Coriolis Mass Flowmeter	0330	02/02	Enhanced DD	

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
287	KROHNE MESSTECHNIK	OptiFlex 2200 C/F	TDR Level Meter	0220	01/01	Enhanced DD	
288	KROHNE MESSTECHNIK	OptiSonic UFC 400	Ultrasonic Flowmeter	0370	01/02	Enhanced DD	
289	L. BERNARD S.A	BERNARD_ ACTUATOR	Actuator	0001	01/01	M1.3 TI.1H 4.5	
290	L. BERNARD S.A	Intelli+ FF Interface	Actuator Communication Interface	0002	01/03	Enhanced DD	
291	MAGNETROL	705	Guided Wave Radar Level	0705	01/01	Obsolete	
292	MAGNETROL	E3 Modulelevel	Displacer Level Transmitter	0003	01/01		
293	MAGNETROL	Eclipse Enhanced Model 705 3X	Guided Wave Radar Level	0001	01/01		
294	MAGNETROL	Eclipse Enhanced Model 705 3X	Guided Wave Radar Level	0001	01/01	Mdl705FF Ver3.0k	
295	MAGNETROL	Eclipse Enhanced Model 705 3X	Guided Wave Radar Level	0001	02/01		
296	MAGNETROL	Eclipse Model 706	Guided Wave Radar Level Transmitter	0005	01/01	Enhanced DD	
297	MAGNETROL	Eclipse Model 706	Guided Wave Radar Level Transmitter	0005	02/01	Enhanced DD	
298	MAGNETROL	Orion Jupiter Model 2xx	Magnetostrictive Level Transmitter	0002	01/01		
299	MAGNETROL	Thermatel Enhanced Model TA2 2x	Magnetostrictive Level Transmitter	0004	01/01	Enhanced DD	
300	MAGNETROL	Orion Jupiter Model JM4	Magnetostrictive Level Transmitter	0006	01/01	Enhanced DD	
301	MAGNETROL	Orion Jupiter Model JM4	Magnetostrictive Level Transmitter	0006	01/02	Enhanced DD	
302	MAGNETROL	Pulsar Model R96	Non-Contact Radar Level Transmitter	0007	01/01	Enhanced DD	
303	MAGNETROL	Pulsar Model R86	Non-Contact Radar Level Transmitter	0008	01/01	Enhanced DD	

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
304	MAGNETROL	Model R86	Non-Contact Radar Level Transmitter	0008	02/01	Enhanced DD	
305	MICROMOTION	MVD2700	Mass Flow Sensor	2000	03/02		
306	MICROMOTION	MVD2700	Coriolis Mass Flowmeter	2000	04/01		
307	MICROMOTION	MVD2700	Coriolis Mass Flowmeter	2000	05/01	Tested with STARDOM/CENTUM	
308	MICROMOTION	MVD2700	Coriolis Mass Flowmeter	2000	06/01		
309	MICROMOTION	MVD2700	Coriolis Mass Flowmeter	2000	07/01	Enhanced DD	
310	MICROMOTION	MVD2700	Coriolis Mass Flowmeter	2000	08/01	Enhanced DD	
311	MICROMOTION	Micro Motion MVD 2700	Coriolis Mass Flowmeter	2000	09/01	Enhanced DD	
312	MICROMOTION	Micro Motion MVD 5700	Advanced Coriolis Flow / Density Transmitter	5700	01/01	Enhanced DD	
313	MICROMOTION	Micro Motion MVD 5700	Advanced Coriolis Flow / Density Transmitter	5700	01/02	Enhanced DD	
314	METTLER TOLEDO	Cond 7100e FF	Conductivity Meter	1BBC	01/01		
315	METTLER TOLEDO	Cond Ind 7100e FF	Torodial Conductivity Transmitter	1BBD	01/01		
316	METTLER TOLEDO	M400(G) FF	Multi-parameter transmitter	0400	01/01	Enhanced DD	
317	METTLER TOLEDO	M700 FF700	Measuring System for Liquid Analysis	00F0	01/01		
318	METTLER TOLEDO	O2 4100eFF	O2 Transmitter	1004	01/01		
319	METTLER TOLEDO	pH2100e FF	pH Transmitter	0834	01/01		
320	MTL	9331-TI	Temperature Transmitter	9331	01/01		
321	MTL	F809F	Fieldbus Diagnostic Module	0001	01/01		
322	MTL	F809F	Fieldbus Diagnostic Module	0001	02/01		
323	MTL	F809F-Plus	Fieldbus Diagnostic Module	0001	03/01	Enhanced DD	
324	OHMART	GEN2000	Nuclear Level Gauge	0003	02/01		
325	OHMART	GEN2000	Nuclear Density Gauge	0003	03/02		
326	OHMART	GEN2000 Density	Nuclear Density Gauge	0004	03/01		

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
327	ORANGE INSTRUMENTS BIFOLD	IS210F FISCO	Actuator Positioner	F210	01/01	Enhanced DD	
328	OVAL CORPORATION	ALTI <sub>mass</sub>	Coriolis Mass Flowmeter	0DD9	01/01	Enhanced DD	
329	OVAL CORPORATION	EX-DELTA	Vortex Flowmeter	0065	01/02		
330	OVAL CORPORATION	EX-DELTA Electrical	Vortex Flowmeter	0065	02/01		
331	OVAL CORPORATION	ULTRAM <sub>mass</sub> MKII	Flowmeter	24B9	01/01		
332	OVAL CORPORATION	CT9401	Flowmeter	24B9	02/01		
333	PEPPERL+FUCHS	F2D0-TI-Ex8.FF	Temperature Multiplexer	0003	01/01		
334	PEPPERL+FUCHS	F2D0-TI-Ex8.FF	Temperature Multiplexer	0003	01/07		
335	PEPPERL+FUCHS	F2D0-TI-Ex8.FF	Temperature Multiplexer	0003	02/01	Enhanced DD	
336	PEPPERL+FUCHS	F2D0-TI-Ex8.FF	Temperature Multiplexer	0003	02/02	Enhanced DD	
337	PEPPERL+FUCHS	D0-MIO-Ex12.FF	Multi-Input/Output Device	0007	01/03	Enhanced DD	
338	PEPPERL+FUCHS	FD0-VC-Ex4.FF	Valve Coupler Fieldbox	0001	01/01		
339	PEPPERL+FUCHS	FD0-VC-Ex.4FF	Valve Coupler Fieldbox	0001	02/01		
340	PEPPERL+FUCHS	HD2-GT-2AD.FFIO	Diagnostic Gateway	0005	01/02		
341	PEPPERL+FUCHS	LB 8110-FB 8210	FF Remote IO	8010	02/01		
342	PHOENIX CONTACT	FB-DIAG/FF/LI & FB-DIAG/FF/NC	Field Diagnostics Module	0321	01/01	Enhanced DD	
343	POWER GENEX LTD	SS	Smart Valve Positioner	0001	01/01	Enhanced DD Tested as Basic device	X: Supported
344	PR ELECTRONICS	PR <sub>etop</sub> 5350	Temperature Transmitter	0080	01/01		
345	PR ELECTRONICS	PR <sub>etop</sub> 5350	Temperature Transmitter	0080	02/01		
346	PR ELECTRONICS	PR6350	Temperature Transmitter	0081	01/01		
347	R STAHL SCHALTGERATE GMBH	9413	Digital I/O Coupler 9413/21 (4-wire)	24C5	01/01		

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
348	R STAHL SCHALTGERATE GMBH	9413 (4-wire version)	Digital I/O Coupler	24C5	03/01		
349	R STAHL SCHALTGERATE GMBH	DCM 9415	Diagnosis Communication Module	0001	01/01		
350	ROTORK CONTROLS LTD	FF-01	Valve Actuator	0001	02/01		
351	ROTORK CONTROLS LTD	FF01 MK2	Valve Positioner	0002	01/01	SW_REV: M1.2T1.1 H1.0	
352	ROTORK CONTROLS LTD	FF01 MK2 Network Interface	Valve Positioner	0002	02/01	Tested with STARDOM/CENTUM	
353	ROTORK CONTROLS LTD	IQ3	Multi-Turn Electric Valve Actuator	0003	01/01	Enhanced DD	
354	ROTORK YTC LIMITED	YT-3300	Smart Positioner	0009	01/01	Enhanced DD	
355	SAMSON AG	Positioner 3787	Valve Positioner	0001	02/01		
356	SAMSON AG	Positioner 3730-5	Valve Positioner	0002	01/01		
357	SAMSON AG	3738-50	SMART Discrete Valve Controller	0003	01/01	Enhanced DD	
358	SAMSON AG	373x-5	Valve Positioner / Final Control Element	0002	02/01	Enhanced DD	
359	SAMSON AG	373x-5	Valve Positioner / Final Control Element	0002	03/01	Enhanced DD	
360	SCHNEIDER ELECTRIC	240FF	Intelligent Transmitter	2506	01/01		
361	SCHNEIDER ELECTRIC	240FF	Intelligent Transmitter	2506	08/01	Enhanced DD	
362	SCHNEIDER ELECTRIC	SRD960	Intelligent Positioner	2481	12/01	Enhanced DD	
363	SCHNEIDER ELECTRIC	SRD991	Intelligent Valve Positioner	2401	10/01		
364	SCHNEIDER ELECTRIC	SRD991	Intelligent Positioner	2401	12/01	Enhanced DD	

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
365	SCHNEIDER ELECTRIC	83	Vortex Flow Transmitter	BD33	03/01	REV_INFO: 3.55/3.2	
366	SCHNEIDER ELECTRIC	IAP10	Single Variable Pressure Transmitter	BA30	30/01		
367	SCHNEIDER ELECTRIC	IMT25	Magnetic Flowmeter	BC29	02/01	REV_INFO: 3.10/3.2	
368	SCHNEIDER ELECTRIC	RTT15-F	Temperature Transmitter	1036	01/01		
369	SCHNEIDER ELECTRIC	RTT30	2 Channel Temperature Transmitter	C034	02/01	Enhanced DD	
370	SCHNEIDER ELECTRIC	RTT80	2 Channel Temperature Transmitter	C035	02/03	Enhanced DD	
371	SCHNEIDER ELECTRIC	IGP10S	Series S Single Pressure Transmitter	BA30	32/02	Enhanced DD	
372	SCHNEIDER ELECTRIC	IDP50S-F Premium Performance	Pressure Transmitter	BA40	01/01	Enhanced DD	
373	SIEMENS AG	SIPART PS2 FF	Valve Positioner	0015	01/01		
374	SIEMENS AG	SIPART PS2 FF	Valve Positioner	0015	02/01		
375	SIEMENS AG	SIPART PS2 FF	Valve Positioner	0015	02/02	Enhanced DD	
376	SIEMENS AG	SIPART PS2 FF	Valve Positioner	0015	04/01	Enhanced DD	
377	SIEMENS AG	SITRANS F M MAG6000	Electromagnetic Flowmeter	0018	01/01		
378	SIEMENS AG	SITRANS F C MASS6000	Coriolis Mass Flowmeter	0019	01/01		
379	SIEMENS AG	SITRANS LR250	Radar Level Transmitter	1954	01/01		
380	SMAR	FI302	Fieldbus to Current Converter	0005	04/01		
381	SMAR	FP302	Fieldbus-Pneumatic Signal Converter	0004	04/01		X: Supported
382	SMAR	FY302	Fieldbus Positioner	0006	04/07		
383	SMAR	IF302	Current to Fieldbus Converter	0003	04/01		
384	SMAR	TT302	Universal Temperature Transmitter	0002	04/01		

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
385	STONEL	461052	Discrete IO (Bus Powered Outputs)	0052	01/01		
386	STONEL	461088	Analog I/O (Externally powered outputs)	00F2	01/01		
387	STONEL	Function Option 93 Discrete VCT	Discrete VCT (Bus Powered Outputs)	0051	02/01		
388	STONEL	I/O module (2DI, 2DO, 1AI, 1AO)	Discrete and Analog I/O Block	00F2	02/01		
389	STONEL	VCT/I/O Module (2DI, 2DO)	VCT/Univ. Discrete I/O Block	0052	02/01		
390	TLV CO LTD	iTrapSensor	Sensor for Steam Trap	0001	01/01	Enhanced DD	
391	TOKYO KEISO	FST4000FB	Torque Tube Displacement Level Transmitter	0002	03/01		
392	TOKYO KEISO	FST4000FB	Torque Tube Displacement Level Transmitter	0002	04/01	Enhanced DD	
393	TOPWORX	D2-FF	Valve Controller	0200	02/03	Enhanced DD	X: Supported
394	TOPWORX	TopWorx D2-FF	Discrete Valve Controller/Positioner	0200	03/01	Enhanced DD	
395	TOPWORX	Valvetop DXP/DVC-FF	Lumitech Discrete Valve Controller (On/Off)	0100	02/01	Topworx Rev 1.2.7	X: Supported
396	TOPWORX	Valvetop DXP/DVC-FF	Lumitech Discrete Valve Controller (On/Off)	0100	02/03	Topworx Rev 1.3.4	
397	TURCK	KMU-40Ex/1GD	Temperature Transmitter	FF9C	01/01		
398	VALMET FLOW CONTROL OY	NDX FF	Positioner	000EA	01/01		X: Supported
399	VALMET FLOW CONTROL OY	LCP9000F	Local Control Panel	232A	01/01		
400	VALMET FLOW CONTROL OY	ND800FF	Digital Valve Positioner	0320	03/02		
401	VALMET FLOW CONTROL OY	ND9000F	Digital Valve Positioner	2328	01/02		

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
402	VALMET FLOW CONTROL OY	ND9000F	Digital Valve Positioner	2328	02/01	F09424-1. 31	
403	VALMET FLOW CONTROL OY	ND9000F	Digital Valve Positioner	2328	02/01	F09424-1. 492	
404	VALMET FLOW CONTROL OY	ND9000F	Digital Valve Positioner	2328	03/01	F09424-1. 55	
405	VALMET FLOW CONTROL OY	ND9000F	Digital Valve Positioner	2328	03/01	F09424-1. 57	
406	VALMET FLOW CONTROL OY	ND9000F	Digital Valve Positioner	2328	05/01		
407	VALMET FLOW CONTROL OY	ND9000F	Intelligent Valve Positioner	2328	06/01	Enhanced DD	
408	VALMET FLOW CONTROL OY	NDX FF	Intelligent Valve Controller	00EA	01/01		
409	VALMET FLOW CONTROL OY	VG9000F	Smart Valve Controller	2329	01/01		
410	VALMET FLOW CONTROL OY	VG9000F	Intelligent Safety Solenoid with PST	2329	03/01	Enhanced DD	
411	VALMET FLOW CONTROL OY	VG9000F	Intelligent Safety Solenoid with PST	2329	03/02	Enhanced DD	
412	VALVE AUTOMATION	CAM228/CAM28 FF	Electric Actuator	EDC3	01/01	Enhanced DD	X: Supported
413	VEGA	FIBERTRAC 31	Radiation-based Sensor for Continuous Level Measurement	0CF2	02/01	Enhanced DD	
414	VEGA	FIBERTRAC 31	Radiation-based Sensor for Continuous Level Measurement	0CF2	03/01	Enhanced DD	
415	VEGA	FIBERTRAC 32	Radiation-based Sensor for Continuous Level Measurement	0CF3	02/01	Enhanced DD	
416	VEGA	MINITRAC 31	Radiation-based Sensor for Density Measurement and Level Detection	0CF5	02/01	Enhanced DD	

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
417	VEGA	MINITRAC 31	Radiation-based Sensor for Density Measurement and Level Detection	0CF5	03/01	Enhanced DD	
418	VEGA	POINTRAC 31	Radiation-based Sensor for Level Detection	0D48	02/01	Enhanced DD	
419	VEGA	POINTRAC 31	Radiation-based Sensor for Level Detection	0D48	03/01	Enhanced DD	
420	VEGA	SOLITRAC 31	PreRadiation-based Sensor for Continuous Level Measurement	0CF4	02/01	Enhanced DD	
421	VEGA	SOLITRAC 31	Radiation-based Sensor for Continuous Level Measurement	0CF4	03/01	Enhanced DD	
422	VEGA	VEGABAR	Pressure Transmitter	076F	01/01	Firmware R3.07	
423	VEGA	VEGABAR	Pressure Transmitter	076F	01/01	Firmware R3.11.01	
424	VEGA	VEGABAR	Pressure Transmitter	076F	03/01		
425	VEGA	VEGABAR	Pressure Transmitter	076F	04/01		
426	VEGA	VEGABAR 80 Series FF	Pressure Transmitter	0BF9	01/01	Enhanced DD	
427	VEGA	VEGABAR 80 Series FF	Pressure Transmitter	0BF9	02/02	Enhanced DD	
428	VEGA	VEGABAR 80 Series FF	Pressure Transmitter	0BF9	03/01	Enhanced DD	
429	VEGA	VEGACAL	Admittance Level Transmitter	076E	03/01		
430	VEGA	VEGACAL	Admittance Level Transmitter	076E	04/01		
431	VEGA	VEGAFLEX	Guided Microwave Level Transmitter	0771	01/01	Firmware R3.07	
432	VEGA	VEGAFLEX	Guided Microwave Level Transmitter	0771	01/01	Firmware R3.11.01	
433	VEGA	VEGAFLEX	Guided Microwave Level Transmitter	0771	03/01		

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
434	VEGA	VEGAFLEX	Guided Microwave Level Transmitter	0771	04/01		
435	VEGA	VEGAFLEX 80 Series	Guided Wave Radar Level Transmitter	0BF5	01/01	Enhanced DD	
436	VEGA	VEGAFLEX 80 Series	Guided Wave Radar Level Transmitter	0BF5	02/01	Enhanced DD	
437	VEGA	VEGAFLEX 80 Series	Guided Microwave Transmitter	0BF5	03/01	Enhanced DD	
438	VEGA	VEGAPULS	RADAR Level Transmitter	0772	01/01	Firmware R3.07	
439	VEGA	VEGAPULS	RADAR Level Transmitter	0772	01/01	Firmware R3.11.01	
440	VEGA	VEGAPULS	RADAR Level Transmitter	0772	03/01		
441	VEGA	VEGAPULS	RADAR Level Transmitter	0772	04/01		
442	VEGA	VEGAPULS 61	RADAR Level Transmitter	0BFC	06/01	Firmware R4.5.0 Build 7	
443	VEGA	VEGAPULS 62	RADAR Level Transmitter	0BFD	06/01	Firmware R4.5.0 Build 7	
444	VEGA	VEGAPULS 63	RADAR Level Transmitter	0BFE	06/01	Firmware R4.5.0 Build 7	
445	VEGA	VEGAPULS 65	RADAR Level Transmitter	0BFF	06/01	Firmware R4.5.0 Build 7	
446	VEGA	VEGAPULS 66	RADAR Level Transmitter	0C00	06/01	Firmware R4.5.0 Build 7	
447	VEGA	VEGAPULS 67	RADAR Level Transmitter	0C01	06/01	Firmware R4.5.0 Build 7	
448	VEGA	VEGAPULS 68	RADAR Level Transmitter	0C02	06/01	Firmware R4.5.0 Build 7	
449	VEGA	VEGAPULS 69	RADAR Level Transmitter	0BFA	01/01	Enhanced DD	
450	VEGA	VEGAPULS 69	RADAR Level Transmitter	0BFA	02/01	Enhanced DD	

No.	Vendor	Model	Description	Device Type	Dev/DD REV	Remarks	Device Viewer
451	VEGA	VEGAPULS WL 61	RADAR Level Transmitter	0CDB	06/01	Firmware R4.5.0 Build 7	
452	VEGA	VEGAPULS SR 68	RADAR Level Transmitter	0CDC	06/01	Firmware R4.5.0 Build 7	
453	VEGA	VEGASON	Ultrasonic Level Transmitter	0770	01/01	Firmware R3.07	
454	VEGA	VEGASON	Ultrasonic Level Transmitter	0770	01/01	Firmware R3.11.01	
455	VEGA	VEGASON	Ultrasonic Level Transmitter	0770	03/01		
456	VEGA	VEGASON	Ultrasonic Level Transmitter	0770	04/01		
457	VEGA	WEIGHTRAC 31	Radiation-based Sensor for Mass Flow Detection	0CF8	02/01	Enhanced DD	
458	VEGA	VEGADIF 85	Differential Pressure Transmitter	0BF6	03/02	Enhanced DD	
459	WESTLOCK CONTROLS	EL40106	FPAC Valve Controller	0001	01/01		
460	WESTLOCK CONTROLS	Intellis ICoT FF	IS Pneumatic Positioner	1100	01/01		
461	WIKA	IPT-1x-4	Pressure Transmitter	00EC	03/01		
462	WIKA	T53.10	Temperature Transmitter	5310	01/01		
463	Wonder Engineering Technologies Pte Ltd, c/o Yangzhou Hengchun Electronics Co., Ltd	CKD Series Electric Actuator	Electric Actuator	0001	01/01		
464	Zhejiang SUPCON Technology Co., Ltd	CXT	Pressure Transmitter	0004	02/01		