

## PRESS RELEASE

### ***FOR IMMEDIATE RELEASE***

Date: August 27, 2012

Contact: [info@us.yokogawa.com](mailto:info@us.yokogawa.com)

Contact Phone: 1-800-888-6400

Release #: 1043

### **Yokogawa Releases New DC mA Clamp-on Process Meter**

Yokogawa Corporation of America is pleased to announce the release of another high quality and well-engineered product, the CL420 Clamp-on Process Meter. The CL420 will safely measure 0-120 mA DC process control signals without breaking the loop. Typical application examples include distributed control systems, programmable logic controllers, pressure and temperature transmitters, and loop powered isolators and indicators.

Outstanding features of the Yokogawa CL420 include:

- 0.2% Accuracy and 0.01 mA Resolution from 0-20 mA DC
- mA Measurement and % of Span for 4-20 mA
- Dual LCD Numeric Display.
- LED Torch Light
- Data Hold Function
- 6mm Clamp Diameter
- Analog Output Available

The Yokogawa CL420 is complementary to our existing portfolio of calibrators, such as the CA11 Loop Calibrator, CA71 and CA150 Multifunction Calibrators, and the CA450 Process

Meter. The analog output can be used as an input to the XL120 data logger, TY500/700 Multimeters, or chart recorders.

Standard accessories provided with the CL420 are a carrying case, 4 AA batteries, and an instruction manual. Optional accessories include analog output cables with banana plugs or screw terminals. The CL420 has a 1 year warranty.

The Yokogawa CL420 Clamp-on Process Meter is available through Yokogawa distributors and representatives at a suggested list price of \$625. For more information on the Yokogawa CL420 and additional Yokogawa Meter and Instruments products, visit [www.tmi.yokogawa.com](http://www.tmi.yokogawa.com) or contact us via email at [meters-instr@us.yokogawa.com](mailto:meters-instr@us.yokogawa.com).

## **About Yokogawa Corporation of America**

Yokogawa Corporation of America is the North American division of Yokogawa Electric Corporation and a key part of Yokogawa's global network of 25 manufacturing facilities and 80 companies spanning 55 countries. Since its founding in 1915, the US\$4 billion company has been engaged in cutting-edge research and innovation, securing more than 7,200 patents and registrations, including the world's first digital sensors for flow and pressure measurement. Industrial automation and control, test and measurement, information systems and industry support are the core businesses of Yokogawa. For more information about Yokogawa, please visit our website [www.yokogawa.com/us](http://www.yokogawa.com/us).

## **About Yokogawa**

Yokogawa's global network of 90 companies spans over a total of 55 countries. Founded in 1915, the US\$4 billion corporation conducts cutting-edge research and innovation. Yokogawa is engaged in industrial automation and control (IA), test and measurement, and other business segments. The IA segment plays a vital role in a wide range of industries including oil, chemicals, natural gas, power, iron and steel, pulp and paper, pharmaceuticals, and food. For more information about Yokogawa, please visit our website [www.yokogawa.com](http://www.yokogawa.com).