

Temperature Sensing Solutions

Solving measurement problems using edge solution products

Temperature Sensing Solutions

Solving measurement problems using edge solution products



FA-M3
VITESSE™

e-RT3 Plus
anyone anytime anywhere



SMARTDAC+™



DTSX®



Sensing Inaccessible Temperatures

Application 1

Temperature measurement of plasma environment

Key Products 


DTSX Distributed Temperature Sensor FA-M3V/e-RT3 Plus Edge Controller

■ Challenge

Measuring internal chamber temperatures in plasma surface treatment used in semiconductor and printed circuit board manufacturing is difficult as metallic and conductive sensors cannot be used.

■ Yokogawa's Solution

Internal chamber temperatures are measured using a fiber-optic cable as temperature sensor as it is not affected by plasma. Chamber environment information helps to improve process quality. Moreover, acquired measurement data can be uploaded to FA-M3V/e-RT3 Plus for equipment control, storage or transfer to host systems.



Application 2

In-line mold temperature measurement (deterioration monitoring)

Key Products 


FA-M3V/e-RT3 Plus Edge Controller GA10 Data Logging Software

■ Challenge

Temperature mottles caused by mold deterioration directly impacts workpiece quality. As it is difficult to install a temperature sensor inside a mold, non-contact sensors such as thermal cameras are often used. The required proprietary systems are, however, costly and does not integrate well with host systems.

■ Yokogawa's Solution

The FA-M3V Edge Controller is directly connected to a thermal camera to deliver cost-effective computation and decision processing using a general-purpose controller, which integrates well with host systems. It can also be used with Data Logging Software GA10 to enable extended data storage.



Sensing Long-Distant Temperatures

Application 3

Long-range temperature monitoring (1)

Key Products 


GX20 Paperless Recorder Thermal Camera Solution

■ Challenge

The risk of cable fire increases when cable junction connections loosen and power cables age. **Periodic monitoring of underground long distance cables is, however, difficult due to distance and installed location.**

■ Yokogawa's Solution

Fiber-optic cables are installed alongside power cables to detect cable fires and temperature anomalies. The DTSX3000 Distributed Temperature Sensor provides temperature monitoring of long distance fiber-optic sensing cables; GA10 and FA-M3V/e-RT3 plus enables temperature monitoring from a PC and generation of alarm signals.



Application 4

Long-range temperature monitoring (2)

Key Products 

DTSX200 Distributed Temperature Sensor GA10 Data Logging Software


■ Challenge

As shown in the figure on the right, long-range, wide-area temperature monitoring, typical of coal conveyors, are mostly done by:

- Human patrol, or
 - Installing numerous thermal cameras and point sensors.
- The challenges faced are monitoring lapses, as well as high initial and maintenance costs.

■ Yokogawa's Solution

Temperature can be monitored over a far, wide area and any abnormality detected promptly simply by connecting the DTSX Distributed Temperature Sensor to a fiber-optic cable laid over the area. This enables an early response to minimize any damage. Acquired data can be graphically displayed using the GA10 Data Logging Software to help pinpoint the problem location.



Sensing Wide-Area Temperatures

Application 5

Wide-area temperature sensing with thermal camera

Key Products 

GX20 Paperless Recorder Thermal Camera Solution

■ Challenge

Waste disposal sites are faced with risks of stored waste igniting spontaneously. Due to a large site area and varying waste volume, however, it is difficult to install temperature sensors to enable early detection of a temperature rise in stored waste to prevent a fire outbreak.

■ Yokogawa's Solution

A FLIR high performance thermal camera is connected to a Yokogawa GX20 paperless recorder to perform noncontact temperature monitoring over a large area where installing conventional temperature sensors is infeasible. Non-contact monitoring is not affected by varying waste volumes. When excessive temperatures are detected, a command can be issued to activate a sprinkler from a GX20 alarm contact or an FA-M3V connected via a network.



Other Publications



VARIETY OF APPLICATION NOTES

Yokogawa's Distributed Temperature Sensing Cable design provides the insight needed to proactively prevent abnormal situations, reduce safety and fire risks, and identify irregular conditions and shifts in process applications.

DOWNLOAD



E-BOOK

Looking to maintain operations and protect your assets? Want to avoid heat-induced equipment failures and abnormalities caused by them? By placing the DTSX distributed temperature sensor along the pipeline surface you can detect temperature changes and be alerted to irregularities.

DOWNLOAD



INDUSTRY RELATED BROCHURES

DTSX fiber optic sensor monitors provide 24/7, real-time monitoring of temperatures in large, areas difficult to monitor by previously existing methods, contributing to heat detection and risk prevention, without blind spots.

DOWNLOAD

BU-P-20221102-01

Yokogawa Corporation of America
12530 W. Airport Blvd.,
Sugar Land, TX 77478
www.yokogawa.com/us

Yokogawa Canada, Inc.
Bay 4, 11133 40th Street SE,
Calgary, AB T2C 2Z4
www.yokogawa.com/ca

Yokogawa de México, SA de CV
Urbina No. 18
Parque Industrial Naucalpan
Naucalpan de Juárez, Estado de México
C.P. 53370
www.yokogawa.com/mx