

# TOP 10 FEATURES

## ROTAMASS

Total Insight

### CORIOLIS FLOW METERS

01

#### DIRECT MASS MEASUREMENT

Measures mass flow, density, and temperature directly — no conversion needed for accuracy that lasts.



#### FEATURES ON DEMAND

Activate advanced functions anytime — concentration, batching, viscosity, heat quantity, or net oil computing.

02



03

#### TOTAL HEALTH CHECK

Predictive diagnostics monitor meter condition without interrupting the process.



#### PRESSURE STABILITY CONTROL

Dynamic Pressure Compensation keeps readings precise during process pressure changes.

04



05

#### BUILT FOR ANY ENVIRONMENT

Performs reliably in extreme temperatures, corrosive media, and viscous or abrasive fluids.



#### LONG-LIFE MATERIALS

Thickest measuring tubes and corrosion-resistant wetted parts ensure long-term durability.

06



#### SMART TUBE DIAGNOSTICS

Tube Health Check detects stiffness changes from corrosion, abrasion, or clogging — before failure occurs.

07



#### ENTRAINED GAS SMART POWER MEASUREMENT

Maintains a stable oscillation even at low amplitudes associated with gas-rich flows.


08



09

#### BOX-IN-BOX DESIGN

Dual housing isolates the measuring element from vibration and piping stress for greater accuracy.



#### CUSTOM LAY-LENGTH

Fits exactly into your pipework or skidded assembly without modifying welds or using spools.

10



YOKOGAWA

Co-innovating tomorrow™