General Specifications

GS 77J01H11-01E

VJHF Isolator (Super Speed Response Type) (Isolated Single-output and Isolated Dual-output Types)

NTXUL


General

The VJHF is a compact, plug-in, super speed isolator that converts DC voltage or DC current signals into isolated DC voltage or DC current signals.

The VJHF transmitter features:

- Ultra-fast 50 μs signal conversion for a 63% response;
- · a wide choice of input and output signal ranges;
- four isolated ports (input, output-1, output-2, power supply and grounding) on a dual-output model;
- a withstanding voltage of 2000 V AC;
- a wide supply voltage range supporting both 100 V and 200 V power lines of AC or DC; and
- · close side-by-side mounting.

■ Model and Suffix Codes



Items to be specified when ordering

• Model and Suffix Code: e.g. VJHF-026-AAA0

■ Input/Output Specifications

Type of input: DC voltage or DC current signal Input resistance:

- Voltage input: approx. 1 $M\Omega$ (or 100 $k\Omega$ when turned off)
- Current input: $250~\Omega$ for 4 to 20 mA range $500~\Omega$ for 2 to 10 mA range $1~k\Omega$ for 1 to 5 mA range $250~\Omega$ for 0 to 20 mA range $250~\Omega$ for 0 to 16 mA range $500~\Omega$ for 0 to 10 mA range $1~k\Omega$ for 0 to 1 mA range $100~\Omega$ for 10 to 50 mA range

Allowable input level:

- Voltage input: Within ±30 V DC
- Current input: Any level that satisfies the following condition.

 $(Input current)^2 x Input resistance \le 0.5 W$

Output signal: DC voltage or DC current Allowable load resistance:

• Output 1

Output Range	Output Range
4 to 20 mA DC: 750 Ω maximum	0 to 10 mV DC: 250 $k\Omega$ minimum
2 to 10 mA DC: 1500 Ω maximum	0 to 100 mV DC: 250 $k\Omega$ minimum
1 to 5 mA DC: 3000 Ω maximum	0 to 1 V DC: 2 $k\Omega$ minimum
0 to 20 mA DC: 750 Ω maximum	0 to 10 V DC: 10 $k\Omega$ minimum
0 to 16 mA DC: 900 Ω maximum	0 to 5 V DC: 2 k Ω minimum
0 to 10 mA DC: 1500 Ω maximum	1 to 5 V DC: 2 $k\Omega$ minimum
0 to 1 mA DC: 15 kΩ maximum	-10 to +10 V DC: 10 $k\Omega$ minimum

Output 2

Output Range Output Range
4 to 20 mA DC: 350 Ω maximum 1 to 5 V DC: 2 kΩ minimum

Zero and span adjustment: Within ±5% of span for both zero and span adjustment



GS 77J01H11-01E ©Copyright Mar. 1999 (MC) 4th Edition Mar. 2016 (YK)

■ Standard Performance

Accuracy rating: ±0.1% of span (aside from the ±0.1% accuracy of the external resistor on current-input models)

Response: 50 μ s for a 63% response (10 to 90%

change of range)

Insulation resistance: 100 M Ω minimum at 500 V DC input, output-1, output-2, power supply and grounding terminals mutually

Withstanding voltage: 2000 V AC for one minute between input, (output-1, output-2), power supply and grounding terminals mutually except input (output-1, output-2); 1500 V AC for one minute between input (output-1, output-2) terminals; 1000 V AC for one minute between output-1 and output-2 terminals

Operating temperature range: 0 to 50°C
Operating humidity range: 5 to 90% RH (no condensation)

Supply voltage range: 100-240 V AC/DC \approx (-15, +10%) 50/60 Hz or 15-30 V DC = (\pm 20%)

Effects of power line regulation: Up to ±0.1% of span for a supply voltage range of 85 to 264 V AC (47 to 63 Hz), 85 to 264 V DC or 12 to 36 V DC

Effects of ambient temperature variations: Up to ±0.2% of span per 10°C

Current consumption: 156 mA at 24 V DC

Power consumption:

3.8 W at 24 V DC; 3.3 W at 110 V DC 6.6 VA at 100 V AC; 8.7 VA at 200 V AC

Mounting and Appearance

Material: ABS resin (casing)

Mounting: Wall mounting, DIN rail mounting, or mounting on a side-by-side multiple

mounting base

Connection: Terminals with M3 size screws External dimensions: 76 (H) x 29.5 (W) x 124.5 (D)

mm

Weight: Main unit = approx. 124 g; socket = approx. 51 g

Accessories

Tag number label: One

Resistor module: One (for current input models)

■ EMC Standards

KC marking: Electromagnetic wave interference prevention standard, electromagnetic wave protection standard compliance.

KC-certified models mean those which are KC-certified on condition that they be operated over a supply voltage range of 15-30 V DC (±20%) only.


■ Customized Signal Specifications

Table 1 Manufacturable Ranges

	Current Signal	Voltage Signal
Input range	0 to 70 mA DC	-300 to +300 V DC
Span	1 to 70 mA DC	1 to 600 V DC
Zero elevation	0 to 25%	-125% to +25%
Output range	0 to 24 mA DC	-10 to +10 V DC
Span	1 to 24 mA DC	10 mV to 20 V DC
Zero elevation	0 to 200%	-100% to +200%

T01.EPS

■ Terminal Assignments




1	INPUT	(+)
2	OUTPUT 2	(+)
3	INPUT	(-)
4	N.C.	
5	OUTPUT 2	(-)
6	N.C.	
7	OUTPUT 1	(+)
8	GND	
9	OUTPUT 1	(-)
10	SUPPLY	(L+)
11	SUPPLY	(N-)


Note: For single-output models, OUTPUT2 is N.C.

F03 FPS

■ Block Diagram



■ External Dimensions



• The information covered in this document is subject to change without notice for reasons of improvements in quality and/or performance.