

PC Software Support Model List

Updated on September 30, 2018

Software	Model	Model code	SMARTDAC+	DXAdvanced				CX	FX	DAQMASTER		DARWIN	μR	DX	DX-P	FX	MV	MVAdvanced	
			GX10 GX20 GP10 GP20 GM10	DX1000 DX2000 DX1000N		DX1000T DX2000T		CX1000 CX2000	FX1000	MX100	MW100	DA100 DC100 DR130 DR230 DR240	μR10000 μR20000	DX100 DX200 DX100L DX200C	DX100P DX200P	FX100	MV100 MV200	MV1000 MV2000	
				Std	w/AS1	Std	w/AS1												
SMARTDAC+ GA10	Data Logging Software	GA10	✓*6	✓*6	✓*6	✓*6	✓*6	✓*6	✓*6	✓*6	✓*6	✓*6	✓*6	—	—	—	—	✓*6	
DAQWORX	Base	MXLOGGER	—	—	—	—	—	—	—	✓	—	—	—	—	—	—	—	—	
		DAQEXPLORER	—	✓	—	✓*1*3	—	✓	✓	—	—	—	—	✓	—	✓	✓	✓	
Others	File searching and waveform viewing	DAQManager	—	✓	—	✓*1	—	—	—	—	—	—	—	✓	—	✓	—	✓	
	Driver	LabVIEW driver	—	✓	✓	—	—	✓	—	✓	✓	✓	—	✓	—	—	—	✓	
	Viewer/settings	SMARTDAC+ STANDARD Universal Viewer	—	✓	✓	✓	✓	✓	✓	✓	—	—	—	—	✓	✓	✓	✓	✓
		SMARTDAC+ STANDARD Hardware Configurator	—	✓	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—
		DAQSTANDARD	DXA120	—	✓	✓	✓	✓	✓	—	—	—	—	—	✓	✓*10	—	✓	✓
		DAQStudio	DXA170	✓	✓	✓	✓*1	✓*1	—	—	—	—	—	—	—	—	—	—	—
		DAQSTANDARD for FX	FXA100	—	—	—	—	—	—	—	—	—	—	—	✓	—	✓	✓	—
		DAQSTANDARD for FX1000	FXA120	—	—	—	—	—	—	—	✓	—	—	—	✓	—*11	—	✓	—
		MX100 Standard Software	MX180	—	—	—	—	—	—	—	✓	—	—	—	—	—	—	—	—
MW100 Viewer Software	MW180	—	—	—	—	—	—	—	—	✓	—	—	—	—	—	—	—		
Configuration Software for μR10000/μR20000	RXA10	—	—	—	—	—	—	—	—	—	—	—	✓	—	—	—	—	—	

*1 DX1000T/DX2000T are recognized and displayed as DX1000/DX2000 respectively.

*3 Settings for the touch panel lock cannot be done for DX1000T/DX2000T. Please set the function with the main unit.

*6 Please check detail on "Connectable Devices and Software" in the GA10 General Specification (GS04L65B01-01EN)

*7 DC100 isn't supported.

*10 DXA120 includes DX-P Hardware Configurator.

*11 FXA120 does not include DX-P Hardware Configurator.