

Performance, Integrity, Security



Powerful, flexible, easy to use


- Small I/O capability - use where a simple one-way link is required Uni-directional, one way communications
- Transmitter and receiver units factory-configured as a matching pair, or user-configurable as part of a larger wireless I/O network
- Secure data encryption
- WIB-net intelligent wireless protocol, peer-to-peer communications, immediate exception reporting plus configurable high-scan updates, multi-hop mesh repeater
- Up to 3000 wireless units per network
- Power supply 9 – 30VDC, 24VDC analog loop supply internally generated
- RS232 Configuration and diagnostics port
- Compatible with the 905U Wireless I/O and Wireless Gateway family
- Class 1 Div 2 hazardous areas approval

905U-L-T Transmitter unit

- Powerful 900MHz frequency-hopping 1W transmitter
- External inputs – two digital/pulse inputs, one analog input (0-20mA, 4-20mA), and one thermocouple mV input
- Internally calculated values – analog and thermocouple setpoint status, pulse count, power supply voltage
- Thermocouple input –20 to +100mV with cold-junction compensation and linearization for J, K, T or E-type
- Local output for setpoint status: generated by comparing analog input to high and low setpoints.
- RS232 Configuration and diagnostics port

905U-L-R Receiver unit

- Three digital contact outputs and one analog output (0-20mA, 4-20mA)
- Communications failure indication and configurable output
- Outputs can be configured as retained or reset (fail-safe) on communications failure
- LED indication of radio signal strength



Different Models

905U-L-T Input Transmitter unit
905U-L-R Output Receiver unit

Standards Compliance

Radio: EN 300 220, Part 15.247, RSS-210, AS4295, AS4768.1
v compliant 89/336 EEC, AS3548, FCC Part 15, EN301489
Hazardous rating: Class 1 Div 2 (USA/Canada)
Electrical: EN60950

General Specifications

Environmental -40 to 60°C / -40 to 140°F, 0-99% RH (non-condensing)
Housing DIN-rail thermo-plastic enclosure.
100 x 22 x 120 mm / 3.9 x 0.9 x 4.7 inches.

SMA connector for antenna or coaxial cable connection.
Power Supply 9 – 30 VDC.
Power consumption @12VDC – Receiver 100mA.
Transmitter 40mA quiescent, during radio transmission (30 msec) 300mA.
Periodically scans AI to save power
Analog loop supply internally generated, 24VDC 30mA
Internal monitoring of supply voltage – may be transmitted as an “input” (Transmitter unit only)
Hazardous rating: Class 1 Div 2 (USA/Canada) pending

Transmitter Inputs

Digital/Pulse Input, two inputs, suitable for voltage free contacts / NPN, or voltage input 0-1 VDC on / >3 VDC off
Pulse input max rate 10 Hz, 50 msec on time, pulse input counted as 2 x 16 bit register

Analog input, 0-20 mA, 4-20mA, span and zero configurable (default 4-20mA), “floating” differential input, resolution 16 bit, accuracy < 0.1 %

Thermocouple input, -20mV to +100mV, J, K or T type linearization with on-board cold-junction compensation, accuracy better than 1°C

Analog & thermocouple setpoint status, setpoint status sets (on) when input value < low setpoint and resets (off) when input value > high setpoint, status transmitted as per digital input, setpoint values are settable via front-panel rotary switch or configuration software

Receiver Outputs

Digital Output, three relay contact outputs, 260VAC, 1A rating
Analog Output, 0-20mA, 4-20mA, configurable span and zero (default 4-20mA), source output, 12-bit resolution, 0.1% accuracy
Comms-Fail, internal status based on configurable time-out value. Comms-fail output. ok output, FET, 30VDC, 500mA
Fail-safe, on “comms-fail”, outputs user-configurable as retained (last correct value) or reset (fail-safe)

Wireless

Frequency hopping spread spectrum 902-928MHz, sub-bands available, 1W Approved to FCC Part 15.247, RS210
Line of sight range 20 miles (4W ERP), 15km (1W ERP);
3000 ft / 1000 m in obstructed industrial environments
Radio distances can be increased by up to 5 intermediate repeater units
Each transmission may be configured to be sent 1 to 5 times

Communications

WIB-net wireless protocol, enabling peer-to-peer communications. Input values are transmitted on immediate change plus timed updates (maximum rate 5 times per second).
Wireless messages are data encrypted for security protection.

Serial Port

RS232 RJ45 female DCE, used for configuration and diagnostics

LED Indication

Transmitter unit:
Power/OK, Radio TX, DIN1, DIN2, Analog Setpoint status
Receiver unit:
Power/OK, Radio RX, DO1, DO2, DO3, Communications fail
LED's also used to provide radio signal strength indication

Configuration and Diagnostics

Factory configuration transmitter/receiver matched pair.
User configuration via serial port. Unidirectional units can be configured to network with Multi-I/O and Gateway units.
Diagnostics features – read input values, write output values, radio signal strength, monitor communication messages.

Specifications subject to change without notice

vigilantplant.[®]

The clear path to operational excellence

SEE
CLEARLY

KNOW
IN ADVANCE

ACT
WITH AGILITY

VigilantPlant is Yokogawa's automation concept for safe, reliable, and profitable plant operations. VigilantPlant aims to enable an ongoing state of Operational Excellence where plant personnel are watchful and attentive, well-informed, and ready to take actions that optimize plant and business performance.

Yokogawa Corporation of America

North America

2 Dart Road, Newnan, GA 30265-1094, USA
Phone: 800-888-6400 Fax: 770-254-0928

12530 West Airport Blvd., Sugar Land, TX 77478
Phone: 281-340-3800 Fax: 281-340-3838

Mexico

Urbina No. 18
Fracc. Parque Industrial Naucalpan
Naucalpan de Juarez, Estado de Mexico, CP 53489
Phone: (55) 5955-7400 Fax: (55) 5955-7417

Yokogawa Canada, Inc.

Bay 4, 11133 40th Street SE, Calgary, AB Canada T2C2Z4
Phone: 403-258-2681 Fax: 403-258-0182

<http://www.yokogawa.com/us/>

Represented by: