


Customer Maintenance Parts List

EJA210E
Flange Mounted
Differential Pressure Transmitter
(Pressure-detector Section)

DPharp **EJA**™

Horizontal Impulse Piping Type



Item	Part No.	Qty	Description
1	Below F9900GH F9900GT	1	O-ring Buna-N For Option code /HE, Fluoro-rubber
2	D0114RB	1	Gasket, PTFE Teflon (Note 1)
3	Below F9340XY F9340XW F9340XZ F9340XX	1	Process connector Rc 1/4, ASTM CF-8M Rc 1/2, ASTM CF-8M 1/4 NPT, ASTM CF-8M 1/2 NPT, ASTM CF-8M
4	Below F9900AU F9900AS F9340AZ	2	Process connector bolt ASTM-B7M carbon steel 316L SST ASTM grade 660 stainless steel
5	Below F9340SA F9340SB	1	Vent plug R 1/4 with Wetted parts material code S, 316 SST 1/4 NPT with Wetted parts material code S, 316 SST
6	D0114PB	1	Vent screw, SUS316
7	Below F9200CS D0114RZ	1	Drain plug (Note 1) R 1/4 with Wetted parts material code S, 316 SST 1/4 NPT with Wetted parts material code S, 316 SST
8	Below F9275EC F9275ED	1	Vent plug (degreased), 316 SST R 1/4 1/4 NPT
9	F9275EE	1	Needle assembly (degreased), 316 SST
10	—	2	Bolt (see Table 3)
11	—	1	Ring Assembly (see Table 1) (Note 1)
12	—	1	Gasket (see Table 2)

(Note 1) In case of degrease cleansing treatment (Option code /K1, /K2, /K5, or /K6), consult Yokogawa local office.

Table 1. Ring Assembly Part Number (Note 2)

Flange Size	Standard	Drain/Vent Plug	Gasket Contact Surface	Part Number (Item 13)
3 inch (80mm)	JIS / JPI ANSI ANSI	R1/4 1/4 NPT 1/4 NPT	Flat (no serration) Flat (no serration) Serration	F9970WA F9970WB F9350TV
2 inch (50mm)	JIS / JPI ANSI ANSI	R1/4 1/4 NPT 1/4 NPT	Flat (no serration) Flat (no serration) Serration	F9970WC F9970WD F9350TT
1 1/2 inch (40mm)	JIS / JPI ANSI ANSI	R1/4 1/4 NPT 1/4 NPT	Flat (no serration) Flat (no serration) Serration	F9970WE F9970WG F9970WF

(Note 2) It consists of a ring, vents, holders, screws, and a gasket.

Table 2. Gaske Part Number

Gasket Size	Description	Part Number (Item 14)
ø100 × ø120 × t 4.5	For Flange size 3 inch (80mm) For Flange size 3 inch (80mm) , degreased	F9350SV F9970XF
ø70 × ø90 × t 4.5	For Flange size 2 inch (50mm) For Flange size 2 inch (50mm) , degreased	F9350ST F9970XD
ø60 × ø75 × t 4.5	For Flange size 1 1/2 inch (40mm) For Flange size 1 1/2 inch (40mm) , degreased	F9346ZH F9970XB

Table 3. Bolt Part Number

		Part Number (Item 12)				
		Flush			Extended	
Flange Size Flange Rating		3 inch (80 mm)	2 inch (50 mm)	1 1/2 inch (40 mm)	4 inch (100 mm)	3 inch (80 mm)
JIS 10K		Y9525YU	Y9520YU	Y9520YU	Y9525YU	Y9525YU
JIS 20K		Y9530YU	Y9525YU	Y9525YU	Y9530YU	Y9530YU
ANSI Class 150		Y9530YU	Y9525YU	Y9525YU	Y9530YU	Y9530YU
ANSI Class 300		Y9535YU	Y9530YU	Y9525YU	Y9540YU	Y9535YU
JPI Class 150		Y9530YU	Y9525YU	Y9525YU	Y9530YU	Y9530YU
JPI Class 300		Y9535YU	Y9530YU	Y9525YU	Y9540YU	Y9535YU