

General Specifications

Model SC25V
Combined pH electrode

GS 12B06J01-40EN-P

■ Overview

Having a stable, reliable and accurate measurement is of vital importance for pH measurement and control. The SC25 pH sensor has been developed and designed to make sure that this sensor will deliver these results in every application.

The build-in temperature sensor is located close to the pH measuring glass. This will result in an increased accuracy of the temperature compensation and therefore also the pH measurement. The integrated large Titanium liquid earth will improve the stability measurement countering any stray or ground loop currents that can destroy the reference sensor.

■ Features

- External titanium Liquid Earth
- Pt1000 integration in pH compartment giving highly accurate temperature compensation
- Certified for hazardous area
- CIP and Steam cleaning possible
- Useable up to 130°C (L-Glass type)
- Measuring in applications from 10 $\mu\text{S}/\text{cm}$
- SC25V-*LP25 for chemically harsh applications and high temperatures
- SC25V-*GP25 for all General-Purpose applications
- Variopin connector meets IP67



■ 1. General Specifications SC25V

1-1 Measuring elements

- pH glass electrode
- Silver Chloride reference
- Pt1000 temperature sensor

1-2 Wetted parts construction materials

Sensor body	: PEEK and AR-Glass
O-rings	: FKM (backed-up with EPDM)
Measuring sensor	: Glass (type G or L)
Reference junction	: PTFE
Liquid Earth	: Titanium

1-3 Functional Specifications (@25°C)

Isothermal point	: pH 7
Reference system	: Ag/AgCl with saturated KCl
Glass impedance	<ul style="list-style-type: none"> • *GP25 nominal 200MΩ • *LP25 nominal 700MΩ
Junction resistance	: < 5K Ω
Temperature element	: Pt1000 to IEC 751
Asymmetry potential	: 8 ± 15 mV
Linearity PH (Slope)	: > 96 % (of theoretical value)
Sensor length	: 120 mm and 225 mm

1-4 Dynamic specifications (at 25°C)

Response time pH step (7 to 4)	: < 15 sec for 90%
Response time temp step (10°C)	
Stabilization time (0.02 pH unit/10 sec.)	: < 2 minutes

1-5 Operating range

pH	: 0 - 14
Temperature	<ul style="list-style-type: none"> • *GP25 : -10°C to 80°C (14°F to 176°F) • *LP25 : 15°C to 130°C (59°F to 266°F)
Pressure	: 0 to 10 bar (0 to 142 PSIG)
Conductivity	: > 10 µS/cm

Note: The pH operating range at room temperature is 0-14 pH, but at high temperatures or range outside 2-12 pH the lifetime will be seriously shortened.

Note: The upper process temperature for the intrinsically safe

version is limited by the ambient temperature (Tamb.) defined for each temperature class (T3, T4, T5 and T6)

1-6 Shipping Details

SC25V-.....-120	
Package size (LxWxH)	: 300 x 100 x 75 mm
	: 11.8 x 3.9 x 3.0 inch
Package weight (max.)	: 0.26 kg (0.57 lbs)
SC25V-.....-225	
Package size (LxWxH)	: 435 x 60 x 60 mm
	: 17.2 x 2.4 x 2.4 inch
Package weight (max.)	: 0.28 kg (0.62 lbs)

1-7 Enviromental conditions

Storage temperature	: -10 to +50 °C (14 to 122 °F)
Ingress Protection	: IP67 (conform IEC 60529)
Sterilizable	: Up to 135 °C (275 °F)
CIP cleaning possible	: YES

1-8 Mechanical Specifications

Process connection	: PG13.5
--------------------	----------

1-9 Regulatory compliance:

Item	Description
LVD	<ul style="list-style-type: none"> • ANSI/ISA 61010-1 • CAN/CSA C22.2 No. 61010-1
RoHS	EU Directive 2011/65/EU and Commission Delegated Directive (EU) 2015/863 amending Annex II, applying Annex IV as regards the application of the sensors, detectors and electrodes per <ul style="list-style-type: none"> • EN-IEC 63000
PED	EU Directive 2011/68/EU applying Article 4.3: Sound Engineering Practice.
WEEE	EU directive 2012/19/EU This sensor is intended to be sold and used only as a part of equipment which is excluded from the WEEE directive, such as large-scale stationary industrial tools, a large-scale fixed installation etc., and therefore it is in principle fully compliant with WEEE directive. The sensor should be disposed in accordance with applicable national legislations/regulations respectively.
Ingress Protection	IP67
Explosion proof	For details see Section Equipment ratings and Section Approvals and certification

1-10 Equipment ratings:

Item	Description	
Electrical parameters	<ul style="list-style-type: none"> • Max. input voltage • Max. input current • Max. input power • Max. internal capacitance • Max. internal inductance 	<ul style="list-style-type: none"> • $U_i = 18 \text{ VDC}$ • $I_i = 170 \text{ mA}$ • $P_i = 400 \text{ mW}$ • $C_i = 0.0 \text{ nF}$ for connector types without ID-chip • $= 0.4 \text{ nF}$ for connector types with ID-chip • $L_i = 0.0 \text{ mH}$ for connector types
Temperature class	<ul style="list-style-type: none"> • T6 • T5 • T4 • T3 	<ul style="list-style-type: none"> • $-40^\circ\text{C} \leq T_a \leq +40^\circ\text{C}$ • $-40^\circ\text{C} \leq T_a \leq +55^\circ\text{C}$ • $-40^\circ\text{C} \leq T_a \leq +55^\circ\text{C}$ • $-40^\circ\text{C} \leq T_a \leq +105^\circ\text{C}$
Specific conditions of use	<p>Potential electrostatic charging hazard: pH sensors containing accessible plastic parts and/or external conductive parts must be installed and used in such a way, that dangers of ignition due to hazardous electrostatic charges cannot occur, especially in the case that the process medium is non-conductive. Use a damp cloth for cleaning the equipment.</p>	

1-11 Approvals and certifications:

Type	Approval or certification
ATEX (EU)	EU Directive 2014/34/EU, ATEX approval: DEKRA 11ATEX0014 X, 0344 II 1 G Ex ia IIC T3...T6 Ga Applied standards: EN IEC 60079-0 / EN 60079-11
IECEx	IECEx approval: IECEx DEK 11.0064X, Ex ia IIC T3...T6 Ga Applied standards: IEC 60079-0 / IEC 60079-11
FM (Canada/ United States)	FM approval Canada: FM20CA0062X, IS SI CL I, DIV 1, GP ABCD, T3...T6, CL I, ZN 0, Ex ia IIC, T3...T6 Ga Control Drawing: D&E 2020-023-A51 Applied standards: CAN/CSA-C22.2 No. 60079-0 / CAN/CSA-C22.2 No. 60079-11 / CAN/CSA-C22.2 No. 61010-1 FM approval United States: FM20US0123X, IS CL I, DIV 1, GP ABCD, T3...T6, CL I, ZN 0, AEx ia IIC, T3...T6 Ga Control Drawing: D&E 2020-023-A50 Applied standards: FM Class 3600 / FM Class 3610 / ANSI/ISA 60079-0 / ANSI/ISA 60079-11 / ANSI/ISA 61010-1
NEPSI (China)	NEPSI approval: GYJ21.2891X, Ex ia IIC T3...T6 Ga Applied standards: GB 3836.1 / GB 3836.4 / GB 3836.20
PESO (India)	PESO approval: PESO approval is based on ATEX approval DEKRA 11ATEX0014 X, iss. 2 – 29.11.2019 Equipment reference numbers: P512760/1 Applied standards: EN IEC 60079-0 / EN 60079-11
TS (Taiwan)	TS approval: TS Safety Label is based on IECEx approval IECEx DEK 11.0064X / Identification Number: TD04000C Applied standards: IEC 60079-0 / IEC 60079-11
EAC Ex (Russia)	EAC Ex certificate: RU C-NL.AA87.B.00754, 0Ex ia IIC T6...T3 Ga X Applied standards: GOST 31610.0 (IEC 60079-0) / GOST 31610.11 (IEC 60079-11) / GOST IEC 60079-14

1-12 Cables:

For details concerning the cables please consult the respective General specifications

- Single and Dual Coax WU10 - GS12B06W02
- Extension cable WE10 - GS12B06W02

Specifications Combined pH electrodes with Temperature + Liquid earth

Type	Membrane	Resistance in M Ω /25°C	pH-range	Temp. range (°C)	Pressure range kPa	Reference liquid	Ref.	Diaph. system	Atex
SC25V- *GP25	Universal pH-glass	140 - 260	0-14	-10 - 80	0 - 1000	Oversaturated KCl	Ag / AgCl (wire)	PTFE	Yes
SC25V- *LP25	Chem.Res. pH-glass dome	650 - 900	0-14	+15 - 130	0 - 1000	Oversaturated KCl	Ag / AgCl (wire)	PTFE	Yes


2. Dimensions

Figure 1: Dimensional drawing SC25V




Figure 2: Dimensional drawing K1520JN, K1500DV, K1520JP

■ 3. Model Codes & Parts

Table 1: Model and suffix codes for SC25V

Model	Suffix Code	Description
SC25V		Combined 12mm sensor: pH, Ref, LE, Temperature Equipped with Variopin connector
Sensor type	-AGP25	General purpose, Analog, IS for ATEX/IECEX/FM-US/FM-CAN
	-ALP25	High temp. chemical resist., Analog, IS for ATEX/IECEX/FM-US/FM-CAN
	-BGP25	General purpose, SENCOM ID-chip, IS for ATEX/IECEX/FM-US/FM-CAN
	-BLP25	High temp. chemical resistant, SENCOM ID-chip, IS for ATEX/IECEX/FM-US/FM-CAN
Sensor length	-120	120 mm
	-225	225 mm

Table 2: Spare Parts

Part Number	Description
Sealings	
K1500BV	O-RINGS EPDM 11X3 (6 PCS.)
K1500BZ	O-RINGS VITON 11X3 (6 PCS.)
K1500GR	O-RINGS SILICON 11X3 (8PCS)
K1524AA	Set of O-ring 11x3 and slide ring Ryton
FP20-R12	Blind plug set for 1-hole
Adapters	
K1523JA	Adapter Pg13.5 in F*40 PPO
K1523JB	Adapter PG13.5 to 3/4"NPT PPO
K1523JC	Adapter Pg13.5 in F*40 SS
K1523JD	Adapter PG13.5 to 3/4"NPT SS
K1520JN	Adapter M25x1.5 - PG13.5 PVC
K1520JP	Adapter M25x1.5 - PG13.5 RVS
K1500DV	Adapter M25x1.5 - PG13.5 PVDF
K1598AC	Flow fitting (3.1), for SC4A (In combination with K1523JB/JD)
Consumables	
K1521TA	Buffer Capsules for pH 1.68 @25°C (1 bottle= e80 capsules)
K1521TB	Buffer Capsules for pH 4.01 @ 25°C (1 bottle= e80 capsules)
K1521TC	Buffer Capsules for pH 6.87 @ 25°C (1 bottle= e80 capsules)
K1521TD	Buffer Capsules for pH 10.01 @ 25°C (1 bottle= e80 capsules)
K1521TE	Buffer Capsules for pH 12.45 @ 25°C (1 bottle= e80 capsules)
K1521TF	Buffer Capsules Combo Package for pH 4.01/6.87/10.01@ 25°C (1 bottle= e80 capsules for each)

■ Addendum 1: Typical Installations




Figure 3a. Adapter to fit sensors with a PG13.5 process connection in FF40/FS40 and FD40 fittings.
Material: Polypropylene
K1523JA Noryl adapter PG13.5
K1523JC Stainless Steel adapter PG13.5


Figure 3b. Stainless Steel Flow fitting option /FF K1598AC (incl. 3.1 B certificate) with Adapter K1523JB (Noryl) or K1523JD (SS) to fit sensors with PG13.5 process connection

■ Addendum 2: Available model codes

Table 3: SC25V Available models

Available Models
SC25V-AGP25-120
SC25V-ALP25-120
SC25V-AGP25-225
SC25V-ALP25-225
SC25V-BGP25-120
SC25V-BLP25-120
SC25V-BGP25-225
SC25V-BLP25-225

■ Addendum 3: Control Drawings



Remarks:


1. No revision to this drawing without prior approval of FM.
2. Installation must be in accordance with the National Electrical Code (ANSI/NFPA 70), ANSI/ISA-RP12.06.01, and relevant local codes.
3. The sensor shall be installed to a certified intrinsically safe HOST with the following maximum values:
 $U_o = 18\text{ V}$, $I_o = 170\text{ mA}$, $P_o = 400\text{ mW}$.
4. The sensor does not provide isolation from earth. Installers shall take necessary measures to prevent the possibility of sparking resulting from differing earth potentials between the sensors and interconnecting equipment. This can be realized for example by selecting interconnecting equipment which provides input-to-output and input-to-earth isolation up to 500 V rms.
5. **Sensor Model code:**

Model	Suffix Codes	Option Codes
SC25V	- abcde - fgh	/ j

- abcde	Type + Region:	AGP25 Glass body/Straight Thread/Bulb shaped G-glass/without ID-chip/IS for ATEX/IECEX, FM-US, FM-CAN ALP25 Glass body/Straight Thread/Bulb shaped L-glass/without ID-chip/IS or ATEX/IECEX, FM-US, FM-CAN
- fgh	Sensor length:	Up to three alphanumeric characters (0 to 9)
/ j	Option code:	Up to ten alphanumeric characters (A to Z, 0 to 9 or hyphen)

6. **WARNING** - POTENTIAL ELECTROSTATIC CHARGING HAZARD – (See Instructions)

pH sensors containing accessible plastic parts and/or external conductive parts, must be installed and used in such a way, that dangers of ignition due to hazardous electrostatic charges cannot occur, especially in the case that the process medium is non-conductive



Remarks:

1. No revision to this drawing without prior approval of FM.
2. Installation must be in accordance with the National Electrical Code (ANSI/NFPA 70), ANSI/ISA-RP12.06.01, and relevant local codes.
3. The sensor shall be installed to a certified intrinsically safe Smart Adapter, model SA11-P1 with the following maximum values: $U_o = 6.6 \text{ V}$, $I_o = 100 \text{ mA}$, $P_o = 165 \text{ mW}$.
4. The installers shall take necessary measures to prevent the possibility of sparking resulting from differing earth potentials between the sensors and interconnecting equipment. The sensor itself does not provide 500 V rms isolation from earth, the interconnecting equipment Model SA11-P1 Smart Adapter however provide this required isolation.

5. Sensor Model code:

Model	Suffix Codes	Option Codes
SC25V	- abcde - fgh	/ j

- abcde Type + Region: BGP25 Glass body/Straight Thread/Bulb shaped G-glass/with ID-chip/IS for

ATEX/IECEX, FM-US, FM-CAN

BLP25 Glass body/Straight Thread/Bulb shaped L-glass/with ID-chip/IS for

ATEX/IECEX, FM-US, FM-CAN

- fgh Sensor length: Up to three alphanumeric characters (0 to 9)

/ j Option code: Up to ten alphanumeric characters (A to Z, 0 to 9 or hyphen)

6. **WARNING** - POTENTIAL ELECTROSTATIC CHARGING HAZARD – (See Instructions)

pH sensors containing accessible plastic parts and/or external conductive parts, must be installed and used in such a way,

that dangers of ignition due to hazardous electrostatic charges cannot occur, especially in the case that the process medium

is non-conductive.

FM-Canada

Applying standards	: CAN/CSA-C22.2 No. 60079-0 CAN/CSA-C22.2 No. 60079-11
Certificate no.*	: FM20CA0062X IS CL I, DIV 1, GP ABCD, T3...T6 CL I, ZN 0, Ex ia IIC, T3...T6 Ga Control Drawing: D&E 2020-023-A51
Electrical data	: (See Note)
Specific conditions of use	: See Control Drawing D&E 2020-023-A51.


Note: Intrinsically safe, entity, for Class I, Division 1, Groups A, B, C and D; Class I, Zone 0, Ex ia IIC, Ga (entity) for hazardous (classified) locations when installed per control drawing D&E 2020-023-A51.
Sensor input parameters: $U_i = 18 \text{ V}$; $I_i = 170 \text{ mA}$; $P_i = 0.4 \text{ W}$; $L_i = 0 \text{ mH}$ $C_i = 0.4 \text{ nF}$
(Suffix SC25V-B...with ID chip): $C_i = 0 \text{ nF}$ (Suffix SC25V-A...without ID-chip)
Ambient temperature: $-40 \text{ }^\circ\text{C}$ to $+40 \text{ }^\circ\text{C}$ for temperature class T6, $-40 \text{ }^\circ\text{C}$ to $+55 \text{ }^\circ\text{C}$ for temperature class T4 and T5, $-40 \text{ }^\circ\text{C}$ to $+105 \text{ }^\circ\text{C}$ for temperature class T3.



When the sensor has been connected to non intrinsically safe equipment which exceeds the restrictions regarding the sensor input circuits, the sensor is not suitable anymore for intrinsically safe use.

* Certification is subject to change, due to new regulations or changes in the product itself. When a certificate is updated, a new revision under the same certificate number is created with a new date.

- **FM-Canada: FM20CA0062X** (effective from 03-2021)



Remarks:

1. No revision to this drawing without prior approval of FM.
2. Installation must be in accordance with the Canadian Electrical Code (CEC) CSA22.1, and relevant local codes.
3. The sensor shall be installed to a certified intrinsically safe HOST with the following maximum values:
 $U_o = 18\text{ V}$, $I_o = 170\text{ mA}$, $P_o = 400\text{ mW}$.
4. The sensor does not provide isolation from earth. Installers shall take necessary measures to prevent the possibility of sparking resulting from differing earth potentials between the sensors and interconnecting equipment. This can be realized for example by selecting interconnecting equipment which provides input-to-output and input-to-earth isolation up to 500 V rms.

5. Sensor Model code:

Model	Suffix Codes	Option Codes
SC25V	- abcde - fgh	/ j


- abcde	Type + Region:	AGP25 Glass body/Straight Thread/Bulb shaped G-glass/ without ID-chip/IS for ATEX/IECEX, FM-US, FM-CAN ALP25 Glass body/Straight Thread/Bulb shaped L-glass/without ID-chip/IS or ATEX/IECEX, FM-US, FM-CAN
- fgh	Sensor length:	Up to three alphanumeric characters (0 to 9)
/ j	Option code:	Up to ten alphanumeric characters (A to Z, 0 to 9 or hyphen)

6. WARNING - POTENTIAL ELECTROSTATIC CHARGING HAZARD – (See Instructions)

pH sensors containing accessible plastic parts and/or external conductive parts, must be installed and used in such a way, that dangers of ignition due to hazardous electrostatic charges cannot occur, especially in the case that the process medium is non-conductive.

AVERTISSEMENT - DANGER POTENTIEL DE CHARGES ÉLECTROSTATIQUES – (Voir Les Instructions)

Les sondes de pH contenant des pièces en plastique accessibles et / ou des pièces conductrices externes doivent être installées et utilisées de manière à éviter tout risque d'inflammation dû à des charges électrostatiques dangereuses, en particulier dans le cas où le fluide de procédé n'est pas conducteur.



Remarks:

1. No revision to this drawing without prior approval of FM.
2. Installation must be in accordance with the Canadian Electrical Code (CEC) CSA22.1, and relevant local codes.
3. The sensor shall be installed to a certified intrinsically safe Smart Adapter, model SA11-P1 with the following maximum values:
 $U_o = 6.6 \text{ V}$, $I_o = 100 \text{ mA}$, $P_o = 165 \text{ mW}$.
4. The installers shall take necessary measures to prevent the possibility of sparking resulting from differing earth potentials
 between the sensors and interconnecting equipment. The sensor itself does not provide 500 V rms isolation from earth,
 the interconnecting equipment Model SA11-P1 Smart Adapter however provide this required isolation.

5. Sensor Model code:

Model	Suffix Codes	Option Codes
SC25V	- abcde - fgh	/ j

- abcde	Type + Region:	BGP25 Glass body/Straight Thread/Bulb shape G-glass/with ID-chip/IS for ATEX/IECEX, FM-US, FM-CAN BLP25 Glass body/Straight Thread/Bulb shaped L-glass/with ID-chip/IS for ATEX/IECEX, FM-US, FM-CAN
- fgh	Sensor length:	Up to three alphanumeric characters (0 to 9)
/ j	Option code:	Up to ten alphanumeric characters (A to Z, 0 to 9 or hyphen)

6. **WARNING** - POTENTIAL ELECTROSTATIC CHARGING HAZARD – (See Instructions)

pH sensors containing accessible plastic parts and/or external conductive parts, must be installed and used in such a way,
 that dangers of ignition due to hazardous electrostatic charges cannot occur, especially in the case that the process medium
 is non-conductive.

DANGER - POTENTIEL DE CHARGES ÉLECTROSTATIQUES – (Voir Les Instructions)

Les sondes de pH contenant des pièces en plastique accessibles et / ou des pièces conductrices externes doivent être installées et utilisées de manière à éviter tout risque d'inflammation dû à des charges électrostatiques dangereuses, en particulier dans le cas où le fluide de procédé n'est pas conducteur.

<p>YOKOGAWA ELECTRIC CORPORATION World Headquarters 9-32, Nakacho 2-chome, Musashino-shi Tokyo 180-8750 Japan www.yokogawa.com</p> <p>YOKOGAWA CORPORATION OF AMERICA 2 Dart Road Newnan GA 30265 USA www.yokogawa.com/us</p> <p>YOKOGAWA EUROPE BV Euroweg 2 3825 HD AMERSFOORT The Netherlands www.yokogawa.com/eu</p>	<p>YOKOGAWA ELECTRIC ASIA Pte. LTD. 5 Bedok South Road Singapore 469270 Singapore www.yokogawa.com/sg</p> <p>YOKOGAWA CHINA CO. LTD. Room 1801, Tower B, THE PLACE No.100 Zunyi Road Changning District, Shanghai, China www.yokogawa.com/cn</p> <p>YOKOGAWA MIDDLE EAST B.S.C.(c) P.O. Box 10070, Manama Building 577, Road 2516, Busaiteen 225 Muharraq, Bahrain www.yokogawa.com/bh</p>	<p>Yokogawa has an extensive sales and distribution network. Please refer to the European website (www.yokogawa.com/eu) to contact your nearest representative.</p> <p>YOKOGAWA ◆</p>
---	--	---

Printed in The Netherlands 03-2506