# General Specifications

## GS 01C31B03-01EN

EJA120E Differential Pressure Transmitter

DP harp **EJA**™

[Style: S2]

The high performance draft range differential pressure transmitter EJA120E features single crystal silicon resonant sensor and is suitable to measure liquid, gas, or steam flow as well as liquid level, density and pressure. EJA120E outputs a 4 to 20 mA DC signal corresponding to the measured differential pressure.

Other key features include quick response, remote set-up using communications and self-diagnostics. FOUNDATION Fieldbus, PROFIBUS PA and 1 to 5 V DC with HART (Low Power) protocol types are also available. EJA-E series models in their standard configuration, with the exception of the Fieldbus, PROFIBUS and Low Power types, are certified as complying with SIL 2 for safety requirement.

## STANDARD SPECIFICATIONS

Refer to GS 01C31T02-01EN for Fieldbus communication type and GS 01C31T04-01EN for PROFIBUS PA communication type for the items marked with "◊."

## SPAN AND RANGE LIMITS

Measurement Span/Range		kPa	inH2O (/D1)	mbar (/D3)	mmH2O (/D4)
_	Span	0.1 to 1	0.4 to 4	1 to 10	10 to 100
	Range	-1 to 1	-4 to 4	-10 to 10	-100 to 100

## PERFORMANCE SPECIFICATIONS

Zero-based calibrated span, linear output, wetted parts material code S and silicone oil, unless otherwise mentioned.

For Fieldbus and PROFIBUS PA communication types, use calibrated range instead of span in the following specifications.

#### **Specification Conformance**

EJA-E series ensures specification conformance to at least  $\pm 3\sigma$ .

## **Reference Accuracy of Calibrated Span**

(includes terminal-based linearity, hysteresis, and repeatability)

Measurem	ent span	E
Reference	X ≤ span	±0.2% of Span
accuracy	X > span	±(0.15+0.02 URL/span)% of Span
Х		0.4 kPa (1.6 inH2O)
URL (upper range limit)		1 kPa (4 inH2O)

## [When /HAC is specified]

Measurement span		E
Reference	X ≤ span	±0.09% of Span
accuracy	X > span	±(0.015+0.03 URL/span)% of Span
Х		0.4 kPa (1.6 inH2O)
URL (upper range limit)		1 kPa (4 inH2O)



#### Square Root Output Accuracy

The square root accuracy is a percent of flow span.

Output	Accuracy
50% or Greater	Same as reference accuracy
50% to Dropout point	Reference accuracy × 50 Square root output (%)

## Ambient Temperature Effects per 28°C (50°F) Change

±(0.15% Span + 0.2% URL)

# Stability (All normal operating condition, including overpressure effects)

±0.3% of URL per one year

Power Supply Effects(Output signal code D and J) ±0.005 % per Volt (from 21.6 to 32 V DC, 350Ω)

## Vibration Effects

<u>Amplifier housing code 1 and 3:</u> Less than 0.1% of URL when tested per the requirements of IEC60770-1 field or pipeline with high vibration level (10-60 Hz, 0.21 mm displacement/60-2000 Hz 3 g) <u>Amplifier housing code 2:</u> Less than  $\pm 0.1\%$  of URL when tested per the requirements of IEC60770-1 field with general application or pipeline with low vibration level (10-60

Hz 0.15mm displacement /60-500 Hz 2g)

#### **Mounting Position Effects**

Rotation in diaphragm plane has no effect. Tilting up to 90 degree will cause zero shift up to 0.4 kPa (1.6 inH<sub>2</sub>O) which can be corrected by the zero adjustment.

# Response Time (Differential pressure) "◊" 150 ms

When amplifier damping is set to zero and including dead time of 45 ms (nominal)



#### FUNCTIONAL SPECIFICATIONS

#### Output "◊"

#### For 4 to 20 mA HART / BRAIN (Output signal code D and J)

Two wire 4 to 20 mA DC output with digital communications, linear or square root programmable. BRAIN or HART FSK protocol are superimposed on the 4 to 20 mA signal.

Output range: 3.6 mA to 21.6 mA

Output limits conforming to NAMUR NE43 can be pre-set by option code C2 or C3.

## For 1 to 5 V HART (Output signal code Q)

Three or four wire low power 1 to 5 V DC output with HART, linear or square root programmable. HART protocol are superimposed on the 1 to 5 V DC signal. Output range: 0.9 V to 5.4 V DC

#### Failure Alarm

## For 4 to 20 mA HART / BRAIN

(Output signal code D and J)

Analog output status at CPU failure and hardware error;

Up-scale: 110%, 21.6 mA DC or more (standard) Down-scale: -5%, 3.2 mA DC or less

For 1 to 5 V HART (Output signal code Q) Analog output status at CPU failure and hardware error;

Up-scale: 110%, 5.4 V DC or more (standard) Down-scale: -5%, 0.8 V DC or less

#### Damping Time Constant (1st order)

Amplifier damping time constant is adjustable from 0.00 to 100.00 s by software and added to response time.

Note: For BRAIN protocol type, when amplifier software damping is set to less than 0.5 s, communication may occasionally be unavailble during the operation, especially while output changes dynamically. The default setting of damping ensures stable communication.

### Update Period "0"

Differential pressure: 45 ms

#### Zero Adjustment Limits

Zero can be fully elevated or suppressed, within the lower and upper range limits of the capsule.

#### **External Zero Adjustment**

External zero is continuously adjustable with 0.01% incremental resolution of span. Re-range can be done locally using the digital indicator with rangesetting switch.

## Integral Indicator (LCD display, optional) "◊" 5-digit numerical display, 6-digit unit display and bar

graph. The indicator is configurable to display one or up to four of the following variables periodically.; Measured differential pressure, differential pressure in %, scaled differential pressure. See also "Factory Setting."

## Local Parameter Setting

(Output signal code D, J and Q)

Parameter configuration by the external zero adjustment screw and push button (Integral indicator code E) offers easy and quick setup for parameters of Loop test, Tag number, Unit, LRV, URV, Damping, Output mode (linear/square root), Display out 1, and Re-range by applying actual pressure (LRV/URV) and Device Information.

#### **Self Diagnostics**

CPU failure, hardware failure, configuration error, and overrange error for differential pressure, and capsule temperature. User-configurable process high/low alarm for differential pressure is also available.

## Signal Characterizer

**(Output signal code D, J and Q)** User-configurable 10-segment signal characterizer for 4 to 20 mA output.

## SIL Certification

EJA-E series transmitters except Fieldbus, PROFIBUS PA and 1-5V DC with HART (Low Power) communication types are certified in compliance with the following standards;

IEC 61508: 2010; Functional Safety of Electrical/electronic/programmable electronic related systems; SIL 2 capability for single

transmitter use, SIL 3 capability for dual transmitter use. Reliability Data different depending on hardware and software revision.

For details, refer to Functional Safety Data Sheet. (Document number: TI 01C25A05-01EN or TI 01C25A05-21EN for option code SLT ) The document can be downloaded from the website

of Yokogawa. (Website address: https://www.yokogawa.com/ solutions/products-platforms/field-instruments/)

## NORMAL OPERATING CONDITION (Optional features or approval codes may affect limits.)

Ambient Temperature Limits -25 to 80°C (-13 to 176°F)


Process Temperature Limits -25 to 80°C (-13 to 176°F)


Ambient Humidity Limits 0 to 100% RH

Working Pressure Limits (Silicone oil) -50 to 50 kPa (-7.25 to 7.25 psi)

#### Supply & Load Requirements (Output signal code D and J. Optional features or approval codes may affect electrical requirements.)

With 24 V DC supply, up to a  $550\Omega$  load can be used. See graph below.





## Supply Voltage "◊"

#### For 4 to 20 mA HART / BRAIN (Output signal code D and J)

## 10.5 to 42 V DC for general use and flameproof type.

10.5 to 32 V DC for lightning protector

(option code /A.) 10.5 to 30 V DC for intrinsically safe, type n, or nonincendive

Minimum voltage limited at 16.6 V DC for digital communications, BRAIN and HART

#### For 1 to 5 V HART (Output signal code Q) Power supply :

9 to 28 V DC for general use and flame proof type. Power Consumption :

0.96 mA to 3 mA, 27 mW

## Load for 4 to 20 mA HART / BRAIN

(Output signal code D and J)

0 to  $1290\Omega$  for operation 250 to  $600\Omega$  for digital communication

Output Load for 1 to 5 V HART

#### (Output signal code Q)

1  $M\Omega$  or greater (meter input impedance) Note that with three-wire connection, the cable length may affect the measurement accuracy of the output signal.

#### Communication Requirements "0"

(Approval codes may affect electrical requirements.) **BRAIN** 

#### **Communication distance**

Up to 2 km (1.25 miles) when using CEV polyethylene-insulated PVC-sheathed cables. Communication distance varies depending on type of cable used.

## Load capacitance

0.22 µF or less

Load inductance 3.3 mH or less

# Input impedance of communicating device 10 k $\Omega$ or more at 2.4 kHz.

#### **EMC** Conformity Standards

EN 61326-1 Class A, Table2 EN 61326-2-3 EN 61326-2-5 (for fieldbus)

# European Pressure Equipment Directive 2014/68/EU

Sound Engineering Practice (for all capsules)

#### EU RoHS Directive EN IEC 63000

#### Safety Requirement Standards

EN 61010-1,

C22.2 No.61010

- Installation category: I (Anticipated transient overvoltage 330 V)
- Pollution degree: 2
- Indoor/Outdoor use

## D PHYSICAL SPECIFICATIONS

#### Wetted Parts Materials

Diaphragm, cover flange, process connector, capsule gasket, and vent/drain plug Refer to "MODEL AND SUFFIX CODES."

Process connector gasket PTFE Teflon

Fluorinated rubber for option code N2 and N3

## Non-wetted Parts Materials

Bolting B7 carbon steel, 316L SST or 660 SST

## Housing

- Low copper cast aluminum alloy
- Low copper cast aluminum alloy with corrosion resistance properties (copper content ≤ 0.03%, iron content ≤ 0.15%) (optional)
- ASTM CF-8M Stainless steel (optional)

## Coating of housing

[for aluminum housing] Polyester resin powder coating Mint-green paint (Munsell 5.6BG 3.3/2.9 or its equivalent) [for option code /P□ or /X2]

Epoxy and polyurethane resin solvent coating

#### Degrees of protection IP66/IP67, Type 4X

**Cover O-rings** Buna-N, fluoro-rubber (optional)

Name plate and tag 316 SST Fill fluid Silicone oil

## Weight

[Installation code 7, 8 and 9] 3.7 kg (8.2 lb) without integral indicator, mounting bracket, and process connector. Add 1.5 kg (3.3lb) for Amplifier housing code 2.

#### Connections

Refer to "MODEL AND SUFFIX CODES." Process connection of cover flange: IEC61518

#### < Related Instruments>

Power Distributor: Refer to GS 01B04T01-02E or GS 01B04T02-02E BRAIN TERMINAL: Refer to GS 01C00A11-00E

#### < Reference >

- *DPharp***EJA**; Registered trademark of Yokogawa Electric Corporation.
- FieldMate; Registered trademark of Yokogawa Electric Corporation.
- Teflon; Trademark of E.I. DuPont de Nemours & Co.
- Hastelloy; Trademark of Haynes International Inc.
- HART<sup>®</sup>: Registered trademark of FieldComm Group.
- FOUNDATION Fieldbus; Trademark of FieldComm Group.
- PROFIBUS; Registered trademark of Profibus Nutzerorganisation e.v., Karlsruhe, Germany.

Other company names and product names used in this material are registered trademarks or trademarks of their respective owners.

## ■ MODEL AND SUFFIX CODES

Model	Suffix Codes	Description
EJA120E		. Differential pressure transmitter
Output signal	-D	<ul> <li>4 to 20 mA DC with digital communication (HART 5/HART 7 protocol)<sup>*1</sup></li> <li>Digital communication (FOUNDATION Fieldbus protocol, refer to GS 01C31T02-01EN)</li> </ul>
	-Q	
Measurement span (capsule)	E	0.1 to 1 kPa (0.4 to 4 inH <sub>2</sub> O)
Wetted parts material *2		. Refer to "Wetted Parts Material" Table.
Process connect	ions 0 1 2 3 ↓ 5	<ul> <li>with Rc1/4 female process connector</li> <li>with Rc1/2 female process connector</li> </ul>
Bolts and nuts m	aterial J G C	316L SST
Installation  -789U		<ul> <li>Horizontal piping and right side high pressure</li> <li>Horizontal piping and left side high pressure</li> </ul>
Amplifier housing	1 3 2	Cast aluminum alloy with corrosion resistance properties*3
Electrical connec	tion	<ul> <li>1/2 NPT female, two electrical connections without blind plugs</li> <li>M20 female, two electrical connections without blind plugs</li> <li>G1/2 female, two electrical connections and a blind plug<sup>*5</sup></li> <li>1/2 NPT female, two electrical connections and a blind plug<sup>*5</sup></li> <li>M20 female, two electrical connections and a blind plug<sup>*5</sup></li> <li>G1/2 female, two electrical connections and a blind plug<sup>*5</sup></li> <li>G1/2 female, two electrical connections and a blind plug<sup>*5</sup></li> <li>G1/2 female, two electrical connections and a SUS316 blind plug</li> <li>1/2 NPT female, two electrical connections and a SUS316 blind plug</li> <li>M20 female, two electrical connections and a SUS316 blind plug</li> </ul>
Integral indicator	D E ► N	. Digital indicator with the range setting switch (push button)*7
Mounting bracke	· · · · ·	<ul> <li>304 SST 2-inch pipe mounting, flat type (for horizontal piping)</li> <li>304 SST 2-inch pipe mounting, L type (for vertical piping)</li> <li>316 SST 2-inch pipe mounting, flat type (for horizontal piping)</li> <li>316 SST 2-inch pipe mounting, L type (for vertical piping)</li> <li>316 SST 2-inch pipe mounting, position adjustable L type (for vertical piping)*8</li> </ul>
Optional Codes		□/ Optional specification

The "▶" marks indicate the most typical selection for each specification.

 \*1: HART 5 or HART 7 is selectable. Specify upon ordering.
 \*2: 
 <sup>A</sup> Users must consider the characteristics of selected wetted parts material and the influence of process fluids. The use of inappropriate materials can result in the leakage of corrosive process fluids and cause injury to personnel and/or damage to plant facilities. It is also possible that the diaphragm itself can be damaged and that material from the broken diaphragm and the fill fluid can contaminate the user's process fluids. Be very careful with highly corrosive process fluids such as hydrochloric acid, sulfuric acid, hydrogen sulfide, sodium

hypochlorite, and high-temperature steam (150°C [302°F] or above). Contact Yokogawa for detailed information of the wetted parts material. Not applicable for electrical connection code 0, 5, 7, 9 and A.

- Not applicable for electrical connection code 0, 5, 7 and 9.
- \*3: \*4: \*5: \*6: Material of a blind plug; aluminum alloy for code 5 and 9, and SUS304 for code 7.
- Not applicable for output signal code G.
- \*7:
- Not applicable for output signal code F. For position adjustable bracket, refer to SD 01C25B14-01EN. \*8:

#### Table. Wetted Parts Materials

Wetted parts material code	Cover flange and process connector	Capsule	Capsule gasket	Vent/Drain plug
S #	ASTM CF-8M *1*3	Hastelloy C-276 <sup>*2</sup> (Diaphragm) F316L SST, 316L SST (Others)	PTFE Teflon	316 SST

\*1: \*2: Cast version of 316 SST. Equivalent to SCS14A.

Hastelloy C-276 or ASTM N10276.

\*3: Intergranular corrosion test passed according to ASTM A262 Practice E.

The '#'marks indicate the construction materials conform to NACE material recommendations per MR0175/ISO15156. Please refer to the latest standards for details. Selected materials also conform to NACE MR0103.

## ■ OPTIONAL SPECIFICATIONS (For Explosion Protected type) "◊"

For other agency approvals and marine approvals, please refer to GS 01C25A20-01EN.

Please select appropriate equipment in accordance with the laws and regulations of the relevant country/region, when it is used in a location where explosive atmospheres may be present.

Item	Description	Code
Factory Mutual (FM)	FM Explosionproof Approval *1 Applicable Standard: FM3600, FM3615, FM3810, NEMA 250, ANSI/UL 61010-1, ANSI/UL 61010-2-30 Explosionproof for Class I, Division 1, Groups B, C and D, Dust-ignitionproof for Class II/III, Division 1, Groups E, F and G, in Hazardous locations, indoors and outdoors (Enclosure: Type 4X) "FACTORY SEALED, CONDUIT SEAL NOT REQUIRED." Temperature class: T6, Amb. Temp.: -40 to 60°C (-40 to 140°F)	FF1
	<ul> <li>FM Intrinsically safe Approval <sup>*1*3</sup> Applicable Standard: FM 3600, FM 3610, FM 3611, FM 3810, ANSI/ISA-60079-0, ANSI/ISA-60079-11, ANSI/ISA-61010-1, NEMA 250 Intrinsically Safe for Class I, Division 1, Groups A, B, C &amp; D, Class II, Division 1, Groups E, F &amp; G and Class III, Division 1, Class I, Zone 0, in Hazardous Locations, AEx ia IIC Nonincendive for Class I, Division 2, Groups A, B, C &amp; D, Class II, Division. 2, Groups F &amp; G, Class I, Zone 2, Group IIC, in Hazardous Locations Enclosure: Type 4X, Temp. Class: T4, Amb. Temp.: -60 to 60°C (-75 to 140°F) Intrinsically Safe Apparatus Parameters [Groups A, B, C, D, E, F and G] Vmax=30 V, Imax=220 mA, Pmax=1 W, Ci=6 nF, Li=0 µH </li> </ul>	FS1
	Combined FF1 and FS1 *1*3	FU1
ATEX	ATEX Flameproof Approval <sup>*1</sup> Applicable Standard: EN IEC 60079-0, EN 60079-1, EN 60079-31 Certificate: KEMA 07ATEX0109 X II 2 G Ex db IIC T6T4 Gb, II 2 D Ex tb IIIC T85°C Db Degree of protection: IP66/IP67 Amb. Temp. (Tamb) for gas-proof : T4; -50 to 75°C (-58 to 167°F), T5; -50 to 80°C (-58 to 176°F), T6; -50 to 75°C (-58 to 167°F) Process Temp. for gas-proof (Tp): T4; -50 to 120°C (-58 to 248°F), T5; -50 to 100°C (-58 to 212°F), T6; -50 to 85°C (-58 to 185°F) Max. surface Temp. for dust-proof: T85°C (Tamb: -30 to 75°C, Tp: -30 to 85°C) <sup>*2</sup>	KF22
	ATEX Intrinsically safe Approval *1*3 Applicable Standard: EN IEC 60079-0, EN 60079-11 Certificate: DEKRA 11ATEX0228 X II 1 G Ex ia IIC T4 Ga, II 2 D Ex ia IIIC T85°C T100°C T120°C Db Degree of protection: IP66/IP67 Amb. Temp. (Tamb) for EPL Ga: -50 to 60°C (-58 to 140°F) Maximum Process Temp. (Tp) for EPL Ga:120°C Electrical data: Ui=30 V, Ii=200 mA, Pi=0.9 W, Ci=27.6 nF, Li=0 μH Amb. Temp. for EPL Db: -30 to 60°C *2 Max. surface Temp. for EPL Db: T85°C (Tp: 80°C), T100°C (Tp: 100°C), T120°C (Tp: 120°C)	KS21
	Multiple types of protection (KF22, KS21 or Intrinsically safe Ex ic) <sup>*1*3</sup> Applicable Standard: EN IEC 60079-0, EN 60079-11 II 3 G Ex ic IIC T4 Gc, Amb. Temp.: –30 to 60°C (–22 to 140°F) <sup>*2</sup> Ui=30 V, Ci=27.6 nF, Li=0 μH	KU22

## <<Contents>> <<Index>>

Standards Association       Certificate: 2014354       Certificate: 2014354         Applicable Standard: C22.2 No. 25, C22.2 No. 30, CAN/CSA-C22.2 No. 94, CAN/CSA-C22.2 No. 61010-1, CAN/CSA-C22.2 No. 60079-0, CAN/CSA-C22.2 No. 60079-1, CAN/CSA-C22.2 No. 60529       Explosion-proof for Class I, Groups B, C and D. Dustignition-proof for Class II/III, Groups E, F and G.       CF1         When installed in Division 2, "SEAL NOT REQUIRED" Enclosure: Type 4X, Temp. Code: 16T4       Ex d IIC 16T4 Enclosure: IP66/IP67       CF1         Max. Process Temp.: T4;120°C(248°F), T5;100°C(212°F), T6; 85°C(185°F)       Amb. Temp.: -50 to 75°C(-58 to 167°F) for T450 to 80°C(-58 to 176°F) for T5, -50 to 75°C(-58 to 167°F) for T6 <sup>-2</sup> Process Sealing Certification       Dual Seal Certified by CSA to the requirement of ANSI/ISA-12.27.01 No additional sealing required       Primary seal failure annunciation: at the zero adjustment screw         CSA Intrinsically safe Approval <sup>11/3</sup> Certificate: 1606623 [For Division System]       Applicable Standard: C22.2 No.0, C22.2 No.94, C22.2 No.157, C22.2 No.61010-1, C22.2 No.61010-2-030       Intrinsically Safe for Class I, Division 1, Groups A, B, C & D, Class II, Division 1, Groups E, F & G, Class III, Division 1, Nonincendive for Class I, Division 2, Groups A, B, C & D, Class II, Division 2, Groups F, F & G, Class III, Division 1, Nonincendive for Class I, Division 2, Groups A, B, C & D, Class II, Division 2, Groups F & G, Class III, Division 1       Enclosure: Type 4X, Temp. Code: T4 Amb. Temp: -50 to 60°C(-58 to 140°F) <sup>-2</sup> Electrical Parameters: [Intrinsically Safe] Ymax=30V, Imax=200mA, Pmax=0.9W, Ci=10nF, Li=0 µH [Nonincendive] Ymax=30V, Ci=10nF, Li=0 µH       CS1         M	ltem	Description	Code
Certificate: 1606623 [For Division System] Applicable Standard: C22.2 No.0, C22.2 No.94, C22.2 No.157, C22.2 No.213, C22.2 No.61010-1, C22.2 No.61010-2-030 Intrinsically Safe for Class I, Division 1, Groups A, B, C & D, Class II, Division 1, Groups E, F & G, Class III, Division 1, Nonincendive for Class I, Division 2, Groups A, B, C & D, Class II, Division 2, Groups F & G, Class III, Division 1 Enclosure: Type 4X, Temp. Code: T4 Amb. Temp.: –50 to 60°C(–58 to 140°F) *2 Electrical Parameters: [Intrinsically Safe] Vmax=30V, Imax=200mA, Pmax=0.9W, Ci=10nF, Li=0 μH [Nonincendive] Vmax=30V, Ci=10nF, Li=0 μH [For Zone System] Applicable Standard: CAN/CSA-C22.2 60079-0, CAN/CSA-E60079-11, CAN/CSA-E60079-15, CAN/CSA-C22.2 No.60529 Ex ia IIC T4, Ex nL IIC T4 Enclosure: IP66/IP67 Amb. Temp.: –50 to 60°C(–58 to 140°F)*2, Max. Process Temp.: 120°C(248°F) Electrical Parameters: [Ex ia] Ui=30V, Ii=200mA, Pi=0.9W, Ci=10nF, Li=0 μH [Ex nL] Ui=30V, Ci=10nF, Li=0 μH Process Sealing Certification Dual Seal Certified by CSA to the requirement of ANSI/ISA-12.27.01 No additional sealing required	Canadian Standards Association (CSA)	Certificate: 2014354 Applicable Standard: C22.2 No. 25, C22.2 No. 30, CAN/CSA-C22.2 No. 94, CAN/CSA-C22.2 No. 61010-1, CAN/CSA-C22.2 No. 61010-2-030, CAN/CSA-C22.2 No. 60079-0, CAN/CSA-C22.2 No. 60079-1, CAN/CSA-C22.2 No. 60529 Explosion-proof for Class I, Groups B, C and D. Dustignition-proof for Class II/III, Groups E, F and G. When installed in Division 2, "SEAL NOT REQUIRED" Enclosure: Type 4X, Temp. Code: T6T4 Ex d IIC T6T4 Enclosure: IP66/IP67 Max.Process Temp.: T4;120°C(248°F), T5;100°C(212°F), T6; 85°C(185°F) Amb.Temp.: -50 to 75°C(-58 to 167°F) for T4, -50 to 80°C(-58 to 176°F) for T5, -50 to 75°C(-58 to 167°F) for T6 *2 Process Sealing Certification Dual Seal Certified by CSA to the requirement of ANSI/ISA-12.27.01 No additional sealing required	CF1
		Certificate: 1606623 [For Division System] Applicable Standard: C22.2 No.0, C22.2 No.94, C22.2 No.157, C22.2 No.213, C22.2 No.61010-1, C22.2 No.61010-2-030 Intrinsically Safe for Class I, Division 1, Groups A, B, C & D, Class II, Division 1, Groups E, F & G, Class III, Division 1, Nonincendive for Class I, Division 2, Groups A, B, C & D, Class II, Division 2, Groups F & G, Class III, Division 1 Enclosure: Type 4X, Temp. Code: T4 Amb. Temp.: –50 to 60°C(–58 to 140°F) *2 Electrical Parameters: [Intrinsically Safe] Vmax=30V, Imax=200mA, Pmax=0.9W, Ci=10nF, Li=0 μH [Nonincendive] Vmax=30V, Ci=10nF, Li=0 μH [For Zone System] Applicable Standard: CAN/CSA-C22.2 60079-0, CAN/CSA-E60079-11, CAN/CSA-E60079-15, CAN/CSA-C22.2 No.60529 Ex ia IIC T4, Ex nL IIC T4 Enclosure: IP66/IP67 Amb. Temp.: –50 to 60°C(–58 to 140°F) *2, Max. Process Temp.: 120°C(248°F) Electrical Parameters: [Ex ia] Ui=30V, Ii=200mA, Pi=0.9W, Ci=10nF, Li=0 μH [Ex nL] Ui=30V, Ci=10nF, Li=0 μH	CS1

#### <<Contents>> <<Index>>

ltem	Description	Code
IECEX	IECEx Flameproof Approval *1 Applicable Standard: IEC 60079-0, IEC 60079-1, IEC 60079-31 Certificate: IECEx DEK 14.0046X Enclosure: IP66/IP67 Ex db IIC T6T4 Gb, Ex tb IIIC T85°C Db Amb. Temp. (Tamb) for gas-proof : T4; -50 to 75°C (-58 to 167°F), T5; -50 to 80°C (-58 to 176°F), T6; -50 to 75°C (-58 to 167°F) Process Temp. for gas-proof (Tp): T4; -50 to 120°C (-58 to 248°F), T5; -50 to 100°C (-58 to 212°F), T6; -50 to 85°C (-58 to 185°F) Max. surface Temp. for dust-proof: T85°C (Tamb: -30 to 75°C, Tp: -30 to 85°C) *2	SF22
	IECEx Intrinsically safe and SF22 *1*3 Intrinsically safe Ex ia Certificate: IECEx DEK 11.0081X Applicable Standard: IEC 60079-0, IEC 60079-11 Ex ia IIC T4 Ga Enclosure: IP66/IP67 Amb. Temp.: –50 to 60°C (–58 to 140°F), Max. Process Temp.: 120°C (248°F) Electrical Parameters: Ui=30V, Ii=200mA, Pi=0.9W, Ci=27.6nF, Li=0 μH Intrinsically safe Ex ic Certificate: IECEx DEK 13.0061X Applicable Standard: IEC 60079-0, IEC 60079-11 Ex ic IIC T4 Gc IP code: IP66 Amb. Temp.: –30 to 60°C (–22 to 140°F) * <sup>2</sup> , Max. Process Temp.: 120°C (248°F) Electrical Parameters: Ui=30V,Ci=27.6 nF, Li=0 μH Flameproof Refer to SF22	SU22

Applicable for Electrical connection code 2, 4, 7, 9, C and D. Lower limit of ambient temperature is  $-15^{\circ}$ C ( $5^{\circ}$ F) when /HE is specified. Not applicable for output signal code Q.

\*1: \*2: \*3:

## ■ OPTIONAL SPECIFICATIONS


ltem		Description			Code	
High accurac	<u> </u>	High accuracy				HAC
Painting	Color change	Amplifier cover only*2				P□
		Amplifier cover and terminal cov	ver, Munsell 7	.5 R4/14		PR
	Coating change	Anti-corrosion coating*1				X2
316 SST exte	erior parts	316 SST zero-adjustment screw and setscrews <sup>*3</sup>			HC	
Fluoro-rubbe	r O-ring	All O-rings of amplifier housing. Lower limit of ambient temperature: –15°C (5°F)				HE
Lightning pro		· · ·	e: 10.5 to 32 (1×40 μs), Re	V DC (10.5 to peating 1000	0 30 V DC for intrinsically safe type.)	Α
Oil-prohibited	d use <sup>*4</sup>	Degrease cleansing treatment				K1
		Degrease cleansing treatment			With certificates	K41
Oil-prohibited	d use with	Degrease cleansing and dehyd	ating treatme	ent		K5
dehydrating t		Degrease cleansing and dehyd	-		With certificates	K45
Calibration u		P calibration (psi unit)	ung round		With oor informed	D1
Calibration u		. ,		(Cao Tabla f	or Span and Dange Limite )	
		bar calibration (bar unit)			or Span and Range Limits.)	D3
		M calibration (kgf/cm <sup>2</sup> unit)				D4
Plug option <sup>*1</sup>	8*19	code K1 and K5: 130 mm. Mate			l length when combining with option	U1
		Without vent and drain plugs				UN
Output limits operation* <sup>7</sup>	and failure	Failure alarm down-scale: Outp or less for 4 to 20 mA output typ			d hardware error is −5%, 3.2mA DC ss for 1 to 5 V output type.	C1
		NAMUR NE43 Compliant Output signal limits:			e: Output status at CPU or is −5%, 3.2 mA DC or less.	C2
		3.8 mA to 20.5 mA <sup>*16</sup>			Output status at CPU or is 110%, 21.6 mA or more.	C3
Body option*8 Terminal Side L		Right side high pressure, without drain and vent plugs			N1	
		N1 and Process connection, based on IEC61518 with female thread on both sides of cover flange, with blind kidney flanges on back.			N2	
		N2, and Material certificate for cover flange, diaphragm, capsule body, and blind kidney flange			N3	
Wired tag pla	ite	316 SST tag plate wired onto transmitter (Tag No.: Maximum. 16 characters.)			N4	
Data configu	ration at factory <sup>*9</sup>	Data configuration for HART communication type         Software damping, Descriptor, M		mping, Descriptor, Message	CA	
		Data configuration for BRAIN communication type		Software da	mping	СВ
		Data configuration for HART communication type		Software damping, Descriptor, Message, External zero adjustment prohibition setting		CJ
		Data configuration for BRAIN Software damping, External zero adjustme prohibition setting			СК	
Material certi	ficate <sup>*10</sup>	Cover flange *11				M01
		Cover flange, Process connecto	or *12			M11
		Cover flange, Diaphragm, Caps		)		MA1
		Cover flange, Process connector	,		dv*12*20	MC1
		Cover flange, Bolt and Nut for cover flange, Diaphragm, Capsule body, Vent and Drain plug, Vent screw, Capsule gasket*11*17*19			MG1	
		Cover flange, Process connector, Bolt and nut for cover flange, Bolt for process connector, Diaphragm, Capsule body, Vent and Drain plug, Vent screw, Capsule gasket*12*17*19			MH1	
Calibration certificate		Text, Traceability				L4
		Text, Traceability, Primary stand	ards list			L5
		Text, Traceability, Primary standards list, Calibration equipment list Text, Traceability, Primary standards list, Calibration equipment list, Calibration equipment certificate			L6 L9	
Pressure test Leak test cer		Test Pressure: 50 kPa (7.25 psi	)		Nitrogen Gas <sup>*14</sup> Retention time: one minute	T04
Parameter list <sup>*21</sup>		List of setting and adjustment pa	arameters			YP
		I LISCOL SCHING AND AUDSUNCTIL P	1 411101013			16
Bug screen*2	2	With bug screen to the process		ort of the low	sido covor flanco	BS

- Not applicable with color change option. \*1·
- Not applicable for amplifier housing code 2 and 3.
- \*2: \*3: 316 or 316L SST. The specification is included in amplifier housing code 2.
- \*4: Applicable for Wetted parts material code S.
- \*5: The unit of MWP (Max. working pressure) on the name plate of a housing is the same unit as specified by option codes D1, D3 and D4
- \*6: Applicable for vertical impulse piping type (Installation code 7) and Wetted parts material code S.
- \*7: Applicable for output signal codes D and J. The hardware error indicates faulty amplifier or capsule.
- \*8: Applicable for wetted parts material code S; process connection codes 3, 4, and 5; installation code 9; and mounting bracket code N. Process connection faces on the other side of zero adjustment screw.
- \*9: Also see 'Ordering Information'.
- \*10: Material traceability certification, per EN 10204 3.1B.
- \*11: Applicable for process connections codes 0 and 5.
- \*12: Applicable for process connections codes 1, 2, 3, and 4.
- \*13: The unit on the certificate is always Pa unit regardless of selection of option code D1, D3 or D4.
- \*14: Dry nitrogen gas is used for oil-prohibited use (option codes K1, K5, K41, and K45).
- \*15: Not applicable for output signal code Q.
- \*16: The 1 to 5 V voltage output corresponding to 4 to 20 mA current output is applied to output signal code Q which is noncompliant to NAMUR NE43.
- Not applicable with plug option code UN. Not applicable for installation code -U. \*17:
- \*18:
- \*19: Not applicable with option code N1, N2, and N3.
- \*20: Applicable for option code UN and N1.
- \*21: Applicable for output signal code D and J.
- \*22: Applicable for process connection 0, 1, 2, 3, 4, 5, C, D, Q, R.
- \*23: Not applicable for electrical connection codes 0, 2, and 4.


## DIMENSIONS

Unit: mm (approx.inch)

#### Vertical Impulse Piping Type




## • Horizontal Impulse Piping Type (Installation code 9)



- \*1: When Installation code 2, 3, or 8 is selected, high and low pressure side on the above figure are reversed. (i.e. High pressure side is on the right side.)
- When Option code K1, K5, K41, or K45 is selected, add 15 mm (0.59 inch) to the value in the figure. \*2:
- When Option code K1, K5, K41, or K45 is selected, add 30 mm (1.18 inch) to the value in the figure.
- \*3: \*4: \*5: When electrical connection code 7 or C is selected, a blind plug is protruded up to 8 mm (0.31 inch) from the conduit connection.
- When option code UN is specified, Vent/Drain holes and plugs are not applicable.
- \*6: When option code BS is selected, a bug screen is attached in the process connection port on the cover flange of low pressure side.
  - No process connector for low pressure side is attached in that case.
- \*7: When option code PP is selected, a blind plug is attached to the conduit connection on both sides.


Unit: mm (approx.inch)



## • Universal Flange (Installation code U)

- \*1: When Option code K1, K5, K41, or K45 is selected, add 30 mm (1.18 inch) to the value.
- \*2: When electrical connection code 7 or C is selected, a blind plug is protruded up to 8 mm (0.31 inch) from the conduit connection.
- \*3: When option code PP is selected, a blind plug is attached to the conduit connection on both sides.

## Terminal Configuration



## • Terminal Wiring for 4 to 20 mA output, FOUNDATION Fieldbus and PROFIBUS PA communication types

SUPPLY	+ -	$\begin{bmatrix} 1\\ 2 \end{bmatrix}$ Power supply and output terminals
CHECK	+	$\begin{bmatrix} 3\\ 2 \end{bmatrix}$ External indicator (ammeter) terminals <sup>*1*2</sup>
		Ground terminal

\*1: When using an external indicator or check meter, the internal resistance must be 10  $\Omega$  or less.

\*2: Not available for FOUNDATION Fieldbus and PROFIBUS PA communication types.

## • Terminal Wiring for 1 to 5 V output

SUPPLY	+ -	$\begin{bmatrix} 1\\ 2 \end{bmatrix}$ Power supply terminals
VOUT	+ -	③
		Ground terminal

Three or four wire connection. For four wire connection, both supply and signal lines use SUPPLY - terminal.

F06E.ai

## < Ordering Information > "\0"

Specify the following when ordering

- 1. Model, suffix codes, and option codes
- 2. Calibration range and units
  - Calibration range can be specified with range value specifications up to 5 digits (excluding any decimal point) for low or high range limits within the range of -32000 to 32000. When reverse range is designated, specify Lower Range Value(LRV) as greater than Upper Range Value(URV). When square root output mode is specified, LRV must be "0 (zero)".
  - Specify only one unit from the table, 'Factory setting.'
- Select linear or square root for output mode and display mode.

Note: If not specified, the instrument is shipped set for linear mode.

- Display scale and units (for transmitters equipped with the integral indicator only) Specify either 0 to 100 % or 'Range and Unit' for engineering units scale: Scale range can be specified with range limit specifications up to 5 digits (excluding any decimal point) for low or high range limits within the range of -32000 to 32000. Unit display consists of 6-digit, therefore, if the specified scaling unit excluding '/' is longer than 6-characters , the first 6 characters will be displayed on the unit display.
   HART PROTOCOL
- When output signal code is "J", specify the HART protocol revision "5" or "7".
- TAG NO (if required) Specified characters (up to 16 characters for BRAIN, 22 characters for HART, or 16 characters for /N4 tag) are engraved on the stainless steel tag plate fixed on the housing.
- SOFTWARE TAG (for HART only. if required) Specified characters (up to 32 characters) are set as "Tag" (the first 8 characters) and "Long tag"\*1 (32 characters) in the amplifier memory. Use alphanumeric capital letters. When the "SOFTWARE TAG" is not specified, specified "TAG NO" is set as "Tag" (the first 8 characters) and "Long tag"\*1 (22 characters) in the amplifier memory.
  \*1: applicable only when HART 7 is selected.
- Other factory configurations (if required) Specifying option code /CA, /CB, /CJ, or /CK will allow further configuration at factory. Following are configurable items and setting range.

[/CA, /CJ : For HART communication type]

- 1) Descriptor (up to 16 characters)
- 2) Message (up to 30 characters)
- 3) Software damping in second (0.00 to 100.00)
- [/CB, /CK : For BRAIN communication type]
- 1) Software damping in second (0.00 to 100.00)

# < Factory Setting > "◊"

Tag number	As specified in order
Software damping *1	'2.00 s' or as specified in order
Output mode	'Linear' unless otherwise specified in order
Calibration range lower range value	As specified in order
Calibration range upper range value	As specified in order
Calibration range unit	Selected from mmH <sub>2</sub> O, mmH <sub>2</sub> O(68°F), mmAq <sup>*2</sup> , mmWG <sup>*2</sup> , mmHg, Pa, hPa <sup>*2</sup> , kPa, MPa, mbar, bar, gf/cm <sup>2</sup> , kgf/cm <sup>2</sup> , inH <sub>2</sub> O, inH <sub>2</sub> O(68°F), inHg, ftH <sub>2</sub> O, ftH <sub>2</sub> O(68°F) or psi. (Only one unit can be specified.)
Display setting	Designated differential pressure value specified in order. (% or user scaled value.) Display mode 'Linear' or 'Square root' is also as specified in order.

- \*1: To specify these items at factory, option code /CA, /CB, /CJ, or /CK is required.
- \*2: Not available for HART protocol type.

#### < Material Cross Reference >

ASTM	JIS
316	SUS316
F316	SUSF316
316L	SUS316L
F316L	SUSF316L
304	SUS304
F304	SUSF304
660	SUH660
B7	SNB7
CF-8M	SCS14A

## <Information on EU WEEE Directive>

EU WEEE (Waste Electrical and Electronic Equipment) Directive is only valid in the EU.

This instrument is intended to be sold and used only as a part of equipment which is excluded from WEEE Directive, such as large-scale stationary industrial tools, a large-scale fixed installation and so on, and, therefore, subjected to the exclusion from the scope of the WEEE Directive. The instrument should be disposed of in accordance with local and national legislation/regulations.