

Contents

Documentation

GS No.	Model	Title	Issued	Edition
GS48C00Z02-00E		ProSafe-SLS Overview	March, 2019	2 nd

Hardware

GS No.	Model	Title	Issued	Edition
GS48C02Z02-00E	PS-502-02	Power Supply Module (24/20Vdc)	January, 2017	1 st
GS48C02A02-00E	PS-502-A2	Power Supply Module (24/24Vdc)	January, 2017	1 st
GS48C03Z00-00E	PD-503-00	Power Distribution board (XD-board)	January, 2017	1 st
GS48C08Z00-00E	SR-508-00	Safety Relay Module	January, 2017	6 th
GS48C09Z01-00E	FD-509-01	Decoupling Module	January, 2017	1 st
GS48C11Z06-00E	DI-511-06	Digital Input Module (Fail-Safe)	January, 2017	1 st
GS48C17B02-00E	AI-517-02	Analogue Input Module (open < 2.8 mA)	January, 2017	1 st
GS48C17Z02-00E	AI-517-B2	Analogue Input Module (open < 3.8 mA)	January, 2017	1 st
GS48C20Z01-00E	RE-520-01	Relay Module (24 Vdc, 0.5 A)	January, 2017	1 st
GS48C23Z03-00E	DO-523-03	Solid State Output Module	January, 2017	1 st
GS48C23A03-00E	DO-523-A3	Solid State Inverted Output Module	January, 2017	1 st
GS48C24Z03-00E	DO-524-03	Relay Output Module (pulse input, 0.5A)	January, 2017	1 st
GS48C26Z03-00E	FO-526-03	Fail-Safe Output Module (24 Vdc, 20 W)	January, 2017	1 st
GS48C29Z03-00E	FO-529-03	Fail-Safe Output Module (24 Vdc, 5 W)	January, 2017	1 st
GS48C30Z03-00E	CL-530-03	Clock Module	January, 2017	1 st
GS48C30A03-00E	CL-530-A3	Clock Module (redundant use)	January, 2017	1 st
GS48C33Z04-00E	AF-533-04	Fuse Module (2 A fast)	January, 2017	1 st
GS48C33A04-00E	AF-533-A4	Fuse Module (400 mA fast)	January, 2017	1 st
GS48C33B04-00E	AF-533-B4	Fuse Module (50 mA medium slow)	January, 2017	1 st
GS48C34C01-00E	AC-534-C1	Line Monitoring Module (24 Vdc outputs, 0.2 - 20 W)	January, 2017	1 st
GS48C35Z01-00E	AC-535-01	Line Monitoring Module (normally de-energized inputs)	January, 2017	1 st
GS48C39Z01-00E	SA-539-01	System Alarm Module	January, 2017	1 st

Continued

GS No.	Model	Title	Issued	Edition
GS48C40Z02-00E	TI-540-02	Timer Module (0.5 sec - 70 h)	January, 2017	1 st
GS48C44Z01-00E	TI-544-01	Fail-Safe Timer Module	January, 2017	1 st
GS48C46Z01-00E	DR-546-01	Multi Purpose Module	January, 2017	5 th
GS48C47Z01-00E	IO-547-01	Lamp Driver Output Module	January, 2017	1 st
GS48C50Z03-00E	FM-550-03	Logic module	January, 2017	1 st
GS48C51Z04-00E	FM-551-04	Logic module	January, 2017	1 st
GS48C52Z04-00E	FM-552-04	Logic module	January, 2017	1 st
GS48C53Z03-00E	FM-553-03	Logic module	January, 2017	1 st
GS48C56Z01-00E	FM-556-01	Logic module	January, 2017	1 st
GS48C57Z01-00E	FM-557-01	Logic module	January, 2017	1 st
GS48C62C03-00E	MC-562-C3	Analogue Data Collector (0 - 12 V)	January, 2017	1 st
GS48C62D03-00E	MC-562-D3	Analogue Data Collector (0 - 1.2 V)	January, 2017	1 st
GS48C69Z02-00E	MC-569-02	Power Supply Module (24/8 Vdc)	January, 2017	1 st
GS48C73A02-00E	MC-573-A2	Digital Data Storage Module	January, 2017	1 st
GS48C76A02-00E	MC-576-A2	Output Driver Module with Fail-Safe enable input	January, 2017	1 st
GS48C81Z02-00E	MC-581-02	DC Input Data Collector Module	January, 2017	1 st
GS48D17Z00-00E	AI-917-00	Analogue Input Module (2x 0 - 20mA, 2x 0 - 10V)	January, 2017	8 th
GS48D17A00-00E	AI-917-A0	Analogue Input Module (4x 0 - 20mA)	January, 2017	7 th
GS48D17B00-00E	AI-917-B0	Analogue Input Module (4x 0 - 10V)	January, 2017	7 th
GS48D17C00-00E	AI-917-C0	Analogue Input Module (2x 0 - 1V, 2x 0 - 10V)	January, 2017	5 th
GS48D17D00-00E	AI-917-D0	Analogue Input Module (1x 0 - 20mA, 1x 0 - 1V, 2x 0 - 10V)	January, 2017	5 th
GS48D17E00-00E	AI-917-E0	Analogue Input Module (4x 0 - 1V)	January, 2017	5 th
GS48D20Z01-00E	CO-920-01	ProSafe-COM Controller	January, 2017	2 nd
GS48D53C00-00E	CD-953-C0	ProSafe-SLS Event Display application	September, 2018	1 st