General Specifications


Model FH0V Output Isolator (Voltage I/O Type) **NTXUL**

GS 77J08H10-01E

■ General

The FH0V is a compact, front terminal connection type output isolator that receives 1 to 5 V DC signals, and converts them into isolated DC voltage signals.

■ Model and Suffix Codes



- 1: 0 to 10 mV DC
- 2: 0 to 100 mV DC
- 3: 0 to 1 V DC
- 4: 0 to 10 V DC
- 5: 0 to 5 V DC
- 6: 1 to 5 V DC
- 0: (Custom order) Voltage signal

(See "Custom Order Specifications")

Power supply 24 V DC±10%

■ Ordering Information

Specify the following when ordering.

 Model and suffix codes: e.g. FH0V-66*C Note: It is a custom order if necessary to be mounted into F-RACK (X015).

■ Input/Output Specifications


Input signal: 1 to 5 V DC

Input resistance: 1 M Ω (100 k Ω during power off) Maximum allowable input: ± 30 V DC or less

Output signal: DC voltage signal Allowable load resistance:

Output range	Allowable load resistance
0 to 10 mV DC	250 kΩ or more
0 to 100 mV DC	250 kΩ or more
0 to 1 V DC	2 kΩ or more
0 to 10 V DC	10 kΩ or more
0 to 5 V DC	$2 \text{ k}\Omega$ or more
1 to 5 V DC	2 kΩ or more

Zero adjustment: -1 to +1% Span adjustment: 95 to 105%



■ Standard Performance

Accuracy rating:

±0.1% of span

Response speed: 150 ms, 63% response (10 to 90%) Insulation resistance: 100 M Ω or more at 500 V DC between input and output, output and power supply, and input and power supply.

Withstand voltage: 1500 V AC/min. between (input and power supply) and output. 500 V AC/min. between input and power supply.

■ Environmental Conditions

Operating temperature range: 0 to 50°C Operating humidity range: 5 to 90% RH (no condensation)

Power supply voltage: 24 V DC±10% (percentage ripple is 5%p-p or less)

Effect of power supply voltage fluctuations: ±0.1% or less for the fluctuation within the operating range of power supply voltage specification

Effect of ambient temperature change: ±0.2% of span or less for a temperature change of 10°C Current consumption: 24 V DC 50 mA

■ Mounting and Dimensions

Material: ABS resin (Case body)
Mounting method: Rack, Wall or DIN rail mounting
Connection method: M4 screw terminals
External dimensions: 72 × 24 × 127 mm (H x W x D)

Weight: Approx.130 g

■ Standard Accessories

Tag number label: 1 Mounting block: 2

Mounting screw: M4 screw x 2




■ Custom Order Specifications

Output range	0 to 10 V DC
Span	10 mV to 10 V DC
Zero elevation	0% only

Mounting into the F-RACK (X015)

Note that the terminal assignments are different from that of standard. (See the table below)

■ Terminal Assignments




Output (+) 2 Output 3 (-)4 Input (+) 5 Input (-) Supply (+) 6 Supply 7 (-)

F-RACK(X015) mounting type (Custom order)

Signals

Z: Zero-adjustment volume S: Span-adjustment volume

■ Block Diagram



■ External Dimensions

