

This CT protector is used by setting it between CT connecting terminals of plug-in type Transmitter to input current from CT.  
When removing transmitter main body from socket, it protects CT burning by high voltage be induced in secondary side of CT.

CTP-5  
Type ———  
Rated Current ———  
5 : 5A

**ORDERING INFORMATION**  
● Type Code : CTP-5

### SPECIFICATIONS :

Rated current : 5A

Rated over current :

10A for 10 seconds

50A for 3 seconds

(As this protector is diode protective type, rated over current time should be as short as possible)


Temperature range : 0~50°C

Humidity range : 5~90% RH



(No condensation)

Weight : Abt. 10g

### BLOCK DIAGRAM



### EXTERNAL DIMENSION



Unit : mm

Subject to change without notice for grade up quality and performance

---

GS CTP5-01E