

User's Manual

Model ISC40FF, ISC40FS, ISC40FD
Sensor fitting



Contents

1. PREFACE.....	4
1.1 Introduction.....	4
1.2 Unpacking and Checking	4
1.3 Warranty and Service	4
1.4 Serial number	5
2. ISC40FF FLOW FITTING	6
2.1 General Specifications.....	6
2.1.1 Materials	6
2.1.2 Operating range	6
2.1.3 Shipping details (Without options).....	6
2.1.4 Process connections.....	6
2.2 INSTALLATION OF ISC40 SENSOR IN ISC40FF	7
2.3 DIMENSIONS	8
2.4 MODEL CODE ISC40FF FITTING	10
2.5 SPARE PARTS ISC40FF FITTING.....	11
3. ISC40FS FLOW FITTING SUBASSEMBLY	12
3.1 General Specifications.....	12
3.1.1 Materials	12
3.1.2 Operating range	12
3.1.3 Shipping details	12
3.1.4 Process connections.....	12
3.2 INSTALLATION OF ISC40 SENSOR IN ISC40FS	13
3.3 DIMENSIONS	14
3.4 MODEL CODE ISC40FS FLOW FITTING SUBASSEMBLY.....	15
3.5 SPARE PARTS ISC40FS FLOW FITTING SUBASSEMBLY	16
4. ISC40FD IMMERSION FITTING	17
4.1 General Specifications.....	17
4.1.1 Materials	17
4.1.2 Operating range	17
4.1.3 Shipping details	17
4.1.4 Process connections.....	17
4.2 INSTALLATION OF ISC40 SENSOR IN ISC40FD	18
4.3 DIMENSIONS ISC40FD.....	19
4.4 MODEL CODE ISC40FD	21
4.5 SPARE PARTS ISC40FD	22
5. CHEMICAL COMPATIBILITY	23

1. PREFACE

1.1 Introduction

The ISC40 sensor fitting program for inductive conductivity measurement is designed to meet the most common installation requirements in terms of material compatibility, process connections and flow dynamics. The various installation possibilities are described and illustrated in this manual.

The following categories of installation can be recognised:

1. Direct mounting of sensors in tank wall or customer supplied flanges
2. Cost effective installation of sensors using process adapters
3. Maintenance friendly installation of sensors using in-line subassemblies
4. Installation in flow chambers for measurements in sample streams or bypass loops
5. Installation in immersion fittings for measurement in open tanks or channels

Within the wide range of process adapters, subassemblies, flow fittings and immersion fittings it is easy to find the appropriate installation that fits the application (a wide choice of materials), the plant installation practice (a wide choice of process connections) and the maintenance procedures.

1.2 Unpacking and Checking

Upon delivery, unpack the product carefully and inspect it to ensure it was not damaged during shipment. If damage is found, retain the original packing materials and then immediately notify the carrier and the relevant Yokogawa sales office. Make sure the Model Code and Serial Number on the fitting are the same as on the packing list. Also, check any option(s) that were ordered are included and correct.

1.3 Warranty and Service

Yokogawa products and parts are guaranteed free from defects in workmanship and material under normal use and service for a period of (typically) 12 months from the date of shipment from the manufacturer. Individual sales organizations can deviate from the typical warranty period, and the conditions of sale relating to the original purchase order should be consulted. Damage caused by wear and tear, inadequate maintenance, corrosion, or by the effects of chemical processes are excluded from this warranty coverage. In the event of warranty claim, the defective goods should be sent (freight paid) to the Service Department of the relevant sales Organization for repair or replacement (at Yokogawa's discretion).

The following information must be included in the letter accompanying the returned goods:

- Model Code and Serial Number.
- Original Purchase Order and Date.
- Length of time in service and description of the process.
- Description of the fault and circumstances of the failure.
- Process/environmental conditions that may be related to the failure of the fitting (option)
- Statement as to whether warranty or non-warranty service is requested.
- Complete shipping and billing instructions for return of material, plus the name and phone number of a contact person that can be reached for further information.
- Clean Statement

Returned goods that have been in contact with process fluids must be decontaminated and disinfected prior to shipment. Goods should carry a certificate to this effect, for the health and safety of our employees. Material Safety Data sheets must be included for all components of the process to which the fitting (options) have been exposed.

1.4 Serial number

The Serial number is defined by nine (9) alphanumeric characters:

X₁X₂

X₃X₄

X₅X₆ X₇X₈ X₉

Production location

Year/Month code

Tracking number

Example: N3P400123

Table 1: Production Year code

Year	Year code	Year	Year code
2014	P	2026	3
2015	R	2027	4
2016	S	2028	5
2017	T	2029	6
2018	U	2030	7
2019	V	2031	8
2020	W	2032	9
2021	X	2033	A
2022	Y	2034	B
2023	Z	2035	C
2024	1	2036	D
2025	2	2037	E

Table 2: Production Month code

Month	Month code
January	1
February	2
March	3
April	4
May	5
June	6
July	7
August	8
September	9
October	A
November	B
December	C

2. ISC40FF FLOW FITTING

2.1 General Specifications

2.1.1 Materials

Wetted parts fitting	
Model ISC40FF-S	: AISI 316 SS; Viton
Model ISC40FF-P ⁽¹⁾	: Polypropylene; Viton
Model ISC40FF-F ⁽¹⁾	: PVDF (Kynar); Viton
Non-wetted parts fitting	: AISI 304 SS or AISI 316 SS

2.1.2 Operating range

Temperature

Model ISC40FF-S	: Max. 150°C (302°F)
Model ISC40FF-P ⁽¹⁾	: Max. 100°C (212°F)
Model ISC40FF-F ⁽¹⁾	: Max. 130°C (266°F)

Pressure

Model ISC40FF-S	: Max. 10 bar (150 PSI) at operating temperature
Model ISC40FF-P ⁽¹⁾	: Max. 6 bar (90 PSI) at 20°C (68°F) Max. 1 bar (15 PSI) at 100°C (212°F)
Model ISC40FF-F ⁽¹⁾	: Max. 10 bar (150 PSI) at 20°C (68°F) Max. 1 bar (15 PSI) at 130°C (266°F)

2.1.3 Shipping details (Without options)

Package size (LxWxH)	: 250 x 150 x 140 mm (9.84 x 5.90 x 5.51 inch)
Package weight (max)	: 1.5 kg (3.3 lbs)

2.1.4 Process connections

1/2" NPT in flow fitting, connected with optional flange adapters to the actual installation.

Note ⁽¹⁾: If required the ISC40 sensor type -GG and -TG can be supplied with a Viton gasket K1500AM (ordered as spare part). This gasket may be used with the older series of ISC40FF fittings. It should be discarded when the sensor is mounted in combination with the ISC40FF type -PA and -FA.

2.2 INSTALLATION OF ISC40 SENSOR IN ISC40FF

Installation of the flow fittings involves two steps:

- Installation of the sensor

The sensor has to be mounted in the flow fitting. It is important that the position of the sensor in the fitting allows easy flow through the hole of the sensor donut (refer to Section 3 of ISC40 manual). Generally good flow is assured if the flats of the sensor are oriented perpendicular to the outlet piping. It is also important that the sample piping is oriented in such a way that the direction of the flow is upwards to assure complete filling of the flow chamber

- Installation of the fitting on wall, railing or stanchion

For this purpose, the flow fitting has an optional pipe/wall mounting kit /MS or /MP (see Figure 1 and Figure 2 for details). This kit consists of a clamp ring with bolts and nuts which clamps around the flow chamber. Therefore, the flow chamber can be turned in the mounting assembly allowing more flexibility in installation. The mounting plate can be mounted on a wall or panel with 2-4 anchor bolts with a diameter of 10 mm (3/8") max. For those installations where pipe mounting is requested (2" nominal pipe), either horizontal or vertical, a saddle and U-bolt have to be used.




Figure 1: Pipe/wall mounting kit /MS




Figure 2: Pipe/wall mounting kit /MP

2.3 DIMENSIONS

Dimensions in mm (inches)




Figure 3: Flow fitting ISC40FF-P, ISC40FF-F
IM 12D07K04-01EN-P




Figure 4: Flow fitting ISC40FF-S

2.4 MODEL CODE ISC40FF FITTING

Table 3: Model and suffix code table

Model	Suffix Code	Option	Description
ISC40FF			Flow fitting for inductive conductivity
Material	-F		Polyvinylidene fluoride (PVDF)
	-P		Polypropylene (PP)
	-S		Stainless steel AISI 316 (SS)
Process connection	A		½" NPT Screw thread acc to ANSI / ASME
Flange adapters		/FF1	PVDF DN15-PN10 flange adapters
		/FF2	PVDF DN25-PN10 flange adapters
		/FF3	PVDF ½"-150lbs flange adapters
		/FF4	PVDF 1"- 150lbs flange adapters
		/FP1	PP DN15-PN10 flange adapters
		/FP2	PP DN25-PN10 flange adapters
		/FP3	PP ½"- 150lbs flange adapters
		/FP4	PP 1"- 150lbs flange adapters
		/FS1	Stainless steel DN15-PN10 flange adapters
		/FS2	Stainless steel DN25-PN10 flange adapters
		/FS3	Stainless steel ½"-150lbs flange adapters
		/FS4	Stainless steel 1"- 150lbs flange adapters
Mounting set		/MS	Wall/pipe mounting set for SS flow fitting
		/MP	Wall/pipe mounting set for PP/PVDF flow fitting
Material certificate		/M	3.1 acc. EN 10204 - wetted metal parts only

2.5 SPARE PARTS ISC40FF FITTING

Options ISC40FF Flow fitting, flange adapters				
Part no.	Description	Process connection		
K1521AL	/FF1	DN15 PN10		
K1521AP	/FF2	DN25 PN10		
K1521AE	/FF3	ANSI ½" - 150lbs		
K1521AH	/FF4	ANSI 1"-150lbs		
K1521AM	/FP1	DN15 PN10		
K1521AQ	/FP2	DN25 PN10		
K1521AF	/FP3	ANSI ½" - 150lbs		
K1521AJ	/FP4	ANSI 1"- 150lbs		
K1521AK	/FS1	DN15 PN10		
K1521AN	/FS2	DN25 PN10		
K1521AD	/FS3	ANSI ½" - 150lbs		
K1521AG	/FS4	ANSI 1"- 150lbs		
Parts ISC40FF Flow fitting				
Part no.	Description	Dimensions	Material	O-ring(s)
K1541KD	Holder, *-F	2"	PVDF	Viton
K1541KL	Holder, *-P	2"	Polypropylene	Viton
K1541KA	Holder, -S	2"	AISI 316 SS	Viton
K1541ZU	/MP for ISC40FF-P/F			
K1541ZZ	/MS for ISC40FF-S			
K1500DZ	Nut FF/S20-3* + ISC40FF/S		AISI 316 SS	
Parts ISC40FF Flow fitting				
O-rings -SA				
Part no.	Description	Dimensions	Material	Quantity
K1500DB	O-ring set	40.64 x 5.33; 26.57 x 3.53; Ring DN50	EPDM	5 sets
K1500DA	O-ring set	40.64 x 5.33; 26.57 x 3.53; Ring DN50	Viton	5 sets
K1500DC	O-ring set	40.64 x 5.33; 26.57 x 3.53; Ring DN50	Silicon	5 sets
K1500CD	O-ring	40.64 x 5.33	FFKM	1
K1500CH	O-ring	26.57 x 3.53	FFKM	1
K1500DD	O-ring	53.34 x 5.33	FFKM	1
O-rings -PA, -FA				
Part no.	Description	Dimensions	Material	Quantity
K1500DF	O-ring set	40.64 x 5.33; 26.57 x 3.53; 56.52 x 5.33	EPDM	5 sets
K1500DE	O-ring set	40.64 x 5.33; 26.57 x 3.53; 56.52 x 5.33	Viton	5 sets
K1500DG	O-ring set	40.64 x 5.33; 26.57 x 3.53; 56.52 x 5.33	Silicon	5 sets
K1500CD	O-ring	40.64 x 5.33	FFKM	1
K1500CH	O-ring	26.57 x 3.53	FFKM	1
K1541ZM	O-ring	56.52x5.33	Viton	5

Note O-ring 53.34 x 5.33 (K1500DD) is used as a FFKM replacement for the Ring DN50.

3. ISC40FS FLOW FITTING SUBASSEMBLY

3.1 General Specifications

3.1.1 Materials

Wetted parts fitting	
Model ISC40FS-FCSA ⁽²⁾	: PVDF (Kynar); Viton
Model ISC40FS-PCSA ⁽²⁾	: Polypropylene; Viton
Model ISC40FS-SCSA	: AISI 316 SS; Viton
Model ISC40FS-SCWN	: AISI 316 SS; Viton

Non-wetted parts fitting	
Nut	: AISI 304 SS

3.1.2 Operating range

Temperature

Model ISC40FS-FCSA	: Max. 130°C (266°F)
Model ISC40FS-PCSA	: Max. 100°C (212°F)
Model ISC40FS-SCSA	: Max. 150°C (302°F)
Model ISC40FS-SCWN	: Max. 150°C (302°F)

Pressure

Model ISC40FS-FCSA	: Max. 10 bar (150 PSI) at 20°C (68°F) Max. 1 bar (15 PSI) at 130°C (266°F)
Model ISC40FS-PCSA	: Max. 6 bar (90 PSI) at 20°C (68°F) Max. 1 bar (15 PSI) at 100°C (212°F)
Model ISC40FS-SCSA	: Max. 10 bar (150 PSI) at operating temperature
Model ISC40FS-SCWN	: Max. 10 bar (150 PSI) at operating temperature

3.1.3 Shipping details

Package size (LxWxH)	
Model -FCSA and -PCSA	: 215 x 150 x 100 mm (8.46 x 5.90 x 2.17 inch)
Model -SCSA and -SCWN	: 215 x 150 x 55 mm (8.46 x 5.90 x 2.17 inch)
Package weight (max.)	: 0.9 kg (2.0 lbs)

3.1.4 Process connections

2" screw-in coupling or weld-in coupling

Note ⁽²⁾: If required the ISC40 sensor type GG and TG can be supplied with a Viton gasket K1500AM (ordered as spare part). This gasket may be used with the older series of ISC40FS fittings. It should be discarded when the sensor is mounted in combination with the ISC40FS type FCSCA and PCSCA.

3.2 INSTALLATION OF ISC40 SENSOR IN ISC40FS

The key difference between a sensor adapter and a subassembly is, that with subassembly installation the sensor can be removed from the process installation without removing the subassembly first. This allows easier access to the sensor for maintenance activities.

Generally, the subassembly consists of three parts of which one part is fitted permanently to the process installation (welded or threaded); the second part is fitted to the sensor and the third part holds the earlier parts together. In addition to these parts there are elastomeric seals were appropriate. Standard O-ring material is Viton, other O-ring materials are available as spare part (see Figure 5 and 6).




Figure 5: ISC40 sensor in screw-in subassembly ISC40FS-SCSA




Figure 6: ISC40 sensor in weld-in subassembly ISC40FS-SCWN

3.3 DIMENSIONS

Dimensions in mm (inches)




Figure 7: Dimensions ISC40FS with sensor installed (dimensions in mm (inches))

3.4 MODEL CODE ISC40FS FLOW FITTING SUBASSEMBLY

Table 4: Model and suffix code table

Model	Suffix Code	Option	Description
ISC40FS			inductive conductivity flow fitting, subassembly
Material	-F		Polyvinylidene fluoride (PVDF)
	-P		Polypropylene (PP)
	-S		Stainless steel (SS)
Process connection	-CS		2" coupling screw-in
	-CW		coupling weld acc to DIN 11851 (only for -S)
Screw thread NPT or R	-A		screw thread acc to ANSI / ASME (only for -CS)
	-N		no thread (only for -CW weld-in couplings)
Options		/M	material certificate 3.1 (EN 10 204) wetted metal parts only

3.5 SPARE PARTS ISC40FS FLOW FITTING SUBASSEMBLY

Parts ISC40FS subassembly				
Part no.	Description	Dimensions	Material	O-ring(s)
K1541KD	Holder+O-rings	2"	PVDF	Viton
K1541KL	Holder+O-rings	2"	Polypropylene	Viton
K1541KA	Holder+O-rings	2"	AISI 316 SS	Viton
K1541KB	Holder, ISC40FS-STWN			
K1541KC	Holder, ISC40FS-S2WN			
K1541ZM	O-rings	56.52x5.33 (5)		Viton
K1500BP	Clamp seal ring	2"		EPDM
K1500CB	O-ring	(5 sets of 2) ISC40/options		Viton
K1500DZ	Nut FF/S20-3* + ISC40FF/S		AISI 316 SS	
Parts ISC40FS subassembly				
O-rings -FCSA, -PCSA, -FCWN, -PCWN				
Part no.	Description	Dimensions	Material	Quantity
K1500DF	O-ring set	40.64 x 5.33; 26.57 x 3.53; 56.52 x 5.33	EPDM	5 sets
K1500DE	O-ring set	40.64 x 5.33; 26.57 x 3.53; 56.52 x 5.33	Viton	5 sets
K1500DG	O-ring set	40.64 x 5.33; 26.57 x 3.53; 56.52 x 5.33	Silicon	5 sets
K1500CD	O-ring	40.64 x 5.33	FFKM	1
K1500CH	O-ring	26.57 x 3.53	FFKM	1
O-rings -SCSA, -SCWN, -S2WN				
Part no.	Description	Dimensions	Material	Quantity
K1500DB	O-ring set	40.64 x 5.33; 26.57 x 3.53; Ring DN50	EPDM	5 sets
K1500DA	O-ring set	40.64 x 5.33; 26.57 x 3.53; Ring DN50	Viton	5 sets
K1500DC	O-ring set	40.64 x 5.33; 26.57 x 3.53; Ring DN50	Silicon	5 sets
K1500CD	O-ring	40.64 x 5.33	FFKM	1
K1500CH	O-ring	26.57 x 3.53	FFKM	1
K1500DD	O-ring	53.34 x 5.33	FFKM	1
K1500DJ	O-ring sets		Viton	2
K1500DK	O-ring sets		Silicon	2
K1541ZH	O-ring sets		EPDM	2
K1541ZK	O-ring sets		EPDM	2

Note ⁽³⁾ O-ring 53.34 x 5.33 (K1500DD) is used as a FFKM replacement for the Ring DN50.

4. ISC40FD IMMERSION FITTING

4.1 General Specifications

4.1.1 Materials

Wetted parts without options

Model ISC40FD-S : AISI 316 SS, Viton

Model ISC40FD-V : PVC-C, Viton

Flange ISC40FD-S-**-SF* : AISI 316 SS

Non-wetted parts fitting

Tube pigtail : plastic

4.1.2 Operating range

Temperature

Model ISC40FD-S : Max. 150°C (302°F)

Model ISC40FD-V : Max. 80°C (176°F)

Pressure

Model ISC40FD-S : Max. 10 bar (150 PSI) at operating temperature

Model ISC40FD-V : Max. 2 bar (30 PSI) at 20°C (68°F)

Max. 1 bar (15 PSI) at 80°C (176°F)

4.1.3 Shipping details

Package size (LxWxH) and Package weight (max.) is dependable on fitting length.

4.1.4 Process connections

Flange AISI 316 SS 2" or AISI 316 SS DN50, for the type -V an adjustable optional flange is available with ANSI 2" 150 lbs and DN50 PN10 hole pattern.

Note: If required the ISC40 sensor type -GG and -TG can be supplied with a Viton gasket K1500AM (ordered as spare part). This gasket may be used with the older series of ISC40FD fittings. It should be discarded when the sensor is mounted in combination with the ISC40FD type -S and -V.

4.2 INSTALLATION OF ISC40 SENSOR IN ISC40FD

Installation of the immersion fittings involves two steps:

- Installation of the sensor

The sensor has to be mounted in the immersion fitting (see Figure 8).

- Installation in the application

» On a railing or stanchion

For this purpose the immersion fitting has an optional rail mounting kit /MS1. This kit consists of a piece of guide pipe and two pipe clamps. The guide pipe is mounted horizontally to the stanchion using one pipe clamp. The second pipe clamp connects the guide pipe to the immersion fitting. The distance between the pipe clamps determines the distance between the stanchion and immersion fitting (see Figure 9).

» With flange

For this purpose a stainless steel immersion fitting can be ordered as type -SFD (DN50) or type -SFA (2"). The PVC immersion fitting has an optional depth adjustable mounting flange /FA (with DN50 and ANSI 2" 150 lbs hole pattern) which is illustrated in Figure 10. You must assure that the mating flange has the same hole pattern as the supplied flange.




Figure 8: Installation of ISC40 sensor in immersion fitting




Figure 9: Installation on stanchion with /MS1




Figure 10: Option /FA

Alternative ways of mounting the immersion fitting are:

- Guide pipe

To facilitate this type of mounting the immersion fitting has a larger diameter at the top. The user supplied guide pipe (internal diameter > 52 mm) is fitted to the wall or mounting rail. The immersion fitting slides into this guide pipe and therefore the sensor can be easily removed for inspection.

- Platform mounting

Sometimes there is a walking platform that can be used to mount the immersion fitting. The top of the immersion fitting has a larger diameter than the shaft. The only thing to do is to drill a precise hole in the platform to slide the fitting through.

4.3 DIMENSIONS ISC40FD

Dimensions in mm [inch]




Figure 11: Immersion fitting ISC40FD




Figure 12: Pipe mounting set - option /MS1




Figure 13: Adjustable flange - option /FA




Figure 14: Protection hose, option /PH5, /PH10

4.4 MODEL CODE ISC40FD

Table 5: Model and suffix code table

Model	Suffix Code	Option	Description
ISC40FD			Immersion fitting
Material	-S		SS AISI 316, Length incl. sensor length
	-V		PVC-C, Length excl. sensor length
Length	-5		0.5 meter
	-6		0.6 m
	-7		0.7 m
	-8		0.8 m
	-9		0.9 m
	-10		1.0 m
	-11		1.1 m
	-12		1.2 m
	-13		1.3 m
	-14		1.4 m
	-15		1.5 m
	-16		1.6 m
	-17		1.7 m
	-18		1.8 m
	-19		1.9 m
	-20		2.0 m
Flange	-SFD		AISI316 SS DN50
	-SFA		AISI316 SS 2"
	-NFL		No flange
Options		/MS1	pipe mounting set
		/FA	adjustable flange with DN50-PN10 and ANSI 2" 150 lbs hole pattern (only pvc)
		/M	material certificate 3.1 (only for SS wetted parts)
		/PH5	protection hose for 5 m cable
		/PH10	protection hose for 10 m cable

4.5 SPARE PARTS ISC40FD

Options ISC40FD Immersion fitting				
Part no.	Description	Process connection	Material	
K1541ZY	/MS1		Carbon steel	
K1520EV	/FA	DN50 PN10; ANSI 2" lbs	PP	
K1500CJ	/PH5		PVC, PA6.6	
K1500CK	/PH10		PVC, PA 6.6	
K1500EM	/PH25 for immersion holders			
K1500AW	Flexible conduit			5 m
K1500AX	Flexible conduit			10 m
K1500AB	Cable gland 1/2 inch NPT			10
K1500AY	Connection parts for conduit			
K1500CB	O-ring (5 sets of 2) viton ISC40/options			
K1541ZS	O-rings viton 44.17x1.78 (5)			
K1500AJ	O-rings EPDM for /FA (2pcs)			
O-rings ISC40FD Immersion fitting				
O-rings -S				
Part no.	Description	Dimensions	Material	Quantity
K1500CE	O-ring set	39.35 x 2.62; 26.57 x 3.53	EPDM	5 sets
K1500CF	O-ring set	39.35 x 2.62; 26.57 x 3.53	Viton	5 sets
K1500CG	O-ring set	39.35 x 2.62; 26.57 x 3.53	Silicon	5 sets
K1500CH	O-ring	26.57 x 3.53	FFKM	1
K1500DB	O-ring set		EPDM	5 sets
K1500DC	O-ring set		Silicon	5 sets
O-rings -V				
Part no.	Description	Dimensions	Material	Quantity
K1500CX	O-ring set	39.35 x 2.62; 26.57 x 3.53; 44.17 x 1.78	EPDM	5 sets
K1500CW	O-ring set	39.35 x 2.62; 26.57 x 3.53; 44.17 x 1.78	Viton	5 sets
K1500CY	O-ring set	39.35 x 2.62; 26.57 x 3.53; 44.17 x 1.78	Silicon	5 sets
K1500DF	O-ring sets		EPDM	5 sets
K1500DG	O-ring sets		Silicon	5 sets

5. CHEMICAL COMPATIBILITY

Table 6: Chemical compatibility chart

Chemical Compatibility Chart			Material																	
		Conc. %	Temp. °C	Viton		Kalrez		EPDM		Silicon		SS 316(I)		PVDF (Kynar)		PP		PVC		
				20	60	100	20	60	100	20	60	100	20	60	100	20	60	100	20	60
Inorganic acid	Sulfuric acid	10																		
		50																		
		95																		
	Hydrochloric acid	fuming																		
		10																		
		sat.																		
	Nitric acid	25																		
		50																		
		95																		
	Phosphoric acid	fuming																		
		25																		
		50																		
	Hydrofluoric acid	95																		
		40																		
75																				
Organic acid	Acetic acid	10																		
		glacial																		
	Formic acid	80																		
	Citric acid	50																		
Alkali	Calcium hydroxide	sat.																		
	Potassium hydroxide	50																		
	Sodium hydroxide	40																		
	Ammonia in water	30																		
Acid salt	Ammonium chloride	sat.																		
	Zinc chloride	50																		
	Iron(III) chloride	50																		
	Sodium sulfite	sat.																		
Basic salt	Sodium carbonate	sat.																		
	Potassium chloride	sat.																		
	Sodium sulfate	sat.																		
	Calcium chloride	sat.																		
Neutral salt	Sodium chloride	sat.																		
	Sodium nitrate	50																		
	Aluminium chloride	sat.																		
	Hydrogen peroxide	30																		
Oxidizing agent	Sodium Hypochloride	50																		
	Potassium dichromate	sat.																		
	Chlorinated lime																			
	Ethanol	80																		
Organic solvent	Cyclohexane																			
	Toluene																			
	Trichloroethane																			
	Water																			

o = can be used x = shortens useful life - = cannot be used Blank = no data currently available

Note : Information in this list is based on our general experience and literature data and given in good faith.

However Yokogawa is unable to accept responsibility for claims related to this information.

YOKOGAWA ELECTRIC CORPORATION World Headquarters 9-32, Nakacho 2-chome, Musashino-sh Tokyo 180-8750 Japan www.yokogawa.com	YOKOGAWA ELECTRIC ASIA Pte. LTD. 5 Bedok South Road Singapore 469270 Singapore www.yokogawa.com/sg	Yokogawa has an extensive sales and distribution network. Please refer to the European website (www.yokogawa.com/eu) to contact your nearest representative.
YOKOGAWA CORPORATION OF AMERICA 2 Dart RoadNewnan GA 30265 USA www.yokogawa.com/us	YOKOGAWA CHINA CO. LTD. 3F Tower D Cartelo Crocodile Building No.568 West Tianshan Road Changling District Shanghai, China www.yokogawa.com/cn	
YOKOGAWA EUROPE BV Euroweg 23825 HD AMERSFOORT The Netherlands www.yokogawa.com/eu	YOKOGAWA MIDDLE EAST B.S.C.(c) P.O. Box 10070, Manama Building 577, Road 2516, Busaiteen 225 Muharraq, Bahrain www.yokogawa.com/bh	

YOKOGAWA 

IM 12D07K04-01EN-P

Subject to change without notice
Copyright©