# General Specifications

# ROTA*MASS* Total Insight Coriolis Mass Flow and Density Meter Intense



GS 01U10B05-00EN-R



# Rotamass Intense - For high pressure applications

#### Features and benefits

- Most robust design for high pressure applications with process pressures up to 700 barg (10000 psig)
- Optimum decoupling of core measuring element from any external influences and stresses
- Ability to handle gas with Gas Void Fraction from 0-100 %
- The Process guard and advanced self-diagnostic functions support a safe operation and reduce maintenance efforts
- Thick measuring tubes and wetted parts made of alloy C-22 for long term stability
- Dynamic Pressure compensation for accurate measurement even at changing process pressure



- Meter Performance under wide process conditions
- Meter Verification in line by Tube Health Check function

# **Table of contents**

1	Intro	ntroduction		
	1.1	About	this General Specification	4
	1.2	Applica	able documents	4
	1.3	Measu	ring system	5
	1.4	Transn	nitter	6
2	App	lication	and measuring ranges	7
	2.1		red quantities	
	2.2		low	
	2.3		ire loss	
	2.4		у	
	2.5		ss fluid temperature range	9
^				
3		-		
	3.1	_	ew	_
	3.2		oint stability of the mass flow	
	3.3		low accuracy	
	3.4		ncy of density	
		3.4.1	For Jacobs	
	2.5	3.4.2	For gases	
	3.5	3.5.1	cy of mass flow and density according to the model code	
		3.5.2	For gases	
	3.6		e flow accuracy	
	5.0	3.6.1	For liquids	
		3.6.2	For gases	
	3.7		icy of temperature	
	3.8		tability	
	3.9	•	ation conditions	
	0.0	3.9.1	Mass flow calibration and density adjustment	
		3.9.2	Density calibration	
	3.10	) Proces	s conditions	19
		3.10.1	Process pressure effect	
		3.10.2	Process fluid temperature effect	
	3.11	Analog	output specification	21
4	One	erating co	onditions	22
•	4.1	_	on and position of installation	22
		4.1.1	Sensor installation position	22
	4.2		s conditions	23
		4.2.1	Pressure	
		4.2.2	Secondary containment	
	4.3	Ambiei	nt conditions	27
	-	4.3.1	Allowed ambient temperature for sensor	
		4.3.2	Temperature specification in hazardous areas	

5	Med	hanical s	specification	45
	5.1	Design		45
	5.2	Materia	l	46
		5.2.1	Sensor	46
		5.2.2	Transmitter	47
		5.2.3	Nameplates	48
		5.2.4	Heat tracing	48
	5.3	Proces	s connections, dimensions and weights of sensor	49
	5.4	Transm	nitter dimensions and weights	55
6	Elec	ctrical sp	ecification	57
	6.1	Power	supply	57
	6.2	Electric	al interfaces	57
		6.2.1	Analog inputs and outputs	58
		6.2.2	Digital inputs and outputs	61
		6.2.3	HART	65
		6.2.4	Modbus	
		6.2.5	PROFIBUS PA	
		6.2.6		71
	6.3		and microSD card	
	6.4	Cable s	specifications	74
7	App	rovals ar	nd declarations of conformity	75
	7.1	Legal e	quipment standards and norms	75
	7.2	Applica	tion and industry related standards	76
	7.3	Commi	unication interface standards	77
	7.4	Other s	tandards and guidelines	77
	7.5	Hazard	ous area	78
8	Ord	ering info	ormation	82
	8.1	Model	code description	82
	8.2	Availab	le model codes per basic model	90
	8.3	Model	code combinations	93
	8.4		g Instructions	94
		8.4.1	Mandatory ordering instructions	
		8.4.2	Optional ordering instructions	

# 1 Introduction

This specification provides overview about Rotamass Total Insight portfolio. Complete specification is available per product line.

# 1.1 About this General Specification

All available properties of the Rotamass Coriolis flow meter are specified by means of a model code.

One model code position may include several characters depicted by means of dashed lines.

The positions of the model code relevant for the respective properties are depicted and highlighted in blue. Any values that might occupy these model code positions are subsequently explained.




Fig. 1: Highlighted model code positions

A complete description of the model code is included in the chapter 8 Ordering information [ 82].

#### 1.2 Applicable documents

The following documents supplement this specification:

Document title	Document number
General Specifications:	
General Specifications Rotamass Specification Overview	GS 01U10B00-00R <sup>1)</sup>
<ul> <li>General Specifications Rotamass Features on Demand (FOD)</li> </ul>	GS 01U10B20-00R <sup>1)</sup>
<ul> <li>General Specifications Rotamass Spare Transmitter</li> </ul>	GS 01U10B21-00R <sup>1)</sup>
Instruction Manuals:	
General Instruction Manual	IM 01U10B00-00R <sup>1)</sup>
Quick Reference Instruction Manual	IM 01U10A00-00R1)
Quick Reference Instruction Manual for Spare	IM 01U10A01-00R <sup>1)</sup>
Explosion proof type Manuals:	
<ul> <li>Explosion Proof Type Manual ATEX</li> </ul>	IM 01U10X01-00R <sup>1)</sup>
<ul> <li>Explosion Proof Type Manual IECEx</li> </ul>	IM 01U10X02-00R <sup>1)</sup>
<ul> <li>Explosion Proof Type Manual FM</li> </ul>	IM 01U10X03-00R <sup>1)</sup>
<ul> <li>Explosion Proof Type Manual INMETRO</li> </ul>	IM 01U10X04-00R <sup>1)</sup>
<ul> <li>Explosion Proof Type Manual PESO</li> </ul>	IM 01U10X05-00R <sup>1)</sup>
<ul> <li>Explosion Proof Type Manual NEPSI</li> </ul>	IM 01U10X06-00R <sup>1)</sup>
<ul> <li>Explosion Proof Type Manual Korea-Ex</li> </ul>	IM 01U10X07-00R <sup>1)</sup>
<ul> <li>Explosion Proof Type Manual EAC-Ex</li> </ul>	IM 01U10X08-00R <sup>1)</sup>
<ul> <li>Explosion Proof Type Manual Japan Ex</li> </ul>	IM 01U10X09-00R <sup>1)</sup>
<ul> <li>Explosion Proof Type Manual UKEx</li> </ul>	IM 01U10X11-00R <sup>1)</sup>
Software Instruction Manuals:	
Software Instruction Manual HART	IM 01U10S01-00R <sup>1)</sup>
<ul> <li>Software Instruction Manual FOUNDATION Fieldbus</li> </ul>	IM 01U10S02-00R <sup>1)</sup>
Software Instruction Manual Modbus	IM 01U10S03-00R <sup>1)</sup>
Software Instruction Manual PROFIBUS PA	IM 01U10S04-00R <sup>1)</sup>

<sup>1)</sup> The "\_" symbols are placeholder for the corresponding language version of the document (EN, DE, etc.).



The complete product documentation is stored on the microSD card delivered with the device and is available at:

- Yokogawa Customer Portal (<a href="http://myportal.yokogawa.com/s/documents">http://myportal.yokogawa.com/s/documents</a>)
- Yokogawa Device Lifecycle Management app

Please enter the serial number of the device or scan the QR code on the device.

# 1.3 Measuring system

The Rotamass Coriolis flow meter consists of:

- Sensor
- Transmitter

When the integral type is used, sensor and transmitter are firmly connected.




Fig. 2: Configuration of the Rotamass integral type

- 1 Transmitter
- 2 Sensor
- 3 Process connections

When the remote type is used, sensor and transmitter are linked via connecting cable. As a result, sensor and transmitter can be installed in different locations.




Fig. 3: Configuration of the Rotamass remote type

Process connections

1	Transmitter	4	Sensor terminal box
2	Sensor	5	Connecting cable



3

Introduction Transmitter




Fig. 4: Configuration of the Rotamass remote type - long neck


1	Transmitter	4	Sensor terminal box
2	Sensor	5	Connecting cable
3	Process connections		

# 1.4 Transmitter

The sensor can be combined with different transmitters. The transmitter type is visible in the indicator.



#### **Essential Transmitter**



#### **Ultimate Transmitter**



Model code position 1	Transmitter type	Description	Communication Interfaces
E	Essential	Basic functions	HART, Modbus
U	Ultimate	Advanced filinctions	HART, Modbus, PROFIBUS PA, FOUNDATION Fieldbus

Transmitter functions are described in detail in the Specification overview GS01U10B00-00\_\_-R.

For details about available functions per transmitter type refer to chapter Ordering information [ 82].

# 2 Application and measuring ranges

(i)	In this chapter, all values related to pressure are gauge pressure values.
(i)	For process specific results, please refer to the FlowConfigurator online sizing and configuration tool: <a href="http://www.FlowConfigurator.com">http://www.FlowConfigurator.com</a>

# 2.1 Measured quantities

The Rotamass Coriolis flow meter can be used to measure the following fluids:

- Liquids
- Gases
- Mixtures, such as emulsions, suspensions, slurries

Possible limitations applying to measurement of mixtures must be checked with the responsible Yokogawa sales organization.

The following variables can be measured using Rotamass:

- Mass flow
- Density
- Temperature

Based on these measured quantities, the transmitter also calculates:

- Volume flow
- Partial component concentration of a two-component mixture
- Partial component flow rate of a mixture consisting of two components (net flow)

The net flow is calculated based on the known partial component concentration and the overallflow.

The mass flow, volume flow, net flow measurements can be bi-directional.


#### Measured quantities for NTEP custody transfer approval

Measurement variables for NTEP approval options /Q20 are:

- Mass flow unidirectional
- Volume flow unidirectional

#### 2.2 Mass flow

For Rotamass Intense the following meter sizes to be determined using the *Model code description* [> 82] are available.



#### Mass flow of liquids

Meter size	Typical connection size	Q <sub>nom</sub> in t/h (lb/min)	Q <sub>max</sub> in t/h (lb/min)	Model code position 3
Intense 08	9/16"	0.045 (1.7)	0.094 (3.5)	08
Intense 10	9/16"	0.170 (6.2)	0.300 (11)	10
Intense 34	1/2"	3 (110)	5 (180)	34
Intense 36	1"	10 (370)	17 (620)	36
Intense 38	2"	32 (1200)	50 (1800)	38

# Mass flow measuring range for NTEP custody transfer approval

Tab. 1: Mass flow measuring ranges (/Q20)

Meter size	Q <sub>min</sub> in t/h (lb/min)	Q <sub>max</sub> in t/h (lb/min)
Intense 34	0.300 ( 11.023)	1.920 ( 70.548)
Intense 36	1.500 ( 55.116)	13.500 (496.040)
Intense 38	3.000 (110.231)	27.000 (992.080)

Q<sub>nom</sub> - Nominal mass flow

Q<sub>max</sub> - Maximum mass flow

 $\boldsymbol{Q}_{\text{min}}$  - Minimum mass flow

The nominal mass flow  $Q_{nom}$  is defined as the mass flow of water (temperature: 20 °C) at 1 bar (14.5 psi) pressure loss across the flow meter.

#### Mass flow of gases

When using Rotamass for measuring the flow of gases, the mass flow is usually limited by the pressure loss generated and the maximum flow velocity.

Type of gas	Meter size	Maximum flow velocity
Oxygen	Intense 34, 36, 38	60 m/s
Methane Natural gas	Intense 34, 36, 38	60 m/s
Other gases	Intense 34, 36, 38	33 % of sound velocity

#### 2.3 Pressure loss

The pressure loss along the flow meter is heavily dependent on the application. The pressure loss of 1 bar at nominal mass flow  $Q_{nom}$  also applies to water and is considered the reference value.

# 2.4 Density

Meter size	Measuring range of density in kg/l (lb/ft³)
Intense 08	
Intense 10	
Intense 34	0 – 5 (0 – 312)
Intense 36	
Intense 38	

# Density measuring range for NTEP custody transfer approval

Tab. 2: Density measuring ranges (/Q20)

Option	Measuring range of density in kg/l (lb/ft³)
/Q20	0.74 - 1.40 (46 - 87)

#### **Density of gases**

Rather than being measured directly, density of gas is usually calculated using its reference density, process fluid temperature and process pressure.

#### 2.5 Process fluid temperature range



Allowed process fluid and ambient temperature ranges in hazardous areas depend on classifications defined by applications, refer to *Temperature specification in hazardous areas* [> 31].

For Rotamass Intense the following process fluid temperature ranges are available:



Temperature range	Model code position 8	Process fluid temperature in °C (°F)	Design type	Model code position 10
Standard	0	-50 – 150 (-58 – 302)	Integral type	0, 2
Standard	0	-70 – 150 (-94 – 302)		A, B, E, F, J, K
Medium	2	-70 – 230 (-94 – 446)	Remote type	D E IV
High	3	0 – 350 (32 – 662)		B, F, K

Accuracy Overview

# 3 Accuracy

In this chapter, maximum deviations are indicated as absolute values.



All accuracy data are given in ± values.

#### 3.1 Overview

#### Achievable accuracies for liquids

The value  $D_{\text{flat}}$  specified for accuracy of mass flow applies for flow rates exceeding the mass flow limit  $Q_{\text{flat}}$ . If the flow rate is less than  $Q_{\text{flat}}$ , other effects have to be considered.

If the flow rate is higher than  $Q_{\text{nom}}$ , other effects might influence the accuracy (e.g. cavitation).

The following values are achieved at calibration conditions when the device is delivered, see *Calibration conditions* [> 18].

Measured quantity		Accuracy for transmitters		
		Essential	Ultimate	
Mass flow <sup>1)</sup>	Accuracy <sup>2)</sup> D <sub>flat</sub>	0.15 % of measured value	0.1 % of measured value	
IVIASS IIOW	Repeatability <sup>3)</sup>	0.08 % of measured value	0.05 % of measured value	
Volume flow (water) <sup>1)</sup>	Accuracy <sup>2)</sup> D <sub>V</sub>	0.43 % of measured value	0.12 % of measured value	
	Repeatability <sup>3)</sup>	0.22 % of measured value	0.06 % of measured value	
Donaitre	Accuracy <sup>2)</sup>	4 g/l (0.25 lb/ft³)	0.5 g/l (0.03 lb/ft³)	
Density	Repeatability <sup>3)</sup>	2 g/l (0.13 lb/ft³)	0.3 g/l (0.02 lb/ft³)	
Temperature	Accuracy <sup>2)</sup>	0.5 °C (0.9 °F)	0.5 °C (0.9 °F)	

#### Achievable accuracies for gases

Measured quantity		Accuracy for transmitters	
		Essential	Ultimate
Mass flow / standard	Accuracy <sup>2)</sup> D <sub>flat</sub>	0.75 % of measured value	0.5 % of measured value
volume flow <sup>1)</sup>	Repeatability <sup>3)</sup>	0.6 % of measured value	0.4 % of measured value
Temperature	Accuracy <sup>2)</sup>	0.5 °C (0.9 °F)	0.5 °C (0.9 °F)

<sup>&</sup>lt;sup>1)</sup> Based on the measured values of the pulse output. This means that the flow accuracy and repeatability considers the combined measurement uncertainties including sensor, electronic and pulse output interface.



<sup>&</sup>lt;sup>2)</sup> Best mass flow accuracy per transmitter type.

<sup>&</sup>lt;sup>3)</sup> The stated repeatability is included in the accuracy.

# Accuracy

# 3.2 Zero point stability of the mass flow

In case of no flow, the maximum measured flow rate is called *Zero point stability*. Zero point values are shown in the table below.

Meter size	Zero point stability Z in kg/h (lb/h)
Intense 08	0.005 (0.011)
Intense 10	0.018 (0.040)
Intense 34	0.15 (0.33)
Intense 36	0.5 (1.1)
Intense 38	1.6 (3.5)



Accuracy Mass flow accuracy

#### 3.3 Mass flow accuracy

Above mass flow  $Q_{\text{flat}}$ , maximum deviation is constant and referred to as  $D_{\text{flat}}$ . It depends on the product version and can be found in the tables in chapter *Accuracy of mass flow and density according to the model code* [> 15].

 $\boldsymbol{Q}_{\text{flat}}$ 

Use the following formulas to calculate the maximum deviation *D*:

$$Q_m \ge Q_{flat}$$

$$D = D_{flat}$$

$$Q_m < Q_{flat}$$

$$D = \frac{a \times 100 \%}{Q_m} + b$$

D Maximum deviation in %

Maximum deviation for high flow rates in %

Q<sub>m</sub> Mass flow in kg/h

Mass flow value above which  $D_{\text{flat}}$  applies, in kg/h

#### a, b Constants

 $D_{\mathsf{flat}}$ 

Meter size	Model code	$D_{flat}$	$Q_{flat}$	а	b
(Q <sub>nom</sub> in kg/h)	position 9	in %	in kg/h	in kg/h	in %
Intense 08	E8	0.2	4.0	0.0075	0.0132
(45)	C8	0.1	5.0	0.0054	-0.0088
Intense 10	E7	0.2	8.5	0.021	-0.05
(170)	C3, C7	0.1	14	0.0097	0.031
	E7	0.2	150	0.38	-0.05
	D7	0.15	200	0.21	0.043
Intense 34 (3000)	C2, C3	0.1	250	0.17	0.032
(3000)	70	0.75	150	0.38	0.5
	50	0.5	200	0.21	0.393
	E7	0.2	500	1.3	-0.05
	D7	0.15	670	0.71	0.044
Intense 36 (10000)	C2, C3	0.1	830	0.57	0.032
(10000)	70	0.75	500	1.3	0.5
	50	0.5	670	0.71	0.394
	E7	0.2	1600	4	-0.05
Intense 38 (32000)	D7	0.15	2100	2.3	0.04
	C2, C3	0.1	2670	1.8	0.032
(02000)	70	0.75	1600	4	0.5
	50	0.5	2100	2.3	0.39

Accuracy Mass flow accuracy

# Accuracy using water at 20 °C as an example




Fig. 5: Schematic dependency of the maximum deviation on the mass flow

D	Maximum deviation in %	$Q_{\rm m}$	Mass flow in kg/h
$Q_{nom}$	Nominal mass flow in kg/h	$Q_{flat}$	Mass flow above which $D_{\text{flat}}$ applies, in kg/h

Accuracy Accuracy Accuracy of density

#### 3.4 Accuracy of density

#### 3.4.1 For liquids

Meter size	Transmitter	Maximum deviation of density <sup>1)</sup> in g/l (lb/ft³)	
Intense 34			
Intense 36	Essential	Down to 4 (0.25)	
Intense 38			
Intense 08			
Intense 10	Ultimate		
Intense 34		Down to 0.5 (0.03)	
Intense 36			
Intense 38			

<sup>1)</sup> Deviations possible depending on product version (meter size, type of calibration)

The maximum deviation depends on the product version selected, see also Accuracy of mass flow and density according to the model code [> 15].

#### 3.4.2 For gases

In most applications, density at standard conditions is programmed into the transmitter and used to calculate the standard volume flow based on mass flow.

If gas pressure is a known value, after entering a reference density, the transmitter is able to calculate gas density from temperature and pressure as well (while assuming an ideal gas).

Alternatively, gas density can be measured. In order to do so, it is necessary to adapt the lower density limit value in the transmitter.


For most applications the direct measurement of the gas density will have less accuracy as stated for liquids.



# 3.5 Accuracy of mass flow and density according to the model code

Accuracy for flow rate as well as density is selected via model code position 9. Here a distinction is made between devices for measuring liquids and devices for measuring gases. No accuracy for density measurement is specified for gas measurement devices.

#### 3.5.1 For liquids



#### **Essential**

Model code position 9		······································			
		Intense 34	Intense 36	Intense 38	
E7	4	0.2	0.2	0.2	
D7 <sup>2)</sup>	4	0.15	0.15	0.15	

<sup>1)</sup> Specified maximum deviation is achieved within the applicable measuring range for density.

#### **Ultimate**

Model code position 9	tion 9 density <sup>1)</sup> in %					
	in g/l	Intense 08	Intense 10	Intense 34	Intense 36	Intense 38
E8	8	0.2	-	0.2	0.2	0.2
E7	4	-	0.2	0.2	0.2	0.2
C8 <sup>2)</sup>	8	0.1	-	0.2	0.2	0.2
C7 <sup>2)</sup>	4	-	0.1	0.1	0.1	0.1
C3 <sup>2)</sup>	1	-	0.1	0.1	0.1	0.1
C2 <sup>2),3)</sup>	0.5	-	-	0.1	0.1	0.1

<sup>1)</sup> Specified maximum deviation is achieved within the applicable measuring range for density.

<sup>&</sup>lt;sup>3)</sup> Specified deviation of density is achieved within the following limits, see table below:

	Limits for density specific $D_{ ext{flat}}$ for mass flow		
	Intense 34	Intense 36	Intense 38
Q <sub>min</sub> of C2 in kg/h	300	700	
Ambient temperature range in °C (°F)	-10 – 50 (14 – 122)		

<sup>&</sup>lt;sup>2)</sup> Notice: In case of a spare sensor combined with a transmitter in use, the original accuracy specification may be affected. For calibration services, please contact Yokogawa Service department.

<sup>&</sup>lt;sup>2)</sup> Notice: In case of a spare sensor combined with a transmitter in use, the original accuracy specification may be affected. For calibration services, please contact Yokogawa Service department.

Accuracy Volume flow accuracy

#### 3.5.2 For gases



#### **Essential**

Model code position 9	Maximum deviation $D_{\mathrm{flat}}$ for mass flow in %
70	0.75

#### **Ultimate**

Model code position 9	Maximum deviation $D_{\mathrm{flat}}$ for mass flow in %
50 <sup>1)</sup>	0.5

<sup>&</sup>lt;sup>1)</sup> Notice: In case of a spare sensor combined with a transmitter in use, the original accuracy specification may be affected. For calibration services, please contact Yokogawa Service department.

# 3.6 Volume flow accuracy

#### 3.6.1 For liquids

The following formula can be used to calculate the accuracy of liquid volume flow:

$$D_{V} = \sqrt{D^2 + \left(\frac{\Delta \rho}{\rho} \times 100\%\right)^2}$$


 $D_{\rm V}$  Maximum deviation of volume flow in %  $\Delta \rho$  Maximum deviation of density in kg/l D Maximum deviation of mass flow in %

ρ Density in kg/l

#### 3.6.2 For gases

Accuracy of standard volume flow for gas with a fixed reference density equals the maximum deviation *D* of the mass flow.

$$D_{\vee} = D$$



# 3.7 Accuracy of temperature

Accuracy of temperature depends on the sensor temperature range selected (see *Process fluid temperature range [» 9]*) and can be calculated as follows:

Formula for specified temperature range Standard and Medium

$$\Delta T = 0.5 \, ^{\circ}\text{C} + 0.005 \times \left| \right. T_{pro} - 20 \, ^{\circ}\text{C} \left| \right.$$

$\Delta T$	Maximum deviation of temperature				
$T_{\rm pro}$	Process fluid temperature in °C measured by Rotamass Total Insight				
	Sensor size				
$D_{T}$	08	10	34	36	38
	0.00	)75		0.0050	

 $D_{\mathsf{T}}$  Deviation of temperature

Formula for specified temperature range High

$$\Delta T = 1.0 \,^{\circ}\text{C} + 0.008 \times |T_{pro} - 20 \,^{\circ}\text{C}|$$

 $\Delta T$  Maximum deviation of temperature

 $T_{pro}$  Process fluid temperature in °C




Fig. 6: Temperature accuracy

- 1 Temperature specifications Standard and Medium
- 2 Temperature specification High

Accuracy Repeatability

#### 3.8 Repeatability

#### For liquids

When using default damping times, the specified repeatability of mass flow, density and temperature measurements equals half of the respective maximum deviation.

$$R = \frac{D}{2}$$

R Repeatability

D Maximum deviation

#### For gases

In deviation hereto, the following applies to mass and standard volume flow of gases:

$$R = \frac{D}{1.25}$$

#### 3.9 Calibration conditions

#### 3.9.1 Mass flow calibration and density adjustment

The calibration laboratory at Rota Yokogawa is accredited according to DIN EN ISO/IEC 17025:2018. All Rotamass are calibrated in accordance with standard calibration procedure and each device comes with a standard calibration certificate. Optionally, a 5 point-calibration (option K2) or a 10 point-calibration with DAkkS calibration certificate (option K5) can be performed.

Each Rotamass device comes with a standard calibration certificate.

Calibration takes place at reference conditions. Specific values are listed in the standard calibration certificate.

	Reference conditions	
Fluid	Water	
Density	0.9 – 1.1 kg/l (56 – 69 lb/ft³)	
Fluid temperature	10 – 35 °C (50 – 95 °F)	
Fluid temperature	Average temperature: 22,5 °C (72.5 °F)	
Ambient temperature	10 – 35 °C (50 – 95 °F)	
Process pressure (absolute)	1 – 5 bar (15 – 73 psi)	

The accuracy specified is achieved at as-delivered calibration conditions stated.

#### 3.9.2 Density calibration

Density calibration is performed for maximum deviation of 0.5 g/l (0.03 lb/ft<sup>3</sup>), (model code pos. 9: C2 or D2).

Density calibration includes:

- Determination of calibration constants for fluid densities at 0.7 kg/l (44 lb/ft³), 1 kg/l (62 lb/ft³) and 1.65 kg/l (103 lb/ft³) at 20 °C (68 °F) fluid temperature
- Check of results for fluid densities at 0.7 kg/l (44 lb/ft³), 1 kg/l (62 lb/ft³) and 1.65 kg/l (103 lb/ft³) at 20 °C (68 °F) fluid temperature
- Special flow meter configuration:
  - Specific insulation of temperature sensors
  - Preaging for long-term stability
- Creation of density calibration certificate



#### 3.10 Process conditions



For process specific results, please refer to the FlowConfigurator online sizing and configuration tool: <a href="http://www.FlowConfigurator.com">http://www.FlowConfigurator.com</a>

#### 3.10.1 Process pressure effect

Process pressure effect is defined as the change in sensor flow and density deviation due to process pressure change away from 1barg reference condition. This effect can be corrected by dynamic pressure input or a fixed process pressure.

Tab. 3: Process pressure effect, wetted parts stainless steel 1.4404/ 316L and Ni alloy C-22/ 2.4602

Meter size	Material	Deviation of Flow		Deviation of Density	
		in % of rate per bar	in % of rate per psi	in g/l per bar	in g/l per psi
Intense 08	1.4404/316L and C-22/2.4602	-0.0001	-0.00001	0.007	0.0014
Intense 10	1.4404/316L and C-22/2.4602	-0.0001	-0.00126	0.02	-0.0023
Intense 34	1.4404/316L	-0.0005	-0.00003	-0.066	-0.0046
IIILEIISE 34	C-22/2.4602	-0.0005	-0.00003	-0.076	-0.0052
Intongo 26	1.4404/316L	-0.0024	-0.00017	-0.193	-0.0133
Intense 36	C-22/2.4602	-0.0023	-0.00016	-0.192	-0.0132
Intense 38	1.4404/316L	-0.0034	-0.00023	-0.378	-0.0261
ilitelise 30	C-22/2.4602	-0.0035	-0.00024	-0.381	-0.0263

#### 3.10.2 Process fluid temperature effect

For mass flow and density measurement, process fluid temperature effect is defined as the change in sensor flow and density accuracy due to process fluid temperature change away from 20°C reference condition. For temperature ranges, see *Process fluid temperature range* [> 9].

#### Temperature effect on Zero

Temperature effect on Zero of mass flow can be corrected by zeroing at the process fluid temperature.

#### Temperature effect on mass flow

The process fluid temperature is measured and the temperature effect compensated. However due to uncertainties in the compensation coefficients and in the temperature measurement an uncertainty of this compensation is left. The typical rest error of Rotamass Total Insight temperature effect on mass flow is:

Tab. 4: All models

Temperature range	Uncertainty of flow
Standard	±0.0011 % of rate / °C (±0.0006 % of rate / °F)
Medium	±0.001 % of rate / °C (±0.00056 % of rate / °F)
High	±0.0011 % of rate / °C (±0.0006 % of rate / °F)

The temperature used for calculation of the uncertainty is the difference between process fluid temperature and the temperature 20°C reference condition.

Accuracy Process conditions

# Temperature effect on density measurement (liquids)



Process fluid temperature influence:

#### Formula for metric values

$$D'_{\rho} = \pm k \times \text{abs} (T_{\text{pro}} - 20 \,^{\circ}\text{C})$$

#### Formula for imperial values

$$D'_{\rho} = \pm k \times \text{abs} (T_{\text{pro}} - 68 \,^{\circ}\text{F})$$

D'<sub>ρ</sub> Additional density deviation due to the effect of fluid temperature in g/l (lb/ft³)

T pro Process fluid temperature in °C measured by Rotamass Total Insight

k Constant for temperature effect on density measurement in g/l × 1/°C (lb/ft $^3$  × 1/°F)

Tab. 5: Constants for particular meter size and model code position (see also *Process fluid temperature range* [▶ 9] and *For liquids* [▶ 15])

Meter size	Model code position 4	Model code position 8	Model code position 9	$k \text{ in g/l} \times 1/^{\circ}\text{C}$ (lb/ft <sup>3</sup> × 1/°F)
Intense 08	К	0	C8, E8	0.67 (0.0232)
Intense 10		U	C3, C7, E7	0.56 (0.0194)
		0, 2	C3, D7, E7	0.15 (0.0052)
	S	3		0.4 (0.0139)
	3	0	C2	0.068 (0.0024)
Interna 24		3	C2	0.218 (0.0076)
Intense 34		0, 2	C3, D7, E7	0.17 (0.0059)
	Н	3		0.36 (0.0125)
	П	0	C2	0.027 (0.0009)
		3	C2	0.115 (0.0040)
		0, 2	C3, C5, D7, E7	0.11 (0.0038)
	S	3		0.27 (0.0094)
	5	0	C2	0.034 (0.0012)
Intense 36		3		0.13 (0.0045)
intense 36		0, 2	C3, C5, D7, E7	0.09 (0.0031)
	Н	3		0.09 (0.0031)
	П	0	C2	0.24 (0.0083)
		3		0.019 (0.0007)
		0, 2	C3, C5, D7, E7	0.07 (0.0024)
	S	3		0.19 (0.0066)
	5	0	C2	0.028 (0.0010)
Intense 38		3	C2	0.104 (0.0036)
		0, 2	C3, C5, D7, E7	0.06 (0.0021)
	11	3		0.14 (0.0049)
	Н	0	CO	0.018 (0.0006)
		3	C2	0.068 (0.0024)

#### 3.11 Analog output specification

#### Analog output specification lout

If mass- or volume flow, density, temperature, pressure or concentration is measured via current output *lout* two additional deviation effects have to be taken into account.

- The lout –base specification ∆I<sub>base</sub> contains all combined effects of output adjustment, linearity, power supply variation, load resistance variation, short and long term drift for one year.
- The *lout* –ambient temperature specification  $\Delta I(T_{amb})$  gives an additional deviation effect if the ambient temperature of the transmitter differs from 20 °C.

Both additional output deviation effects have to be added to the basic mass- or volume flow, density, temperature, pressure or concentration deviation. They are based on a 95 % ( $2\sigma$ ) confidence level.

#### Deviation of mass- or volume flow, density, temperature, pressure or concentration by lout

The following formula can be used to calculate the deviation of mass- or volume flow:

$$D_{I} = \sqrt{D^{2} + \left(\frac{\Delta I_{base}}{I(Q)} \times 100 \%\right)^{2} + \left(\frac{\Delta I(T_{amb})}{I(Q)} \times 100 \%\right)^{2}}$$

$D_{I}$	Maximum deviation of mass- or volume flow, density, temperature, pressure or concentration
	by lout in %

$$\Delta I_{\text{base}}$$
 Maximum deviation of lout by combined effects

$$\Delta I_{\text{base}} = a \times I(Q) + b$$
 $\Delta I(T_{\text{amb}})$ 
Maximum deviation of lout by deviation of the transmitter ambient temperature from 20 °C

$$\Delta I(T_{amb}) = (c \times I(Q) + d) \times (T - 20 \, ^{\circ}C)$$

Description	Model code pos. 13	a in ppm	b in <i>µ</i> A	c in ppm/°C	d in <i>µ</i> A/°C
Non-intrinsically safe lout (active or passive)	JA, JB, JC, JD, JE, JF, JG, JH, JJ, JK, JL, JM, JN, M6	170	2.3	7	0
Intrinsically safe lout (passive)	JP, JQ, JR, JS				0.06

<sup>&</sup>lt;sup>1)</sup>Formula or value for accuracy of specific output parameter, please see chapters:

- 3.4 Accuracy of density [> 14]
- 3.6 Volume flow accuracy [> 16]
- 3.7 Accuracy of temperature [> 17]

# 4 Operating conditions

# 4.1 Location and position of installation

Rotamass Coriolis flow meters can be mounted horizontally, vertically and at an incline. The measuring tubes should be completely filled with the fluid during flow measurement as accumulations of air or formation of gas bubbles in the measuring tube may result in errors in measurement. Straight pipe runs at inlet or outlet are usually not required.

Avoid the following installation locations and positions:

- Measuring tubes as highest point in piping when measuring liquids
- Measuring tubes as lowest point in piping when measuring gases
- Immediately in front of a free pipe outlet in a downpipe
- · Lateral positions




Fig. 7: Installation position to be avoided: Flow meter in sideways position

#### 4.1.1 Sensor installation position

Sensor installation position as a function of the fluid

Installation position	Fluid	Description
Horizontal, measuring tubes at bottom	Liquid	The measuring tubes are oriented toward the bottom. Accumulation of gas bubbles is avoided.
Horizontal, measuring tubes at top	Gas	The measuring tubes are oriented toward the top. Accumulation of liquid, such as condensate is avoided.

Installation position	Fluid	Description
Vertical, direction of flow towards the top (recommended)		
	Liquid/gas	The sensor is installed on a pipe with the direction of flow towards the top. Accumulation of gas bubbles or solids is avoided. This position allows for complete self-draining of the measuring tubes.

#### 4.2 Process conditions



The pressure and temperature ratings presented in this section represent the design values for the devices. For individual applications (e.g. marine applications with option MC\_) further limitations may apply according to the respective applicable regulations. For details see chapter *Application and industry related standards* [> 76] under the heading Marine approvals.



In this chapter, all values related to pressure are gauge pressure values.

#### 4.2.1 Pressure

The maximum allowed process pressure depends on the selected process connection and process temperature.

The given process temperature and process pressure ranges are calculated and approved without corrosion or erosion effects.

The following diagrams shows the process pressure as a function of process temperature as well as the process connection used (type and size of process connection).

Calculations for ASME flanges are based on ASME B16.5 Material group 2.2 (316/316L dual certified).

#### ASME class 900 compatible to process connection ASME B16.5




Fig. 8: Allowed process pressure as a function of process connection temperature

#### ASME class 1500 compatible to process connection ASME B16.5




Fig. 9: Allowed process pressure as a function of process connection temperature

- 1 Process connection compatible to ASME B16.5 class 1500: Intense with material wetted parts H (without ASME compliance); Intense with meter size 34, material wetted parts S (without ASME compliance); Intense with meter size 34, material wetted parts H (option P15)
- 2 Process connection compatible to ASME B16.5 class 1500: Intense with meter size 36, material wetted parts S (without ASME compliance); Intense with meter size 34, material wetted parts S (option P15); Intense with meter size 36, material wetted parts H (option P15)



#### Process connection with internal thread G and NPT




Fig. 10: Allowed process pressure as a function of temperature

#### Process connection compatible to medium pressure autoclave




Fig. 11: Allowed process pressure as a function of process connection temperature

#### Rupture disc

The rupture disc is located on the sensor housing. It is available as an option, see model code position 15 in the table of chapter *Model code description* [ 82] under the same heading Rupture disc. The rupture disc's bursting pressure is 20 bar (291 psi), the nominal diameter is 8 mm (0.315 in.). In the case of big nominal diameters and high pressures, it is not possible to ensure that the entire process pressure is released across the rupture disc. In such case it is possible to request a customized design from the responsible Yokogawa sales organization. In the event of a burst pipe, the rupture disc provides an acoustic signal in applications with gases.

Operating conditions Process conditions

# 4.2.2 Secondary containment

Some applications or environment conditions require secondary containment retaining the process pressure for increased safety. All Rotamass Total Insight have a secondary containment filled with inert gas. The typical burst pressure values of the secondary housing are defined in the table below.

#### Typical burst pressure at room temperature

	Burst pressure in bar (psi)				
Intense 08 Intense 10 Intense 34 Intense 36			Intense 36	Intense 38	
49 (710)			120 (1740)		

#### 4.3 Ambient conditions

Allowed ambient and storage temperature of Rotamass Total Insight depends on the below components and their own temperature limits:

- Sensor
- Transmitter
- Connecting cable between sensor and transmitter (for remote design type)

#### **Ambient temperature**

Device surrounding air temperature is considered as ambient temperature. If the device is operating outdoors make sure that the solar irradiation does not increase the surface temperature of the device higher than the allowed maximum ambient temperature. Transmitter display has limited legibility below -20 °C (-4 °F).

Maximum ambient temperature range				
integral type:		-40 – 60 °C (-40 – 140 °F)		
remote type				
with standard cable	Sensor <sup>1)</sup> :	-50 – 80 °C (-58 – 176 °F)		
(option L):	Transmitter:	-40 – 60 °C (-40 – 140 °F)		
with fire retardant cable <sup>2)</sup>	Sensor <sup>1)</sup> :	-35 – 80 °C (-31 – 176 °F)		
(option Y):	Transmitter:	-35 – 60 °C (-31 – 140 °F)		

#### Ambient temperature range for NTEP custody transfer approval

Maximum ambient temperature range (/Q20)				
integral type:		-40 – 50 °C(-40 – 122 °F)		
remote type				
with standard cable	Sensor <sup>1)</sup> :	-50 – 80 °C(-58 – 176 °F)		
(option L):	Transmitter:	-40 – 50 °C (-40 – 122 °F)		
with fire retardant cable <sup>2)</sup>	Sensor <sup>1), 2)</sup> :	-35 – 80 °C(-31 – 176 °F)		
(option Y):	Transmitter:	-35 – 50 °C (-31 – 122 °F)		

¹) Check derating for high fluid temperature, see *Process fluid temperature range* [▶ 9], *Process conditions* [▶ 23] and *Allowed ambient temperature for sensor* [▶ 28]

#### Storage temperature

Maximum storage temperature range			
integral type		-40 – 60 °C (-40 – 140 °F)	
remote type			
with standard cable	Sensor:	-50 – 80 °C (-58 – 176 °F)	
(option L):	Transmitter:	-40 – 60 °C (-40 – 140 °F)	
with fire retardant cable	Sensor:	-35 – 80 °C (-31 – 176 °F)	
(option Y):	Transmitter:	-35 – 60 °C (-31 – 140 °F)	

<sup>2)</sup> Lower temperature specification valid for fixed installation only

#### **Further ambient conditions**

Ranges and specifications	
Relative humidity	0 – 95 %
IP code	IP66/67 for transmitters and sensors when using the appropriate cable glands
Allowable pollution degree in surrounding area acc.: EN 61010-1	4 (in operation)
Resistance to vibration acc.: IEC 60068-2-6 (not with option $T_{}$ )	Transmitter: 10 – 500 Hz, 1g Sensor: 25 – 100 Hz, 4g
Electromagnetic compatibility (EMC)  IEC/EN 61326-1, Table 2  IEC/EN 61326-2-3  IEC/EN 61326-2-5  NAMUR NE 21 recommendation  DNV-CG-0339 Section 3, Chapter 14  This includes  Surge immunity acc.:  EN 61000-4-5 for lightning protection  Emission acc.:  IEC/EN 61000-3-2, Class A  IEC/EN 61000-3-3, Class A  NAMUR NE 21 recommendation  DNV-CG-0339 Section 3, Chapter 14	Immunity assessment criterion: The output signal fluctuation is within ±1 % of the output span.
Maximum altitude	2000 m (6600 ft) above mean sea level (MSL)
Overvoltage category according to IEC/EN 61010-1	П

#### 4.3.1 Allowed ambient temperature for sensor

The allowed ambient temperature of the sensor depends on the following product properties:

- Process fluid temperature, see Process fluid temperature range [ 9]
- Design type
  - Integral type
  - Remote type
- Connecting cable type (options L\_\_\_ and Y\_\_\_)



The allowed combinations of process fluid and ambient temperature for the sensor are illustrated as gray areas in the diagrams below.



Allowed process fluid and ambient temperature ranges in hazardous areas depend on classifications defined by applications, refer to *Temperature specification in hazardous areas* [> 31].



# Temperature range specification Standard, integral type




Fig. 12: Allowed process fluid and ambient temperatures, integral type

 $T_{amb}$  Ambient temperature  $T_{pro}$  Process fluid temperature

#### Temperature range specification Standard, remote type




Fig. 13: Allowed process fluid and ambient temperatures, remote type

- 1 Standard cable option L\_\_\_
- 2 Limitation for fire retardant cable option Y\_\_\_ for standard neck
- 3 Limitation for fire retardant cable option Y\_\_\_ for long neck

#### Temperature range specification Medium, remote type




Fig. 14: Allowed process fluid and ambient temperatures, remote type

- 1 Standard cable option L\_\_\_
- 2 Limitation for fire retardant cable option Y\_\_\_ without option T\_\_
- 3 Limitation for fire retardant cable option Y\_\_\_ with option T\_\_

#### Temperature range specification High, remote type




Fig. 15: Allowed process fluid and ambient temperatures, remote type

- 1 Standard cable option L\_\_\_
- 2 Limitation for fire retardant cable option Y\_\_\_

#### 4.3.2 Temperature specification in hazardous areas

Please select appropriate equipment in accordance with the laws and regulations of the relevant country/region, when it is used in a location where explosive atmospheres may be present.

The maximum ambient and process fluid temperatures of Integral type and Remote Sensor depending on explosion groups and temperature classes can be determined via the model code or via the model code together with the Ex code (see the corresponding Explosion Proof Type Manual).

#### Variant 1:

Model code:

Pos. 2: T

Pos. 3: 08, 10

Pos. 8: 0


Pos. 10: 0, 1, 2

Pos. 11:,

Ex code:

\_

The following figure shows the relevant positions of the model code:



Tab. 6: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)	Maximum process fluid temperature in °C (°F)
T6	42 (107)	75 (167)
T5	57 (134)	90 (194)
T4	60 (140)	125 (257)
Т3	60 (140)	150 (302)
T2	60 (140)	150 (302)
T1	60 (140)	150 (302)

#### Model code:


Pos. 2: T

Pos. 8: 0

Pos. 10: 0, 2

Pos. 11: \_F21, FF11

Ex code: 6.85.86.87.54.10



Tab. 7: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)	Maximum fluid temperature in °C (°F)
T6	43 (109)	66 (150)
T5	58 (136)	82 (179)
T4	60 (140)	118 (244)
T3	60 (140)	150 (302)
T2	60 (140)	150 (302)
T1	60 (140)	150 (302)

Pos. 2: T

Pos. 3: 08, 10


Pos. 8: 0

Pos. 10: A, C, E, J

Pos. 11:, Ex code:

\_

The following figure shows the relevant positions of the model code:



Tab. 8: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	43 (109)	43 (109)	75 (167)
T5	58 (136)	58 (136)	90 (194)
T4	80 (176)	74 (165)	125 (257)
T3	80 (176)	60 (140)	150 (302)
T2	80 (176)	60 (140)	150 (302)
T1	80 (176)	60 (140)	150 (302)

#### Variant 2:

Model code:

Pos. 2: T

Pos. 3: 08 Pos. 8: 0

Pos. 10: 0, 1, 2

Pos. 11: ,

Ex code:

\_



Tab. 9: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)	Maximum process fluid temperature in °C (°F)
T6	60 (140)	75 (167)
T5	60 (140)	90 (194)
T4	60 (140)	125 (257)
T3	60 (140)	150 (302)
T2	60 (140)	150 (302)
T1	60 (140)	150 (302)

Pos. 2: T

Pos. 3: 08


Pos. 8: 0

Pos. 10: A, C, E, J

Pos. 11: ,

Ex code:

The following figure shows the relevant positions of the model code:



Tab. 10: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	67 (152)	67 (152)	75 (167)
T5	80 (176)	77 (170)	90 (194)
T4	80 (176)	74 (165)	125 (257)
T3	80 (176)	60 (140)	150 (302)
T2	80 (176)	60 (140)	150 (302)
T1	80 (176)	60 (140)	150 (302)

#### Model code:

Pos. 2: T

Pos. 3: 10


Pos. 8: 0

Pos. 10: 0,1, 2

Pos. 11:,

Ex code:

\_



Tab. 11: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)	Maximum process fluid temperature in °C (°F)
T6	56 (133)	75 (167)
T5	60 (140)	90 (194)
T4	60 (140)	125 (257)
Т3	60 (140)	150 (302)
T2	60 (140)	150 (302)
T1	60 (140)	150 (302)

Pos. 2: T Pos. 3: 10


Pos. 8: 0

Pos. 10: A, C, E, J

Pos. 11:, Ex code:

\_

The following figure shows the relevant positions of the model code:



Tab. 12: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	58 (136)	58 (136)	75 (167)
T5	73 (163)	73 (163)	90 (194)
T4	80 (176)	74 (165)	125 (257)
T3	80 (176)	60 (140)	150 (302)
T2	80 (176)	60 (140)	150 (302)
T1	80 (176)	60 (140)	150 (302)

#### Model code:

Pos. 2: T Pos. 8: 0 Pos. 10: 0, 2

Pos. 11: \_F21, FF11 Ex code: 6.85.86.87.54.10



Tab. 13: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)	Maximum process fluid temperature in °C (°F)
T6	43 (109)	66 (150)
T5	58 (136)	82 (179)
T4	60 (140)	118 (244)
Т3	60 (140)	150 (302)
T2	60 (140)	150 (302)
T1	60 (140)	150 (302)

Pos. 2: T Pos. 8: 0 Pos. 10: 0, 2

Pos. 11: \_F22, FF12 Ex code: 2.78.79.81.54.10

The following figure shows the relevant positions of the model code:



Tab. 14: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)	Maximum process fluid temperature in °C (°F)
T6	59 (138)	59 (138)
T5	60 (140)	75 (167)
T4	60 (140)	112 (233)
T3	60 (140)	150 (302)
T2	60 (140)	150 (302)
T1	60 (140)	150 (302)


#### Model code:

Pos. 2: T

Pos. 8: 0

Pos. 10: 0, 1, 2

Pos. 11: JF54, JF53



Tab. 15: Temperature classification

Temperature class	Maximum ambient temperature in °C	Maximum process fluid temperature in °C
T4	60	118
T3	60	150

Pos. 2: T Pos. 8: 0

Pos. 10: A, E, J Pos. 11: \_F21, FF11

Ex code: 6.85.86.87.54.10

The following figure shows the relevant positions of the model code:



Tab. 16: Temperature classification


Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	41 (105)	41 (105)	66 (150)
T5	56 (132)	56 (132)	82 (179)
T4	80 (176)	62 (143)	118 (244)
T3	78 (172)	49 (120)	150 (302)
T2	78 (172)	49 (120)	150 (302)
T1	78 (172)	49 (120)	150 (302)

#### Model code:

Pos. 2: T Pos. 8: 0

Pos. 10: A, E, J Pos. 11: \_F22

Ex code: 2.78.79.81.54.10



Tab. 17: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	59 (138)	59 (138)	59 (138)
T5	75 (167)	75 (167)	75 (167)
T4	80 (176)	65 (149)	112 (233)
T3	78 (172)	49 (120)	150 (302)
T2	78 (172)	49 (120)	150 (302)
T1	78 (172)	49 (120)	150 (302)

Pos. 2: T

Pos. 8: 0

Pos. 10: A, E, J

Pos. 11: FF12

Ex code:

2.78.79.81.54.10

The following figure shows the relevant positions of the model code:



Tab. 18: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	59 (138)	59 (138)	59 (138)
T5	75 (167)	70 (158)	75 (167)
T4	80 (176)	65 (149)	112 (233)
T3	78 (172)	49 (120)	150 (302)
T2	78 (172)	49 (120)	150 (302)
T1	78 (172)	49 (120)	150 (302)

### Model code:


Pos. 2: T

Pos. 8: 0

Pos. 10: A, E

Pos. 11: JF54, JF53

Ex code:



Tab. 19: Temperature classification

Temperature class	Maximum ambient temperature in °C		Maximum fluid temperature in °C
	Option L	Option Y	
T4	80	_	118
T3	78	_	150

Pos. 2: T Pos. 8: 0

Pos. 10: B, F, K Pos. 11: \_F21

Ex code: 6.85.86.87.54.10

The following figure shows the relevant positions of the model code:



Tab. 20: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	47 (116)	47 (116)	66 (150)
T5	62 (143)	62 (143)	82 (179)
T4	80 (176)	74 (165)	118 (244)
T3	80 (176)	70 (158)	150 (302)
T2	80 (176)	70 (158)	150 (302)
T1	80 (176)	70 (158)	150 (302)

### Model code:


Pos. 2: T Pos. 8: 0

Pos. 10: B, F, K

Pos. 11: FF11

Ex code:

6.85.86.87.54.10



Tab. 21: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	47 (116)	47 (116)	66 (150)
T5	62 (143)	62 (143)	82 (179)
T4	80 (176)	70 (158)	118 (244)
T3	80 (176)	70 (158)	150 (302)
T2	80 (176)	70 (158)	150 (302)
T1	80 (176)	70 (158)	150 (302)

Pos. 2: T


Pos. 8: 0

Pos. 10: B, F, K

Pos. 11: \_F22

Ex code: 2.78.79.81.54.10

The following figure shows the relevant positions of the model code:



Tab. 22: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	59 (138)	59 (138)	59 (138)
T5	75 (167)	75 (167)	75 (167)
T4	80 (176)	74 (165)	112 (233)
T3	80 (176)	70 (158)	150 (302)
T2	80 (176)	70 (158)	150 (302)
T1	80 (176)	70 (158)	150 (302)

### Model code:


Pos. 2: T

Pos. 8: 0

Pos. 10: B, F, K Pos. 11: FF12

Ex code:

2.78.79.81.54.10




Tab. 23: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	59 (138)	59 (138)	59 (138)
T5	75 (167)	70 (158)	75 (167)
T4	80 (176)	70 (158)	112 (233)
Т3	80 (176)	70 (158)	150 (302)
T2	80 (176)	70 (158)	150 (302)
T1	80 (176)	70 (158)	150 (302)

Pos. 2: T Pos. 8: 0 Pos. 10: B, F

Pos. 11: JF54, JF53

The following figure shows the relevant positions of the model code:



Tab. 24: Temperature classification


Temperature class	Maximum ambient temperature in °C		Maximum fluid temperature in °C
	Option L	Option Y	
T4	80	_	118
Т3	78	_	150

### Model code:

Pos. 2: T Pos. 8: 2

Pos. 10: B, F, K Pos. 11: \_F21

Ex code: 6.85.86.87.89.80



Tab. 25: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	47 (116)	47 (116)	66 (150)
T5	62 (143)	62 (143)	82 (179)
T4	80 (176)	70 (158)	118 (244)
T3	80 (176)	64 (147)	185 (365)
T2	80 (176)	59 (138)	220 (428)
T1	80 (176)	59 (138)	220 (428)

Pos. 2: T

Pos. 8: 2


Pos. 10: B, F, K

Pos. 11: FF11

Ex code:

6.85.86.87.89.80

The following figure shows the relevant positions of the model code:



Tab. 26: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	47 (116)	47 (116)	66 (150)
T5	62 (143)	62 (143)	82 (179)
T4	80 (176)	70 (158)	118 (244)
T3	80 (176)	64 (147)	185 (365)
T2	80 (176)	59 (138)	220 (428)
T1	80 (176)	59 (138)	220 (428)


### Model code:

Pos. 2: T

Pos. 8: 2

Pos. 10: B, F, K Pos. 11: \_F22

Ex code: 2.78.79.81.85.80



Tab. 27: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	59 (138)	59 (138)	59 (138)
T5	75 (167)	75 (167)	75 (167)
T4	80 (176)	74 (165)	112 (233)
T3	80 (176)	64 (147)	181 (357)
T2	80 (176)	59 (138)	220 (428)
T1	80 (176)	59 (138)	220 (428)

Pos. 2: T

Pos. 8: 2


Pos. 10: B, F, K

Pos. 11: FF12

Ex code:

2.78.79.81.85.80

The following figure shows the relevant positions of the model code:



Tab. 28: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	59 (138)	59 (138)	59 (138)
T5	75 (167)	70 (158)	75 (167)
T4	80 (176)	70 (158)	112 (233)
Т3	80 (176)	64 (147)	181 (357)
T2	80 (176)	59 (138)	220 (428)
T1	80 (176)	59 (138)	220 (428)


### Model code:

Pos. 2: T

Pos. 8: 2

Pos. 10: B, F

Pos. 11: JF52



Tab. 29: Temperature classification

Temperature class	Maximum ambient temperature in °C		Maximum fluid temperature in °C
	Option L	Option Y	
T2	80	_	220

Pos. 2: T

Pos. 8: 3

Pos. 10: B, F, K Pos. 11: \_F21, \_F22

Ex code: -

The following figure shows the relevant positions of the model code:



Tab. 30: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	62 (143)	62 (143)	65 (149)
T5	77 (170)	77 (170)	80 (176)
T4	80 (176)	74 (165)	115 (239)
T3	80 (176)	65 (149)	180 (356)
T2	73 (163)	50 (122)	275 (527)
T1	60 (140)	40 (104)	350 (662)

### Model code:

Pos. 2: T


Pos. 8: 3

Pos. 10: B, F, K

Pos. 11: FF11, FF12

Ex code:

\_



Tab. 31: Temperature classification


Temperature class	Maximum ambient temperature in °C (°F)		Maximum process fluid temperature in °C (°F)
	Option L	Option Y	
T6	62 (143)	62 (143)	65 (149)
T5	77 (170)	70 (158)	80 (176)
T4	80 (176)	70 (158)	115 (239)
T3	80 (176)	65 (149)	180 (356)
T2	73 (163)	50 (122)	275 (527)
T1	60 (140)	40 (104)	350 (662)

Pos. 2:T

Pos. 8: 3

Pos. 10: B, F

Pos. 11: JF51



Tab. 32: Temperature classification

Temperature class	Maximum ambient temperature in °C	Maximum process fluid temperature in °C
T1	60	350

# 5 Mechanical specification

# 5.1 Design

The Rotamass Intense flow meter is available with two design types:

- Integral type, sensor and transmitter are firmly connected
- Remote type
  - Standard neck
  - Long neck




Fig. 16: Remote type sensor with standard neck for meter size 08 and 10





Fig. 17: Remote type sensor with standard and long neck for meter size 34, 36 and 38



Design type	Design version	Process fluid temperature range	Model code position 10
Integral type	Direct connection		0, 2
Domoto tuno	Standard neck	Standard	A, E, J
Remote type	Long neck		B, F, K


The design influences the temperature specification for Ex-approved Rotamass, see Explosion Proof Type Manual (IM 01U10X\_\_-00\_\_-R).

# 5.2 Material

#### 5.2.1 Sensor

# **Material wetted parts**

Sensor parts which are wetted by process fluid are available with the following materials:




Material	Model code position 4
Measuring tubes made of nickel alloy C-22/2.4602, process connections of stainless steel alloy 1.4404/316L	К
Stainless steel 1.4404/316L	S
Nickel alloy C-22/2.4602	Н

The customer is responsible to ensure chemical compatibility of the material of the wetted parts with the measured process fluid.

For corrosive fluids, use of a corrosion-resistant nickel alloy (nickel alloy C-22/2.4602) is recommended for wetted parts. It is not recommended for gaseous hydrogen applications according to ASME B31.12.

### Sensor housing material

Sensor housing is available in the following materials:



Housing part	Material	Model code position 7
Junction box	Stainless steel 1.4404/316L	0, 1
Neck	Stainless steel 1.4409 (CF3M) <sup>1)</sup>	1
Neck	Stainless steel 1.4404/316L <sup>2)</sup>	0, 1
Pody	Stainless steel 1.4301/304	0
Body	Stainless steel 1.4404/316L	1


<sup>1)</sup> for meter sizes 08 and 10

<sup>2)</sup> for meter sizes 34, 36 and 38

### 5.2.2 Transmitter

# **Transmitter housing**

The transmitter housing is available with different materials and coatings:




Housing material	Coating	Design type	Model code position 10
	Standard coating	Integral type	0
Aluminum		Remote type	A, B
Al-Si10Mg(Fe)	Corrosion protection coating	Integral type	2
		Remote type	E, F
Stainless steel CF8M	_	Remote type	J, K

- Standard coating: Urethane-cured polyester powder coating
- Corrosion protection coating: Three-layer coating with high chemical resistance (polyurethane coating on two layers of epoxy coating)
- Color Mint green (Munsell 5.6BG3.3/2.9)

# **Display window**

This is relevant for all transmitters having a display:



p ,	Model code position 14
Glass	1

#### **Bracket material**

The bracket is available for remote type devices only:

Bracket material	3 7	Model code position 10
Stainless steel 1.4404/316L	Remote type	A, B, E, F, J, K

# 5.2.3 Nameplates

# Sensor


Sensor housing material	Process fluid temperature range	Sensor nameplate material
1.4301/304	Standard	Polyester film
1.4301/304	Medium, High	1.4404/316L
1.4404/316L	all	1.4404/316L

### **Transmitter**

Transmitter housing material	Transmitter nameplate material
Aluminum AL-Si10MG(Fe)	Foil
Stainless steel CF8M	1.4404/316L

# 5.2.4 Heat tracing

These device options are available only for remote type with long neck.




### **Material of components**

Component	Material
Insulation housing	Stainless steel 1.4301/304
Insulation material	Mineral wool, RAL-quality label, approved acc. EU directive 97/69 note Q, European class A1 non-combustible (EN 13 501), termal conductivity 0,031 W/(m*K) at 0 °C (acc. P-MPA-E-99-521)
Heat tracing and purging lines	Stainless steel 1.4571/316Ti and 1.4404/316L
Heat tracing and purging connections	Stainless steel 1.4404/316L; flanges acc. ASME or EN

For dimensions of insulation and heat tracing components see *Process connections, dimensions and weights of sensor* [> 49].

# 5.3 Process connections, dimensions and weights of sensor



\*with process connection adapter 16TA9

\*\*with process connection 20TA9

Fig. 18: Dimensions for Intense 08 and 10 in mm




Fig. 19: Dimensions in mm




Fig. 20: Dimensions in mm: version with insulation housing for meter sizes Intense 34, 36 and 38 only

Tab. 33: Dimensions without length L1

Meter size	L2	L3	L4	L5	W1	W2	W3	D1	D2
		in mm (inch)							
Intense 08	240 (9.5)	195 (7.7)	-	-	50 (2.0)	-	-	-	-
Intense 10	240 (9.5)	195 (7.7)	-	-	50 (2.0)	-	-	-	-
Intense 34	272 (10.7)	212 (8.3)	420 (16.5)	310 (12.2)	60 (2.4)	80 (3.1)	240 (9.4)	200 (7.9)	330 (13)
Intense 36	400 (15.7)	266 (10.5)	540 (21.3)	439 (17.3)	76 (3)	90 (3.5)	260 (10.2)	250 (9.8)	380 (15)
Intense 38	490 (19.3)	267 (10.5)	640 (25.2)	530 (20.9)	89 (3.5)	110 (4.3)	260 (10.2)	250 (9.8)	430 (16.9)

Tab. 34: Dimensions without length L1

Meter size	H1	НЗ	H4	H5	H6	H7	H8	H9
				in mm	(inch)			
Intense 08	138 (5.4)	-	59 (2.3)	140 (5.5)	-	-	-	-
Intense 10	138 (5.4)	-	59 (2.3)	140 (5.5)	-	-	-	-
Intense 34	177 (7)	267 (10.5)	80 (3.1)	138 (5.4)	218 (8.6)	411 (16.2)	273 (10.7)	138 (5.4)
Intense 36	230 (9.1)	267 (10.5)	80 (3.1)	138 (5.4)	218 (8.6)	464 (18.3)	326 (12.8)	138 (5.4)
Intense 38	268 (10.6)	277 (10.9)	100 (3.9)	148 (5.8)	228 (9)	524 (20.6)	376 (14.8)	148 (5.8)

# Overall length L1 and weight

The overall length of the sensor depends on the selected process connection (type and size of flange). The following tables list the overall length and weight as functions of the individual process connection.

The weights in the tables are for the remote type with standard neck. Additional weight for the remote type with long neck: 1 kg (2.2 lb). Additional weight for the integral type: up to 3.2 kg (7.1 lb).

# Process connections medium pressure autoclave compatible



*Tab. 35:* Overall length L1 and weight of sensor (process connections: medium pressure autoclave, wetted parts: stainless steel 1.4404/316L and Ni alloy C-22/2.4602) and for  $^9$ /<sub>16</sub> Autoclave adapter

Process connections	Model code position		Inten	se 08	Intense 10		
	5	6	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)	
Autoclave <sup>9</sup> / <sub>16</sub> " adapter	16	TAO	275 (10.8)	7 (15.4)	275 (10.8)	7 (15.4)	
Autoclave ¾"	20	TA9	240 (9.5)	7 (15.4)	240 (9.5)	7 (15.4)	

### Process connections compatible to ASME B16.5 (AISI 316/ AISI 316L dual certified)



Tab. 36: Overall length L1 and weight of sensor (process connections: ASME, wetted parts: stainless steel)

Process connections	Model cod	Model code position		ise 34	Inten	se 36	Inten	se 38
	5	6	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)
ASME ½" class 900, raised face (RF)		BA5	400 (15.7)	12.6 (28)	_	_	_	_
ASME ½" class 900, ring joint (RJ)		CA5	400 (15.7)	13 (29)	<u>-</u>	<del>_</del>	<u>-</u>	_
ASME ½" class 1500, raised face (RF)	15	BA6	400 (15.7)	12.6 (28)	_	_	_	_
ASME ½" class 1500, ring joint (RJ)		CA6	400 (15.7)	13 (29)	_	_	_	_
ASME 1" class 900, raised face (RF)		BA5	450 (17.7)	16.4 (36)	540 (21.3)	20.6 (45)	_	_
ASME 1" class 900, ring joint (RJ)	25	CA5	450 (17.7)	16.6 (37)	540 (21.3)	20.4 (45)	_	_
ASME 1" class 1500, raised face (RF)	25	BA6	450 (17.7)	16.4 (36)	<del>_</del>	<del>_</del>	_	_
ASME 1" class 1500, ring joint (RJ)		CA6	450 (17.7)	16.6 (37)	_	_	_	_
ASME 2" class 900, raised face (RF)	50	BA5	_	_	660 (26)	35.2 (78)	720 (28.3)	43 (95)
ASME 2" class 900, ring joint (RJ)	50	CA5	_	_	660 (26)	35.6 (78)	720 (28.3)	43.4 (96)

Meaning of "-": not available




Tab. 37: Overall length L1 and weight of sensor (process connections: ASME, wetted parts: Ni alloy C-22/2.4602)

Process connections	Model cod	le position	Inten	se 34	Inten	se 36	Inten	se 38
	5	6	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)
ASME 1" class 900, raised face (RF)		BA5	400 (15.7)	16.4 (36)	_	_	_	_
ASME 1" class 900,ring joint (RG)	25	CA5	_	_	580 (23)	21 (46)	_	_
ASME 1" class 1500, raised face (RF)	25	BA6	400 (15.7)	16.4 (36)	_	_	_	_
ASME 1" class 1500,ring joint (RG)		CA6	_	_	580 (23)	21 (46)	_	_
ASME 2" class 900,raised face (RF)		BA5	<del>_</del>	_	580 (23)	34 (75)	710 (28)	44 (97)
ASME 2" class 900,ring joint (RG)	50	CA5	_	_	580 (23)	36 (80)	710 (28)	44 (97)
ASME 2" class 1500,ring joint (RG)		CA6	_	_	580 (23)	36 (80)	710 (28)	44 (97)
ASME 3" class 900,raised face (RF)	80	BA5	_	_	_	_	710 (28)	50 (110)
ASME 3" class 900,ring joint (RG)	OU	CA5	_	_	_	_	710 (28)	52( 115)

Meaning of "-": not available

### Process connections with internal thread G




Tab. 38: Overall length L1 and weight of sensor (process connections: G thread, wetted parts: stainless steel)

Process connections	Model cod	Model code position		Intense 34		Intense 36		se 38
	5	6	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)
G 3/8"	80		390 (15.4)	9.4 (21)	_	_	_	_
G ½"	15	TG9	390 (15.4)	9.4 (21)	<u>-</u>	_	<u>-</u>	_
G ¾"	20		390 (15.4)	9.4 (21)	_	_	_	_

Meaning of "-": not available

### **Process connections with internal thread NPT**



Tab. 39: Overall length L1 and weight of sensor (process connections: NPT thread, wetted parts: stainless steel)

Process connections	Model cod	Model code position		nse 34 Inte		se 36	Intense 38	
	5	6	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)
NPT %"	80		390 (15.4)	9.4 (21)	_	_	_	_
NPT ½"	15	TT9	390 (15.4)	9.4 (21)	_	_	_	_
NPT 3/4"	20		390 (15.4)	9.4 (21)	_	_	_	_

Meaning of "-": not available

# Typical dimensions of measuring tubes

Tab. 40: Typical dimensions of measuring tubes

Meter size	Material of wetted parts	Model code pos. 4	Internal diameter in mm (inch)	Wall thickness in mm (inch)
Intense 08	Measuring tubes made of nickel alloy C-22/2.4602,	K	1.2 (0.05)	0.35 (0.022)
Intense 10	process connections of stain- less steel alloy 1.4404/316L	K	2.1 (0.08)	0.55 (0.022)
	Stainless steel 1.4404/316L	S	7.75 (0.305)	0.89 (0.035)
Intense 34	Nickel alloy C-22/2.4602	Н	7.70 (0.303)	0.91 (0.036)
	Stainless steel 1.4404/316L	S	13.40 (0.528)	1.24 (0.049)
Intense 36	Nickel alloy C-22/2.4602	Н	13.4 (0.528)	1.24 (0.049)
	Stainless steel 1.4404/316L	S	22.10 (0.870)	1.65 (0.065)
Intense 38	Nickel alloy C-22/2.4602	Н	22.1 (0.870)	1.65 (0.065)

# 5.4 Transmitter dimensions and weights

### **Transmitter dimensions**




Fig. 21: Dimensions of transmitter in mm (left: transmitter with display, right: transmitter without display)

Tab. 41: Overall length L1 - L4 and height H1 - H4 of transmitter (material: stainless steel, aluminum)

Material	L1	L2	L3	L4	H1	H2	H3	H4
	in mm	in mm	in mm	in mm	in mm	in mm	in mm	in mm
	(inch)	(inch)	(inch)	(inch)	(inch)	(inch)	(inch)	(inch)
Stainless	255.5	110.5	69	235	201	184	24	150.5
steel	(10.06)	(4.35)	(2.72)	(9.25)	(7.91)	(7.24)	(0.94)	(5.93)
Aluminum	241.5	96.5	70	221	192	175	23	140
	(9.51)	(3.8)	(2.76)	(8.7)	(7.56)	(6.89)	(0.91)	(5.51)





Fig. 22: Dimensions of transmitter in mm, attached to mounting bracket.

# **Transmitter weights**



Model code (pos. 10)	Design type	Housing material of transmitter	Weight in kg (lb)	
A, B, E, F	Remote	Aluminum	max. 4.4 (9.7)	
J, K	Remote	Stainless steel	12.5 (27.6)	

# 6 Electrical specification

# 6.1 Power supply

#### **Power supply**

Alternating-current voltage (rms):

- $\bullet$  Power supply  $^{1)}$ : 24  $V_{AC}$  +20 % -15 % or 100 240  $V_{AC}$  +10 % -20 %
- Power frequency: 47 63 Hz

Direct-current voltage:

• Power supply<sup>1)</sup>: 24  $V_{DC}$  +20 % -15 % or 100 - 120  $V_{DC}$  +8.3 % -10 %

 $^{1)}$  for option MC\_ (DNV approval) supply voltage is limited to 24 V; in addition NE21 testing indicates a tolerable area of 24 V<sub>DC</sub> ±20 % under NE21 test conditions.

#### **Power consumption**

P ≤ 10 W (including sensor)

#### Power supply failure


In the event of a power failure, the flow meter data are backed up on a non-volatile internal memory. In case of devices with display, the characteristic sensor values, such as nominal diameter, serial number, calibration constants, zero point, etc. and the error history are also stored on a microSD card.


### **Galvanic** isolation

All circuits for inputs, outputs and power supply are galvanically isolated from each other.

#### 6.2 Electrical interfaces

Depending on the selected interface protocol up to 4 in and/or outputs (I/O) are available, partially configurable.





Model code position 13	Interface proto- col	IO1 +/-	IO2 +/-	IO3 +/-	104 +/-	
J_	HART	Active or Pas- sive Analog Output + HART	Passive Pulse or Status Out-	Configurable Configurable		
M_	Modbus	Configurable put		Modbus		
G_ <sup>1)</sup>	PROFIBUS PA	PROFIBUS PA	Passive Pulse	_	_	
F_1)	FOUNDATION Fieldbus	FOUNDATION Fieldbus	Output	_	_	

<sup>1)</sup>Only with Ultimate Transmitter

Details about in and outputs and communication interfaces are specified in the following chapters.

# Spare Sensor I/O

Model code position 13	Specification
NN	Spare sensor without transmitter, all communication types and I/Os apply

# 6.2.1 Analog inputs and outputs

# 6.2.1.1 Analog outputs

### Active current output lout

One or two current outputs are available depending on model code position 13.

Depending on the measured value, the active current output delivers 4 - 20 mA.

It may be used for output of the following measured values:

- Flow rate (mass, volume, net partial component flow of a mixture)
- Density
- Temperature
- Pressure
- Concentration

For HART communication devices, it is supplied on the current output *lout1*. The current output may be operated in compliance with the NAMUR NE43 standard.

	Value
Nominal output current range	4 – 20 mA
Maximum output current range	2.4 – 21.6 mA
Load resistance	≤ 750 Ω
Load resistance for secure HART communication	230 – 600 Ω




Fig. 23: Active current output connection lout HART

① Receiver

### Passive current output lout

	Value
Nominal output current range	4 – 20 mA
Maximum output current range	2.4 – 21.6 mA
External power supply	$10.5 - 32  V_{DC}$
Load resistance for secure HART communication	230 – 600 Ω
Load resistance at current output	≤ 911 Ω




Fig. 24: Maximum load resistance as a function of an external power supply voltage

R Load resistance

U External power supply voltage

The diagram shows the maximum load resistance R as a function of voltage U of the connected voltage source. Higher load resistances are allowed with higher power supply values. The usable zone for passive power output operation is indicated by the hatched area.




Fig. 25: Passive current output connection lout

# 6.2.1.2 Analog inputs

### Active current input lin

An individual analog power input is available for external analog devices.

The active current input *lin* is provided for connecting a two-wire transmitter with an output signal of 4 - 20 mA.

	Value
Nominal input current range	4 – 20 mA
Maximum input current range	2.4 – 21.6 mA
Internal power supply	24 V <sub>DC</sub> ±20 %
Internal load resistance Rotamass	≤ 160 Ω




Fig. 26: Connection of external device with passive current output

① External passive current output device

### Passive current input lin

The passive current input *lin* is provided for connecting a four-wire transmitter with an output signal of 4-20 mA.

	Value
Nominal input current range	4 – 20 mA
Maximum input current range	2.4 – 21.6 mA
Internal load resistance Rotamass	≤ 160 Ω




Fig. 27: Connection of external device with active current output

① External active current output device

# 6.2.2 Digital inputs and outputs

### 6.2.2.1 Digital outputs

### Active pulse output P/Sout

Connection of an electronic counter

Maximum voltage and correct polarity must be observed for wiring.

Terms	Value
Load resistance	> 1 kΩ
Internal power supply	24 V <sub>DC</sub> ±20 %
Maximum pulse rate	10000 pulses/s
Frequency range	0 – 12.5 kHz




Fig. 28: Active pulse output connection P/Sout

- ① Load resistance
- ② Electronic counter

#### Connection of an electromechanical counter

Terms	Value
Maximum current	150 mA
Average current	≤ 30 mA
Internal power supply	24 V <sub>DC</sub> ±20 %
Maximum pulse rate	2 pulses/s
Pulse width	20, 33, 50, 100 ms




Fig. 29: Active pulse output P/Sout connection with electromechanical counter

- ① Protective diode
- ② Electromechanical counter

# Active pulse output P/Sout with internal pull-up resistor

	Value
Internal power supply	24 V <sub>DC</sub> ±20 %
Internal pull-up resistor	2.2 kΩ
Maximum pulse rate	10000 pulses/s
Frequency range	0 – 12.5 kHz




Fig. 30: Active pulse output P/Sout with internal pull-up resistor

# Electronic counter

# Passive pulse output P/Sout

Maximum voltage and correct polarity must be observed for wiring.

	Value
Maximum load current	≤ 200 mA
Power supply	≤ 30 V <sub>DC</sub>
Maximum pulse rate	10000 pulses/s
Frequency range	0 – 12.5 kHz




Fig. 31: Passive pulse output connection P/Sout with electronic counter

- Passive pulse or status output
- 2 Load resistance
- 3 Electronic counter




Fig. 32: Passive pulse output P/Sout connection with electromechanical counter

- Passive pulse or status output
- 2 Protective diode
- ③ Electromechanical counter

### Active status output P/Sout

Since this is a transistor contact, maximum allowed current as well as polarity and level of output voltage must be observed during wiring.

	Value
Load resistance	> 1 kΩ
Internal power supply	24 V <sub>DC</sub> ±20 %




Fig. 33: Active status output connection P/Sout

### ① External device with load resistance

#### Active status output P/Sout with internal pull-up resistor

	Value
Internal pull-up resistor	2.2 kΩ
Internal power supply	24 V <sub>DC</sub> ±20 %




Fig. 34: Active status output P/Sout with internal pull-up resistor

# ① External device

# Passive status output P/Sout or Sout

	Value
Output current	≤ 200 mA
Power supply	≤ 30 V <sub>DC</sub>




Fig. 35: Passive status output connection P/Sout or Sout

### External device




Fig. 36: Passive status output connection P/Sout or Sout for solenoid valve circuit

- ① Relay
- ② Solenoid valve
- 3 Magnetic valve power supply
- 4 Protective diode

A relay must be connected in series to switch alternating voltage.

### Passive pulse or status output P/Sout (NAMUR)

Output signals according to EN 60947-5-6 (previously NAMUR, worksheet NA001):




Fig. 37: Passive pulse or status output with switching amplifier connected in series

- Passive pulse or status output
- ② Switching amplifier

### 6.2.2.2 Digital inputs

### Status input Sin



Do not connect a signal source with electric voltage.

The status input is provided for use of voltage-free contacts with the following specification:

Switching status	Resistance
Closed	< 200 Ω
Open	> 100 kΩ




Fig. 38: Status input connection

# 6.2.3 HART

For HART communication devices, it is supplied on the current output lout1. The current output may be operated in compliance with the NAMUR NE43 standard. HART is available with non-intrinsically and intrinsically safety outputs.

# HART I/O

Model code	Connection to	Connection terminal assignment					
position 13	I/O1 +/-	I/O2 +/-	I/O3 +/-	I/O4 +/-	WP		
JA	lout1	P/Sout1			Write-protect		
JA	Active	Passive	_	_	vvrite-protect		
JB	lout1	P/Sout1	P/Sout2	lout2	Write protect		
JD	Active	Passive	Passive	Active	Write-protect		
JC	lout1	P/Sout1	Sin	lout2	Mrita protect		
JC	Active	Passive	SIII	Active	Write-protect		
JD	lout1	P/Sout1	Sout	P/Sout2	Mrita protect		
שנ	Active	Passive	Passive	Passive	Write-protect		
JE	lout1	P/Sout1	Sin	P/Sout2	Write protect		
JE	Active	Passive	SIII	Passive	Write-protect		
				P/Sout2			
JF	lout1	P/Sout1	Sin	Active	Write-protect		
	Active	Passive	Ciri	Internal pull-up resistor	vviite-protect		
JG	lout1	P/Sout1	Sin	P/Sout2	Write-protect		
JG	Active	Passive	SIII	Active	vvrite-protect		
JH	lout1	P/Sout1	lout2	lin	Write-protect		
311	Active	Passive	Passive	Active	vviile-protect		
JJ	lout1	P/Sout1	P/Sout2	lin	Write-protect		
33	Active	Passive	Passive	Active	vviile-protect		
JK	lout1	P/Sout1	Sin	lin	Write-protect		
JK	Active	Passive	SIII	Active	vvrite-protect		
JL	lout1	P/Sout1	lout2	lin	Write-protect		
JL	Active	Passive	Passive	Passive	vville-protect		
JM	lout1	P/Sout1	P/Sout2	lin	Write-protect		
JIVI	Active	Passive	Passive	Passive	vviile-protect		
JN	lout1	P/Sout1	Sin	lin	Write-protect		
JIN	Active	Passive	SIII	Passive	vville-protect		

lout1 Analog current output with HART communication

Iout2Analog current outputIinAnalog current inputP/Sout1Pulse or status outputP/Sout2Pulse or status output

Sin Status input
Sout Status output

# **HART I/O intrinsically safe**

Model code	Connection termin	minal assignment				
position 13	I/O1 +/-	I/O2 +/-	I/O3 +/-	I/O4 +/-	WP	
JP	lout1	P/Sout1	lout2		Write-protect	
JF	Passive	Passive	Passive	_	write-protect	
10	lout1	P/Sout1	lout2	P/Sout2	Write protect	
JQ	Passive	Passive	Passive	Passive	Write-protect	
	lout1	P/Sout1	lout2			
JR	Passive	Passive	Passive	_	Write-protect	
	rassive	NAMUR	rassive			
	lout1	P/Sout1	lout2	P/Sout2		
JS		Passive		Passive	Write-protect	
	Passive	NAMUR	Passive	NAMUR		

lout1 Analog current output with HART communication

Iout2 Analog current output
P/Sout1 Pulse or status output
P/Sout2 Pulse or status output

Intrinsically safe outputs are only available in combination with selecting Ex approval of the device, see model code position 11 in the table of chapter *Model code description* [> 82].

# 6.2.4 Modbus

Modbus interface is available with configurable I/O option.

Tab. 42: Connection terminal assignment for Modbus


Model code		Connection terminal assignment					
position 13	I/O1 +/-	I/O2 +/-	I/O3 +	I/O3 -	I/O4 +	I/O4 -	WP
MO	_	P/Sout1	_	Modbus C	Modbus B	Modbus A	Write-
		Passive					protect
M2	lin	P/Sout1	_	Modbus C	Modbus B	Modbus A	Write-
IVIZ	Active	Passive		Wodbus O	Wodbus B	Wodbus A	protect
M3	P/Sout2	P/Sout1	_	Modbus C	Modbus B	Modbus A	Write-
IVIO	Passive	Passive		Wodbas C	Wodbas B	Wodbas 71	protect
M4	P/Sout2	P/Sout1	_	Modbus C	Modbus B	Modbus A	Write-
IVIT	Active	Passive		Wodbus C		Wodbus A	protect
	P/Sout2						
M5	Active	P/Sout1	_	Modbus C	Modbus B	Modbus A	Write-
IVIO	Internal pull- up resistor	Passive		Wodbus C	IVIOUDUS D	NIOUDUS A	protect
M6	lout1	P/Sout1	_	Modbus C	Modbus B	Modbus A	Write-
IVIO	Active	Passive	_	WIOGDUS C	IVIOGDUS D	IVIOGDUS A	protect
M7	lin	P/Sout1	_	Modbus C	Modbus B	Modbus A	Write-
1717	Passive	Passive	_	IVIOGDUS C	IVIOGDUS D	IVIOGDUS A	protect

Iout Analog current output, no HART

linAnalog current inputP/Sout1Pulse or status outputP/Sout2Pulse or status output

# **Output Signal**

Digital communication signal according to EIA485 standard (RS485).



### 6.2.5 PROFIBUS PA

PROFIBUS PA interface is available with and without intrinsically safety.

Model code	Connection termin	Connection terminal assignment				
position 13	I/O1 +/-	I/O2 +/-	I/O3 +/-	I/O4 +/-	WP	
G0	PROFIBUS PA	Pulse Passive	_	_	Write-protect	
G1	PROFIBUS PA (IS)	Pulse Passive (IS)	_	_	Write-protect	

PROFIBUS PA PA communication

Pulse Passive Pulse / Frequency output

Intrinsically safe (IS) outputs are only available in combination with selecting Ex approval of the device, see model code position 11 of the table in chapter *Model code description* [> 82].

### **Output Signal**

Digital communication signal according to IEC 61158/61784.

Maximum voltage and correct polarity must be observed for wiring.

	Value
Power supply	$9-32 V_{DC}$
Current draw	15 mA (maximum)




Fig. 39: PROFIBUS PA connection

- ① PROFIBUS PA
- ② Termination
- ③ DP/PA-Coupler
- PROFIBUS DP
- ⑤ HOST

# **Supported Functions**

Profile PA Rev. 3.02 compliant, supporting:

- Condensed Status (NE107)
- Device identification number (IDENT\_NUMBER) adaption

Function Blocks	Description			
	FTB	Flow		
	СТВ	Concentration		
Transducer	LTB	LCD Indicator		
	MTB	Maintenance		
	ADTB	Advanced Diagnostics		

Function Blocks	Description	
	Al1	Mass flow
	Al2	Density
Analog Input1)	Al3	Temperature
Analog Input <sup>1)</sup>	Al4	Volume flow
	AI5	Reference density
	Al6	Corrected volume flow
	TOT1	Mass
Totalizer <sup>1)</sup>	TOT2	Volume
	TOT3	Corrected volume
Analog Output1)	AO	Pressure

<sup>&</sup>lt;sup>1)</sup>Factory default setting. Assignment can be changed by parameter "channel".

ID	Description	Device descrip-			Applicat	ole funct	ion bloc	ks	
		tion file (GSD)	AI1	Al2	AI3	AI4-6	TOT1	TOT2-3	AO
0x45A0	Manufacturer specific	YEC45A0.gsd	•	•	•	•	•	•	•
0x9740		pa139740.gsd	•				•		
0x9741	Profile specific	pa139741.gsd	•	•			•		
0x9742		pa139742.gsd	•	•	•		•		

meaning of "●": available

# 6.2.6 FOUNDATION Fieldbus

FOUNDATION Fieldbus interface is available with and without intrinsically safety.

### **Functions overview**

Model code	Connection termination	Connection terminal assignment					
position 13	I/O1 +/-	I/O2 +/-	I/O3 +/-	I/O4 +/-	WP		
F0	FOUNDATION Fieldbus	Pulse Passive	_	_	Write-protect		
F1	FOUNDATION Fieldbus (IS)	Pulse Passive (IS)	_	_	Write-protect		

Intrinsically safe (IS) outputs are only available in combination with selecting Ex approval of the device, see model code position 11 in the table of chapter *Model code description* [> 82].

# **Output Signal**

Digital communication signal according to IEC 61158/61784.

Maximum voltage and correct polarity must be observed for wiring.

	Value
Power supply	$9-32 V_{DC}$
Current draw	15 mA (maximum)




Fig. 40: FOUNDATION Fieldbus connection

- Fieldbus power supply and condition
- 2 Termination
- 3 HOST

### **Supported Functions**

Compliance to ITK6.3:

Function Blocks	Description	
	FCB	Flow
	СТВ	Concentration
Transducer	LTB	LCD Indicator
	MTB	Maintenance
	ADTB	Advanced Diagnostics
	AI1	Mass flow
	Al2	Density
Analog Input	Al3	Temperature
Arialog iriput	Al4	Volume flow
	AI5	Reference density
	Al6	Corrected volume flow

Function Blocks	Description	
Integrator	IT	Depends on FOUNDATION Fieldbus configuration (up to 3)
Multi Analog Output	MAO	Depends on FOUNDATION Fieldbus configuration

ID	Description
594543	Manufacturer
0013	Device Type

## 6.3 Display and microSD card

Display attributes	Specifications	Model code position 14
Туре	4-line dot-matrix display	
Resolution	128(W) x 64 (H) dots	1
Size	64.6 mm x 31.2 mm	<b> </b>
Control	via IR switches	

All of the functions described here are also available via digital communication. Numerical values that are entered via the display are limited to 6 digits for process variables and 8 digits for totalizer.




Fig. 41: Display layout

1	Measured quantities and units	4	IR switches
2	Status icon and time	5	Alarm symbol
3	Measured quantity abbreviation		

The controls on the display are IR switches. They respond as soon as an object, such as a finger, is in close proximity. It is not necessary to apply pressure to the display surface.

# i Display unit

The display unit includes a slot for the microSD card.

SD card attributes	Specifications
Туре	Industrial Grade microSD card
SD specification	Compliant with SD Specification version 2.0
Physical dimension	15 mm x 11 mm x 1.0 mm (+/-0.1 mm)
Capacity	1 GB
Seq. Read (MB/s)	24.01
Seq. Write (MB/s)	17.96

It is recommended to use the microSD card included with the Rotamass Total Insight. Functionality of the device cannot be guaranteed if other cards are used.

For status icon placement on the display see figure at *Display* [> 73], No. 1, 2 or 5.

## 6.4 Cable specifications

For remote type devices, a connecting cable has to be used to connect the sensor to the transmitter. The device specifications, stated in this document, are valid only if one of the original Rota Yokogawa connecting cables is used.

Cable length limitations to be considered:

Cable type	Option code	Maximum length to keep the specification	Maximum allowable length in hazardous areas
Standard connecting cable	L	30 m	171 m
Fire retardant connecting cable with DNV certificate	Y	30 m	95 m

Cables longer than 30 m must be ordered as separate item. For this purpose please check the "Customer Maintainance Parts List" (CMPL 01U10B01-00EN-R) or consult our Yokogawa Service team.

# 7 Approvals and declarations of conformity

### **CE** marking

The Rotamass Total Insight meets the statutory requirements of the applicable EU Directives. By attaching the CE mark, Rota Yokogawa confirms conformity of the field instrument with the requirements of the applicable EU Directives. The EU Declaration of Conformity is enclosed with the product on a data carrier.

#### Pressure equipment approvals

The Rotamass Total Insight is in compliance with the statutory requirements of the applicable EU Pressure Equipment Directive (PED) for fluid groups 1 and 2.

The customer is fully responsible of selecting proper materials which withstand corrosive or erosive conditions. In case of heavy corrosion and/or erosion the instrument may not withstand the pressure and an incident may happen with human and/or environmental harm. Yokogawa will not take any liability regarding damage caused by corrosion or erosion. If corrosion or erosion may happen, the user has to check periodically if the necessary wall thickness is still in place.

#### **RoHS and WEEE Intended Use**

Rotamass Total Insight flow meter is intended to be sold and used in large-scale stationary industrial applications, large-scale fixed installation, means of transport vehicles for persons or goods, excluding two-wheel vehicles which are not type approved. The instrument should be disposed in accordance with applicable national legislations or regulations, respectively.

Details about all standards that are fulfilled are show in the tables below.

Not all options are available in all countries. For details please contact your local Yokogawa Sales Organization.

#### 7.1 Legal equipment standards and norms

### Legal equipment standards and norms

Approval type	Approval or certificate
Electromagnetic Compatibility	EU directive 2014/30/EU per EN 61326-1 Class A Table 2 and EN 61326-2-3 and EN 61328-2-5 (PROFIBUS PA, FOUNDATION Fieldbus)
	RCM in Australia/New Zealand: Rotamass Total Insight meets the EMC requirements of the Australian Communications and Media Authority (ACMA).
(EMC)	KC mark in Korea
	TR CU 020 in EAEU area
	CMIM mark in Morocco
	UKCA mark in Great Britain
	EU directive 2014/35/EU (LVD) per:
	• EN 61010 1
	• EN 61010 2 030
Low Voltage	TR CU 004 in EAEU area
Low voltage	CMIM mark in Morocco
	UKCA mark in Great Britain
	ANSI/UL 61010-1
	CAN/CSA-C22.2 N0. 61010-1/US)

Approval type	Approval or certificate
	EU directive 2014/68/EU per AD 2000 Code (PED)
	ASME B31.3 compliance
	TR CU 032 in EAEU area
Pressure Equipment	CRN registered in Canada
	UKCA mark in Great Britain
	ANSI/UL 61010-1 Annex G
	CAN/CSA-C22.2 N0. 61010-1 Annex G
	Licensing rules for special equipment and charging units TSG 07 Pressure pipe supervision inspection rules TSG D7006
	EU Directives 2011/65/EU, 2015/863/EU per EN IEC 63000
RoHS	China RoHS
	Environmental Conditions; compliance to ISA-71.04G standard

## 7.2 Application and industry related standards

### **General industrial standards**

Approval type	Approval or certificate
NAMUR	EMC according to NE 21
	<ul> <li>Homologation according to NE 95</li> </ul>
	<ul> <li>Mounting length according to NE 132</li> </ul>
NACE	Chemical composition of wetted materials 316L/316/1.4404/1.4401/1.4435 and Ni-Alloy C-22/2.4602 is conform to:
	<ul> <li>ANSI / NACE-MR0175 / ISO15156-2</li> </ul>
	<ul> <li>ANSI / NACE-MR0175 / ISO15156-3</li> </ul>
	NACE MR0103
	For details please see Rota Yokogawa declaration about NACE conformity 8660001.

## Marine approvals

Approval type	Approval or certificate
IMO	Material Declaration and Ship recycling compliances to IMO Resolution MEPC.269 (68)
DNV	Marine type approval according to DNV Type approval scheme DNV-CP-0338 and EU RO Mutual Recognition type approval required by article 10.1 of EU regulation 391/2009.
	For thermal oil applications please consider X-ray inspection (option /RT or /RTA); see [> 82].
KR	Marine type approval according to KR Rules for Classification of Steel Ships Pt.6, Ch.2, Art.301
ABS	<ul> <li>Product device assessment according to ABS rules for building and classing</li> <li>Marine Vessels 4-8-3/1.7, 1.9, 1.11.1, 1.17.1 &amp; 13.1, 4-8-4/27.1, 4-9-9/13.1, 13.5 and Table 1</li> <li>Offshore units 4-3-1/9, 11, 15 &amp; 17.1, 4-3-3/9.1.1 and 9.1.2</li> </ul>
LR	Marine type approval according to LR test specification

## **Functional Safety**

Approval type	Approval or certificate
	Exida Certifcate per IEC61508:2010 Parts 1-7
SIL	SIL 2 @ HFT=0; SIL 3 @ HFT =1
	for both 420 mA analog outputs

## **Metrological Regulations**

Approval type	Approval or certificate
NTEP	Compliance with NIST Handbook 44 Requirements. Certificate number: 12-080
ISO	Measurement of fluid flow in closed conduits. Guidance to the selection, installation and use of Coriolis flowmeters (mass flow, density and volume flow measurements) according to Manufacturer Declaration: ISO 10790
Local type approvals	Rotamass Total Insight is registered as a measuring instrument in the following countries:  China  Russia  Belarus  Kazakhstan  Uzbekistan  Please contact your Yokogawa representative regarding respective "Pattern Approval Certificate of Measuring Instruments" and for export to these countries.

## 7.3 Communication interface standards

### **Communication interface standards**

Approval type	Approval or certificate
HART	Registered at FieldComm Group
FOUNDATION Fieldbus	Registered at FieldComm Group acc. to ITK 6
PROFIBUS PA	Certified at PROFIBUS Nutzerorganisation e.V acc. to PA-Profile 3.02

## 7.4 Other standards and guidelines

## Other standards and guidelines

Approval type	Approval or certificate
IGC	Intergranular Corrosion testing of wetted parts according EN ISO 3651-2 and ASTM. IGC test and certificate available with option P6.
WEEE	EU directive 2012/19/EU (Waste Electrical and Electronic Equipment) is only valid in the European Economic Area.
Dual Seal	Dual Seal approval acc. UL 12.27.01

## 7.5 Hazardous area

Ex approvals: All data relevant for explosion protection are included in separate Explosion Proof Type Manuals.

Approval type	Approval or certificate		
	EU Directive 2014/34/EU		
	ATEX approval:		
	DEKRA 15ATEX0023 X		
	CE <sub>0344</sub> II2G or II2(1)G or II2D or II2(1)D		
ATEV	Applied standards:		
ATEX	■ EN 60079-0		
	■ EN 60079-1		
	■ EN 60079-7		
	■ EN 60079-11		
	■ EN 60079-31		
	IECEx approval:		
	IECEx DEK 15.0016X		
	Applied standards:		
IECEx	• IEC 60079-0		
LOLX	• IEC 60079-1		
	■ IEC 60079-7		
	■ IEC 60079-11		
	• IEC 60079-31		
	FM approvals:		
	US Cert No. FM16US0095X  OA OA AND FM16US0095X		
	CA Cert No. FM16CA0031X		
	Applied standards:		
	<ul><li>Class 3600</li><li>Class 3610</li></ul>		
	• Class 3615		
	• Class 3616		
	• Class 3810		
	• ANSI/UL 60079-0		
	• ANSI/UL 60079-11		
	<ul> <li>ANSI/UL 61010-1</li> </ul>		
FM (CA/US)	ANSI/NEMA 250		
(CA/03)	<ul> <li>ANSI/IEC 60529</li> </ul>		
	• UL 122701		
	• CSA-C22.2 No. 0.4		
	• CSA-C22.2 No. 0.5		
	• CSA-C22.2 No. 25		
	• CSA-C22.2 No. 30		
	• CSA-C22.2 No. 94.1		
	• CSA-C22.2 No. 94.2		
	• CSA-C22.2 No. 60079-0		
	• CSA-C22.2 No. 60079-11		
	<ul> <li>CSA-C22.2 No. 61010-1</li> <li>CSA-C22.2 No. 60529</li> </ul>		
	- COA-CZZ.Z NO. 000Z9		

Approval type	Approval or certificate		
INMETRO	INMETRO approval:		
	DEKRA 16.0012X		
	Applied standards:		
	<ul> <li>ABNT NBR IEC 60079-0</li> </ul>		
(BR)	<ul> <li>ABNT NBR IEC 60079-1</li> </ul>		
	<ul> <li>ABNT NBR IEC 60079-7</li> </ul>		
	<ul> <li>ABNT NBR IEC 60079-11</li> </ul>		
	ABNT NBR IEC 60079-31		
	NEPSI approval:		
	GYJ22.1889X		
	Applied standards:		
NEPSI (CN)	• GB/T 3836.1		
(014)	<ul> <li>GB/T 3836.2</li> <li>GB/T 3836.3</li> </ul>		
	• GB/T 3836.4		
	• GB/T 3836.31		
	PESO approval: PESO approval is based on ATEX certification by DEKRA		
	DEKRA 15ATEX0023 X		
	PESO approval is only valid for type of protection "d" flameproof enclosure. Option Q11 must be ordered for conformity of device with PESO requirements.		
	Equipment Reference Numbers:		
	P434956/_		
	P434884/_		
	P434885/_		
PESO	P431901/_		
(IN)	P431875/_		
	P432033/_		
	P434983/_		
	P434957/_		
	P434887/_		
	Applied standards:		
	■ EN 60079-0 +A11		
	■ EN 60079-1		
	■ EN 60079-11		
Safety Label (TW)	Please refer to IECEx approval for specifications. A device with IECEx approval (model code position 11, value: SF2_) must be ordered to comply with Safety Label requirements. For export to Taiwan and to get the Safety Label the Yokogawa representative in Taiwan must be contacted in advance.		
	Identification Number:		

Approval type	pproval type Approval or certificate			
Korea Ex	Korea Ex certificates:  18-KA4BO-0507X  18-KA4BO-0508X  18-KA4BO-0513X  18-KA4BO-0526X  18-KA4BO-0509X  18-KA4BO-0510X  18-KA4BO-0539X  18-KA4BO-0540X  18-KA4BO-0541X  18-KA4BO-0681X  18-KA4BO-0682X  18-KA4BO-0527X  18-KA4BO-0527X  18-KA4BO-0533X  18-KA4BO-0533X  18-KA4BO-0533X  18-KA4BO-0533X  18-KA4BO-0533X  18-KA4BO-0538X  Applied standards:  Notice of Ministry of Labor No 2016-54 harmonized with  IEC 60079-1  IEC 60079-7  IEC 60079-11  IEC 60079-31			
EAC Ex	RU C-DE.AA71.B.00517  Applied standards:			
Japan Ex	<ul> <li>DEK 18.0067 X</li> <li>DEK 18.0076 X</li> <li>DEK 18.0087 X</li> <li>Applied standards:</li> <li>JNIOSH-TR-46-1: 2015</li> <li>JNIOSH-TR-46-2: 2018</li> <li>UKEx approval: JNIOSH-TR-46-6: 2015</li> </ul>			

Approval type	Approval or certificate		
	UKCA Ex approval:		
UKEx	DEKRA 21UKEX0356X		
	CE 8505 II2G or II2(1)G or II2D or II2(1)D		
ECAS Ex	20-04-10410 / E20-04-000730		
Ukraine Ex	DEKRA 15ATEX0023 X		


## 8 Ordering information

## 8.1 Model code description

The model code of the Rotamass Total Insight is explained below.

Items 1 through 14 are mandatory entries and must be specified at the time of ordering.

Device options (item 15) can be selected and specified individually by separating them with slashes.



Basic model code (pos. 1-4)

Model code positions 5-14 (Mandatory items)

Model code position 15 (device options)

In general, the selection of one option per option group is possible. In option group "Calibration certificate" all 3 options can be combined.

Model code position	Model code	Description
Transmitter		
1	E	Essential (base function)
1	U	Ultimate (high function)
1	N	Spare sensor without transmitter, combinable with Rotamass TI transmitter
Sensor		
2	Т	Intense
Meter size		
3	08	Nominal mass flow: 0.045 t/h (1.7 lb/min) Maximum mass flow: 0.094 t/h (3.5 lb/min)
3	10	Nominal mass flow: 0.17 t/h (6.2 lb/min) Maximum mass flow: 0.3 t/h (11 lb/min)
3	34	Nominal mass flow: 3 t/h (110 lb/min) Maximum mass flow: 5 t/h (180 lb/min)
3	36	Nominal mass flow: 10 t/h (370 lb/min) Maximum mass flow: 17 t/h (620 lb/min)
3	38	Nominal mass flow: 32 t/h (1200 lb/min) Maximum mass flow: 50 t/h (1800 lb/min)
Material wetted part	S	
4	S	Stainless steel 1.4404/316L
4	Н	Nickel alloy C-22/2.4602
4	К	Measuring tubes: Nickel alloy C-22/2.4602 Process connnections: Stainless steel 1.4404/316L

Model code position	Model code	Description
Process connection	size	·
5	08	<sup>3</sup> / <sub>8</sub> in.
5	15	DN15, ½ in.
5	16	<sup>9</sup> / <sub>16</sub> in.
5	20	DN20, ¾ in.
5	25	DN25, 1 in.
5	50	DN50, 2 in.
Process connection		
6	BA5	ASME flange class 900, compatible to ASME B16.5, raised face (RF)
6	CA5	ASME flange class 900, compatible to ASME B16.5, ring joint (RJ)
6	BA6	ASME flange class 1500, compatible to ASME B16.5, raised face (RF)
6	CA6	ASME flange class 1500, compatible to ASME B16.5, ring joint (RJ)
6	TG9	Process connection with internal thread G
6	TT9	Process connection with internal thread NPT
6	TA9	Medium pressure autoclave compatible connection
Sensor housing mat		process added a companio component
7	0	Stainless steel 1.4301/304, 1.4404/316L
7	1	Stainless steel 1.4404/316L
Process fluid tempe		Ottaining Green 1.110 We fee
8	0	Standard temperature range
8	2	Medium temperature range
8	3	High temperature range
Mass flow and dens		riigii temperature range
9	E8	Liquid: 0.2 % maximum mass flow deviation, 8 g/l density deviation
9	E7	Liquid: 0.2 % maximum mass flow deviation, 4 g/l density deviation
9	D7	Liquid: 0.15 % maximum mass flow deviation, 4 g/l density deviation
9	C8	Liquid: 0.1 % maximum mass flow deviation, 8 g/l density deviation
9	C7	Liquid: 0.1 % maximum mass flow deviation, 4 g/l density deviation
9	C3	Liquid: 0.1 % maximum mass flow deviation, 1 g/l density deviation
9	C2	Liquid: 0.1 % maximum mass flow deviation, 0.5 g/l density deviation
9	70	Gas: 0.75 % maximum mass flow deviation
9	50	Gas: 0.50 % maximum mass flow deviation
Design and housing		Internal true with Broathan and a discrete and a discrete
10	0	Integral type with "urethane-cured polyester powder coating" coated aluminum transmitter housing
10	2	Integral type with "corrosion protection coating" coated aluminum transmitter housing
10	А	Remote type with "urethane-cured polyester powder coating" coated aluminum transmitter housing and standard neck sensor
10	В	Remote type with "urethane-cured polyester powder coating" coated aluminum transmitter housing and long neck sensor
10	Е	Remote type with "corrosion protection coating" coated aluminum transmitter housing and standard neck sensor
10	F	Remote type with "corrosion protection coating" coated aluminum transmitter housing and long neck sensor
10	J	Remote type stainless steel transmitter and standard neck sensor
10	K	Remote type stainless steel transmitter and long neck sensor
.~	1.,	. temete type claimed deed transmitted and long front defined

Model code position	Model code	Description
Ex Approvals		
11	NN00	None
11	KF21	ATEX, explosion group IIC and IIIC
11	KF22	ATEX, explosion group IIB and IIIC
11	SF21	IECEx, explosion group IIC and IIIC
11	SF22	IECEx, explosion group IIB and IIIC
11	FF11	FM, groups A, B, C, D, E, F, G
11	FF12	FM, groups C, D, E, F, G
11	UF21	INMETRO, explosion group IIC and IIIC
11	UF22	INMETRO, explosion group IIB and IIIC
11	NF21	NEPSI, explosion group IIC and dust proof
11	NF22	NEPSI, explosion group IIB and dust proof
11	GF21	EAC Ex, explosion group IIC and IIIC
11	GF22	EAC Ex, explosion group IIB and IIIC
11	PF21	Korea Ex, explosion group IIC and IIIC
11	PF22	Korea Ex, explosion group IIB and IIIC
11	JF53	Japan Ex, Temperature class T3, gas group IIC
11	JF54	Japan Ex, Temperature class T4, gas group IIC
11	BF21	UKEx, explosion group IIC and IIIC
11	BF22	UKEx, explosion group IIB and IIIC
Cable entries		, , , , , , , , , , , , , , , , , , , ,
12	2	ANSI ½ in. NPT
12	4	ISO M20x1.5
Communication typ	e and I/O	
13	JA	1 active current output HART, 1 passive pulse or status output
13	JB	2 active current outputs one with HART, 2 passive pulse or status outputs
13	JC	2 active current outputs one with HART, 1 passive pulse or status output, 1 voltage-free status input
13	JD	1 active current output HART, 2 passive pulse or status outputs, 1 passive status output
13	JE	1 active current output HART, 2 passive pulse or status outputs, 1 voltage-free status input
13	JF	1 active current output HART, 1 passive pulse or status output, 1 active pulse or status output with pull-up resistor, 1 voltage-free status input
13	JG	1 active current output HART, 1 passive pulse or status output, 1 active pulse or status output, 1 voltage-free status input
13	JH	1 active current output HART, 1 passive pulse or status output, 1 passive current output, 1 active current input
13	JJ	1 active current output HART, 2 passive pulse or status outputs, 1 active current input
13	JK	1 active current output HART, 1 passive pulse or status output, 1 voltage-free status input, 1 active current input
13	JL	1 active current output HART, 1 passive pulse or status output, 1 passive current output, 1 passive current input
13	JM	1 active current output HART, 2 passive pulse or status outputs, 1 passive current input
13	JN	1 active current output HART, 1 passive pulse or status output, 1 voltage-free status input, 1 passive current input



Model code position	Model code	Description		
13	JP	2 passive current outputs one with HART, 1 passive pulse or status output		
13	JQ	2 passive current outputs one with HART, 2 passive pulse or status outputs		
13	JR	2 passive current outputs one with HART, 1 passive Namur pulse or status output		
13	JS	2 passive current outputs one with HART, 2 passive Namur pulse or status outputs		
13	F0	FOUNDATION Fieldbus, 1 passive pulse output		
13	F1	FOUNDATION Fieldbus, intrinsically safe, 1 passive pulse output		
13	MO	Modbus output, 1 passive pulse or status output		
13	M2	Modbus output, 1 passive pulse or status output, 1 active current input		
13	M3	Modbus output, 2 passive pulse or status outputs		
13	M4	Modbus output, 1 passive pulse or status output, 1 active pulse or status output		
13	M5	Modbus output, 1 passive pulse or status output, 1 active pulse or status output with pull-up resistor		
13	M6	Modbus output, 1 passive pulse or status output, 1 active current output		
13	M7	Modbus output, 1 passive pulse or status output, 1 passive current input		
13	G0	Profibus PA, 1 passive pulse output		
13	G1	Profibus PA, intrinsically safe, 1 passive pulse output		
13	NN	Spare sensor without transmitter, all communication types and I/Os apply		
Display	'			
14	0	No display		
14	1	With display		
14	N	Spare sensor without transmitter, no display applied		
Model code position	Model code	Description		
Additional nameple	ate information			
15	/BG	Customer-specific tag number on nameplate		
Pre-setting of cust	omer parameters	S		
15	/PS	Presetting of selected parameters based on customer data		
Country-specific d	Country-specific delivery			
15	/PJ	Delivery to Japan incl. SI units pre-setting and Quality Inspection Certificate (EN/JP)		
15	/CN	Delivery to China including China RoHS mark		
15	/KC	Delivery to Korea including KC mark		
15	ΝE	Delivery to EAEU area including EAC mark		
15	/VB	Delivery to EAEU area including EAC mark and Belarussia Pattern Approval mark		
15	/VR	Delivery to EAEU area including EAC mark and Russia Pattern Approval mark		
10		provarmark		

Model code position	Model code	Description	
Country-specific application			
15	/Q11	PESO approval delivery	
15	/QR2	Kazakhstan Pattern Approval mark and Primary verification, including certificate	
15	/QR3	Uzbekistan Pattern Approval and Primary verification	
15	/TS1	China TSG Approval Pressure Class GC1	
15	/TS2	China TSG Approval Pressure Class GC2	
15	/CS	CRN (Canadian Registration Number)	
Concentration and F	Petroleum meas	urement	
15	/CST	Standard concentration measurement	
15	/AC0	Advanced concentration measurement, customer settings	
15	/AC1	Advanced concentration measurement, one default data set	
15	/AC4	Advanced concentration measurement, four default data sets	
15	/C52	Net Oil Computing (NOC) following API standard	
15	/RD	Rupture disc	
Customer-specific c	alibration		
15	/K2	Customer-specific 5-point mass flow calibration with measuring range on factory calibration certificate (mass flow or volume flow of water). A table listing the desired calibration points must be supplied with the order.	
15	/K5	Customer-specific 10-point mass flow calibration with measuring range on DAkkS calibration certificate (mass flow or volume flow of water). A table listing the desired calibration points must be supplied with the order.	
Accordance with ter	ms of order		
15	/P2	Declaration of compliance with the order 2.1 according to EN 10204	
15	/P3	Inspection certificate 3.1 according to EN 10204 (Quality Inspection Certificate). Declaration of compliance with the order including inspection results.	
<b>Material certificates</b>			
15	/P6	Certificate of Marking Transfer and Raw Material Certificates (Inspection Certificate 3.1 according to EN 10204), including IGC and conform to NACE MR0175 and MR0103. For details and exceptions please refer to Rota Yokogawa declaration about NACE conformity, document no. 8660001.	
Pressure testing			
15	/P8	Hydrostatic Pressure Test Certificate (Inspection Certificate 3.1 according to EN 10204)	
Surfaces free of oil and grease			
15	/H1	Degreasing of wetted surfaces according to ASTM G93/G93M-19 (Level C), including test report	

Model code position	Model code	Description
Welding certificate	IVIOUEI COULE	<u> Дезоприон</u>
15	/WP	Welding certificates for butt welding between process connection and flow divider:  WPS according to DIN EN ISO 15609-1  WPQR according to DIN EN ISO 15614-1  WQC according to DIN EN 287-1 or DIN EN ISO 6906-4
15	/WPA	Welding procedures and certificate according ASME IX for butt welding between process connection and flow divider:  • WPS  • WPQR  • WQP
ASME B31.3 complia	ance	
15	/P15	ASME B31.3 compliance NORMAL FLUID SERVICE
X-ray inspection of f	lange weld sear	n
15	/RT	X-ray inspection of flange weld seam according to DIN EN ISO 17636-1/B. Evaluation according to AD2000HP 5/3 and DIN EN ISO 5817/C, including certificate
15	/RTA	X-ray inspection according ASME V
Positive Material Ide	ntification of we	etted parts
15	/PM	Positive Material Identification of wetted parts, including certificate (Inspection Certificate 3.1 according to EN 10204)
Dye penetrant test o	f weld seams	
15	/PT	Dye penetrant test of process connection weld seams according to DIN EN ISO 3452-1, including certificate
15	/PTA	Dye penetrant test of flange welding according to ASME V, including certificate
Combined certificate	9	
15	/P10	Combination of:  P3: Quality Inspection Certificate  P6: Certificate of Marking Transfer and Raw Material Certificates  P8: Hydrostatic Pressure Test Certificate
15	/P11	Combination of:  P3: Quality Inspection Certificate  P6: Certificate of Marking Transfer and Raw Material Certificates  PM: Positive Material Identification of wetted parts
15	/P12	Combination of:  P3: Quality Inspection Certificate  P6: Certificate of Marking Transfer and Raw Material Certificates  PT: Dye penetrant test according to DIN EN ISO 3452-1  P8: Hydrostatic Pressure Test Certificate
15	/P13	Combination of:  P3: Quality Inspection Certificate  P6: Certificate of Marking Transfer and Raw Material Certificates  PT: Dye penetrant test according to DIN EN ISO 3452-1  PM: Positive Material Identification of wetted parts  P8: Hydrostatic Pressure Test Certificate  WP: Welding certificates

-		Description		
15	/P14	Combination of:  PM: Positive Material Identification of wetted parts  P8: Hydrostatic Pressure Test Certificate  WP: Welding certificates		
15	/P20	Combination of:  PTA: Dye penetrant test of flange welding according ASME V  WPA: Welding procedures and Certificates according ASME IX  RTA: X-ray test according ASME V		
15	/P21	Combination of:  P3: Quality Inspection Certificate  P6: Certificate of Marking Transfer and Raw Material Certificates  P8: Hydrostatic Pressure Test Certificate  PTA: Dye penetrant test of flange welding according ASME V  WPA: Welding procedures and Certificates according ASME IX  RTA: X-ray test according ASME V		
15	/P22	Combination of:  P3: Quality Inspection Certificate  P6: Certificate of Marking Transfer and Raw Material Certificates  PM: Positive Material Identification of wetted parts  PTA: Dye penetrant test of flange welding according ASME V  WPA: Welding procedures and Certificates according ASME IX  RTA: X-ray test according ASME V		
Tube Health Check				
15	/TC	Tube Health Check		
15	/FE	Ferrite test for flange welding acc. DIN EN ISO 8249, including certificate		
Batching function				
15	/BT	Batching and filling function		
15	/RB	Alignment of transmitter housing rotated 180°		
Viscosity function				
15	/VM	Viscosity computing function for liquids		
Custody transfer me	easurement			
15	/Q20	NTEP approval, accuracy class 0.3 acc. NIST Handbook 44		
Insulation and heat t	tracing			
15	/T10	Insulation		
15	/T21	Insulation and heat tracing, ASME ½ in. class 150, raised face		
15	/T22	Insulation and heat tracing, ASME ½ in. class 300, raised face		
15	/T26	Insulation and heat tracing, EN DN15 PN40		
15	/T31	Insulation, heat tracing with purging, ASME ½ in. class 150, raised face		
15	/T32	Insulation, heat tracing with purging, ASME ½ in. class 300, raised face		
15	/T36	Insulation, heat tracing with purging, EN DN15, PN40		
15	/DS	Dual Seal approval according to UL 122701-2017		
Measurement of hea	Measurement of heat quantity			
15	/CGC	Measurement of the total transported energy content of a fuel in connection with a sensor for determining the fuel's calorific value (e.g., a gas chromatograph, not included in scope of delivery).		

Model code position	Model code	Description		
Marine Approval				
15	/MC2	Marine approval according DNV, EU RO MR TAC, ABS and KR piping class 2		
15	/MC3	Marine approval according DNV, EU RO MR TAC, ABS and KR piping class 3		
Connecting cable ty	pe and length			
15	/L000	Without standard connecting cable		
15	/L005	5 meter (16.4 ft) remote connecting cable terminated; standard gray / Ex blue		
15	/L010	10 meter (32.8 ft) remote connecting cable terminated; standard gray / Ex blue		
15	/L015	15 meter (49.2 ft) remote connecting cable terminated; standard gray / Ex blue		
15	/L020	20 meter (65.6 ft) remote connecting cable terminated; standard gray / Ex blue		
15	/L030	30 meter (98.4 ft) remote connecting cable terminated; standard gray / Ex blue		
15	/Y000	Without fire retardant connecting cable		
15	/Y005	5 meter (16.4 ft) remote fire retardant connecting cable, not terminated, with DNV Type Approval Certificate		
15	/Y010	10 meter (32.8 ft) remote fire retardant connecting cable, not terminated, with DNV Type Approval Certificate		
15	/Y015	15 meter (49.2 ft) remote fire retardant connecting cable, not terminated, with DNV Type Approval Certificate		
15	/Y020	20 meter (65.6 ft) remote fire retardant connecting cable, not terminated, with DNV Type Approval Certificate		
15	/Y030	30 meter (98.4 ft) remote fire retardant connecting cable, not terminated, with DNV Type Approval Certificate		
Cable glands and bl	ind plug			
15	/V52	2 cable glands, 1 blind plug for power, communication and I/O		
15	/V53	3 cable glands for power, communication and I/O		
Adapter for cable er	Adapter for cable entries			
15	/AD2	2 adapter ANSI 1/2 in. NPT to JIS G1/2		
	Steel armored connecting cable			
15	/LAC	Steel armored version of standard connecting cable		

Not all options are available in all countries. For details please contact your local Yokogawa Sales Organization.

## 8.2 Available model codes per basic model

**(i)** 

For complete product configuration, please refer to the FlowConfigurator online sizing and configuration tool: <a href="http://www.FlowConfigurator.com">http://www.FlowConfigurator.com</a>

	Stainle	ess Stee	I Devices	S										Hastel	loy C De	vices						
		tial Tran			te Trans	mitter	Spare	Sensor		Essen	tial Trans	smitter	Ultima	te Trans			Sensor		Ultimat	te	Spare	Senso
																			Transn	nitter	-	
Code	RCET34S	RCET36S	RCET38S	RCUT34S	RCUT36S	RCUT38S	RCNT34S	RCNT36S	RCNT38S	RCET34H	RCET36H	RCET38H	RCUT34H	<b>RCUT36H</b>	RCUT38H	RCNT34H	RCNT36H	RCNT38H	RCUT08K	RCUT10K	RCNT08K	RCNT10K
				N N	N N	X	N N	X	N N	N N	N N	N N	N N	N N	X	N N	N N	N N	N N	N N	N N	X
	s conne	ection siz	ze																			
-15	•			•			•				-											
-25	•	•		•	•		•	•		•	•	-	•	•		•	•					
-50		•	•		•	•		•	•		•	•	-	•	•		•	•			-	
-08	•			•			•				-											
20	•			•			•				-	_	-						•	•	•	•
80											-	•	-		•			•			-	-
-16																			•	•	•	•
	1	ction typ	1	1	1	T	1		1		T							1				_
BA5	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•			-	-
BA6	•			•			•			•	-		•			•					-	-
CA5	•	•	•	•	•	•	•	•	•		•	•	-	•	•		•	•			-	-
CA6	•			•			•				•	•	-	•	•		•	•			-	-
TG9	•			•			•				-		-								-	-
TT9	•			•			•				-		-								-	-
TA9			ial																•	•	•	•
		g mater		1_		1_		1_	1.		Τ.	T_	Τ	1_	1_	_	_					
0	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				-
1 Proces	• fluid t	• emperat	• ure rang	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
roces	1		ure rang		_	1.	1.	1_	1.	1_	Τ.	1.	Τ.	1.	1.	1.		1_	1_	1.	T_	
	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
2	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•			-	_
-3	•	• density	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
	low and	density	accurac	у																		
E8											-	_	-						•		-	-
E7 D7	•	•	•							•	•	•	-							•	-	_
	•	•	•							•	•	•	-						-		-	-
C8 C7											-	-	-						•	_	•	-
C7 C3					-	•					-	_	-		_					•	-	
C2				•	•	-	-	_	_		-	-	•	•	•	_	_	-		•	-	•
70	_	-	_	•	•	•	•	•	•	•	-	-	•	•	•	•	•	•				-
50	•	•	•	•	•	•	•	•	•	•	•	•		•	•	•	•	•			-	+
30				•	•	•	•	•	•		-	-				•	•	•			-	-
	n and ho	ueina		•				•	•							•		•				
Desigi )	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•			1	_
2		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				+
<u>2</u> A		•	•		•		•	•		•	•	•	•	•	•	•	•					
` 3	•	•	•	•	•	•	•	•	•	•	•	•		•	•	•	•	•	-	-	-	+
E .	•		•	•	•	•	•	•	•	•	•	•	•	•		•	•		•	•	•	•
-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	-	-	-	+
J	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
, <	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	-	-	1	+
	orovals	-		-		1			-	-			1	-	-	-	-	1				
NN00		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
KF21		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
KF22		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
BF21		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				+
BF22		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				+
FF11		•	•	•	•	•	•	•	•	•	_		•			•	•	•				+
FF12		•	•	•	•	•	•	•	•	•	+		•			•	•	•				+
SF21		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	
		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	
				-		•	•	•	•	•	•	•	•	•	•	•	•	•	-	+	-	+
SF22 GF21	•																					1
GF21 GF22		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				+

	Stainles	ss Steel	Devices	i										Hastell	loy C De	vices						
		al Trans			e Transr	mitter	Spare S	Sensor		Essent	ial Trans	smitter	Ultimat	e Trans		Spare	Sensor		Ultimat		Spare	Sensor
Code	34S	S98	S88	34S	S98	S88	34S	S98	S88	74 H	H98	H88	34H	96H	H88	34H	96H	H88	Transm		X8	Ş
	RCET34S	RCET36S	RCET38S	RCUT34S	RCUT36S	RCUT38S	RCNT34S	RCNT36S	RCNT38S	RCET34H	RCET36H	RCET38H	RCUT34H	<b>RCUT36H</b>	<b>RCUT38H</b>	RCNT34H	RCNT36H	RCNT38H	RCUT08K	RCUT10K	RCNT08K	RCNT10K
-UF22		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	Œ	Œ	<u> </u>	<u> </u>
-NF21		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
-NF22	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
	•	•	•	•	•	•				•	•	•	•	•	•							
	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		•	•				
-PF22		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
Cable e	entries																					
-2	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
-4 Commi	• unication	• type an	• d I/O	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
-JA	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		Τ
-JB	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-JC	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-JD	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-JE -JF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-JG	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-JH				•	•	•	•	•	•				•	•	•	•	•	•	•	•		
-JJ				•	•	•	•	•	•				•	•	•	•	•	•	•	•		
-JK				•	•	•	•	•	•				•	•	•	•	•	•	•	•		
-JL -JM				•	•	•	•	•	•				•	•	•	•	•	•	•	•		
-JN				•	•	•	•	•	•				•	•	•	•	•	•	•	•		
-JP	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-JQ	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-JR	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-JS -F0	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		-
-F1				•	•	•	•	•	•				•	•			•	•	•	•		
-G0				•	•	•	•	•	•				•	•	•	•	•	•	•	•		
-G1				•	•	•	•	•	•				•	•	•	•	•	•	•	•		
-M0	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-M2 -M3	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-M4	•	•	•	•	•	•	•	•	•	•	•		•	•		•	•	•	•	•		
-M5	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-M6	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
-M7				•	•	•	•	•	•				•	•	•	•	•	•	•	•		
-NN Display	,						•	•	•							•	•	•			•	•
0	•	•	•							•	•	•										
1	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
N							•	•	•							•	•	•			•	•
	nal name					_		_														
/BG Pre-set	ting of c	• ustomer	• parame	eters	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
/PS	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
Country	y-specific	c deliver	у																			
/PJ	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/CN	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/KC /VB	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
/VE	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
/VR	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/UK	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
	y-specific																					
/Q11 /QR2	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				-
/QR3	•	•	•	•	•	•	•	•	•	•	•	•	•	•		•	•	•				
/TS1	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/TS2	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/CS	•	•	•	•	•	•	•	•	•	•			•			•	•	•				

	Stainle	ss Steel	Devices	3										Hastel	oy C De	vices						
		tial Trans			te Trans	mitter	Spare	Sensor		Essen	tial Trans	smitter	Ultima	te Trans	•		Sensor		Ultimat		Spare	Senso
Code	48	S <sub>9</sub>	SS SS	48	S9	S8	48	S9	S8	H <sub>4</sub>	H9	H8	±	H9	H8	H H	H <sub>9</sub>	H8	Transn		% X	¥
	RCET34S	RCET36S	RCET38S	RCUT34S	RCUT36S	RCUT38S	RCNT34S	RCNT36S	RCNT38S	RCET34H	RCET36H	RCET38H	RCUT34H	<b>RCUT36H</b>	<b>RCUT38H</b>	RCNT34H	RCNT36H	RCNT38H	RCUT08K	RCUT10K	RCNT08K	RCNT10K
	ntration	and Petr	oleum n	_																		
/CST /AC0				•	•	•					-		•	•	•							
/AC1					•	•					-		•	•								
/AC4				•	•	•							•	•	•							
/C52				•	•	•							•	•	•							
Ruptur	e disc																					
/RD	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/K2	ner-spec	eific calib	e	•	•	•				•		•	•	•	•				•	•		
/K5	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
	lance wi	th terms	of order																			
/P2	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
/P3	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
	al certific				1		1				_				T		I	I				
/P6 Pressu	re testir	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
/P8	• testii	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Surface	es free o	of oil and	grease																			
/H1	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
	g certific	_																				
/WP	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/WPA	P31 3 c	• omplian	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/P15	•	•	•	•	•	•	•	•	•	•	•		•	•		•	•	•	•	•	•	•
		n of flan						1														
/RT	•	•	•	•	•	•	•	•	•													
/RTA	•	•	•	•	•	•	•	•	•													
		al Identi			_																	
/PM	• notrant	e test of w	eld sear	• ne	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
/PT	•	•	• Seal	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/PTA	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
Combin	ned cert	ificate																				
/P10	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
/P11	•	•	•		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
/P12 /P13	•		1	•					•		•				•	•	•					
	-	•	•	•	•	•	•	•	-	•		•	•	•				•				
	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/P14 /P20	-	-		•	•			-	-				-	•	•							
/P14	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/P14 /P20 /P21 /P22	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/P14 /P20 /P21 /P22 Tube H	• • • • • Health C	• • • • • • heck	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/P14 /P20 /P21 /P22 Tube H	• • • • • Health C	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
/P14 /P20 /P21 /P22 Tube H /TC Ferrite	• • • • • Health C	• • • • • • heck		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
/P14 /P20 /P21 /P22 Tube H /TC Ferrite	Health C     testing	• • • • • • • • • • • • • • • • • • •	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		
/P14 /P20 /P21 /P22 Tube H /TC Ferrite	• • • • • Health C	• • • • • • • • • • • • • • • • • • •		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•			
/P14 /P20 /P21 /P22 Tube F /TC Ferrite /FE Batchir	e e e e e e e e e testing ng functi	• • • • • • • • • • • • • • • • • • •	•		•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/P14 /P20 /P21 /P22 Tube H /TC Ferrite /FE Batchir /BT Transn	Health C testing ng functi	e e e e e e e e e e e e e e e e e e e	•		•	•	•	•	•	•	•	•	•	•	•	•	•	•				
/P14 /P20 /P21 /P22 Tube H /TC Ferrite /FE Batchir /BT Transm /RB	Health C testing ng function	e e e e e e e e e e e e e e e e e e e	• • • • • • • • • • • • • • • • • • •	•	•	•	•	•	•	•	•	•	•			•	•	•	•	•		
/P14 /P20 /P21 /P22 Tube H /TC Ferrite /FE Batchir /BT Transn /RB Viscosi	e e e e e e e e e e e e e e e e e e e	e e e e e e e e e e e e e e e e e e e	• • • • • • • • • • • • • • • • • • •			•	•	•	•	•	•	•	•	•	•	•	•	•				
/P14 /P20 /P21 /P22 Tube H /TC Ferrite /FE Batchir /BT Transn /RB Viscosi /VM Custod	e e e e e e e e e e e e e e e e e e e	e e e e e e e e e e e e e e e e e e e	• • • • • • • • • • • • • • • • • • •		•	•	•	•	•	•	•	•	•			•	•	•	•	•		
/P14 /P20 /P21 /P22 Tube H /TC Ferrite /FE Batchir /BT Transm /RB Viscosi /VM Custod	e e e e e e e e e e e e e e e e e e e	e e e e e e e e e e e e e e e e e e e	e e e e e e e e e e e e e e e e e e e			•	•	•	•	•	•	•	•			•	•	•	•	•		
/P14 /P20 /P21 /P22 Tube H /TC Ferrite /FE Batchir /BT Transm /RB Viscosi /VM Custod	e e e e e e e e e e e e e e e e e e e	er meas	e e e e e e e e e e e e e e e e e e e			•	•	•	•	•	•	•	•			•	•	•	•	•		
/P14 //P20 //P21 Tube H //TC Ferrite //FE Batchir //BT Transn //M Custod //Q20 Insulati //T10	e e e e e e e e e e e e e e e e e e e	er meas	ated 180							•	•								•	•		
/P14 //P20 //P21 Tube H //TC Ferrite //FE Batchir Transn //RB Viscosi //VM Custod //Q20 Insulati //T10 //T21	e e e e e e e e e e e e e e e e e e e	heat trace	ated 180								•		•						•	•		
/P14 //P20 //P21 Tube I- //TC Ferrite Batchir //RB Viscosi //VM Custod //Q20 Insulati //T10 //T21 //T22	e e e e e e e e e e e e e e e e e e e	er meas	ated 180				•			•			•						•	•		
/P14 //P20 //P21 //P22 Tube H //TC Ferrite Batchir //RB Viscosi //VM Custod //Q20 Insulati //T10 //T21	e e e e e e e e e e e e e e e e e e e	heat trace	ated 180								•		•						•	•		

	Stainle	ess Stee	el Device	S										Hastel	loy C De	evices						
	Essen	tial Tran	smitter	Ultima	te Trans	mitter	Spare	Sensor		Essen	tial Tran	smitter	Ultima	te Trans	mitter	Spare	Sensor		Ultimat Transn		Spare	Sensor
Code	RCET34S	RCET36S	RCET38S	RCUT34S	RCUT36S	RCUT38S	RCNT34S	RCNT36S	RCNT38S	RCET34H	RCET36H	RCET38H	RCUT34H	<b>RCUT36H</b>	RCUT38H	RCNT34H	RCNT36H	RCNT38H	RCUT08K	RCUT10K	RCNT08K	RCNT10K
Dual S	eal app	roval																				
/DS		•	•		•	•		•	•													
Measu	rement	of heat	quantity																			
/CGC				•	•	•							•	•	•				•	•		
Marine	Approv	/al																				
/MC2	•	•	•	•	•	•				•	•	•	•	•	•							
/MC3	•	•	•	•	•	•				•	•	•	•	•	•							
Conne	cting ca	ble type	and leng	gth																		
/L000	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
/L005	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
/L010	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
/L015	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
/L020	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
/L030	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
/Y000	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
/Y005	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
/Y010	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
/Y015	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
/Y020	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
/Y030	•	•	•	•	•	•				•	•	•	•	•	•				•	•		
Cable (	glands a	and bline	d plug																			
/V52	•	•	•	•	•	•				•	•	•	•	•	•							
/V53	•	•	•	•	•	•				•	•	•	•	•	•							
Adapte	er for cal	ble entri	es																			
/AD2	•	•	•	•	•	•				•	•	•	•	•	•							
Steel a	rmored	connec	ting cabl	е																		
/LAC	•	•	•	•	•	•				•	•	•	•	•	•				•	•		


### 8.3 Model code combinations



For complete product configuration, please refer to the FlowConfigurator online sizing and configuration tool: <a href="http://www.FlowConfigurator.com">http://www.FlowConfigurator.com</a>

### **AGA11 Declaration of Conformity**

A certificate about AGA11 declaration of conformity will be issued with the following configuration.



Model code position	Code	Description
9	30, 50 or 70	Mass flow accuracy for gases
13	J_	HART Interface
15	/K5	Option Customer-specific 10-point mass flow calibration
15	/TC	Option Tube Health Check



Please note: AGA11 declaration of conformity available with Rotamass Total Insight HART firmware rev.4 or later. For details please contact your local Yokogawa sales organization.

## 8.4 Ordering Instructions

Specify the following information when ordering a product:

#### 8.4.1 Mandatory ordering instructions

The following information have to be specified when ordering a product:

- Model code
- Fluid name
- Rotamass TI is delivered with quick reference hardcopy, a compressed version of the general instruction manual. For delivery choose one of the languages below:
  - English
  - French
  - German
  - Japanese
  - Chinese
  - Korean
  - Russian

#### 8.4.2 Optional ordering instructions

The following information depend on the product configuration and can or have to be selected.

#### Manual and display language

Display language and units depend on the selected language pack:


pack 1	pack 2	pack 3
EN-Pack1 - English	EN-Pack2 - English	EN-Pack3 - English
DE-Pack1 - German	DE-Pack2 - German	DE-Pack3 - German
FR-Pack1 - French	RU-Pack2 - Russian	FR-Pack3 - French
PT-Pack1 - Portuguese	PL-Pack2 - Polish	PT-Pack3 - Portuguese
IT-Pack1 - Italian	KZ-Pack2 - Kazakh	IT-Pack3 - Italian
ES-Pack1 - Spanish		ES-Pack3 - Spanish
JA-Pack1 - Japanese		CN-Pack3 - Chinese

- Unit notation on the display (display only present for value 1 on position 14 of the model code):
  - Metric units
  - Imperial units US
  - Imperial units GB
  - Russia specific units (only available with language pack 2)
  - Japan specific units (only available with language pack 1)



## **Display orientation**

• When display is ordered, its orientation has to be specified.



- In the above the figure, the housing of the Prime sensor is shown. The design of sensor depends on the chosen series.
- The parameter "Installation Orientation" in transmitter must be set by the customer according to the installation direction of the sensor.

### Serial and tag number, customer name

Tag No. engraved on the nameplate and mentioned on the calibration certificate (option BG, up to 17 characters length)

Software Tag No.: short and long (short tag no. mentioned also on the calibration certificate):

Parameter	Value
HART Tag No. (short): up to 8 characters length (Capital letters only)	Default value has 8 space characters
HART Tag No. (long): up to 32 characters length	Default value has 32 space characters
PROFIBUS PANODE ADDRESS (HEX): up to 2 characters length	Default value '0x7E' unless otherwise specified
PROFIBUS PA SOFTWARE TAG: up to 32 characters length	Default value 'FT2001' unless otherwise specified
FOUNDATION Fieldbus NODE ADDRESS (HEX): up to 2 characters length	Default value '0xF6' unless otherwise specified
FOUNDATION Fieldbus SOFTWARE TAG: up to 32 characters length	Default value 'FT2004' unless otherwise specified

Specify the following information when ordering option /SNC for a Spare Transmitter RCUXNNN:

- Serial number of the transmitter to be replaced.
- Customer name for the certificates (option L2, L3, L4: up to 40 characters length)

#### **Concentration measurement**

In case advanced concentration measurement with predefined sets (option AC1, AC4) is ordered, at least one of the following sets have to be selected:

- C01 Sugar / Water 0 85 °Bx, 0 80 °C
- C02 NaOH / Water 2 50 WT%, 0 100 °C
- C03 KOH / Water 0 60 WT%, 54 100 °C
- C04 NH4NO3 / Water 1 50 WT%, 0 80 °C
- C05 NH4NO3 / Water 20 70 WT%, 20 100 °C
- C06 HCI / Water 22 34 WT%, 20 40 °C
- C07 HNO3 / Water 50 67 WT%, 10 60 °C
- C09 H2O2 / Water 30 75 WT%, 4 44 °C
- C10 Ethylene Glycol / Water 10 50 WT%, -20 40 °C
- C11 Amylum = starch / Water 33 43 WT%, 35 45 °C
- C12 Methanol / Water 35 60 WT%, 0 40 °C
- C20 Alcohol / Water 55 100 VOL%, 10 40 °C
- C21 Sugar / Water 40 80 °Bx, 75 100 °C
- C30 Alcohol / Water 66 100 WT%, 15 40 °C
- C37 Alcohol / Water 66 100 WT%, 10 40 °C





### **TRADEMARKS**

HART:	registered trademark of FieldComm Group, Inc., US
Modbus:	registered trademark of SCHNEIDER ELECTRIC USA, INC.
PROFIBUS:	registered trademark of PROFIBUS Nutzerorganisation e.V., Karlsruhe, DE
FOUNDATION Fieldbus:	registered trademark of FieldComm Group, Inc., US
ROTAMASS:	registered trademark of Rota Yokogawa GmbH & Co. KG, DE
FieldMate:	registered trademark of YOKOGAWA ELECTRIC CORPORATION
SD:	registered trademark of SD-3C LLC.
QR code:	registered trademark of DENSO WAVE INCORPORATED

All other company and product names mentioned in this document are trade names, trademarks or registered trademarks of their respective companies. In this document, trademarks or registered trademarks are not marked with  $^{\text{TM}}$  or  $^{\text{R}}$ .

All rights reserved. Copyright © 2023-03-24

Manufacturer:

Rota Yokogawa GmbH & Co. KG Rheinstr. 8 D-79664 Wehr Germany COMPANY WITH QUALITY SYSTEM CERTIFIED BY DNV GL

= ISO 9001 =

For the actual manufacturing location of your device refer to the model code and/or serial number.