
General Specifications

ROTAMASS Total Insight Coriolis Mass Flow and Density Meter Intense





Scope of application

- Precise flow rate measurement of fluids and gases, multi-phase media and media with specific gas content using the Coriolis principle.
- Direct measurement of mass flow and density independent of the medium's physical properties, such as density, viscosity and homogeneity
- Concentration measurement of solutions, suspensions and emulsions
- Medium temperatures of -70 150 °C (-94 – 302 °F)
- Process pressures up to 248 bar
- ASME process connections, up to two nominal diameters per device meter size
- Connection to common process control systems, such as via HART7 or Modbus
- Hazardous area approvals: IECEx, ATEX, FM (USA/Canada), NEPSI, INMETRO, PESO
- Safety-related applications: PED per AD 2000
 Code, SIL 2, secondary containment up to 120 bar
- Marine type approval: DNV GL

Advantages and benefits

- Inline measurement of several process variables, such as mass, density and temperature
- Adapterless installation due to multi-size flange concept
- No straight pipe runs at inlet or outlet required
- Fast and uncomplicated commissioning and operation of the flow meter
- Maintenance-free operation
- Functions that can be activated subsequently (feature on demand)
- Total health check: Self-monitoring of the entire flow meter, including accuracy
- Maximum accuracy due to calibration facility accredited according to ISO/IEC 17025 (for option K5)
- Self-draining installation
- Immune to vibrations thanks to the counterbalanced dual tube flow meter and box-in-box design



Table of contents

1	Intro	oduction		5
	1.1	Applicable	e documents	5
	1.2	Product o	verview	6
2	Mea	suring pri	inciple and flow meter design	7
	2.1		g principleg	
	2.2		er	
3	Δnn	lication ar	nd measuring ranges	13
•	3.1		d quantities	
	3.2		g range overview	
	3.3	`	V	
			OW	
			loss	
	3.6		1000	
		•	ture	
		•		
4		•		
		•	t stability of the mass flow	
	4.3		v accuracy	
			Sample calculation for liquids	
	1 1		Sample calculation for gases	
	4.4	,	For liquids	
			For gases	
	4.5		of mass flow and density according to the MS code	
		-	For liquids	
			For gases	
	4.6	Volume flo	ow accuracy	21
		4.6.1	For liquids	21
		4.6.2	For gases	21
	4.7		of temperature	21
	4.8	Repeatab	oility	22
	4.9	Calibratio	n conditions	22
		4.9.1	Mass flow calibration and density adjustment	22
			Density calibration	
			pressure effect	
	4.11	Process to	emperature effect	24
5	Ope	erating con	nditions	25
	5.1	Location a	and position of installation	25
		5.1.1	Sensor installation position	25
	5.2	Installatio	n instructions	26
	5.3	Process o	conditions	27
			Medium temperature range	
			Density	
		5.3.3	Pressure	28

		5.3.4	Effect of temperature on accuracy	
		5.3.5	Secondary containment	
	5.4		conditions	
		5.4.1	Allowed ambient temperature for sensor	
		5.4.2	Temperature specification in hazardous areas	32
6	Mec	hanical s	specification	35
	6.1	Design		. 35
	6.2	Material		. 36
		6.2.1	Material wetted parts	
		6.2.2	Non-wetted parts	36
	6.3	Process	connections, dimensions and weights of sensor	. 37
	6.4	Transmit	tter dimensions and weights	. 39
7	Trar	nsmitter s	specification	41
	7.1	Inputs ar	nd outputs	. 42
		7.1.1	Output signals	43
		7.1.2	Input signals	49
	7.2	Power s	upply	. 50
	7.3	Cable sp	pecification	. 50
8	Арр	rovals ar	nd declarations of conformity	51
9			ormation	
•		•	w MS code Intense 34	
			w MS code Intense 36	
	9.3		w MS code Intense 38	
	9.4		v options	
	9.5		9	
	9.5	9.5.1	Sensor housing material	
		9.5.2	Transmitter	
		9.5.3	Sensor	
		9.5.4	Meter size	
		9.5.5	Material wetted parts	
		9.5.6	Process connection size	71
		9.5.7	Process connection type	72
		9.5.8	Medium temperature range	72
		9.5.9	Mass flow and density accuracy	72
		9.5.10	Design and housing	73
		9.5.11	Ex approval	74
		9.5.12	Cable entries	74
		9.5.13	Inputs and outputs	
		9.5.14	Display	76
	9.6	•		
		9.6.1	Connecting cable type and length	
		9.6.2	Additional nameplate information	
		9.6.3	Presetting of customer parameters	
		9.6.4	Concentration and petroleum measurement	
		9.6.5	Certificates	
		9.6.6	Country-specific delivery	80

Table of contents

	9.6.7	Rupture disc	81
	9.6.8	Tube health check	81
	9.6.9	Transmitter housing rotated 180°	81
	9.6.10	Measurement of heat quantity	82
	9.6.11	Marine Approval	82
	9.6.12	Customer specific special product manufacture	83
97	Ordering	Instructions	84



1 Introduction

1.1 Applicable documents

For Ex approval specification, refer to the following documents:

- Ex instruction manual ATEX IM 01U10X01-00__-R
- Ex instruction manual IECEx IM 01U10X02-00__-R
- Ex instruction manual FM IM 01U10X03-00__-R
- Ex instruction manual INMETRO IM 01U10X04-00__-R
- Ex instruction manual PESO IM 01U10X05-00__-R

Other applicable User's manuals:

Protection of Environment (Use in China only) IM 01A01B01-00ZH-R



Introduction Product overview

1.2 Product overview

Rotamass Coriolis flow meters are available in various product families distinguished by their applications. Each product family includes several product alternatives and additional device options that can be selected.

The following overview serves as a guide for selecting products.

Overview of Rotamass product families

		go a galaction colocating products.
		For low flow rate applications
		Meter sizes: Nano 06, Nano 08, Nano 10, Nano 15, Nano 20
Rotamass Nano		Connection sizes:
INATIO	the	• DN15, DN25, DN40
		• ½", ½", ¾", 1", 1½"
		Maximum mass flow: 1.5 t/h (55 lb/min)
		Versatility with low costs for the operator
		Meter sizes: Prime 25, Prime 40, Prime 50, Prime 80
Rotamass		Connection sizes:
Prime		 DN15, DN25, DN40, DN50, DN80
		• 3/8", 1/2", 3/4", 1", 11/2", 2", 21/2", 3"
		Maximum mass flow: 76 t/h (2800 lb/min)
		Excellent performance under demanding conditions
Determose		Meter sizes: Supreme 34, Supreme 36, Supreme 38, Supreme 39
Rotamass Supreme	Connection sizes:	Connection sizes:
Capicine		 DN15, DN25, DN40, DN50, DN80, DN100, DN125
		• 3/8", 1/2", 3/4", 1", 11/2", 2", 21/2", 3", 4", 5"
		Maximum mass flow: 170 t/h (6200 lb/min)
		For high process pressure applications
Rotamass	4	Meter sizes: Intense 34, Intense 36, Intense 38
Intense	9	Connection sizes:
		• ½", 1", 2"
		Maximum mass flow: 50 t/h (1800 lb/min)
	G. T.	For food, beverage and pharmaceutical applications
Potomoso		Meter sizes: Hygienic 25, Hygienic 40, Hygienic 50, Hygienic 80
Rotamass Hygienic		Connection sizes:
, 3		 DN25, DN40, DN50, DN65, DN80
		1 ", 1½", 2", 2½", 3"
		Maximum mass flow: 76 t/h (2800 lb/min)
		For high flow rate applications
		Meter sizes: Giga 1F, Giga 2H
Rotamass	V V	Connection sizes:
Giga		• DN100, DN125, DN150, DN200
		• 4", 5", 6", 8"
		Maximum mass flow: 600 t/h (22000 lb/min)



2 Measuring principle and flow meter design

2.1 Measuring principle

The measuring principle is based on the generation of Coriolis forces. For this purpose, a driver system (E) excites the two measuring tubes (M1, M2) in their first resonance frequency. Both pipes vibrate inversely phased, similar to a resonating tuning fork.




Fig. 1: Coriolis principle

M1,M2	Measuring tubes	Е	Driver system
S1, S2	Pick-offs	Α	Direction of measuring tube vibration
F1, F2	Coriolis forces	Q	Direction of medium flow

Mass flow

The medium flow through the vibrating measuring tubes generates Coriolis forces (F1, -F1 and F2, -F2) that produce positive or negative values for the tubes on the inflow or outflow side. These forces are directly proportional to the mass flow and result in deformation (torsion) of the measuring tubes.




Fig. 2: Coriolis forces and measuring tube deformation

1	Measuring tube mount	A_{E}	Rotational axis
2	Medium	F1, F2	Coriolis forces
3	Measuring tube	α	Torsion angle

The small deformation overlying the fundamental vibration is recorded by means of pick-offs (S1, S2) attached at suitable measuring tube locations. The resulting phase shift $\Delta \varphi$ between the output signals of pick-offs S1 and S2 is proportional to the mass flow. The output signals generated are further processed in a transmitter.




Fig. 3: Phase shift between output signals of S1 and S2 pick-offs

Λ.σ	~	E	~	d <i>m</i>
Δψ	_	r _C	~	$\overline{\mathrm{d}t}$

 $\Delta \varphi$ Phase shift

m Dynamic mass

t Time dm/dt Mass flow F_c Coriolis force

Density measurement

Using a driver and an electronic regulator, the measuring tubes are operated in their resonance frequency f. This resonance frequency is a function of measuring tube geometry, material properties and the mass of the medium covibrating in the measuring tubes. Altering the density and the attendant mass will alter the resonance frequency. The transmitter measures the resonance frequency and calculates density from it according to the formula below. Device-dependent constants are determined individually during calibration.




Fig. 4: Resonance frequency of measuring tubes

A Measuring tube displacement

 f_1 Resonance frequency with medium 1

f₂ Resonance frequency with medium 2

$$\rho = \frac{\alpha}{f^2} + \beta$$

ρ Medium density

f Resonance frequency of measuring tubes

 α, β Device-dependent constants

Temperature measurement

The measuring tube temperature is measured in order to compensate for the effects of temperature on the flow meter. This temperature approximately equals the medium temperature and is made available as a measured quantity at the transmitter as well.

2.2 Flow meter

The Rotamass Coriolis flow meter consists of:

- Sensor
- Transmitter

In the integral type, sensor and transmitter are firmly connected.




Fig. 5: Configuration of the Rotamass integral type

- 1 Transmitter
- 2 Sensor
- 3 Process connections

When the remote type is used, sensors and transmitters are linked via connecting cable. As a result, sensor and transmitter can be installed in different locations.




Fig. 6: Configuration of the Rotamass remote type

1	Transmitter	4	Sensor terminal box
2	Sensor	5	Connecting cable

3 Process connections

When the remote type is used, sensors and transmitters are linked via connecting cable. As a result, sensor and transmitter can be installed in different locations.




Fig. 7: Configuration of the Rotamass remote type - long neck

1	Transmitter		4	Sensor terminal box
2	Sensor		5	Connecting cable
_	_	4.		

3 Process connections

General specifications

All available properties of the Rotamass Coriolis flow meter are specified by means of a model code (MS code).

One MS code position may include several characters depicted by means of dashed lines.

The positions of the MS code relevant for the respective properties are depicted and highlighted in blue. Any values that might occupy these MS code positions are subsequently explained.




Fig. 8: Highlighted MS code positions




Fig. 9: Example of a completed MS code

A complete description of the MS code is included in the chapter entitled *Ordering information* [> 57].


Type of design

Position 10 of the MS code defines whether the integral type or the remote type is used. It specifies further flow meter properties, such as the transmitter coating, see *Design and housing* [> 73].



Flow meter	MS code Position 10
Integral type	0, 2
Remote type	A, E, J
Remote type - long neck	B, F, K

Transmitter overview Two different transmitters are available that differ in their functional scope.



Transmitter	Properties	MS code Position 1
Essential	 Down to 0.15 % mass flow accuracy for liquids Down to 0.75 % mass flow accuracy for gases Down to 4 g/l (0.25 lb/ft³) accuracy for density Diagnostic functions HART communication Modbus communication Data backup on microSD card 	E
Ultimate	 Down to 0.1 % mass flow accuracy for liquids Down to 0.5 % mass flow accuracy for gases Down to 0.5 g/l (0.03 lb/ft³) accuracy for density Diagnostic functions HART communication Modbus communication Special functions for special applications, such as dynamic pressure compensation Data backup on microSD card 	U

3 Application and measuring ranges

3.1 Measured quantities

The Rotamass Coriolis flow meter can be used to measure the following media:

- Liquids
- Gases
- Mixtures, such as emulsions, suspensions, slurries

Possible limitations applying to measurement of mixtures must be checked with the responsible Yokogawa sales organization.

The following variables can be measured using the Rotamass:

- Mass flow
- Density
- Temperature

Based on these measured quantities, the transmitter also calculates:

- Volume flow
- Partial component concentration of a two-component mixture
- Partial component flow rate of a mixture consisting of two components (net flow)

In this process, the net flow is calculated based on the known partial component concentration and the overall flow.

3.2 Measuring range overview

	Intense 34	Intense 36	Intense 38	
Mass flow range				
Typical connection size	1/2"	1"	2"	
Q _{nom}	3 t/h (110 lb/min)	10 t/h (370 lb/min)	32 t/h (1200 lb/min)	[1 4]
Q _{max}	5 t/h (180 lb/min)	17 t/h (620 lb/min)	50 t/h (1800 lb/min)	
Maximum volume flow				
(Water)		17 m ³ /h (140 barrel/h)	50 m ³ /h (420 barrel/h)	[14]
Range of medium density				
		0 – 5 kg/l (0 – 310 lb/ft³)		[14]
Medium temperature range				
Standard ¹⁾		-70 – 150 °C (-94 – 302 °F)		[27]

¹⁾ May vary depending on the design.

Q_{nom} - Nominal mass flow


Q_{max} - Maximum mass flow

The nominal mass flow Q_{nom} is defined as the mass flow of water (temperature: 20 °C) at 1 bar pressure loss along the flow meter.



3.3 Mass flow

For Rotamass Intense the following meter sizes to be determined using the *MS code* [> 70] are available.



Mass flow of liquids

Meter size	Typical connection size	Q _{nom} in t/h (lb/min)	Q _{max} in t/h (lb/min)	MS code Position 3
Intense 34	1/2"	3 (110)	5 (180)	34
Intense 36	1"	10 (370)	17 (620)	36
Intense 38	2"	32 (1200)	50 (1800)	38

Mass flow of gases

When using the Rotamass for measuring the flow of gases, the mass flow is usually limited by the pressure loss generated and the maximum flow velocity. Since these depend heavily on the application, please contact the local Yokogawa sales organization.

3.4 Volume flow

Volume flow of liquids (water at 20 °C)

Meter size	Volume flow (at 1 bar pressure loss) in m³/h (barrel/h)	Maximum volume flow in m³/h (barrel/h)
Intense 34	3 (25)	5 (42)
Intense 36	10 (84)	17 (140)
Intense 38	32 (270)	50 (420)

Volume flow of gases

When using the Rotamass for measuring the flow of gases, the flow rate is usually limited by the pressure loss generated and the maximum flow velocity. Since these depend heavily on the application, please contact the local Yokogawa sales organization.

3.5 Pressure loss

The pressure loss along the flow meter is heavily dependent on the application. The pressure loss of 1 bar at nominal mass flow Q_{nom} also applies to water and is considered the reference value.

3.6 Density

Meter size	Measuring range of density
Intense 34	
Intense 36	0 – 5 kg/l (0 – 310 lb/ft³)
Intense 38	

Rather than being measured directly, density of gas is usually calculated using its reference density, process temperature and process pressure.

3.7 Temperature

The temperature measuring range is limited by the allowed process temperature, see *Medium temperature range* [> 27].

Maximum measuring range: -70 – 150 °C (-94 – 302 °F)

4 Accuracy

In this chapter, maximum deviations are indicated as absolute values.



All accuracy data are given in ± values.

4.1 Overview

Achievable accuracies for liquids

The value D_{flat} specified for accuracy of mass flow applies for flow rates exceeding the mass flow limit Q_{flat} . If the flow rate is less then Q_{flat} , other effects have to be considered.

The following values are achieved at calibration conditions when the device is delivered, see *Calibration conditions* [22]. Depending on the product version selected, specifications may not be as accurate, see *Mass flow and density accuracy* [72].

Measured quantity		Accuracy for transmitters		
		Essential	Ultimate	
Mass flow ¹⁾	Accuracy ²⁾ D _{flat}	0.15 % of measured value	0.1 % of measured value	
IVIASS HOW	Repeatability	0.08 % of measured value	0.05 % of measured value	
Volume flow	Accuracy ²⁾ D _V	0.43 % of measured value	0.12 % of measured value	
(water) ¹⁾	Repeatability	0.22 % of measured value	0.06 % of measured value	
Donoity	Accuracy ²⁾	4 g/l (0.25 lb/ft³)	0.5 g/l (0.03 lb/ft³)	
Density	Repeatability	2 g/l (0.13 lb/ft³)	0.3 g/l (0.02 lb/ft³)	
Temperature	Accuracy ²⁾	0.5 °C (0.9 °F)	0.5 °C (0.9 °F)	

¹⁾ Based on the measured values of the pulse output. Includes the combined effects of repeatability, linearity and hysteresis.

The connecting cable may influence the accuracy. The values specified are valid for connecting cables \leq 30 m (98.4 ft) long.

Achievable accuracies for gases

Measured quantity		Accuracy for transmitters		
		Essential	Ultimate	
Mass flow / standard volume	Accuracy ²⁾ D _{flat}	0.75 % of measured value	0.5 % of measured value	
flow ¹⁾	Repeatability	0.6 % of measured value	0.4 % of measured value	
Temperature	Accuracy ²⁾	0.5 °C (0.9 °F)	0.5 °C (0.9 °F)	

¹⁾ Based on the measured values of the pulse output. Includes the combined effects of repeatability, linearity and hysteresis.

In the event of medium temperature jumps, a delay is to be expected in the temperature being displayed due to low heat capacity and heat conductivity of gases.

The connecting cable may influence the accuracy. The values specified are valid for connecting cables \leq 30 m (98.4 ft) long.

²⁾ Best accuracy per transmitter type

²⁾ Best mass flow accuracy per transmitter type

4.2 Zero point stability of the mass flow

In case of no flow, the maximum measured flow rate is called *Zero point stability*. Zero point values are shown in the table below.

Meter size	Zero point stability Z in kg/h (lb/min)
Intense 34	0.15 (0.0055)
Intense 36	0.5 (0.018)
Intense 38	1.6 (0.059)

4.3 Mass flow accuracy

Above mass flow Q_{flat} , maximum deviation is constant and referred to as D_{flat} . It depends on the product version and can be found in the tables in chapter *Accuracy of mass flow* and density according to the MS code [\triangleright 20].

Use the following formulas to calculate the maximum deviation *D*:

$$Q_m \ge Q_{flat}$$

$$D = D_{flat}$$

$$Q_m < Q_{flat}$$

$$D = \frac{a \times 100 \%}{Q_m} + b$$

D Maximum deviation in % $Q_{\rm m}$ Mass flow in kg/h

 D_{flat} Maximum deviation for high flow Q_{flat} Mass flow value above which D_{flat} applies, in kg/h

a, b Constants

Meter size	MS code Position 9	D _{flat} in %	Q _{flat} in kg/h	a in kg/h	b in %
	E7	0.2	150	0.38	-0.05
	D7	0.15	200	0.21	0.043
Intense 34	C2, C3	0.1	300	0.17	0.044
	70	0.75	150	0.25	0.583
	50	0.5	300	0.17	0.444
	E7	0.2	500	1.3	-0.05
	D7	0.15	667	0.71	0.043
Intense 36	C2, C3	0.1	1000	0.56	0.044
	70	0.75	500	0.83	0.583
	50	0.5	1000	0.56	0.444
	E7	0.2	1600	4	-0.05
	D7	0.15	2130	2.3	0.043
Intense 38	C2, C3	0.1	3200	1.8	0.044
	70	0.75	1600	2.7	0.583
	50	0.5	3200	1.8	0.444

Accuracy Mass flow accuracy

4.3.1 Sample calculation for liquids

Accuracy using water at 20 °C as an example




Fig. 10: Schematic dependency of the maximum deviation on the mass flow

D Maximum deviation in % Q_{m} Mass flow in kg/h $\mathbf{Q}_{\mathrm{nom}}$ Mass flow above which D_{flat} Nominal mass flow in kg/h Q_{flat}

applies, in kg/h

Turn down Q_m : Q_{nom}	Maximum deviation D	Water pressure loss
1:100	0.6 %	≈ 0 mbar (0 psi)
1:40	0.3 %	0.7 mbar (0.01 psi)
1:10	0.1 %	10 mbar (0.15 psi)
1:2	0.1 %	250 mbar (3.62 psi)
1:1	0.1 %	1000 mbar (14.50 psi)

Example

Medium: Liquid Maximum deviation D_{flat} : 0.1 % 300 kg/h Q_{flat}: Constant a: 0.17 kg/h Constant b: 0.044 % Value of mass flow Q_m: 75 kg/h

Calculation of flow rate condition:

 $Q_m \ge Q_{flat}$

Check whether

 $Q = 75 \text{ kg/h} < Q_{flat} = 300 \text{ kg/h}$

As a result, accuracy is calculated using the following formula:

$$D = \frac{a \times 100 \%}{Q_m} + b$$

Calculation of accuracy:

 $D = 0.17 \text{ kg/h} \times 100 \% / 75 \text{ kg/h} + 0.044 \%$

D = 0.27 %


Accuracy Mass flow accuracy

4.3.2 Sample calculation for gases

The maximum deviation in the case of gases depends on the product version selected, see also *Mass flow and density accuracy* [> 72].

Example

Calculation of the flow rate condition:



Check whether

$$Q_{\rm m}$$
 = 30 kg/h < $Q_{\rm flat}$ = 300 kg/h

As a result, the accuracy is calculated using the following formula:

$$D = \frac{a \times 100 \%}{Q_m} + b$$

Calculation of accuracy:

$$D = 0.17 \text{ kg/h} \times 100 \% / 30 \text{ kg/h} + 0.444 \%$$

$$D = 1.01 \%$$

4.4 Accuracy of density

4.4.1 For liquids

Meter size	Transmitter	Maximum deviation of density ¹⁾ in g/l (lb/ft³)	
Intense 34			
Intense 36	Essential	Down to 4 (0.25)	
Intense 38			
Intense 34			
Intense 36	Ultimate	Down to 0.5 (0.03)	
Intense 38			

¹⁾ Deviations possible depending on product version (meter size, type of calibration)

The maximum deviation depends on the product version selected, see also Accuracy of mass flow and density according to the MS code [20].

4.4.2 For gases

In most applications, density at standard conditions is fed into the transmitter and used to calculate the standard volume flow based on mass flow.

If gas pressure is a known value, after entering a reference density, the transmitter is able to calculate gas density from temperature and pressure as well (while assuming an ideal gas).

Alternatively, there is an option for measuring gas density. In order to do so, it is necessary to adapt the lower density limit value in the transmitter.


For most applications the direct measurement of the gas density will have insufficient accuracy.



4.5 Accuracy of mass flow and density according to the MS code

Accuracy for flow rate as well as density is selected via MS code position 9. Here a distinction is made between devices for measuring liquids and devices for measuring gases. No accuracy for density measurement is specified for gas measurement devices.

4.5.1 For liquids



Essential

MS code Position 9	Maximum deviation of	Applicable measuring range of accuracy in kg/l Maximum description of the measuring range of accuracy accuracy in kg/l	deviation D_{flat} for mass flow in %		
	density 1) in g/l		Intense 34	Intense 36	Intense 38
E7	4	0.3 - 5	0.2	0.2	0.2
D7	4	0.3 - 5	0.15	0.15	0.15


¹⁾ Specified maximum deviation is achieved within the applicable measuring range for density.

Ultimate

MS code Position 9	Maximum deviation of	Applicable measuring	easuring		deviation $D_{ ext{flat}}$ for mass flow in %	
	density 1) in g/l	range of accuracy in kg/l	Intense 34	Intense 36	Intense 38	
C3	1	0.3 - 5	0.1	0.1	0.1	
C2	0.5	0.3 - 2.5	0.1	0.1	0.1	

¹⁾ Specified maximum deviation is achieved within the applicable measuring range for density.

4.5.2 For gases



Essential

Maximum deviation D_{flat} of mass flow in %	MS code Position 9
0.75	70
Maximum deviation D_{flat} of mass flow	MS code

Ultimate

Maximum deviation D_{flat} of mass flow in %	MS code Position 9
0.5	50

4.6 Volume flow accuracy

4.6.1 For liquids

The following formula can be used to calculate the accuracy of liquid volume flow:

$$D_{V} = \sqrt{D^{2} + \left(\frac{\Delta \rho}{\rho} \times 100\%\right)^{2}}$$

 D_{\vee} Maximum deviation of volume flow D Maximum deviation of mass flow in

Density in kg/l

Maximum deviation of density in

kg/l

4.6.2 For gases

Δρ

Accuracy of standard volume flow for gas with a fixed composition equals the maximum deviation D of the mass flow.

$$D_{\vee} = D$$



In order to determine the standard volume flow for gas, it is necessary to input a reference density in the transmitter. The accuracy specified is achieved only for fixed gas composites. Major deviations may appear if the gas composition changes.

4.7 Accuracy of temperature

Various medium temperature ranges are specified for Rotamass Intense:

- Integral type: -50 150 °C (-58 302 °F)
- Remote type: -70 150 °C (-94 302 °F)

Accuracy of temperature depends on the sensor temperature range selected (see Medium temperature range [▶ 27]) and can be calculated as follows:

Formula for temperature specification Standard

$$\Delta T = 0.5 \,^{\circ}\text{C} + 0.005 \times |T_{pro} - 20 \,^{\circ}\text{C}|$$

ΔΤ Maximum deviation of temperature

 T_{pro} Temperature of medium in °C




Fig. 11: Presentation of temperature accuracy

Accuracy Repeatability

Example

The sample MS code specifies the Standard temperature range.

Temperature of medium T_{pro}: 50 °C

Calculation of accuracy:

$$\Delta T = 0.5 \,^{\circ}C + 0.005 \times |50 \,^{\circ}C - 20 \,^{\circ}C|$$

$$\Delta T = 0.65 \, ^{\circ}C$$

4.8 Repeatability

For liquids

When using default damping times, the specified repeatability of mass flow, density and temperature measurements equals half of the respective maximum deviation.

$$R = \frac{D}{2}$$

R Repeatability

D Maximum deviation

For gases

In deviation hereto, the following applies to mass and standard volume flow of gases:

$$R = \frac{D}{1.25}$$

4.9 Calibration conditions

4.9.1 Mass flow calibration and density adjustment

All Rotamass are calibrated in accordance with the state of the art at Rota Yokogawa. Optionally, the calibration can be performed according to a method accredited by DAkkS in accordance with DIN EN ISO/IEC 17025 (Option K5, see *Certificates* [79]).

Each Rotamass device comes with a standard calibration certificate.

Calibration takes place at reference conditions. Specific values are listed in the standard calibration certificate.

	Reference conditions	
Medium	Water	
Density	0.9 – 1.1 kg/l (56 – 69 lb/ft³)	
Madium tomporatura	10 – 35 °C (50 – 95 °F)	
Medium temperature	Average temperature: 22.5 °C (72.5 °F)	
Ambient temperature	10 – 35 °C (50 – 95 °F)	
Process pressure (absolute)	1 – 2 bar (15 – 29 psi)	

The accuracy specified is achieved at as-delivered calibration conditions stated.



4.9.2 Density calibration

Density calibration is performed for maximum deviation of 0.5 g/l (MS code position 9 _2). Density calibration includes:

- Determination of calibration constants for medium densities at 0.7 kg/l (44 lb/ft³), 1 kg/l (62 lb/ft³) and 1.65 kg/l (103 lb/ft³) at 20 °C (68 °F) medium temperature
- Determination of temperature compensation coefficients at 20 80 °C (68 176 °F)
- Check of results for medium densities at 0.7 kg/l (44 lb/ft³), 1 kg/l (62 lb/ft³) and 1.65 kg/l (103 lb/ft³) at 20 °C (68 °F) medium temperature
- Special flow meter configuration:
 - Specific insulation of temperature sensors
 - Preaging for long-term stability
- · Creation of density calibration certificate

4.10 Process pressure effect

Process pressure effect is defined as the change in sensor flow and density deviation due to process pressure change away from the calibration pressure. This effect can be corrected by dynamic pressure input or a fixed process pressure.

Tab. 1: Process pressure effect for Rotamass Intense models wetted parts Stainless steel 1.4404/316L

Meter size	Deviation of Flow		Deviation of Density	
	% of rate per bar % of rate per psi		g/l per bar	g/l per psi
Intense 34	-0.0005	-0.00003	-0.066	-0.0046
Intense 36	-0.0024	-0.00017	-0.193	-0.0133
Intense 38	-0.0034	-0.00023	-0.378	-0.0261

Tab. 2: Process pressure effect for Rotamass Intense models wetted parts Ni alloy C-22/ 2.4602

Meter size	Deviation of Flow		Deviation of Density	
	% of rate per bar % of rate per psi g		g/l per bar	g/l per psi
Intense 34	-0.0005	-0.00003	-0.076	-0.0052
Intense 36	-0.0023	-0.00016	-0.192	-0.0132
Intense 38	-0.0035	-0.00024	-0.381	-0.0263



4.11 Process temperature effect

For mass flow and density measurement, process temperature effect is defined as the change in sensor flow and density accuracy due to process temperature change away from the calibration temperature. For temperature ranges, see *Medium temperature* range [* 27].

Temperature effect on Zero

Temperature effect on Zero of mass flow can be corrected by zeroing at the process temperature.

Temperature effect on mass flow


The process temperature is measured and the temperature effect compensated. However due to uncertainties in the compensation coefficients and in the temperature measurement an uncertainty of this compensation is left. The typical rest error of Rotamass TI temperature effect on mass flow is:

Tab. 3: All models

Temperature range	Uncertainty of flow
Standard	±0.0011 % of rate / °C (±0.0006 % of rate / °F)

The temperature used for calculation of the uncertainty is the difference between process temperature and the temperature at calibration condition. For temperature ranges, see *Medium temperature range* [> 27].

Temperature effect on density measurement (liquids)



Process temperature influence:

Formula for metric values

$$D'_{\rho} = \pm k \times \text{abs } (T_{\text{pro}} - 20 \,^{\circ}\text{C})$$

Formula for imperial values

$$D'_{\rho} = \pm k \times \text{abs } (T_{\text{pro}} - 68 \,^{\circ}\text{F})$$

 D'_{ρ} Additional density deviation due to the effect of medium temperature in kg/l (lb/ ft³)

T_{pro} Temperature of medium in °C (°F)

k Constant for temperature effect on density measurement in g/l × 1/°C (lb/ft 3 × 1/°F)

Tab. 4: Constants for particular meter size and MS code Position (see also *Medium temperature range* [▶ 27] and *Mass flow and density accuracy* [▶ 72])

Meter size	MS code Position 4	MS code Position 8	MS code Position 9	k in g/l × 1/°C (lb/ft³ × 1/°F)
	S		C2 D7 F7	0.150 (0.0052)
Intense 34	Н		C3, D7, E7	0.160 (0.0055)
intense 34	S		C2	0.060 (0.0021)
	Н		C2	0.022 (0.0008)
	S		C3, D7, E7	0.100 (0.0035)
Intense 36	Н	0	C3, D7, E7	0.090 (0.0031)
intense 36	S	U	00	0.029 (0.0010)
	Н		C2	0.015 (0.0005)
	S		C2 D7 F7	0.070 (0.0024)
Intense 38	Н		C3, D7, E7	0.060 (0.0021)
intense 38	S		C2	0.024 (0.0008)
	Н		62	0.015 (0.0005)

5 Operating conditions

5.1 Location and position of installation

Rotamass Coriolis flow meters can be mounted horizontally, vertically and at an incline. The measuring tubes should be completely filled with the medium during flow measurement as accumulations of air or formation of gas bubbles in the measuring tube may result in errors in measurement. Straight pipe runs at inlet or outlet are usually not required.

Avoid the following installation locations and positions:

- Measuring tubes as highest point in piping when measuring liquids
- Measuring tubes as lowest point in piping when measuring gases
- Immediately in front of a free pipe outlet in a downpipe
- Lateral positions




Fig. 12: Installation position to be avoided: Flow meter in sideways position

5.1.1 Sensor installation position

Sensor installation position as a function of the medium

Installation position	Medium	Description
Horizontal, measuring tubes at bottom	Liquid	The measuring tubes are oriented toward the bottom. Accumulation of gas bubbles is avoided.
Horizontal, measuring tubes at top	Gas	The measuring tubes are oriented toward the top. Accumulation of liquid, such as condensate is avoided.

Installation position	Medium	Description
Vertical, direction of flow towards the top	Liquid/gas	The sensor is installed on a pipe with the direction of flow towards the top. Accumulation of gas bubbles or solids is avoided. This position allows for complete self-draining of the measuring tubes.

5.2 Installation instructions

The following instructions for installation must be observed:

- 1. Protect the flow meter from direct sun irradiation in order to avoid exceeding the maximum allowed internal temperature of the transmitter.
- 2. In case of installing two sensors of the same kind back-to-back redundantly, use a customized design and contact the responsible Yokogawa sales organization.
- 3. Avoid installation locations susceptible to cavitation, such as immediately behind a control valve.
- 4. Avoid installation directly behind rotary and gear pumps to prevent fluctuations in pressure from interfering with the resonance frequency of the Rotamass measuring tubes.
- 5. In case of remote installation: When installing the connection cable between sensor and transmitter, keep the cable temperature above -10 °C (14 °F) to prevent cable damage from the installation stresses.



5.3 Process conditions




The pressure and temperature ratings presented in this section represent the design values for the devices. For individual applications (e.g. marine applications with option MC_) further limitations may apply according to the respective applicable regulations. For details see chapter *Marine Approval* [82]

5.3.1 Medium temperature range



The Rotamass specification for use in Ex areas is different, see Ex instruction manual (IM 01U10X__-00EN).

For Rotamass Intense the following medium temperature ranges are available:



Temperature range	MS code Position 8	Medium temperature in °C (°F)	Design	MS code Position 10
Standard	0	-50 - 150 (-58 - 302)	Integral type	0, 2
Stariuaru	U	-70 – 150 (-94 – 302)	Remote type	A, B, E, F, J, K

5.3.2 Density

Meter size	Measuring range of density	
Intense 34		
Intense 36	0 – 5 kg/l (0 – 310 lb/ft³)	
Intense 38		

Rather than being measured directly, density of gas is usually calculated using its reference density, process temperature and process pressure.

5.3.3 Pressure

The maximum allowed process pressure depends on the process connection temperature and the process connections selected.

The following diagrams show the process pressure as a function of process connection temperature as well as the process connection used (type and size of process connection).

ASME class 900




Fig. 13: Allowed process pressure as a function of process connection temperature, suitable for flange ASME B16.5 class 900

ASME class 1500




Fig. 14: Allowed process pressure as a function of process connection temperature, flange suitable for process connection ASME B16.5 class 1500, Intense 34

- 1 Flange suitable for ASME B16.5 class 1500, Intense 34H with option /P15 and Intense 34S without option /P15
- 2 Flange suitable for ASME B16.5 class 1500, Intense 34S with /P15

Rupture disc

The rupture disc is located on the sensor housing. It is available as an option, see *rupture disc* [81]. The rupture disc's bursting pressure is 20 bar. In the case of big nominal diameters and high pressures, it is not possible to ensure that the entire process pressure is released across the rupture disc. In the event this is necessary, it is possible to request a customized design from the responsible Yokogawa sales organization. In the event of a burst pipe, the rupture disc provides an acoustic signal in applications with gases.

5.3.4 Effect of temperature on accuracy

Effect of medium temperature

The specified accuracy of the density measurement (see *Mass flow and density accuracy* [> 72]) applies at calibration conditions and may deteriorate if medium temperatures deviate from those conditions. The effect of temperature is minimal for the product version with MS code position 9, value _2.



The effect of temperature is calculated as follows:

Formula for metric values

$$D'_{o} = \pm k \times \text{abs} (T_{\text{pro}} - 20 \,^{\circ}\text{C})$$

Formula for imperial values

$$D'_{\rho} = \pm k \times \text{abs } (T_{\text{pro}} - 68 \,^{\circ}\text{F})$$

 D'_{ρ} Additional density deviation due to the effect of medium temperature in kg/l (lb/ ft³)

Temperature of medium in °C (°F)

k Constant for temperature effect on density measurement in g/l × 1/°C (lb/ft 3 × 1/°F)

5.3.5 Secondary containment

Some applications or environment conditions require secondary containment retaining the process pressure for increased safety. All Rotamass TI have a secondary containment filled with inert gas. The rupture pressure typical values of the secondary housing are defined in the below table.

Typical Rupture pressure

Intense 34S	Intense 34H	Intense 36S	Intense 38S
Rupture pressure in bar (psi)			
120 (1740)	120 (1740)	120 (1740)	120 (1740)

5.4 Ambient conditions

Rotamass can be used at demanding ambient conditions.

In doing so, the following specifications must be taken into account:

Ambient temperature

Sensor: see [▶ 31]

Transmitter: $-40 - 60 \, ^{\circ}\text{C} \, (-40 - 140 \, ^{\circ}\text{F})$

Cable:

standard (option L___): -50 °C - 80 °C (-58 °F - 176 °F) fire retardant (option Y___): -35 °C - 80 °C (-31 °F - 176 °F)

Transmitter display has limited legibility

below -20 °C (-4 °F)

Sensor: -50 - 80 °C (-58 - 176 °F) Storage temperature

Transmitter: $-40 - 60 \,^{\circ}\text{C} \, (-40 - 140 \,^{\circ}\text{F})$

Cable:

standard (option L___ -50 °C - 80 °C (-58 °F - 176 °F) fire retardant (option Y___): -35 °C - 80 °C (-31 °F - 176 °F)

Relative humidity

IP code

0 - 95 %

4 (in operation)

IP66/67 for transmitters and sensors when using the appropriate cable glands

Allowable pollution degree in surrounding

area according to EN 61010-1

Vibration resistance according to IEC

60068-2-6

Transmitter: 10 - 500 Hz, 1g

Sensor: 25 - 100 Hz, 4q Requirement during immunity tests: The

Electromagnetic compatibility (EMC) according to IEC/EN 61326-1, Class A, Table 2, IEC/EN 61326-2-3, IEC/EN 61000-3-2, IEC/EN 61000-3-3 as well as NAMUR recommendation NE 21 and environmental tests according to DNVGL-CG-0339

Maximum altitude

±1 % of the output span.

output signal fluctuation is specified within

2000 m (6600 ft) above mean sea level (MSL)


Overvoltage category according to IEC/EN

61010-1

5.4.1 Allowed ambient temperature for sensor

The allowed ambient temperature depends on the following product properties:

- Temperature specification, see *Medium temperature range* [▶ 27]
- Housing design
 - Integral type
 - Remote type
- Connecting cable type (Options L___ and Y___)



The allowed combinations of medium and ambient temperature for the sensor are illustrated as gray areas in the diagrams below.

The Rotamass specification for use in Ex areas is different, see Ex instruction manual (IM 01U10X__-00EN).

The minimum allowed ambient temperature for remote fire retardant connecting cable type Y___ is -35 °C. In case of process temperatures below -35 °C, the minimum allowed ambient temperature has to be reconsidered.

Temperature specification Standard, integral type

(i)




Fig. 15: Allowed medium and ambient temperatures, integral type

T_{amb} Ambient temperature

T_{pro} Medium temperature

Temperature specification Standard, remote type




Fig. 16: Allowed medium and ambient temperatures, remote type

5.4.2 Temperature specification in hazardous areas

Maximum ambient and process temperatures depending on explosion groups and temperature classes can be determined via the MS code or via the MS code together with the Ex code (see the corresponding Ex instruction manual).


MS code:

Pos. 2: T Pos. 8: 0

Pos. 10: 0, 2 Pos. 11: _F21, FF11

Ex code:

6.85.86.87.54.10



The following figure shows the relevant positions of the MS code:

Tab. 5: Temperature classification


Temperature class	Maximum ambient temperature in °C (°F)	Maximum medium temperature in °C (°F)
T6	43 (109)	66 (150)
T5	58 (136)	82 (179)
T4	60 (140)	118 (244)
T3	60 (140)	150 (302)
T2	60 (140)	150 (302)
T1	60 (140)	150 (302)

MS code:

Pos. 2: T Pos. 8: 0 Pos. 10: 0, 2

Pos. 11: _F22, FF12

Ex code: 2.78.79.81.54.10 The following figure shows the relevant positions of the MS code:



Tab. 6: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)	Maximum medium temperature in °C (°F)
T6	59 (138)	59 (138)
T5	60 (140)	75 (167)
T4	60 (140)	112 (233)
T3	60 (140)	150 (302)
T2	60 (140)	150 (302)
T1	60 (140)	150 (302)


MS code: Pos. 2: T

Pos. 8: 0

Pos. 10: A, E, J Pos. 11: _F21, FF11

Ex code: 6.85.86.87.54.10

The following figure shows the relevant positions of the MS code:



Tab. 7: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum medium temperature in °C (°F)	
	Option L	Option Y¹)		
T6	41 (105)	41 (105)	66 (150)	
T5	56 (132)	56 (132)	82 (179)	
T4	80 (176)	62 (143)	118 (244)	
T3	78 (172)	49 (120)	150 (302)	
T2	78 (172)	49 (120)	150 (302)	
T1	78 (172)	49 (120)	150 (302)	

¹⁾ not with MS code Pos. 11: FF11


MS code:

Pos. 2: T Pos. 8: 0

Pos. 10: A, E, J Pos. 11: _F22, FF12

Ex code:

2.78.79.81.54.10



The following figure shows the relevant positions of the MS code:

Tab. 8: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum medium temperature in °C (°F)	
	Option L	Option Y ¹⁾		
T6	59 (138)	59 (138)	59 (138)	
T5	75 (167)	75 (167)	75 (167)	
T4	80 (176)	65 (149)	112 (233)	
T3	78 (172)	49 (120)	150 (302)	
T2	78 (172)	49 (120)	150 (302)	
T1	78 (172)	49 (120)	150 (302)	

¹⁾ not with MS code Pos. 11: FF12

MS code: Pos. 2: T


Pos. 8: 0

Pos. 10: B, F, K Pos. 11: _F21, FF11

Ex code:

6.85.86.87.54.10

The following figure shows the relevant positions of the MS code:



Tab. 9: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum medium temperature in °C (°F)	
	Option L	Option Y¹)		
T6	47 (116)	47 (116)	66 (150)	
T5	62 (143)	62 (143)	82 (179)	
T4	80 (176)	74 (165)	118 (244)	
T3	80 (176)	70 (158)	150 (302)	
T2	80 (176)	70 (158)	150 (302)	
T1	80 (176)	70 (158)	150 (302)	

¹⁾ not with MS code Pos. 11: FF11

MS code: Pos. 2: T Pos. 8: 0

Pos. 10: B, F, K Pos. 11: _F22, FF12

Ex code: 2.78.79.81.54.10

The following figure shows the relevant positions of the MS code:



Tab. 10: Temperature classification

Temperature class	Maximum ambient temperature in °C (°F)		Maximum medium temperature in °C (°F)	
	Option L	Option Y¹)		
T6	59 (138)	59 (138)	59 (138)	
T5	75 (167)	75 (167)	75 (167)	
T4	80 (176)	74 (165)	112 (233)	
T3	80 (176)	70 (158)	150 (302)	
T2	80 (176)	70 (158)	150 (302)	
T1	80 (176)	70 (158)	150 (302)	

¹⁾ not with MS code Pos. 11: FF12

6 Mechanical specification

6.1 Design

The Rotamass flow meter is available with two versions:

- Integral type, sensor and transmitter are firmly connected
- Remote type
 - Standard terminal box
 - Long neck




Fig. 17: Standard terminal box and long neck



Design	Design	MS code	
		Position 10	
Integral type	Direct connection	0, 2	
Domete tune	Standard terminal box	A, E, J	
Remote type	Long neck	B, F, K	




The design influences the temperature specification for Ex-approved Rotamass, see Ex instruction manual (IM 01U10X__-00EN-R).

6.2 Material

6.2.1 Material wetted parts

The wetted parts of Rotamass Intense are available in two material versions.

For corrosive media, use of a corrosion-resistant nickel alloy (nickel alloy C-22/2.4602) is recommended for wetted parts.




Material	MS code Position 4
Stainless steel 1.4404/316L	S
Nickel alloy C-22/2.4602	Н

6.2.2 Non-wetted parts

Housing material of sensor and transmitter are specified via MS code position 7 and position 10.

Sensor housing material



Housing material	MS code Position 7
Stainless steel 1.4301/304, 1.4404/316L	0
Stainless steel 1.4404/316L	1

Transmitter housing material, coating and bracket

The transmitter housing is available with different coatings:

- Standard coating
 Urethane-cured polyester powder coating
- Corrosion protection coating

Three-layer coating with high mechanical and chemical resistance (polyurethane coating on two layers of epoxy coating)



Housing material	Coating	Design	MS code Position 10	Bracket material
Aluminum	Standard coating	Integral type	0	_
		Remote type	A, B	Stainless steel 1.4301/304
Al-Si10Mg(Fe)	Corrosion protection coating	Integral type	2	_
		Remote type	E, F	Stainless steel 1.4301/304
Stainless steel CF8M	_	Remote type	J, K	Stainless steel 1.4404/316L

See also Design and housing [> 73].

Nameplate

For stainless steel transmitter the nameplates are made of stainless steel 1.4404/316L. In case of sensor housing material stainless steel 1.4404/316L (MS code position 7, value 1), nameplates of sensor are made of stainless steel 1.4404/316L.

6.3 Process connections, dimensions and weights of sensor




Fig. 18: Dimensions in mm

Tab. 11: Dimensions without length L1


Meter size	L2	L3	H1	НЗ	H4	H5	H6	W1	W2
		in mm (inch)							
Intense 34	272	212	177	279	80	138	218	60	80
	(10.7)	(8.3)	(7)	(11)	(3.1)	(5.4)	(8.6)	(2.4)	(3.1)
Intense 36	400	266	230	279	80	138	218	76	90
	(15.7)	(10.5)	(9.1)	(11)	(3.1)	(5.4)	(8.6)	(3)	(3.5)
Intense 38	490	267	268	289	100	148	228	89	110
	(19.3)	(10.5)	(10.6)	(11.4)	(3.9)	(5.8)	(9)	(3.5)	(4.3)

Overall length L1 and weight

The overall length of the sensor depends on the selected process connection (type and size of flange). The following tables list the overall length and weight as functions of the individual process connection.

The weights in the tables are for the remote type with standard neck. Additional weight for the remote type with long neck: 1 kg (2.2). Additional weight for the integral type: 3.5 kg (7.7 lb).


Process connections suitable for ASME B16.5



Tab. 12: Overall length L1 and weight of sensor (process connections: ASME, wetted parts: stainless steel)

Process connections		code ition	Inten	se 34	Inten	se 36	Inten	se 38
	5	6	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)
ASME ½" class 900		BA5	400 (15.7)	12.6 (28)	_	_	_	_
ASME ½" class 900, ring joint	15	CA5	400 (15.7)	12.8 (28)	_	_	_	_
ASME ½" class 1500	15	BA6	400 (15.7)	12.6 (28)	_	_	_	_
ASME ½" class 1500, ring joint		CA6	400 (15.7)	12.8 (28)	_	_	_	_
ASME 1" class 900		BA5	450 (17.7)	16.4 (36)	540 (21.3)	20.2 (45)	_	_
ASME 1" class 900, ring joint	25	CA5	450 (17.7)	16.6 (37)	540 (21.3)	20.4 (45)	_	_
ASME 1" class 1500	23	BA6	450 (17.7)	16.4 (36)	_	_	_	_
ASME 1" class 1500, ring joint		CA6	450 (17.7)	16.6 (37)	_	_	_	_
ASME 2" class 900	50	BA5	_	_	660 (26)	35.2 (78)	720 (28.3)	43 (95)
ASME 2" class 900, ring joint	50	CA5	_	_	660 (26)	35.6 (78)	720 (28.3)	43.4 (96)

Meaning of "-": not available



Tab. 13: Overall length L1 and weight of sensor (process connections: ASME, wetted parts: Ni alloy C-22/2.4602)

Process connections	MS o	code ition	Inten	se 34	Inten	se 36	Inten	se 38
	5	6	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)	L1 in mm (inch)	Weight in kg (lb)
ASME 1" class 900	25	BA5	400 (15.7)	16.2 (36)	_	_	_	_
ASME 1" class 1500	25	BA6	400 (15.7)	16.2 (36)	_	_	_	_

Meaning of "-": not available

6.4 Transmitter dimensions and weights

Transmitter dimensions




Fig. 19: Dimensions of transmitter in mm (left: transmitter with display, right: transmitter without display)

Material	L1	L2	L3	L4	H1	H2	H3	H4
	in mm	in mm	in mm	in mm	in mm	in mm	in mm	in mm
	(inch)	(inch)	(inch)	(inch)	(inch)	(inch)	(inch)	(inch)
Stainless steel	255.5	110.5	69	235	201	184	24	150.5
	(10.06)	(4.35)	(2.72)	(9.25)	(7.91)	(7.24)	(0.94)	(5.93)
Alu-	241.5	96.5	70	221	192	175	23	140
minum	(9.51)	(3.8)	(2.76)	(8.7)	(7.56)	(6.89)	(0.91)	(5.51)





Fig. 20: Dimensions of transmitter in mm, attached by sheet metal console (bracket)



Transmitter weights

MS code (Position 10)	Design	Housing material of transmitter	Weight in kg (lb)
A, B, E, F	Remote	Aluminum	4.2 (9.3)
J, K	Kemote	Stainless steel	12.5 (27.6)

7 Transmitter specification

Overview of functional scope of the Rotamass transmitter


	Trans	smitter
Functional scope	Essential	Ultimate
	Essential	Ultimate
MS code (Position 1)	Е	U
4-line Dot-Matrix display	•	•
Universal power supply (V_{DC} and V_{AC})	•	•
Installation		
Integral type	•	•
Remote type	•	•
Special functions		
Wizard	•	•
Event management	•	•
microSD card	•	•
Total-Health-Check	•	•
Special functions for applications		
Dynamic pressure compensation ¹⁾	-	•
Inline concentration measurement	-	•
Measurement of heat quantity ¹⁾	_	•
Inputs and outputs		
Analog output	•	•
Pulse/frequency output	•	•
Status output	•	•
Analog input	_	•
Status input	•	•
Communication		
HART	•	•
Modbus	•	•

¹⁾ Only in combination with an analog input

7.1 Inputs and outputs

Depending on the flow meter specification, there are different configurations of the connection terminal. Following are configuration examples of the connection terminal (value JK and M7 on MS code position 13 - see *Inputs and outputs* [> 74] for details):

HART



I/O1: Current output (active/passive)

lout1

I/O2: P/ Pulse or status output (passive)

Sout1


I/O3: Status input

Sin

I/O4: lin Current input (active/passive)

WP Write-protect bridge

Modbus



I/O1: Iin Current input (passive)

I/O2: P/ Pulse or status output (passive)

Sout

I/O3-I/ RS485 input/output

O4: Modbus

WP Write-protect bridge

7.1.1 Output signals

Galvanic isolation

Active current output lout

All circuits for inputs, outputs and power supply are galvanically isolated from each other.

One or two current outputs are available depending on MS code position 13.

Depending on the measured value, the active current output delivers 4 - 20 mA.

It may be used for output of the following measured values:

- Flow rate (mass, volume, net partial component flow of a mixture)
- Density
- Temperature
- Pressure
- Concentration

For HART communication devices, it is supplied on the current output *lout1*. The current output may be operated in compliance with the NAMUR NE43 standard.

	Value
Nominal output current	4 – 20 mA
Maximum output current range	2.4 – 21.6 mA
Load resistance	≤ 750 Ω
Load resistance for secure HART communication	230 – 600 Ω
Additive maximum deviation	8 µA
Additive output deviation for deviation from 20 °C ambient temperature	0.8 μA/°C




Fig. 21: Active current output connection lout HART

① Receiver

Passive current output *lout*

	Value
Nominal output current	4 – 20 mA
Maximum output current range	2.4 – 21.6 mA
External power supply	10.5 – 32 V _{DC}
Load resistance for secure HART communication	230 – 600 Ω
Load resistance at current output	≤ 911 Ω
Additive maximum deviation	8 μΑ
Additive output deviation for deviation from 20 °C ambient temperature	0.8 μA/°C




Fig. 22: Maximum load resistance as a function of an external power supply voltage

R Load resistance

U External power supply voltage

The diagram shows the maximum load resistance R as a function of voltage U of the connected voltage source. Higher load resistances are allowed with higher power supply values. The usable zone for passive power output operation is indicated by the hatched area.




Fig. 23: Passive current output connection lout

Active pulse output P/Sout

Connection of an electronic counter

Maximum voltage and correct polarity must be observed for wiring.

	Value
Load resistance	> 1 kΩ
Internal power supply	24 V _{DC} ±20 %
Maximum pulse rate	10000 pulses/s
Frequency range	0 – 12.5 kHz




Fig. 24: Active pulse output connection P/Sout

- Load resistance
- ② Electronic counter

Connection of an electromechanical counter

	Value
Maximum current	150 mA
Average current	≤ 30 mA
Internal power supply	24 V _{DC} ±20 %
Maximum pulse rate	2 pulses/s
Pulse width	20, 33, 50, 100 ms




Fig. 25: Active pulse output P/Sout connection with electromechanical counter

- ① Protective diode
- ② Electromechanical counter

Active pulse output P/Sout with internal pull-up resistor

	Value
Internal power supply	24 V _{DC} ±20 %
Internal pull-up resistor	2.2 kΩ
Maximum pulse rate	10000 pulses/s
Frequency range	0 – 12.5 kHz




Fig. 26: Active pulse output P/Sout with internal pull-up resistor

1 Electronic counter

P/Sout

Passive pulse output Maximum voltage and correct polarity must be observed for wiring.

	Value
Maximum load current	≤ 200 mA
Power supply	≤ 30 V _{DC}
Maximum pulse rate	10000 pulses/s
Frequency range	0 – 12.5 kHz




Fig. 27: Passive pulse output connection P/Sout with electronic counter

- 1 Passive pulse or status output
- 2 Load resistance
- (3) Electronic counter




Fig. 28: Passive pulse output P/Sout connection with electromechanical counter

- Passive pulse or status output 1
- 2 Protective diode
- 3 Electromechanical counter

Active status output *P/Sout*

Since this is a transistor contact, maximum allowed current as well as polarity and level of output voltage must be observed during wiring.

	Value
Load resistance	> 1 kΩ
Internal power supply	24 V _{DC} ±20 %




Fig. 29: Active status output connection P/Sout

① External device with load resistance

Active status output P/Sout with internal pull-up resistor

	Value
Internal pull-up resistor	2.2 kΩ
Internal power supply	24 V _{DC} ±20 %




Fig. 30: Active status output P/Sout with internal pull-up resistor

External device

Passive status output *P/Sout*

	Value
Output current	≤ 200 mA
Power supply	≤ 30 V _{DC}




Fig. 31: Passive status output connection P/Sout

External device

A relay must be connected in series to switch alternating voltage.




Fig. 32: Passive status output connection P/Sout for solenoid valve circuit

- ① Relay
- ② Solenoid valve
- 3 Magnetic valve power supply
- Protective diode

Passive pulse or status output *P/Sout* (NAMUR)

According to EN 60947-5-6 (previously NAMUR, worksheet NA001)




Fig. 33: Passive pulse or status output with switching amplifier connected in series

- Passive pulse or status output
- ② Switching amplifier

7.1.2 Input signals

Active current input

An individual analog power input is available for external analog devices.

The active current input lin is provided for connecting a two-wire transmitter with an output signal of 4-20 mA.

	Value
Nominal input current	4 – 20 mA
Maximum input current range	2.4 – 21.6 mA
Internal power supply	24 V _{DC} ±20 %
Internal load resistance Rotamass	≤ 160 Ω




Fig. 34: Connection of external device with passive current output

External passive current output device

Passive current input *lin*

The passive current input lin is provided for connecting a four-wire transmitter with an output signal of 4 - 20 mA.

	Value
Nominal input current	4 – 20 mA
Maximum input current range	2.4 – 21.6 mA
Maximum input voltage	≤ 32 V _{DC}
Internal load resistance Rotamass	≤ 160 Ω




Fig. 35: Connection of external device with active current output

① External active current output device

Status input Sin



Do not connect a signal source with electric voltage.

The status input is provided for use of voltage-free contacts with the following specification:

Switching status	Resistance
Closed	< 200 Ω
Open	> 100 kΩ




Fig. 36: Status input connection

7.2 Power supply

Power supply

- Alternating voltage (rms):
 - Power supply¹: 24 V_{AC} or 100 240 V_{AC}
 - Power frequency: 47 63 Hz
 - Power supply voltage tolerance: 15 %, + 10 %
- Direct-current voltage:
 - Power supply¹: $24 V_{DC}$ or $100 120 V_{DC}$
 - Power supply voltage tolerance: ± 20 %

¹for option MC_{_} (DNV GL approval) supply voltage is limited to 24V

Power consumption

P = 10 W (including sensor)

Power supply failure

In the event of a power failure, the flow meter data are backed up on a non-volatile internal memory. In case of devices with display, the characteristic sensor values, such as nominal diameter, serial number, calibration constants, Zero point, etc. and the error history are also stored on a microSD card.

7.3 Cable specification

With the remote type, the original connecting cable from Rota Yokogawa must be used to connect the sensor with the transmitter. The connecting cable included in the delivery may be shortened. An assembly set along with the appropriate instructions are enclosed for this purpose.

The connecting cable can be ordered in various lengths as a standard type (device options L_{--}) or as marine approved fire retardant cable (device options Y_{--}), see chapters Connecting cable type and length [> 77] and Marine Approval [> 82] for details.



The maximum cable length to keep the specification is 30 m (98.4 ft). Longer cables must be ordered as a separate item.

8 Approvals and declarations of conformity

CE marking The Rotamass Coriolis flow meter meets the statutory requirements of the applicable EU

Directives. By attaching the CE mark, Rota Yokogawa confirms conformity of the field instrument with the requirements of the applicable EU Directives. The EU Declaration of

Conformity is enclosed with the product on a data carrier.

RCM Rotamass Coriolis flow meter meets the EMC requirements of the Australian Communi-

cations and Media Authority (ACMA).

Ex approvals All data relevant for explosion protection are included in separate Ex instruction manuals.

Pressure equipment approvals

The Rotamass Coriolis flow meter is in compliance with the statutory requirements of the applicable EU Pressure Equipment Directive (PED).

Tab. 14: Approvals and certifications

•	provals and certifications
Туре	Approval or certification
	EU Directive 2014/34/EU
	ATEX approval:
	DEKRA 15ATEX0023 X
	CE ₀₃₄₄ II2G or II2(1)G or II2D or II2(1)D
	Applied standards:
	■ EN 60079-0 +A11
	■ EN 60079-1
	■ EN 60079-7
	■ EN 60079-11
	■ EN 60079-31
	Remote transmitter (depending on the MS code):
	Ex db [ia Ga] IIC T6 Gb or Ex db e [ia Ga] IIC T6 Gb or
	Ex db [ia Ga] IIB T6 Gb or
	Ex db e [ia Ga] IIB T6 Gb
ATEX	Ex db [ia Ga] [ia IIC Ga] IIB T6 Gb or Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or
	Ex tb [ia Da] IIIC T75 °C Db
	Remote sensor (depending on the MS code):
	Ex ib IIC T6T1 Gb or
	Ex ib IIB T6T1 Gb Ex ib IIIC T150 °C Db or
	Ex ib IIIC T220 °C Db or
	Ex ib IIIC T350 °C Db
	Integral type (depending on the MS code):
	Ex db ib IIC T6T1 Gb or Ex db e ib IIC T6T1 Gb or
	Ex db e ib ite 16T1 Gb of
	Ex db e ib IIB T6T1 Gb or
	Ex db ib [ia Ga] IIC T6T1 Gb or
	Ex db e ib [ia Ga] IIC T6T1 Gb or Ex db ib [ia IIC Ga] IIB T6T1 Gb or
	Ex db e ib [ia IIC Ga] IIB T6T1 Gb
	Ex ib tb IIIC T150 °C Db or
	Ex ib tb [ia Da] IIIC T150 °C Db

Туре	Approval or certification
	IECEx approval:
	IECEx DEK 15.0016X
	Applied standards:
	■ IEC 60079-0
	• IEC 60079-1
	• IEC 60079-7
	IEC 60079-11IEC 60079-31
	Remote transmitter (depending on the MS code):
	Ex db [ia Ga] IIC T6 Gb or
	Ex db e [ia Ga] IIC T6 Gb or
	Ex db [ia Ga] IIB T6 Gb or Ex db e [ia Ga] IIB T6 Gb
	Ex db [ia Ga] [ia IIC Ga] IIB T6 Gb or
IECEV	Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or Ex tb [ia Da] IIIC T75 °C Db
IECEx	Remote sensor (depending on the MS code):
	Ex ib IIC T6T1 Gb or
	Ex ib IIB T6T1 Gb Ex ib IIIC T150 °C Db or
	Ex ib IIIC T220 °C Db or
	Ex ib IIIC T350 °C Db
	Integral type (depending on the MS code): Ex db ib IIC T6T1 Gb or
	Ex db ib iiC 1611 Gb of Ex db e ib IIC T6T1 Gb or
	Ex db ib IIB T6T1 Gb or
	Ex db e ib IIB T6T1 Gb or Ex db ib [ia Ga] IIC T6T1 Gb or
	Ex db e ib [ia Ga] IIC T6T1 Gb or
	Ex db ib [ia IIC Ga] IIB T6T1 Gb or
	Ex db e ib [ia IIC Ga] IIB T6T1 Gb Ex ib tb IIIC T150 °C Db or
	Ex ib tb [ia Da] IIIC T150 °C Db

Туре	Approval or certification
FM (CA/US)	FM approvals: US Cert No. FM16US0095X CA Cert No. FM16CA0031X Applied standards: Class 3600 Class 3610 Class 3616 Class 3616 Class 3616 NEMA 250 ANSI/IEC 60529 CSA-C22.2 No. 0-10 CSA-C22.2 No. 0.4-04 CSA-C22.2 No. 0.4-04 CSA-C22.2 No. 94.1-07 CAN/CSA-C22.2 No. 60079-0 CAN/CSA-C22.2 No. 60079-11 CAN/CSA-C22.2 No. 60079-11 CAN/CSA-C22.2 No. 30-M1986 CSA-C22.2 No. 30-M1986 CSA-C22.2 No. 84.2-07 Remote transmitter (depending on the MS code): CL I, DIV 1, GP ABCD, CL II/III, DIV 1, GP EFG; CL I ZN 1 GP IIC; Associated Apparatus CL I/II/III DIV 1, GP ABCDEFG; CL I ZN 0 GP IIC Temperature class T6 or CL I, DIV 1, GP CD, CL II/III, DIV 1, GP ABCDEFG; CL I ZN 0 GP IIC Temperature class T6 or CL I, DIV 1, GP CD, CL II/III, DIV 1, GP ABCDEFG; CL I ZN 0 GP IIC Temperature class T6 or CL I, DIV 1, GP CD, CL II/III, DIV 1, GP ABCDEFG; CL I ZN 0 GP IIC Temperature class T6 or CL I, DIV 1, GP CD, CL II/III, DIV 1, GP ABCDEFG; CL I ZN 0 GP IIC Temperature class T6 or CL I, DIV 1, GP CD, CL II/III, DIV 1, GP ABCDEFG; CL I ZN 0 GP IIB Temperature class T6 or CL I, DIV 1, GP CD, CL II/III, DIV 1, GP CDEFG; CL I ZN 0 GP IIB Temperature class T6 or CL I, DIV 1, GP CD, CL II/III, DIV 1, GP ABCDEFG; CL I ZN 0 GP IIB Temperature class T6 Remote sensor (depending on the MS code): IS CL I/II/III, DIV 1, GP ABCDEFG; CL I ZN 0, GP IIB Temperature class T6 Remote sensor (depending on the MS code): IS CL I/II/III, DIV 1, GP ABCDEFG; CL I, ZN 0, GP IIC Temperature class T6 Remote sensor (depending on the MS code): IS CL I/II/III, DIV 1, GP ABCDEFG; CL I, ZN 0, GP IIC Temperature class T6


Туре	Approval or certification
FM (CA/US)	Integral type (depending on the MS code): CL I, DIV 1, GP ABCD, CL II/III, DIV 1, GP EFG; CL I ZN 1 GP IIC Temperature class T* or CL I, DIV 1, GP ABCD, CL II/III, DIV 1, GP EFG; CL I ZN 1 GP IIC Associated Apparatus CL I/II/III DIV 1 GP ABCDEFG; CL I ZN 0 GP IIC Entity Temperature class T* or CL I, DIV 1, GP CD, CL II/III, DIV 1, GP EFG;
	CL I ZN 1 GP IIB Temperature class T* or CL I, DIV 1, GP CD, CL II/III, DIV 1, GP EFG; CL I ZN 1 GP IIB Associated Apparatus CL I/II/III DIV 1 GP ABCDEFG; CL I ZN 0 GP IIC Entity Temperature class T*
	INMETRO approval:
INMETRO	DEKRA 16.0012X Applied standards: ABNT NBR IEC 60079-0 ABNT NBR IEC 60079-1 ABNT NBR IEC 60079-7 ABNT NBR IEC 60079-31 Remote transmitter (depending on the MS code): Ex db [ia Ga] IIC T6 Gb or Ex db e [ia Ga] IIC T6 Gb or Ex db [ia Ga] IIB T6 Gb or Ex db e [ia Ga] IIB T6 Gb Ex db [ia Ga] IIB T6 Gb Ex db [ia Ga] IIB T6 Gb Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or
	Remote sensor (depending on the MS code): Ex ib IIC T6T1 Gb or Ex ib IIB T6T1 Gb Ex ib IIIC T150 °C Db or Ex ib IIIC T220 °C Db or Ex ib IIIC T350 °C Db
	Integral type (depending on the MS code): Ex db ib IIC T6T1 Gb or Ex db e ib IIC T6T1 Gb or Ex db ib IIB T6T1 Gb or Ex db e ib IIB T6T1 Gb or Ex db ib [ia Ga] IIC T6T1 Gb or Ex db e ib [ia Ga] IIC T6T1 Gb or Ex db e ib [ia IIC Ga] IIB T6T1 Gb or Ex db ib [ia IIC Ga] IIB T6T1 Gb or Ex db e ib [ia IIC Ga] IIB T6T1 Gb Ex ib tb IIIC T150 °C Db or Ex ib tb [ia Da] IIIC T150 °C Db

Туре	Approval or certification
NEPSI	NEPSI approval GYJ17.1242X Applied standards: GB3836.1 GB3836.2 GB3836.4 GB3836.19 GB3836.20 Remote transmitter (depending on the MS code): Ex db [ia Ga] IIC T6 Gb or Ex db e [ia Ga] IIC T6 Gb or Ex db e [ia Ga] IIB T6 Gb Ex db e [ia Ga] IIB T6 Gb Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or Ex db e [ia Ga] [ia IIC Ga] IIB T6 Gb or
	Remote sensor (depending on the MS code): Ex ib IIC T6T1 Gb or Ex ib IIB T6T1 Gb Ex ib IIIC T150 °C Db or Ex ib IIIC T220 °C Db or Ex ib IIIC T350 °C Db
	Integral type (depending on the MS code): Ex db ib IIC T6T1 Gb or Ex db e ib IIC T6T1 Gb or Ex db ib IIB T6T1 Gb or Ex db e ib IIB T6T1 Gb or Ex db ib [ia Ga] IIC T6T1 Gb or Ex db ib [ia Ga] IIC T6T1 Gb or Ex db e ib [ia IIC Ga] IIB T6T1 Gb or Ex db ib [ia IIC Ga] IIB T6T1 Gb or Ex db e ib [ia IIC Ga] IIB T6T1 Gb Ex ib tb [ia IIC T150 °C Db or Ex ib tb [ia Da] IIIC T150 °C Db

Туре	Approval or certification
	Certificate Number:
	DEKRA 15ATEX0023 X
	PESO Equip. Ref. No. P4:
	P400958/1
	P400964/1
	P400966/1
	P400967/1
	P400969/1
	P400970/1
	P400971/1
	P400972/1
	P400973/1
PESO	Applied standards:
	■ EN 60079-0 +A11
	• IS/IEC 60079-1
	• EN 60079-11
	Remote transmitter (depending on the MS code):
	Ex db [ia Ga] IIC T6 Gb or Ex db [ia Ga] IIB T6 Gb or
	Ex db [ia Ga] [ia IIC Ga] IIB T6 Gb
	Remote sensor (depending on the MS code):
	Ex ib IIC T6T1 Gb or Ex ib IIB T6T1 Gb
	Integral type (depending on the MS code):
	Ex db ib IIC T6T1 Gb or
	Ex db ib IIB T6T1 Gb or Ex db ib [ia Ga] IIC T6T1 Gb or
	Ex db ib [ia IIC Ga] IIB T6T1 Gb of
Ingress pro- tection	IP66/67 and NEMA 4X
	EU directive 2014/30/EU per EN 61326-1 Class A Table 2 and
	EN 61326-2-3,
EMC	IEC/EN 61000-3-2, IEC/EN 61000-3-3
	NAMUR NE21
	RCM in Australia/New Zealand
LVD	EU directive 2014/35/EU per EN 61010-1 and EN 61010-2-030
PED	EU directive 2014/68/EU per AD 2000 Code
Marine	DNV GL Type approval according to DNVGL-CP-0338 for options MC2 and MC3
RoHS	EU directive 2011/65/EU per EN 50581
SIL	Exida Certifcate per IEC61508:2010 Parts 1-7 SIL 2 @ HFT=0; SIL 3 @ HFT =1

9 Ordering information

9.1 Overview MS code Intense 34




Model code Position	1.	2.	3.	4.	5.	6.	7.	8.	9.	10.	11.	12.	13.	14.	Description	Restriction
Transmitter	Е	,				,		1							Essential (base function)	not with accuracy C2, C3, 50 not with communication type and I/O JH, JJ, JK, JL, JM, JN, M2, M7 not with option CGC, C52
	U														Ultimate (high function)	not with accuracy E7, D7, 70 not with display 0
Sensor		Т													Intense	-
Meter size			34												Nominal mass flow : 3 t/h (110 lb/min) Maximum mass flow: 5 t/h (180 lb/min)	not with option FE
				S											Stainless steel 1.4404/316L	-
Material wette	d pa	rts		Н											Ni alloy C-22/2.4602	not with option RT, RTA, MC_
Process conne	ectio	n size			15										1/2"	_
1 100035 001111	COLIO	11 3126			25	5									1"	
						BA	45								ASME flange class 900, suitable for ASME B16.5	
Process conne	actio	n tunc	,			CA	45								ASME flange class 900, suitable for ASME B16.5, ring joint	see the tables on page [> 38]
FIOCESS COIIIR	ECTIO	птуре	;			BA	46								ASME flange class 1500, suitable for ASME B16.5	see the tables on page [/ 30]
						CA	46								ASME flange class 1500, suitable for ASME B16.5, ring joint	
0		. 4 1					0								Stainless steel 1.4301/304, 1.4404/316L	_
Sensor housing	ig ma	ateriai					1								Stainless steel 1.4404/316L	-
Medium tempe	eratu	re rar	nge					0							Standard, integral type: -50 – 150 °C (-58 – 302 °F), remote type: -70 – 150 °C (-94 – 302 °F)	-
									E7						Liquid: 0.2 % maximum mass flow deviation $D_{\text{flat}},4\text{ g/l}$ density deviation	not with transmitter U
									D7						Liquid: 0.15 % maximum mass flow deviation $D_{\mbox{\tiny flat}},4$ g/l density deviation	not with transmitter o
Mass flow and	l den	sitv a	ccura	icv					С3						Liquid: 0.1 % maximum mass flow deviation D_{flat} , 1 g/l density deviation	not with transmitter E
wass now and	4 0011	oity u	oourc	.cy					C2						Liquid: 0.1 % maximum mass flow deviation $D_{\text{flat}},0.5$ g/l density deviation	not with option RT, RTA, P20
									70						Gas: 0.75 % maximum mass flow deviation D _{flat}	not with transmitter U
									50						Gas: 0.5 % maximum mass flow deviation D _{flat}	not with transmitter E not with option C52
										0					Integral type with "urethane-cured polyester powder coating" coated aluminum transmitter housing	not with option L, MC_,
										2					Integral type with "corrosion protection coating" coated aluminum transmitter housing	Y
										A					Remote type with "urethane-cured polyester powder coating" coated aluminum transmitter housing and standard neck sensor	
										В					Remote type with "urethane-cured polyester powder coating" coated aluminum transmitter housing and long neck sensor	not with option RB
Design and ho	ousin	g								E					Remote type with "corrosion protection coating" coated aluminum transmitter housing and standard neck sensor	
										F					Remote type with "corrosion protection coating" coated aluminum transmitter housing and long neck sensor	
										J					Remote type stainless steel transmitter and standard neck sensor	not with Ex approval KF21, SF21, UF21, NF21, QF21
																not with option RB
										K					Remote type stainless steel transmitter and long neck sensor	not with Ex approval KF21, SF21, UF21, NF21, QF21 not with option RB
															I .	

Model code	1.	2.	3.	4.	5.	6.	7.	8.	9.	10.	11.	12.	13.	14.	Description	Restriction
Position																
											NN0)			None	not with communication type and I/O JP, JQ, JR, JS
											KF21				ATEX, explosion group IIC and IIIC	not with design and housing J, K
											KF22	2			ATEX, explosion group IIB and IIIC	_
											SF21				IECEx, explosion group IIC and IIIC	not with design and housing J, K
											SF22	2			IECEx, explosion group IIB and IIIC	_
											FF11				FM, groups A, B, C, D, E, F, G	not with cable entries 4
Ev ennreval											FF12	!			FM, groups C, D, E, F, G	not with option Y
Ex approval											UF2	I			INMETRO, explosion group IIC and IIIC	not with design and housing J, K
											UF22	2			INMETRO, explosion group IIB and IIIC	_
											NF2	l			NEPSI, explosion group IIC and IIIC	not with design and housing J, K
																only with option CN
											NF22	2			NEPSI, explosion group IIB and IIIC	only with option CN
											QF2	1			PESO, explosion group IIC	not with design and housing J, K
											QF2	2			PESO, explosion group IIB	_
												2			ANSI ½" NPT	-
Cable entries												4			ISO M20x1.5	not with Ex approval FF11 or FF12

Model code Position	1.	2.	3.	4.	5.	6.	7.	8.	9.	10.	11.	12.	13.	14.	Description	Restriction
													JA		1 active current output HART, 1 passive pulse or status output	
													JB		2 active current outputs one with HART, 2 passive pulse or status outputs	
													JC		2 active current outputs one with HART, 1 passive pulse or status output,	
															1 voltage-free status input	
													JD		1 active current output HART, 2 passive pulse or status outputs, 1 passive status output	not with option CGC, C52
													JE		1 active current output HART, 2 passive pulse or status outputs, 1 voltage-free status input	Thot with option CGC, C52
													JF		active current output HART, passive pulse or status output, active pulse or status output with pull-up resistor, voltage-free status input	
													JG		active current output HART, passive pulse or status output, active pulse or status output, voltage-free status input	
													JH		active current output HART, passive pulse or status output, passive current output, active current input	
													JJ		active current output HART, passive pulse or status outputs, active current input	
													JK		active current output HART, passive pulse or status output, voltage-free status input, active current input	not with transmitter E,
Communication	on type	e and	I I/O										JL		active current output HART, passive pulse or status output, passive current output, passive current input	not with option C52
													JM		1 active current output HART, 2 passive pulse or status outputs, 1 passive current input	
													JN		active current output HART, passive pulse or status output, voltage-free status input, passive current input,	
													JP		2 passive current outputs one with HART, 1 passive pulse or status output	
													JQ		2 passive current outputs one with HART, 2 passive pulse or status outputs	not with Ex approval NN00
													JR		2 passive current outputs one with HART, 1 passive NAMUR pulse or status output	not with option CGC, C52, MC2, MC3
													JS		2 passive current outputs one with HART, 2 passive NAMUR pulse or status outputs	
													M0		Modbus output, 1 passive pulse or status output	not with option CGC, PS
													M2		Modbus output, 1 passive pulse or status output, 1 active current input	not with transmitter E, not with option PS
													М3		Modbus output, 2 passive pulse or status outputs	
													M4		Modbus output, 1 passive pulse or status output, 1 active pulse or status output	
													M5		Modbus output, 1 passive pulse or status output, 1 active pulse or status output with pull-up resistor	not with option CGC , PS
													M6		Modbus output, 1 passive pulse or status output, 1 active current output	
													M7		Modbus output, 1 passive pulse or status output, 1 passive current input	not with transmitter E, not with option PS
Display														0	No display	not with transmitter U
														1	With display	_

9.2 Overview MS code Intense 36




Model code Position	1.	2.	3.	4.	5.	6.	7.	8.	9.	10.	11.	12.	13.	14.	Description	Restriction
Transmitter	E														Essential (base function)	not with accuracy C2, C3, 50 not with communication type and I/O JH, JJ, JK, JL, JM, JN, M2, M7 not with option CGC, C52
	U														Ultimate (high function)	not with accuracy E7, D7, 70 not with display 0
Sensor		Т													Intense	-
Meter size			36												Nominal mass flow : 10 t/h (370 lb/min) Maximum mass flow: 17 t/h (620 lb/min)	_
Material wetter	d par	ts		S											Stainless steel 1.4404/316L	_
D					25										1"	
Process conne	ection	i size			50										2"	_
Dr						ВА	5								ASME flange class 900, suitable for ASME B16.5	and the tables on name (1, 201
Process conne	cuor	і іуре				CA	\5								ASME flange class 900, suitable for ASME B16.5, ring joint	see the tables on page [38]
							0								Stainless steel 1.4301/304, 1.4404/316L	_
Sensor housing	g ma	teriai					1								Stainless steel 1.4404/316L	_
Medium tempe	eratur	e ran	ge					0							Standard, integral type: -50 – 150 °C (-58 – 302 °F), remote type: -70 – 150 °C (-94 – 302 °F)	-
									E7						Liquid: 0.2 % maximum mass flow deviation D_{flat} , 4 g/l density deviation	
									D7						Liquid: 0.15 % maximum mass flow deviation $D_{\text{flat}},4$ g/l density deviation	not with transmitter U
Mass flow and	dens	sity ac	cura	icv					СЗ						Liquid: 0.1 % maximum mass flow deviation $D_{\text{flat}},1$ g/l density deviation	
Wass now and	ucii	only ac	Joura	Ю					C2						Liquid: 0.1 % maximum mass flow deviation $D_{\text{flat}},0.5\text{ g/I}$ density deviation	not with transmitter E
									70						Gas: 0.75 % maximum mass flow deviation D _{flat}	not with transmitter U
									50						Gas: 0.5 % maximum mass flow deviation D _{flat}	not with transmitter E not with option C52
										0					Integral type with "urethane-cured polyester powder coating" coated aluminum transmitter housing	not with option L, MC_,
										2					Integral type with "corrosion protection coating" coated aluminum transmitter housing	Y
										А					Remote type with "urethane-cured polyester powder coating" coated aluminum transmitter housing and standard neck sensor	
										В					Remote type with "urethane-cured polyester powder coating" coated aluminum transmitter housing and long neck sensor	not with option RB
Design and ho	Design and housing														Remote type with "corrosion protection coating" coated aluminum transmitter housing and standard neck sensor	
										F					Remote type with "corrosion protection coating" coated aluminum transmitter housing and long neck sensor	
										J					Remote type stainless steel transmitter and standard neck sensor	not with Ex approval KF21, SF21, UF21, NF21, QF21 not with option RB
										K					Remote type stainless steel transmitter and long neck sensor	not with Ex approval KF21, SF21, UF21, NF21, QF21 not with option RB

Model code	1.	2.	3.	4.	5.	6.	7.	8.	9.	10.	11.	12.	13.	14.	Description	Restriction
Position																
											NN0	0			None	not with communication type and I/O JP, JQ, JR, JS
											KF21				ATEX, explosion group IIC and IIIC	not with design and housing J, K
											KF22	2			ATEX, explosion group IIB and IIIC	_
											SF21				IECEx, explosion group IIC and IIIC	not with design and housing J, K
											SF22	2			IECEx, explosion group IIB and IIIC	-
											FF11				FM, groups A, B, C, D, E, F, G	not with cable entries 4
F											FF12	2			FM, groups C, D, E, F, G	not with option Y
Ex approval											UF2	1			INMETRO, explosion group IIC and IIIC	not with design and housing J, K
											UF22	2			INMETRO, explosion group IIB and IIIC	-
											NF2	1			NEPSI, explosion group IIC and IIIC	not with design and housing J, K
																only with option CN
											NF22	2			NEPSI, explosion group IIB and IIIC	only with option CN
											QF2	1			PESO, explosion group IIC	not with design and housing J, K
											QF2	2			PESO, explosion group IIB	-
												2			ANSI ½" NPT	_
Cable entries												4			ISO M20x1.5	not with Ex approval FF11 or FF12

Model code 1. 2. 3. Position	4. 5.	6.	7.	8.	9.	10.	11.	12.	13.	14.	Description	Restriction
									JA		1 active current output HART, 1 passive pulse or status output	
									JB		2 active current outputs one with HART, 2 passive pulse or status outputs	
									JC		2 active current outputs one with HART, 1 passive pulse or status output,	
											1 voltage-free status input	
									JD		1 active current output HART, 2 passive pulse or status outputs, 1 passive status output	not with option CCC CE2
									JE		1 active current output HART, 2 passive pulse or status outputs, 1 voltage-free status input	not with option CGC, C52
									JF		active current output HART, passive pulse or status output, active pulse or status output with pull-up resistor, voltage-free status input	
									JG		active current output HART, passive pulse or status output, active pulse or status output, voltage-free status input	
									JH		active current output HART, passive pulse or status output, passive current output, active current input	
									JJ		active current output HART, passive pulse or status outputs, active current input	
									JK		active current output HART, passive pulse or status output, voltage-free status input, active current input	not with transmitter E,
Communication type and I/O									JL		active current output HART, passive pulse or status output, passive current output, passive current input	not with option C52
									JM		1 active current output HART, 2 passive pulse or status outputs, 1 passive current input	
									JN		active current output HART, passive pulse or status output, voltage-free status input, passive current input,	
									JP		2 passive current outputs one with HART, 1 passive pulse or status output	
									JQ		2 passive current outputs one with HART, 2 passive pulse or status outputs	not with Ex approval NN00
									JR		2 passive current outputs one with HART, 1 passive NAMUR pulse or status output	not with option CGC, C52, MC2, MC3
									JS		2 passive current outputs one with HART, 2 passive NAMUR pulse or status outputs	
									MO		Modbus output, 1 passive pulse or status output	not with option CGC, PS
									M2		Modbus output, 1 passive pulse or status output, 1 active current input	not with transmitter E, not with option PS
									МЗ		Modbus output, 2 passive pulse or status outputs	
									M4		Modbus output, 1 passive pulse or status output, 1 active pulse or status output	
									M5		Modbus output, 1 passive pulse or status output, 1 active pulse or status output with pull-up resistor	not with option CGC , PS
									M6		Modbus output, 1 passive pulse or status output, 1 active current output	
									M7		Modbus output, 1 passive pulse or status output, 1 passive current input	not with transmitter E, not with option PS
Disales										0	No display	not with transmitter U
Display										1	With display	_

9.3 Overview MS code Intense 38




Model code	1.	2.	3.	4.	5.	6.	7.	8.	9.	10.	11.	12.	13.	14.	Description	Restriction
Position																
Transmitter	E														Essential (base function)	not with accuracy C2, C3, 50 not with communication type and I/O JH, JJ, JK, JL, JM, JN, M2, M7
																not with option CGC, C52
	U														Ultimate (high function)	not with accuracy E7, D7, 70 not with display 0
Sensor		Т													Intense	_
			20												Nominal mass flow : 32 t/h (1200 lb/min)	
Meter size			38												Maximum mass flow: 50 t/h (1800 lb/min)	-
Material wetter				S											Stainless steel 1.4404/316L	_
Process conne	ection	ı size			50										2"	-
Process conne	ection	ı type				BA									ASME flange class 900, suitable for ASME B16.5	see the tables on page [38]
						CA	_								ASME flange class 900, suitable for ASME B16.5, ring joint	
Sensor housing	g ma	iterial					0								Stainless steel 1.4301/304, 1.4404/316L	-
							1								Stainless steel 1.4404/316L	-
Medium tempe	eratur	re ran	ige					0							Standard, integral type: -50 – 150 °C (-58 – 302 °F), remote type: -70 – 150 °C (-94 – 302 °F)	-
									E7						Liquid: 0.2 % maximum mass flow deviation $D_{\mbox{\tiny flat}},4$ g/l density deviation	not with transmitter U
		D7													Liquid: 0.15 % maximum mass flow deviation $D_{\text{flat}},4$ g/l density deviation	not with transmitter o
Mass flow and	dens	sity a	ccura	CV					СЗ						Liquid: 0.1 % maximum mass flow deviation $D_{\mbox{\tiny flat}}$ 1 g/l density deviation	
was now and	deni	only a	oouru	.cy					C2						Liquid: 0.1 % maximum mass flow deviation $D_{\text{flat}},0.5\text{ g/l}$ density deviation	not with transmitter E
									70						Gas: 0.75 % maximum mass flow deviation D _{flat}	not with transmitter U
									50						Gas: 0.5 % maximum mass flow deviation D_{flat}	not with transmitter E not with option C52
										0					Integral type with "urethane-cured polyester powder coating" coated aluminum transmitter housing	not with option L, MC_,
										2					Integral type with "corrosion protection coating" coated aluminum transmitter housing	Y
										A					Remote type with "urethane-cured polyester powder coating" coated aluminum transmitter housing and standard neck sensor	
										В					Remote type with "urethane-cured polyester powder coating" coated aluminum transmitter housing and long neck sensor	not with option RB
Design and ho	and housing E F J														Remote type with "corrosion protection coating" coated aluminum transmitter housing and standard neck sensor	
															Remote type with "corrosion protection coating" coated aluminum transmitter housing and long neck sensor	
															Remote type stainless steel transmitter and standard neck sensor	not with Ex approval KF21, SF21, UF21, NF21, QF21 not with option RB
										K					Remote type stainless steel transmitter and long neck sensor	not with Ex approval KF21, SF21, UF21, NF21, QF21 not with option RB

Model code	1.	2.	3.	4.	5.	6.	7.	8.	9.	10.	11.	12.	13.	14.	Description	Restriction
Position																
											NN0)			None	not with communication type and I/O JP, JQ, JR, JS
											KF21				ATEX, explosion group IIC and IIIC	not with design and housing J, K
											KF22	2			ATEX, explosion group IIB and IIIC	_
											SF21				IECEx, explosion group IIC and IIIC	not with design and housing J, K
											SF22	2			IECEx, explosion group IIB and IIIC	_
											FF11				FM, groups A, B, C, D, E, F, G	not with cable entries 4
Ev ennesuel											FF12	!			FM, groups C, D, E, F, G	not with option Y
Ex approval											UF2	I			INMETRO, explosion group IIC and IIIC	not with design and housing J, K
											UF22	2			INMETRO, explosion group IIB and IIIC	_
											NF2	l			NEPSI, explosion group IIC and IIIC	not with design and housing J, K
																only with option CN
											NF22	2			NEPSI, explosion group IIB and IIIC	only with option CN
											QF2	1			PESO, explosion group IIC	not with design and housing J, K
											QF2	2			PESO, explosion group IIB	-
												2			ANSI ½" NPT	-
Cable entries												4			ISO M20x1.5	not with Ex approval FF11 or FF12

Model code Position	1.	2.	3.	4.	5.	6.	7.	8.	9.	10.	11.	12.	13.	14.	Description	Restriction
I JoillOII													JA		1 active current output HART, 1 passive pulse or status output	
													JB		2 active current outputs one with HART, 2 passive pulse or status outputs	-
													JC		2 active current outputs one with HART, 1 passive pulse or status output,	-
													00		1 voltage-free status input	
													JD		1 active current output HART, 2 passive pulse or status outputs, 1 passive status output	
													JE		1 active current output HART, 2 passive pulse or status outputs, 1 voltage-free status input	not with option CGC, C52
													JF		active current output HART, passive pulse or status output, active pulse or status output with pull-up resistor, voltage-free status input	
													JG		active current output HART, passive pulse or status output, active pulse or status output, voltage-free status input	
													JH		active current output HART, passive pulse or status output, passive current output, active current input	
													JJ		1 active current output HART, 2 passive pulse or status outputs, 1 active current input	
													JK		1 active current output HART, 1 passive pulse or status output, 1 voltage-free status input, 1 active current input	not with transmitter E,
Communicati	on ty	pe and	d I/O										JL		active current output HART, passive pulse or status output, passive current output, passive current input	not with option C52
													JM		1 active current output HART, 2 passive pulse or status outputs, 1 passive current input	
													JN		1 active current output HART, 1 passive pulse or status output, 1 voltage-free status input, 1 passive current input	
													JP		2 passive current outputs one with HART, 1 passive pulse or status output	
													JQ		2 passive current outputs one with HART, 2 passive pulse or status outputs	not with Ex approval NN00
													JR		2 passive current outputs one with HART, 1 passive NAMUR pulse or status output	not with option CGC, C52, MC2, MC3
													JS		2 passive current outputs one with HART, 2 passive NAMUR pulse or status outputs	
													M0		Modbus output, 1 passive pulse or status output	not with option CGC, PS
													M2		Modbus output, 1 passive pulse or status output, 1 active current input	not with transmitter E, not with option PS
													МЗ		Modbus output, 2 passive pulse or status outputs	-
													M4		Modbus output, 1 passive pulse or status output, 1 active pulse or status output	
													M5		Modbus output, 1 passive pulse or status output, 1 active pulse or status output with pull-up resistor	not with option CGC , PS
													M6		Modbus output, 1 passive pulse or status output, 1 active current output	
													M7		Modbus output, 1 passive pulse or status output, 1 passive current input	not with transmitter E, not with option PS
Diamles:														0	No display	not with transmitter U
Display														1	With display	-

9.4 Overview options



Option	Option code	Description	Restriction
Additional nameplate information	BG	Nameplate with customer-specific identification	_
Presetting of customer parameters	PS	Presetting according to customer parameters	not with communication type and I/O M_
Country-specific	PJ	Delivery to Japan	_
delivery	CN	Delivery to China	_
Concentration and pe-			not with transmitter type E not with mass flow and
troleum measurement	C52	Total Net Oil computing TNO	density accuracy 70, 50 not with Communica-
			tion type and I/O J_
Rupture disc	RD	Rupture disc	-
Mass flow calibration	K2	Customer-specific 5-point mass flow calibration with factory calibration certificate (mass flow or volume flow of water). A table listing the desired calibration points must be supplied with the order.	
Mass now campianon	K5	Customer-specific 10-point mass flow calibration with DAkkS calibration certificate (mass flow or volume flow of water). A table listing the desired calibration points must be supplied with the order.	
Accordance with terms	P2	Declaration of compliance with the order 2.1 according to EN 10204	
of order	P3	Quality Inspection Certificate (Inspection Certificate 3.1 according to EN 10204)	not with option P10, P11, P12, P13
Material certificates	P6	Certificate of Marking Transfer and Raw Material Certificates (Inspection Certificate 3.1 according to EN 10204)	not with option P10, P11, P12, P13
Pressure testing	P8	Hydrostatic Pressure Test Certificate (Inspection Certificate 3.1 according to EN 10204)	not with option P10, P12, P13, P14
Surfaces free of oil and grease	H1	Degreasing of wetted surfaces according to ASTM G93-03 (Level C), including test report	_
		WPS according to DIN EN ISO 15609-1	
	WP	WPQR according to DIN EN ISO 15614-1	not with option P13,
	VVI	WQC according to DIN EN 287-1 or DIN EN ISO 6906-4	P14, P15, P20
Welding certificates	WPA	Welding procedures and Certificate according to	not with option P12, P13, P14, P20
	VVPA	ASME IX	only with process connection type BA_ or CA_

Option	Option code	Description	Restriction
		X-ray inspection of flange weld seam according to	not with material wet- ted parts H
	RT	DIN EN ISO 17636-1/B	not with option P15, P20
		Evaluation according to AD 2000 HP 5/3 and DIN EN ISO 5817/C, including certificate	for Intense 34: not with mass flow and density accuracy C2, C3
X-ray inspection of flange weld seam			not with material wet- ted parts H
mange were seem			not with option P12, P13, P14, P20
	RTA	X-ray test according to ASME V	not with Intense 34 for mass flow and density accuracy C2, C3
			only with process connection type BA_ or CA_
	PT	Dye penetration test of process connection weld seams according to DIN EN ISO 3452-1, including certificate	not with option P12, P13, P15, P20
Dye penetration test of weld seams		Dye Penetrant test of flange welding according to	not with option P12, P13, P14, P20
	PTA	ASME V	only with process connection type BA_ or CA_
Ferrite testing	FE	Ferrite test for flange welding acc. DIN EN ISO 8249	not with meter size 34
Transmitter housing rotated 180°	RB	Alignment of transmitter housing rotated 180°	not with design and housing A, B, E, F, J, K
Measurement of heat		Measurement of the total transported energy content of a fuel in connection with a sensor for determining	not with transmitter type E
quantity	CGC	the fuel's calorific value (e.g., a gas chromato- graph, not included in scope of delivery)	only with communication type and I/O JH, JJ, JK, JL, JM, JN, M2, M7

Option	Option code	Description	Restriction
	L000	Separate order for standard sensor cable	
	L005	5 meter (16.4 ft) remote sensor cable terminated std. gray / Ex blue	
	L010	10 meter (32.8 ft) remote sensor cable terminated std. gray / Ex blue	not with design and
	L015	15 meter (49.2 ft) remote sensor cable terminated std. gray / Ex blue	housing 0, 2 not with option MC_
	L020	20 meter (65.6 ft) remote sensor cable terminated std. gray / Ex blue	
Sensor cable type and	L030	30 meter (98.4 ft) remote sensor cable terminated std. gray / Ex blue	
length	Y000	Separate ordered remote fire retardant sensor cable	
	Y005	5 meter (16.4 ft) remote fire retardant sensor cable not terminated	
	Y010	10 meter (32.8 ft) remote fire retardant sensor cable not terminated	not with design and
	Y015	15 meter (49.2 ft) remote fire retardant sensor cable not terminated	housing 0, 2; Ex approval FF11, FF12
	Y020	20 meter (65.6 ft) remote fire retardant sensor cable not terminated	
	Y030	30 meter (98.4 ft) remote fire retardant sensor cable not terminated	
Marine Approval	MC2	Marine approval according to DNV GL piping class 2	not with material wet- ted parts H, design and housing 0, 2, commu- nication type and I/O JP, JQ, JR, JS
παιπο Αρριοναι			only with option Y
	MC3	Marine approval according to DNV GL piping class 3	in case of thermal oil applications option RT or RTA is mandatory

Option	Option code	Description	Restriction
Combined certificate	P10	 Combination of: P3: Quality Inspection Certificate P6: Certificate of Marking Transfer and Raw Material Certificates P8: Hydrostatic Pressure Test Certificate 	not with option P3, P6, P8
	P11	 Combination of: P3: Quality Inspection Certificate P6: Certificate of Marking Transfer and Raw Material Certificates PM: Positive Material Identification of wetted parts 	not with option P3, P6, PM
	P12	 Combination of: P3: Quality Inspection Certificate P6: Certificate of Marking Transfer and Raw Material Certificates PT: Dye penetration test according to DIN EN ISO 3452-1 P8: Hydrostatic Pressure Test Certificate 	not with option P3, P6, P8, P15, PT, WPA, RTA, PTA
	P13	 Combination of: P3: Quality Inspection Certificate P6: Certificate of Marking Transfer and Raw Material Certificates PT: Dye penetration test according to DIN EN ISO 3452-1 PM: Positive Material Identification of wetted parts P8: Hydrostatic Pressure Test Certificate WP: Welding certificates 	not with option P3, P6, P8, P15, WP, PM, PT, WPA, RTA, PTA
	P14	 Combination of: PM: Positive Material Identification of wetted parts P8: Hydrostatic Pressure Test Certificate WP: Welding certificates 	not with option P8, P15, WP, PM, WPA, RTA, PTA
	P20	 Combination of: PTA: Dye Penetrant test of flange welding according to ASME V WPA: Welding procedures and Certificates according to ASME IX RTA: X-ray test according to ASME V 	not with option WP, WPA, RT, RTA, PT, PTA not with meter size 34 for mass flow and den- sity accuracy C3, C2
Positive Material Identification of wetted parts	РМ	Positive Material Identification of wetted parts, including certificate (Inspection Certificate 3.1 according to EN 10204)	not with option P11, P13, P14
Tube health check	TC	Tube health check	_
ASME B31.3 compliance	P15	ASME B31.3 compliance NORMAL FLUID SERVICE	not with option WP, RT, PT, P12, P13, P14, T only with process connection type BA_ or CA_

Intense


Ordering information MS code

9.5 MS code

The MS code of the Rotamass TI is explained below.

Items 1 through 14 are mandatory entries and must be specified at the time of ordering.

Device options (item 15) can be selected and specified individually by separating them with slashes.




- Transmitter
- 2. Sensor
- Meter size
- 4. Material wetted parts
- 5. Process connection size
- 6. Process connection type
- 7. Sensor housing material
- 8. Medium temperature range
- 9. Mass flow and density accuracy
- 10. Design and housing
- 11. Ex approval
- 12. Cable entries
- 13. Communication type and I/O
- 14. Display
- 15. Options

9.5.1 Sensor housing material



MS code	Housing material
Position 7	
0	Stainless steel 1.4301/304
1	Stainless steel 316L/1.4404

9.5.2 Transmitter



MS code Position 1	Transmitter
E	Essential
U	Ultimate




9.5.3 Sensor




MS code	Sensor
Position 2	
Т	Intense

9.5.4 Meter size



MS code Position 3	Meter size	Nominal mass flow in t/h (lb/min)	Maximum mass flow in t/h (lb/min)
34	34	3 (110)	5 (180)
36	36	10 (370)	17 (620)
38	38	32 (1200)	50 (1800)


9.5.5 Material wetted parts



MS code Position 4	Material wetted parts
S	Stainless steel 1.4404/316L
Н	Ni alloy C-22/2.4602 (only available for meter size 34)

Non-wetted parts of the process connection are generally made of stainless steel 1.4404/316L.

9.5.6 Process connection size




MS code	Process connection size
Position 5	
15	1/2"
25	1"
50	2"

Available sizes depend on the actual process connection, see also chapter *Process connections, dimensions and weights of sensor* [> 37].


Ordering information MS code

9.5.7 Process connection type



MS code Position 6	Туре	Process connections	
BA5	Flanges suitable for ASME B16.5	ASME flange class 900	
CA5		ASME flange class 900, ring joint	
BA6		ASME flange class 1500	
CA6		ASME flange class 1500, ring joint	


9.5.8 Medium temperature range



MS code Position 8	Temperature range	Medium temperature range
0	Standard	Integral type: -50 – 150 °C (-58 – 302 °F)
		Remote type: -70 – 150 °C (-94 – 302 °F)

For temperature range limits, see chapter *Medium temperature range* [27].

9.5.9 Mass flow and density accuracy





Medium	MS code Position 9	Maximum deviation		MS code
		Mass flow D _{flat} in %	Density in g/l	Position 1
Liquid	E7	0.2	4	E
	D7	0.15	4	E
	C3	0.1	1	U
	C2		0.5	U
Gas	70	0.75	_	E
	50	0.5	_	U

Devices with value $_2$ in MS code position 9 receive an additional density calibration with a corresponding certificate.



9.5.10 Design and housing






MS code Position 10	Design	Transmitter housing material	Transmitter housing coating	Sensor terminal box material	Long neck
0			Standard coating		
2	Integral type	Aluminum	Corrosion protection coating	_	_
Α		Aluminum Coppro	Standard		No
В			coating		Yes
E			Corrosion	Stainless	No
F	Remote type		protection coating	steel	Yes
J		Stainless	_		No
K		Steel	_		Yes

The remote type requires a connecting cable to connect sensor and transmitter. It can be selected in various lengths as a device option, see *Connecting cable type and length* [> 77].

Intense


Ordering information MS code

9.5.11 Ex approval




MS code Position 11	Ex approval
NN00	None
KF21	ATEX, explosion group IIC and IIIC
KF22	ATEX, explosion group IIB and IIIC
SF21	IECEx, explosion group IIC and IIIC
SF22	IECEx, explosion group IIB and IIIC
FF11	FM, group A, B, C, D, E, F, G
FF12	FM, group C, D, E, F, G
UF21	INMETRO, explosion group IIC and IIIC
UF22	INMETRO, explosion group IIB and IIIC
NF21	NEPSI, explosion group IIC and IIIC
NF22	NEPSI, explosion group IIB and IIIC
QF21	PESO, explosion group IIC
QF22	PESO, explosion group IIB

9.5.12 Cable entries



MS code Position 12	Cable entries
2	ANSI 1/2" NPT
4	ISO M20x1.5

9.5.13 Inputs and outputs



HART I/O

MS code	Connection terminal assignment					
Position 13	I/O1 +/-	I/O2 +/-	I/O3 +/-	I/O4 +/-	WP	
JA	lout1	P/Sout1			\\/\nite = ==================================	
JA	Active	Passive	_	_	Write-protect	
ID	lout1	P/Sout1	P/Sout2	lout2	Write-protect	
JB	Active	Passive	Passive	Active		
JC	lout1	P/Sout1	Sin	lout2	Write-protect	
30	Active	Passive		Active		
JD	lout1	P/Sout1	Sout	P/Sout2	Write protect	
JD	Active	Passive	Passive	Passive	Write-protect	
JE	lout1	P/Sout1	Sin	P/Sout2	Write protect	
	Active	Passive	Sin	Passive	Write-protect	



MS code	Connection terminal assignment					
Position 13	I/O1 +/-	I/O2 +/-	I/O3 +/-	I/O4 +/-	WP	
				P/Sout2		
JF	lout1	P/Sout1	Sin	Active	Write-protect	
	Active	Passive	Oiii	Internal pull- up resistor	witte protect	
JG	lout1	P/Sout1	Sin	P/Sout2	Write-protect	
JG	Active	Passive	SIII	Active	vviile-protect	
JH	lout1	P/Sout1	lout2	lin	Write protect	
JH	Active	Passive	Passive	Active	Write-protect	
JJ	lout1	P/Sout1	P/Sout2	lin	Write-protect	
33	Active	Passive	Passive	Active		
JK	lout1	P/Sout1	Sin	lin	Write-protect	
JIX.	Active	Passive	Oll1	Active	vviite-protect	
JL	lout1	P/Sout1	lout2	lin	Write-protect	
JL	Active	Passive	Passive	Passive	vviite-protect	
JM	lout1	P/Sout1	P/Sout2	lin	Write-protect	
	Active	Passive	Passive	Passive	vviite-protect	
JN	lout1	P/Sout1	Sin	lin	Write protect	
JIN	Active	Passive	Siii	Passive	Write-protect	

lout1 Active or passive current output with HART communication

lout2 Active or passive current outputlin Active or passive current inputP/Sout1 Passive pulse or status output

P/Sout2 Active or passive pulse or status output

Sin Status input Sout Status output

HART I/O, intrinsically safe

MS code	Connection terminal assignment					
Position 13	I/O1 +/-	I/O2 +/-	I/O3 +/-	I/O4 +/-	WP	
JP	lout1	P/Sout1	lout2	,	VA/nita manta at	
JP	Passive	Passive	Passive	_	Write-protect	
10	lout1	P/Sout1	lout2	P/Sout2	Mrita protect	
JQ	Passive	Passive	Passive	Passive	Write-protect	
JR	lout1 Passive	P/Sout1 Passive NAMUR	lout2 Passive	_	Write-protect	
JS	lout1 Passive	P/Sout1 Passive NAMUR	lout2 Passive	P/Sout2 Passive NAMUR	Write-protect	

Intrinsically safe outputs are only available in combination with selecting Ex approval of the device, see chapter Ex approval [\triangleright 74].

Ordering information MS code


Modbus I/O

MS code	Connection	n terminal a	ssignment				
Position 13	I/O1 +/-	I/O2 +/-	I/O3 +	I/O3 -	I/O4 +	I/O4 -	WP
MO	_	P/Sout Passive	_	Modbus C	Modbus B	Modbus A	Write- protect
M2	lin Active	P/Sout Passive	_	Modbus C	Modbus B	Modbus A	Write- protect
M3	P/Sout Passive	P/Sout Passive	_	Modbus C	Modbus B	Modbus A	Write- protect
M4	P/Sout Active	P/Sout Passive	_	Modbus C	Modbus B	Modbus A	Write- protect
M5	P/Sout Active Internal pull-up resistor	P/Sout Passive	_	Modbus C	Modbus B	Modbus A	Write- protect
M6	lout Active	P/Sout Passive	_	Modbus C	Modbus B	Modbus A	Write- protect
M7	lin Passive	P/Sout Passive	_	Modbus C	Modbus B	Modbus A	Write- protect

Iout Active current output, no HART In Active or passive current input

P/Sout Active or passive pulse or status output

9.5.14 **Display**



(i)

The display unit includes a slot for the microSD card.


MS code Position 14	Display
0	Without display
1	With display

Devices without a display are available for Essential transmitters only (value E in MS code position 1)



9.6 Options

Additional device options that can be combined may be selected; they are listed sequentially in MS code position 15. In this case, each device option is preceded by a slash.




The following device options are possible:

- Connecting cable length, see chapter Connecting cable type and length [▶ 77]
- Customer-specific adaptation of the nameplate, see chapter Additional nameplate information [> 78]
- Flow meter presetting with customer parameters, see chapter Presetting of customer parameters [> 78]
- Concentration and petroleum measurement, see chapter Concentration and petroleum measurement [▶ 78]
- Certificates to be supplied, see chapter Certificates [▶ 79]
- Positive Material Identification of wetted parts, see chapter Certificates [79]
- Country -specific delivery Country-specific delivery [80]
- Rupture disc, see chapter Rupture disc [81]
- X-ray inspection of flange weld seam, see chapter Certificates [> 79]
- Tube health check, see chapter Tube health check [▶ 81]
- Ferrite testing, see chapter Ferrite testing
- Transmitter housing rotated 180°, see chapter Transmitter housing rotated 180°
 [> 81]
- Measurement of heat quantity, see chapter Measurement of heat quantity [82]
- Marine type approval, see chapter Marine Approval [▶ 82]

9.6.1 Connecting cable type and length


When ordering the remote type, it is mandatory to always provide the desired connecting cable length.



Options	Specification
L000	Separate order for standard sensor cable
L005	5 meter (16.4 ft) remote sensor cable terminated std. gray / Ex blue
L010	10 meter (32.8 ft) remote sensor cable terminated std. gray / Ex blue
L015	15 meter (49.2 ft) remote sensor cable terminated std. gray / Ex blue
L020	20 meter (65.6 ft) remote sensor cable terminated std. gray / Ex blue
L030	30 meter (98.4 ft) remote sensor cable terminated std. gray / Ex blue
Y000	Separate ordered remote fire retardant connecting cable
Y005	5 meter (16.4 ft) remote fire retardant connecting cable, not terminated
Y010	10 meter (32.8 ft) remote fire retardant connecting cable, not terminated
Y015	15 meter (49.2 ft) remote fire retardant connecting cable, not terminated
Y020	20 meter (65.6 ft) remote fire retardant connecting cable, not terminated
Y030	30 meter (98.4 ft) remote fire retardant connecting cable, not terminated

Fire retardant cable is mandatory for DNV GL type approval (Options MC2 and MC3). The minimum permissible ambient temperature for the two cable types differs (see chapter *Allowed ambient temperature for sensor* [> 31]). The cable type intended to be used needs to be indicated (with option L000 or Y000) even if connecting cable is ordered separately.

9.6.2 Additional nameplate information




Options	Specification
BG	Nameplate with customer-specific identification

This marking (Tag No.) must be provided by the customer at the time the order is placed.

9.6.3 Presetting of customer parameters

Rotamass flow meters can be preconfigured with customer-specific data.



Options	Specification
PS	Presetting according to customer parameters.


9.6.4 Concentration and petroleum measurement

Petroleum measurement function NOC (option C52) "NOC" is an abbreviation of "Net Oil Computing" and it is an optional software function that is available only for Ultimate transmitter.

The NOC application can provide real-time measurements of water cut and includes "API" (American Petroleum Institute) correction according to API MPMS Chapter 11.1.

Oil types	Water types
Crude	Standard Mean Ocean Water
Refined Prod- ucts: Fuel, Jet Fuel, Transition, Gasoline	UNESCO 1980
Lubricating	Fresh water density by API MPMS 11.4
Alpha 60	Produced water density by API MPMS 20.1 Appendix A.1
Custom	Brine water density by El-Dessouky, Ettouy (2002)
	Custom

In addition of Water Cut, the function can calculate: Net Oil Mass flow, Net Water Mass flow, Net Oil Volume flow, Net Water Volume flow and Net corrected Oil volume flow.




Options	Specification
C52	Total Net Oil computing TNO

These device options are not available in combination with gas measurement devices (model code position 9 with the values: 70 or 50).

Options with C52 are available only for Ultimate transmitters (value U in MS code position 1).

9.6.5 Certificates



Accor	da	nce	with
terms	of	ord	er

Options	Specification
P2	Declaration of compliance with the order 2.1 according to EN 10204
P3	Quality Inspection Certificate (Inspection Certificate 3.1 according to EN 10204)

Material certificates

Options	Specification
P6	Certificate of Marking Transfer and Raw Material Certificates (Inspection Certificate 3.1 according to EN 10204)

Dye penetration test of weld seams

Options	Specification
PT	Dye penetrant test of process connection weld seams according to DIN EN ISO 3452-1, including certificate
PTA	Dye penetrant test of flange welding according to ASME V

Positive Material Identification of wetted parts

Options	Specification
	Positive Material Identification of wetted parts, including certificate (Inspection Certificate 3.1 according to EN 10204)

Pressure testing

Options	Specification
P8	Hydrostatic Pressure Test Certificate (Inspection Certificate 3.1 according to EN 10204)

Welding certificates

Options	Specification
WP	Welding certificates:
	 WPS according to DIN EN ISO 15609-1
	 WPQR according to DIN EN ISO 15614-1
	 WQC according to DIN EN 287-1 or DIN EN ISO 6906-4
WPA	Welding procedures and Certificate according to ASME IX

Only for the butt welding seam between the process connection and the flow divider.

Mass flow calibration

Water is used as medium for calibrating the Rotamass.

Options	Specification
K2	Customer-specific 5-point mass flow calibration with factory calibration certificate (mass flow or volume flow of water). A table listing the desired calibration points must be supplied with the order.
K5	Customer-specific 10-point mass flow calibration with DAkkS calibration certificate (mass flow or volume flow of water). A table listing the desired calibration points must be supplied with the order.

Surfaces free of oil and grease

Options	Specification
H1	Degreasing of wetted surfaces according to ASTM G93-03 (Level C), including test report

X-ray inspection of flange weld seam

Options	Specification
RT	X-ray inspection of flange weld seam according to DIN EN ISO 17636-1/B
	Evaluation according to AD 2000 HP 5/3 and DIN EN ISO 5817/C, including certificate
RTA	X-ray test according to ASME V

This device option is not available for devices with wetted parts made of Ni alloy C-22/2.4602.



Intense

Ordering information Options

Ferrite testing

Options	Specification
FE	Ferrite test for flange welding according to DIN EN ISO 8249

Determination of ferrite content is possible for flange weld seams according to DIN EN ISO 8249 and ANSI/AWS A4.2. The pass criterion is a ferrite number < 30. An inspection certificate is delivered with the device.


Combined certificates

Options	Specification			
P10	 Combination of: P3: Quality Inspection Certificate P6: Certificate of Marking Transfer and Raw Material Certificates P8: Hydrostatic Pressure Test Certificate 			
P11	Combination of: P3: Quality Inspection Certificate P6: Certificate of Marking Transfer and Raw Material Certificates PM: Positive Material Identification of wetted parts			
P12	Combination of: P3: Quality Inspection Certificate P6: Certificate of Marking Transfer and Raw Material Certificates PT: Dye penetration test according to DIN EN ISO 3452-1 P8: Hydrostatic Pressure Test Certificate			
P13	Combination of: P3: Quality Inspection Certificate P6: Certificate of Marking Transfer and Raw Material Certificates PT: Dye penetration test according to DIN EN ISO 3452-1 PM: Positive Material Identification of wetted parts P8: Hydrostatic Pressure Test Certificate WP: Welding certificates			
P14	Combination of: PM: Positive Material Identification of wetted parts P8: Hydrostatic Pressure Test Certificate WP: Welding certificates			
P20	Combination of: PTA: Dye Penetrant test of flange welding according to ASME V WPA: Welding procedures and Certificates according to ASME IX RTA: X-ray test according to ASME V			

ASME B31.3 compliance

Options	Specification
P15	ASME B31.3 compliance NORMAL FLUID SERVICE

9.6.6 Country-specific delivery




Options	Specification
PJ	Delivery to Japan
CN	Delivery to China



9.6.7 Rupture disc

In the event of a measuring tube break, complete release of process pressure via the rupture disc cannot be ensured in every case.


The rupture disc's bursting pressure is 20 bar (291 psi), the nominal diameter 8 mm (0.315 inch). If a larger nominal diameter is required, the Yokogawa sales organization may be contacted with regard to customized designs.



Options	Specification
RD	Rupture disc


9.6.8 Tube health check


By way of the tube health check, the transmitter can determine whether the tube properties were altered due to corrosion or deposits and, whether they could impact accuracy as a result.



Options	Specification
TC	Tube health check

9.6.9 Transmitter housing rotated 180°





Options	Specification
RB	Alignment of transmitter housing rotated 180°



Intense

Ordering information Options

9.6.10 Measurement of heat quantity




Options	Specification
CGC	Measurement of the total transported energy content of a fuel in connection with a sensor for determining the fuel's calorific value (e.g., a gas chromatograph, not included in scope of delivery).
	This option is available only together with MS code position 13 JH to JN.

The function allows to evaluate the total fuel calorific value of the measured fluid. The function can work with a constant value of the calorific value of the fluid, but to have a precise evaluation is suggested an additional device like a gas chromatograph not included in the supply. The external device that supplies the instantaneous calorific value is connected with the current input of the transmitter (MS code position 13: from JH to JN) Based on the mass flow, the Total Calorific Energy of the fluid is calculated as below: Total Calorific Energy = \sum [(Mass Flow rate) $_i \times H_i \times \Delta t$]

where H_i is the variable Calorific Value and Δt is the time interval between two measurements. Other formula based on Volume and Corrected Volume are included in the function and can be set using the display or the configuration PC software FieldMate.

9.6.11 Marine Approval

By ordering Options MC2 and MC3 the device will carry a type approval mark by DNV GL. Ordering of fire retardant cable (Y___) is mandatory with this option. In case of thermal oil applications option RT or RTA is mandatory. Please note that DNV GL has additional requirements regarding the process conditions as reproduced in the table below. The complete requirements can be found in the classification society's rules concerning the respective use case. Marine approval is not available for all device variants, for details see exclusions in *Overview options* [66].



	Option			
	MC2		MC3	
Dining avatam for	Class II 1)		Class III 1)	
Piping system for	p in bar	T _{pro} in °C	p in bar	T _{pro} in °C
Steam	≤ 16	≤ 300	≤ 7	≤ 170
Thermal oil	≤ 16	≤ 300	≤ 7	≤ 150
Fuel oil, lubricating oil, flammable oil	≤ 16	≤ 150	≤ 7	≤ 60
Other media ²⁾	≤ 40	≤ 300	≤ 16	≤ 200

p: Design pressure

T_{pro}: Design temperature


²⁾ Cargo oil pipes on oil carriers and open ended pipes (drain overflows, vents, boiler escape pipes etc.) independently of the pressure and temperature, are pertaining to class III.

Options	Specification
MC2	Marine approval according to DNV GL piping class 2
MC3	Marine approval according to DNV GL piping class 3



¹⁾ both specified conditions shall be met

9.6.12 Customer specific special product manufacture



Options	Specification
Z	Deviations from the specifications in this document are possible.



9.7 Ordering Instructions

Specify the following information when ordering a product:

- Model code, suffix code, and option code
- Fluid name
- Language of the instruction manual:
 - English
 - French
 - German
 - Japanese
- Display language and language pack (Display only present for value 1 on position 14 of the MS code):
 - EN-Pack1 English
 - DE-Pack1 German
 - FR-Pack1 French
 - PO-Pack1 Portuguese
 - JA-Pack1 Japanese
 - IT-Pack1 Italian
 - EN-Pack2 English
 - DE-Pack2 German
 - RU-Pack2 Russian
 - PL-Pack2 Polish
 - KZ-Pack2 Kazakh
 - EN-Pack3 English
 - DE-Pack3 German
 - FR-Pack3 French
 - PO-Pack3 Portuguese
 - IT-Pack3 Italian
 - ES-Pack3 Spanish
 - CN-Pack3 Chinese
- Orientation of the display (Display only present for value 1 on position 14 of the MS code):

Orientation 1	Orientation 2	Orientation 3
Integral type (Horizontal installation - tubes down)	Integral type (Horizontal installation - tubes up) Remote type	Integral type (vertical installation)

Tag No. to be engraved on the nameplate (option BG, up to 16 characters length)

- Software Tag No. (both short and long):
 - HART Tag No. (short): up to 8 characters length (Capital letters only)
 - HART Tag No. (long): up to 32 characters length
- Customer name for the certificates (option L2, L3, L4: up to 60 characters length)



All rights reserved. Copyright © 2017-07-14

YOKOGAWA FI FCTRIC CORPORATION

Headquarters

Z-9-32, Nakacho, Musashino-shi, Tokyo, 180-8750 JAPAN Phone : 81-422-52-5555 Branch Sales Offices Osaka, Nagoya, Hiroshima, Kurashiki, Fukuoka, Kitakyusyu

YOKOGAWA CORPORATION OF AMERICA

Head Office
12530 West Airport Blvd, Sugar Land,
Texas 77478, USA
Phone : 1-281-340-3800
Fax : 1-281-340-3838
Georgia Office
2 Dart Road, Newnan, Georgia 30265, USA
Phone : 1-800-888-6400/ 1-770-253-7000
Fax : 1-770-254-0928

YOKOGAWA AMERICA DO SUL LTDA.

Praca Acapulco, 31 - Santo Amaro, Sáo Paulo/SP, BRAZIL, CEP-04675-190 Phone: 55-11-5681-2400 Fax: 55-11-5681-4434

YOKOGAWA EUROPE B. V.

Euroweg 2, 3825 HD Amersfoort, THE NETHERLANDS Phone : 31-88-4641000 Fax : 31-88-4641111

YOKOGAWA FI FCTRIC CIS I TD.

Grokholskiy per 13 Building 2, 4th Floor 129090, Moscow, RUSSIA Phone : 7-495-737-7869 Fax : 7-495-737-7869

YOKOGAWA CHINA CO., LTD.

3F Tower D Cartelo Crocodile Building, No.568 West Tianshan Road, Shanghai 200335, CHINA Phone: 86-21-623878662 Fax: 86-21-62387866Z

YOKOGAWA ELECTRIC KOREA CO., LTD.

(Yokogawa B/D, Yangpyeong-dong 4-Ga), 21, Seonyu-ro 45-gil, Yeongdeungpo-gu, Seoul, 150-866, KOREA Phone: 82-2-2628-6000 Fax: 82-2-2628-6400

YOKOGAWA ENGINEERING ASIA PTE. LTD.

5 Bedok South Road, Singapore 469270, SINGAPORE Phone : 65-6241-9933 Fax : 65-6241-2606

YOKOGAWA INDIA I TD.

Plot No.96, Electronic City Complex, Hosur Road, Bangalore - 560 100, INDIA Phone : 91-80-4158-6000 Fax : 91-80-2852-1442

YOKOGAWA AUSTRALIA PTY. LTD.

Tower A, 112-118 Talavera Road, Macquarie Park NSW 2113, AUSTRALIA Phone: 61-2-8870-1100 Fax: 61-2-8870-1111

YOKOGAWA MIDDLE EAST & AFRICA B.S.C.(C)

P.O. Box 10070, Manama, Building 577, Road 2516, Busaiteen 225, Muharraq, Kingdom of BAHRAIN Phone: 973-17358100 Fax: 973-17336100



