



Unit: mm (approx. inch)

- Universal flange type (Installation code -U)
Measurement span code M, H and V, except for option code /HD, /HD2



Measurement span code F or option code /HD, /HD2



*1: When option code K1, K2, K5, or K6 is selected, add 30 mm (1.18 inch) to the value in the figure.


*2: When amplifier housing code 9 is selected, the value is 270 mm (10.63 inch).
In this case, the figure is shown as A.

*3: When amplifier housing code 9 is selected, the value is 289 mm (11.38 inch).
In this case, the figure is shown as A.

*4: Applicable for the external powered type.

*5: When electrical connection code 7 or C is selected, a blind plug is protruded upto 8 mm (0.31 inch) from the electrical connection.

- Infrared Configuration



- Terminal Configuration for the External Powered type

