


Unit: mm (approx. inch)

● Transmitter body section




\*1: When amplifier housing code 9 is selected, the value is 270 mm (10.63 inch).  
In this case, the figure is shown as A.

\*2: When amplifier housing code 9 is selected, the value is 410 mm (16.14 inch).  
In this case, the figure is shown as A.

\*3: Applicable for the external powered type.

\*4: When electrical connection code 7 or C is selected, a blind plug is protruded upto 8 mm from the electrical connection.

● Infrared Configuration



● Terminal Configuration for the External Powered type

