


Drawings

OpreX™ Pressure Transmitter EJX110S with Option Code /N2 and /N3


SD 01C33C10-13EN

Unit: mm (approx. inch)


- Wetted Parts Material Code: S, F, G and Capsule Range Code: M, H, V



- Wetted Parts Material Code: H, M, T or Capsule Range Code: F, J, K, P, Q




- Capsule Range Code: E




| | | | |
|----------|--|----------|---------------------|
| a | External indicator Conduit connection (optional) | e | Display (optional) |
| b | Conduit connection | p | Process connection |
| c | Zero adjustment | u | Blind kidney flange |
| d | Ground terminal | | |

Unit: mm (approx. inch)

- Capsule Range Code: 1, 2, 3, 5, 6 and Bolts and Nuts Material Code: D, F, L




- Capsule Range Code: 1, 2, 3, 5, 6 and Bolts and Nuts Material Code: K, H



| | | | |
|----------|--|----------|---------------------|
| a | External indicator Conduit connection (optional) | e | Display (optional) |
| b | Conduit connection | p | Process connection |
| c | Zero adjustment | u | Blind kidney flange |
| d | Ground terminal | | |

- *1: In case of electrical connection code 7 or C is specified, a blind plug is protruded by up to 8 mm (0.31 inch) from conduit connection.
- *2: In case of optional code /PP specified, a blind plug is attached to conduit connection on both sides.
- *3: In case of optional code /BS specified, a bug screen is installed to the process connection of the low side cover flange.
- *4: In case of Display and interface code N specified, it is 113 mm (4.45 inch).

• Terminal Configuration



• Terminal Wiring

| | | |
|----------|---|---|
| SUPPLY + | ① |] Power supply and output terminals |
| SUPPLY - | ② | |
| CHECK + | ③ |] External indicator (ammeter) terminals *1 |
| CHECK - | ② | |
| | | ⏏ Ground terminal |

- *1: When using an external indicator or check meter, the internal resistance must be 10Ω or less. Not available for PROFINET communication type.