

Drawings

Models DX3004, DX3008,
DX3010, DX3020,
DX3030



Daqstation DX3000






SD 04L75B01-01EN

Unit: mm
(approx. inch)

Dimensions




Panel cut dimensions




Unless otherwise specified, tolerance is $\pm 3\%$ (however, tolerance is ± 0.3 mm when below 10 mm).


Terminal Arrangement




Power Supply Terminal



RS-422-A/485 Terminal




RS-232 Terminal




Input Terminals

M4 Screw Terminals

DX3004, DX3008




DX3010, DX3020, DX3030




Option Terminals


/F1/PM1 Combination




/F1/R1 Combination



/A3/R1 Combination



/A4/TPS4 Combination



/A5/R1 Combination

