


Drawings

MODEL 4371 06
MODEL 4371 12
MODEL 4371 18
MODEL 4371 24


μR20000.

μR20000 RECORDERS (Dot Printing Model)




Terminal Arrangement

Screw Type Input Terminal
RS-422A / 485 Interface (/C3)



Clamped Type Input Terminal
Ethernet (10BASE-T) Interface (/C7)
24V DC/AC Power Supply



Note : See next page for terminal arrangement

If not specified, the tolerance is $\pm 3\%$. However, in cases of less than 10mm, the tolerance is ± 0.3 mm.

Weight :

- Model 4371 06 : Approx. 8.4kg
- Model 4371 12 : Approx. 8.6kg
- Model 4371 18 : Approx. 8.8kg
- Model 4371 24 : Approx. 9.0kg

Drawings

MODEL 4371 06

MODEL 4371 12

MODEL 4371 18


MODEL 4371 24

μR20000 RECORDERS (Dot Printing Model)


μR20000

Input Terminals

6 Dot Screw Type




6 Dot Clamped Type (/H2)




Option Terminals


/A1 /C3 /F1 /R1 Combination




/A2 /C3 /F1 /R1 Combination




/A3 /C3 /R1 Combination




/A3



/A4



/A5




Drawings

MODEL 4371 06 / H5-□
 MODEL 4371 12 / H5-□
 MODEL 4371 18 / H5-□
 MODEL 4371 24 / H5-□

μR20000.

μR20000 Portable Type RECORDERS (Dot Printing Model)



Unit : mm
 (approx. inch)



Terminal Arrangement

Screw Type Input Terminal
 RS-422A / 485 Interface (/C3)

Clamped Type Input Terminal
 Ethernet (10BASE-T) Interface (/C7)



Note : make sure to use the appropriate power cord, matching the power outlet.

Weight :

Model 4371 06 /H5 : Approx. 10.1kg
 Model 4371 12 /H5 : Approx. 10.3kg
 Model 4371 18 /H5 : Approx. 10.5kg
 Model 4371 24 /H5 : Approx. 10.7kg

If not specified, the tolerance is $\pm 3\%$. However, in cases of less than 10mm, the tolerance is $\pm 0.3\text{mm}$.