


Drawings

Model PH8ERG KCl Refillable Type pH Sensor

Unit : mm



Model and code	L	Weight(kg)
PH8ERG - 03 - □□ - N - □ *A	Approx. 3000	Approx. 0.4
PH8ERG - 05 - □□ - N - □ *A	Approx. 5000	Approx. 0.6
PH8ERG - 07 - □□ - N - □ *A	Approx. 7000	Approx. 0.7
PH8ERG - 10 - □□ - N - □ *A	Approx. 10000	Approx. 1.0
PH8ERG - 15 - □□ - N - □ *A	Approx. 15000	Approx. 1.4
PH8ERG - 20 - □□ - N - □ *A	Approx. 20000	Approx. 1.8

Unless otherwise specified, differences in the dimensions are specified as: General tolerance = $\pm$ (Criteria of tolerance class it18 in JIS B0401-1986) / 2.