


Drawings

PH8HF - PP - □PT - T - NN - NN
 PH8HF - S3 - □PT - T - NN - NN
 Flow - Through Type Holder [Style: S2]


EXAPH

Unit: mm



Model and Code	A Screw	a	d	g	h	Weight
PH8HF-PP-JPT-T-NN-NN	Rc1	80	Approx. 60	Approx. 70	Approx. 250	Approx. 0.4kg
PH8HF-PP-NPT-T-NN-NN	1NPT	80	Approx. 60	Approx. 70	Approx. 250	Approx. 0.4kg
PH8HF-S3-JPT-T-NN-NN	Rc1	70	Approx. 60	Approx. 70	Approx. 243	Approx. 3kg
PH8HF-S3-NPT-T-NN-NN	1NPT	70	Approx. 60	Approx. 70	Approx. 243	Approx. 3kg

□ Mounting Hardware (Option Code : /MF1) Weight : Approx. 0.5kg



Unless otherwise specified, differences in the dimensions are specified as: General tolerance = ±(Criteria of tolerance class IT18 in JIS B0401-1998)/2.