


Drawings

PH8HF - □□ - □1□ -T - □□ - □□ Flow - Through Type Holder (with Jet or Brush Cleaner) [Style: S2]


EXA PH

Unit: mm



Model and Code	A	B	C	D	E	a	d	g	h	k	Weight
PH8HF-PP-J10-T-□□-□□	125	90	14	19	-	80	Approx. 60	Approx. 70	Approx. 250	15	Approx. 1.6kg
PH8HF-S3-J10-T-□□-□□	125	90	14	19	-	70	Approx. 60	Approx. 70	Approx. 245	17	Approx. 6kg
PH8HF-PP-A15-T-□□-□□	108	79.4	14.2	15.7	-	80	Approx. 60	Approx. 70	Approx. 250	15	Approx. 1.6kg
PH8HF-S3-A15-T-□□-□□	108	79.2	14.2	15.7	2	70	Approx. 60	Approx. 70	Approx. 245	17	Approx. 6kg

□ Mounting Hardware (Option Code: /MF1) Weight: Approx. 0.5kg



Unless otherwise specified, differences in the dimensions are specified as: General tolerance = \pm (Criteria of tolerance class IT18 in JIS B0401-1998)/2.