


Drawings

PH8HF - □□ - □1□ -T - □□ - C□ Flow - Through Type Holder (with Ultrasonic Cleaner) [Style: S2]


EXAPH

Unit: mm



| Model and Code | A | B | C | D | E | a | d | g | h | k | Weight |
|----------------------|-----|------|------|------|---|----|------------|------------|-------------|----|---------------|
| PH8HF-PP-J10-T-□□-C□ | 125 | 90 | 14 | 19 | - | 80 | Approx. 60 | Approx. 70 | Approx. 250 | 15 | Approx. 1.7kg |
| PH8HF-S3-J10-T-□□-C□ | 125 | 90 | 14 | 19 | - | 70 | Approx. 60 | Approx. 70 | Approx. 245 | 17 | Approx. 6.1kg |
| PH8HF-PP-A15-T-□□-C□ | 108 | 79.4 | 14.2 | 15.7 | - | 80 | Approx. 60 | Approx. 70 | Approx. 250 | 15 | Approx. 1.7kg |
| PH8HF-S3-A15-T-□□-C□ | 108 | 79.2 | 14.2 | 15.7 | 2 | 70 | Approx. 60 | Approx. 70 | Approx. 245 | 17 | Approx. 6.1kg |

□ Mounting Hardware (Option Code : /MF1) Weight : Approx. 0.5kg



Unless otherwise specified, differences in the dimensions are specified as: General tolerance = \pm (Criteria of tolerance class IT18 in JIS B0401-1998)/2.