


## Dissolved-oxygen Metering System DO30G - NN - 25 - □ □ - PN Dissolved - oxygen Sensor

Unit : mm

- Dissolved-oxygen sensor with pin terminals



| Model and Suffix Codes    | L      | Weight (kg) |
|---------------------------|--------|-------------|
| DO30G - NN - 25 - 03 - PN | 3 000  | Approx. 0.6 |
| DO30G - NN - 25 - 05 - PN | 5 000  | Approx. 0.8 |
| DO30G - NN - 25 - 10 - PN | 10 000 | Approx. 1.4 |
| DO30G - NN - 25 - 15 - PN | 15 000 | Approx. 2.0 |
| DO30G - NN - 25 - 20 - PN | 20 000 | Approx. 2.6 |

Unless otherwise specified, differences in the dimensions are specified as : General tolerance= $\pm$ (Criteria of tolerance class IT18 in JIS B0401)/2.