



Drawings

Model VD6DF Flameproof Liquid Density Detector

Unit : mm



Terminal Panel



Terminals	Function
B4	Output Frequency
B5	
A2	Temperature Sensor
A3	
A4	
A5	Power Supply for Pre-amp
A6	Impressed Voltage for Pick-up Electrode
⏏	Grounding Terminal

Unless otherwise specified, difference in the dimensions are specified as : General tolerance = $\pm$ (Criteria of tolerance class IT18 in JIS B0401-1986) / 2