


# Drawings


PH201G  
Distributor

SD 19B01E04-01E

Unit: mm



Terminal configuration



Terminal symbol	Signal name
A	+
B	-
C	OUT1(1 to 5V DC)
D	CMN (Common)
F	OUT2 (1 to 5V DC)
H	CMN (Common)
J	CMN (For safety barrier)
K	(Not used)
1	} (Not used)
2	
3	
4	
5	
6	
7	
8	
a, b c, d e, f	Contact signals HOLD (hold) FAIL (failure) WASH (cleaning)

(Note) Terminal symbol mark of "a" to "F" for contact signals are not printed.

Weight : Approx. 1.7 kg

Unless otherwise specified, differences in the dimensions are specified as: General tolerance =  $\pm$ (Criteria of tolerance class IT18 in JIS B0401-1998)/2.